



LED PAR30 S/L

10PAR30S/EXPERTCOLOR/F40/927/P/D/T/JA8

MasterClass, LEDspot, PAR30S, 75 W, E26, 2700 K, 950 lm, 40000 hour(s), Plastic

Philips LED spots with a single optic beam, provide a clean beam that's free from shadows with beam angles from 10 and 40 degrees to suit every general lighting application.

Product data

General Information	
Cap-Base	E26
Nominal lifetime	40,000 hour(s)
Switching Cycle	50,000
Lighting Technology	LEDspot
Light Technical	
Color Code	927 [CCT of 2700K]
Beam Angle (Nom)	40 degree(s)
Luminous Flux	950 lm
Luminous Intensity (Nom)	2,000 cd
Color Designation	Warm White (WW)
Correlated Color Temperature (Nom)	2700 K
Luminous Efficacy (rated) (Nom)	95 lm/W
Color Consistency	<4
Color rendering index (CRI)	95
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Input Frequency	60 Hz

Power Consumption	10 W
Lamp Current (Nom)	90 mA
Wattage Equivalent	75 W
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.9
Voltage (Nom)	120 V

Temperature	
T-Case Maximum (Nom)	163 °F

Controls and Dimming	
Dimmable	Only with specific dimmers

Mechanical and Housing	
Bulb Finish	Clear
Bulb Material	Plastic
Bulb Shape	PAR30S
UL Wet/ damp/ dry location	Damp location

LED PAR30 S/L

Net Weight (Piece)	0.428 lb
--------------------	----------

Approval and Application

Suitable For Accent Lighting	Yes
EU RoHS compliant	Yes
T20 compliant	Yes
Ambient temperature range	-4 to +113 °F

Application Conditions


can it be used in closed luminaires	Yes
-------------------------------------	-----

Product Data

Order product name	10PAR30S/EXPERTCOLOR/ F40/927/P/D/T/JA8
--------------------	--



Full product name	10PAR30S/EXPERTCOLOR/ F40/927/P/D/T/JA8
Order code	587618
Material Nr. (12NC)	929003755504
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677587611
Numerator - Packs per outer box	6
EAN/UPC - Case	50046677587616

Dimensional drawing



Product	D	C
10PAR30S/EXPERTCOLOR/F40/927/P/D/T/JA8	3-3/4 inch	3-5/8 inch

Photometric data




©2024 Osram Opto Semiconductors AG | Philips Lighting B.V. | Page 11

Spectral Power Distribution Colour - 10PAR30S/EXPERTCOLOR/
F40/927/P/D/T/JA8

Accent Lighting Spots - 10PAR30S/EXPERTCOLOR/F40/927/P/D/T/JA8

LED PAR30 S/L

Photometric data



Light Distribution Diagram - 10PAR30S/EXPERTCOLOR/
F40/927/P/D/T/JA8

Lifetime



Life Expectancy Diagram



Lumen Maintenance Diagram - 10PAR30S/EXPERTCOLOR/
F40/927/P/D/T/JA8

