



CorePro LED PLC 4P

CorePro LED PLC 6.5W 840 4P G24q-2

CorePro, LED, PL-C, HF/Mains, 5-1/16 inch, 6.5 W, 18W PL-C, 4000 K, 770 lm, CRI 82, 30000 hour(s)

CorePro, LED, PL-C, HF/Mains, 5-1/16 inch, 6.5 W, LED alternative to 18W PL-C, 4000 K, 770 lm, CRI 82, 30000 hour(s), 118 lm/W, EEL E, G24Q-2 Rotatable end-cap, Beam angle 120 degree(s), Plastic, SDCM 6, PF 0.9, IP20, SVM 0.4, PstLM 1

Product data

General Information	
Cap-Base	G24Q-2 Rotatable end-cap
Nominal lifetime	30,000 hour(s)
Switching Cycle	200,000
Lighting Technology	LED
Flux measurement reference	Sphere
Warranty period	3 years
Light Technical	
Color Code	840 [CCT of 4000K]
Beam Angle (Nom)	120 degree(s)
Luminous Flux	770 lm
Color Designation	Cool White (CW)
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	118 lm/W
Color Consistency	<6
Color rendering index (CRI)	82
LLMF At End Of Nominal Lifetime (Nom)	70 %


Operating and Electrical	
Input Frequency	50 to 60 Hz
Power Consumption	6.5 W
Lamp Current (Nom)	35 mA
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.9
Voltage (Nom)	220-240 V
LED alternative to fluorescent lamp power	18W PL-C
Inrush current at mains	7
Max. lamp no. on MCB B type 10A - Mains	222
Max. lamp no. on MCB B type 10A – EM ballast without Compensation Capacitor.	-
Max. lamp no. on MCB B type 10A – EM ballast with Compensation Capacitor.	-
Max. lamp no. on MCB B type 16A - Mains	350
Max. lamp no. on MCB B type 16A – EM ballast without Compensation Capacitor.	-
Max. lamp no. on MCB B type 16A – EM ballast with Compensation Capacitor.	-

CorePro LED PLC 4P

Ballast Compatibility	HF/Mains
Temperature	
T-Case Maximum (Nom)	158 °F
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Bulb Finish	Frosted
Bulb Material	Plastic
Product Length	5-1/16 inch
Bulb Shape	PL-C
Net Weight (Piece)	0.22 lb
Approval and Application	
Energy Efficiency Class	E
Energy Saving Product	Yes
Approval Marks	RoHS compliance CE marking KEMA Keur certificate
Energy Consumption kWh/1000 h	7 kWh
EPREL Registration Number	1945437
CE mark	Yes
EU RoHS compliant	Yes

Flickering value (PstLM) - Flickering value as per EN 61000-3-3		1
Stroboscopic effect visibility measure (SVM)		0.4
Ambient temperature range		-4 to +113 °F
Application Conditions		
can it be used in closed luminaires		Yes
Wireless Technology		Not applicable
Product Data		
Order product name	CorePro LED PLC 6.5W 840 4P G24q-2	
Full product name	CorePro LED PLC 6.5W 840 4P G24q-2	
Full product code	872016929047100	
Order code	929003757902	
Material Nr. (12NC)	929003757902	
Numerator - Quantity Per Pack	1	
EAN/UPC - Product/Case	8720169290471	
Numerator - Packs per outer box	10	
EAN/UPC - Case	8720169290488	



Dimensional drawing



Product	D1	D2	A1	A2	A3
CorePro LED PLC 6.5W 840 4P G24q-2	1-3/8 inch	1-3/8 inch	4-5/16 inch	5-1/16 inch	5-11/16 inch


CorePro LED PLC 4P

Photometric data




General uniform lighting - CorePro LED PLC 6.5W 840 4P G24q-2

Light Distribution Diagram - CorePro LED PLC 6.5W 840 4P G24q-2




Spectral Power Distribution Colour - CorePro LED PLC 6.5W 840 4P G24q-2

Lifetime




FailureRate




Life Expectancy Diagram

CorePro LED PLC 4P


Lifetime



Lumen Maintenance Diagram - CorePro LED PLC 6.5W 840 4P G24q-2



LifetimeVsTc



Lumen Maintenance Diagram - CorePro LED PLC 6.5W 840 4P G24q-2

