# **PHILIPS** Lighting

# MASTER LEDtube InstantFit HF T5

# MAS LEDtube HF 600mm HE 7W 840 T5

The Philips MASTER LEDtube integrates a LED light source into a traditional fluorescent form factor. Its unique design creates a perfectly uniform visual appearance, which cannot be distinguished from traditional fluorescent. These T5 lighting tubes are the right choice for absolute performance and are designed to stand up to everyday conditions. Unparalleled savings thanks to low energy consumption and an exceptionally long lifetime make these T5 LED tubes the choice for every demanding application.

#### **Product data**

General Information		
Cap-Base	G5	
Nominal lifetime	60,000 hour(s)	
Switching Cycle	50,000	
Lighting Technology	LED	
Flux measurement reference	Sphere	
Light Technical		
Color Code	840 [CCT of 4000K]	
Beam Angle (Nom)	200 degree(s)	
Luminous Flux	1,050 lm	
Color Designation	Cool White (CW)	
Correlated Color Temperature (Nom)	4000 K	
Luminous Efficacy (rated) (Nom)	150 lm/W	
Color Consistency	<6	
Color rendering index (CRI)	80	
LLMF At End Of Nominal Lifetime (Nom)	70 %	


Photobiological safety according to EN 62471	RGO
Operating and Electrical	
Input Frequency	30K to 100K Hz
Power Consumption	7 W
Lamp Current (Max)	350 mA
Lamp Current (Min)	150 mA
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.92
Voltage (Nom)	40-70 V
LED alternative to fluorescent lamp power	14 W
Inrush current at mains	-
Max. lamp no. on MCB B type 10A - Mains	-
Max. lamp no. on MCB B type 10A - EM ballast	-
without Compensation Capacitor.	
Max. lamp no. on MCB B type 10A - EM ballast	-
with Compensation Capacitor.	



## **MASTER LEDtube InstantFit HF T5**

Max. lamp no. on MCB B type 16A - Main	s -	Energy Consumption kWh/1000 h	7 kWh	
Max. lamp no. on MCB B type 16A – EM ballast -		EPREL Registration Number	1936619	
without Compensation Capacitor.		CE mark	Yes	
Max. lamp no. on MCB B type 16A – EM ballast -		EU RoHS compliant	Yes	
with Compensation Capacitor.		Ambient temperature range	-20 to +45 ℃	
Ballast Compatibility	HF			
		Application Conditions		
Temperature		can it be used in closed luminaires	Yes	
T-Case Maximum (Nom)	50 °C			
		Product Data		
Controls and Dimming		Order product name	MAS LEDtube HF 600mm HE 7	
Dimmable	Yes - Check ballast compatibility		840 T5	
		Full product name	MAS LEDtube HF 600mm HE 7	
Mechanical and Housing			840 T5	
Bulb Finish	Frosted	Full product code	872016930968500	
Bulb Material	Glass	Order code	929003795202	
Product Length	600 mm	Material Nr. (12NC)	929003795202	
Bulb Shape	Τ5	Numerator - Quantity Per Pack	1	
Net Weight (Piece)	0.085 kg	EAN/UPC - Product/Case	8720169309685	
		Numerator - Packs per outer box	10	
Approval and Application		EAN/UPC - Case	8720169309692	
Energy Efficiency Class	D			
Energy Saving Product	Yes			
Approval Marks	RoHS compliance KEMA Keur			
	certificate			

#### Dimensional drawing




Product	D1	D2	A1	A2	A3
MAS LEDtube HF 600mm HE 7W 840 T5	15.7 mm	19 mm	549 mm	556 mm	563 mm


### MASTER LEDtube InstantFit HF T5

#### Photometric data






General uniform lighting - MAS LEDtube HF 600mm HE 7W 840 T5




Spectral Power Distribution Colour - MAS LEDtube HF 600mm HE 7W 840 T5

#### Lifetime



LEDtube 60K 5070 LifetimeVsTc-LED


Light Distribution Diagram - MAS LEDtube HF 600mm HE 7W 840 T5




Lumen Maintenance Diagram - MAS LEDtube HF 600mm HE 7W 840 T5


#### **MASTER LEDtube InstantFit HF T5**


Lifetime





Life Expectancy Diagram





LEDtube 60K 5070 FailureRate-LED



© 2025 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com 2025, April 21 - data subject to change