



MASTER Glass LED bulbs

MAS LEDBulb DT5.9-60W E27 CRI95 A60 FR G

LEDbulb, A60, 60 W, E27, 2200 K, 2700 K, 806 lm, CRI 95, 25000 hour(s), Glass

LEDbulb, A60, 60 W, E27, 2200 K, 2700 K, 806 lm, CRI 95, 25000 hour(s), Glass, 136 lm/W, EEL D, PF 0.6, Beam angle 300 degree(s), RG1, IP20, SVM 0.4, PstLM 0.9

Product data

General Information	
Cap-Base	E27
Nominal lifetime	25,000 hour(s)
Switching Cycle	20,000
Lighting Technology	LEDbulb
Flux measurement reference	Sphere
Warranty period	5 years
Light Technical	
Color Code	922-927 [CCT of 2200K-2700K]
Beam Angle (Nom)	300 degree(s)
Luminous Flux	806 lm
Color Designation	Warm Glow(WG)
Correlated Color Temperature (Nom)	2200 2700 K
Luminous Efficacy (rated) (Nom)	136 lm/W
Color Consistency	<6
Color rendering index (CRI)	95
LLMF At End Of Nominal Lifetime (Nom)	70 %


Photobiological safety according to EN 62471	RG1
Operating and Electrical	
Input Frequency	50 to 60 Hz
Power Consumption	5.9 W
Lamp Current (Nom)	40 mA
Wattage Equivalent	60 W
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.6
Voltage (Nom)	220-240 V
Temperature	
T-Case Maximum (Nom)	158 °F
Controls and Dimming	
Dimmable	Only with specific dimmers

MASTER Glass LED bulbs

Mechanical and Housing	
Bulb Finish	Frosted
Bulb Material	Glass
Bulb Shape	A60
Net Weight (Piece)	0.071 lb
Approval and Application	
Energy Efficiency Class	D
Energy Consumption kWh/1000 h	6 kWh
EPREL Registration Number	1969962
CE mark	Yes
EU RoHS compliant	Yes
EyeComfort	Yes
Flickering value (PstLM) - Flickering value as per EN 61000-3-3	0.9
Stroboscopic effect visibility measure (SVM)	0.4
Ambient temperature range	-4 to +113 °F



Application Conditions	
can it be used in closed luminaires	No
Wireless Technology	Not applicable
Product Data	
Order product name	MAS LEDBulb DT5.9-60W E27 CRI95 A60 FR G
Full product name	MAS LEDBulb DT5.9-60W E27 CRI95 A60 FR G
Full product code	872016931105300
Order code	929003799002
Material Nr. (12NC)	929003799002
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8720169311053
Numerator - Packs per outer box	10
EAN/UPC - Case	8720169311060

Dimensional drawing



Product	D	C
MAS LEDBulb DT5.9-60W E27 CRI95 A60 FR G	2-3/8 inch	4-1/4 inch

Photometric data




General uniform lighting - MAS LEDBulb DT5.9-60W E27 CRI95 A60 FR G

Spectral Power Distribution Colour - MAS LEDBulb DT5.9-60W E27 CRI95 A60 FR G


MASTER Glass LED bulbs

Photometric data



Light Distribution Diagram - MAS LEDBulb DT5.9-60W E27 CRI95 A60 FR G

Lifetime



Life Expectancy Diagram



Lumen Maintenance Diagram - MAS LEDBulb DT5.9-60W E27 CRI95 A60 FR G

