



MASTER Glass LED bulbs

MAS LEDBulb DT7.2-75W E27 CRI95 A60 FR G

LEDbulb, A60, 75 W, E27, 2200 K, 2700 K, 1055 lm, CRI 95, 25000 h, Glass

Featuring a classic heritage design, these filament MASTER glass bulbs combine the familiar shapes of incandescent glass LED bulbs with the benefits of long-lasting LED technology. Ideal for creating a cosy atmosphere for customers, these glass LED bulbs provide excellent quality of light. MASTER glass bulbs can be dimmed for different lumen levels and colour temperatures (dimmable glass led bulbs). They also deliver significant energy savings, using 30% less energy compared to normal LED bulbs. By offering a lifetime of 25,000 hours, these dimmable glass LED bulbs also reduce maintenance costs.

Product data

General Information		Correlated Colour Temperature (Nom)	
Cap base	E27		2200 2700 K
Nominal lifetime	25,000 h	Luminous efficacy (rated) (nom.)	146 lm/W
Switching Cycle	20,000	Colour consistency	<6
Lighting Technology	LEDbulb	Colour rendering index (CRI)	95
Flux measurement reference	Sphere	LLMF at end of nominal lifetime (nom.)	70 %
Warranty period	5 years	Photobiological safety according to EN 62471	RG1
Light Technical		Operating and Electrical	
Colour Code	922-927 [CCT of 2200K-2700K]	Input frequency	50 to 60 Hz
Beam angle (nom.)	300 degree(s)	Power Consumption	7.2 W
Luminous Flux	1,055 lm	Lamp current (nom.)	49 mA
Colour designation	Warm Glow (WG)	Wattage equivalent	75 W
		Starting time (nom.)	0.5 s

MASTER Glass LED bulbs

Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.6
Voltage (nom.)	220-240 V

Temperature

T-Case maximum (nom.)	70 °C
-----------------------	-------

Controls and Dimming

Dimmable	Only with specific dimmers
----------	----------------------------


Mechanical and Housing

Lamp Finish	Frosted
Bulb material	Glass
Bulb shape	A60
Net Weight (Piece)	0.032 kg

Approval and Application

Energy Efficiency Class	D
Energy consumption kWh/1,000 hours	8 kWh
EPREL Registration Number	1969954
CE mark	Yes
EU RoHS compliant	Yes
EyeComfort	Yes

Dimensional drawing



Flickering value (PstLM)	0.9
Stroboscopic effect	0.4
Ambient temperature range	-20 to +45 °C

Application Conditions

Can it be used in closed luminaires	No
Wireless Technology	Not applicable



Product Data

Order product name	MAS LEDBulb DT7.2-75W E27 CRI95 A60 FR G
Full product name	MAS LEDBulb DT7.2-75W E27 CRI95 A60 FR G
Full EOC	872016931107700
Order code	929003799102
Material no. (12 NC)	929003799102
Numerator – quantity per pack	1
EAN/UPC – Product/Case	8720169311077
Numerator – packs per outer box	10
EAN/UPC - Case	8720169311084


Product	D	C
MAS LEDBulb DT7.2-75W E27 CRI95 A60 FR G	60 mm	108 mm

MASTER Glass LED bulbs

Photometric data




Light Distribution Diagram - MAS LEDBulb DT7.2-75W E27 CRI95 A60 FR G General uniform lighting - MAS LEDBulb DT7.2-75W E27 CRI95 A60 FR G




Spectral Power Distribution Colour - MAS LEDBulb DT7.2-75W E27 CRI95 A60 FR G

Lifetime



Life Expectancy Diagram



Lumen Maintenance Diagram - MAS LEDBulb DT7.2-75W E27 CRI95 A60 FR G

MASTER Glass LED bulbs

