

PHILIPS

Xitanium

LED driver



Datasheet

Xitanium non-Isolated DALI Dip Switch

Xitanium 40W 0.1-0.35A 120V DALI DS 230V

9290 040 06806

Xitanium LED non-isolated DALI Dipswitch drivers are ideal for high-voltage (HV) systems. They are based on three pillars: quality of light, reliability, and flexibility. Our drivers' robustness is based on in-depth electronics knowledge and extensive testing. Finally, application-oriented operating windows offer the flexibility required to provide the stable lumen output and quality levels that lighting specifiers and architects demand.

Features

- High efficiency
- Low Ripple less than 5%
- 4 selectable output currents by programmable Dip switches
- 50,000 hours lifetime @ Tc-max
- DC emergency
- DALI dimmable and programmable

Benefits

- High quality of light
- Peace of mind with proven reliability
- Selectable and programmable output current enables flexibility and SKU reduction

Application

- Offices
- Waterproof
- Retail: supermarkets, shopping malls

Logistical data

Specification item	Value
Product name	Xitanium 40W 0.1-0.35A 120V DALI DS 230V
EOC	872790097663200
Logistic code 12NC	9290 040 06806
EAN1 (GTIN)	8727900976632
EAN3 (box)	8727900976649
Pieces per box	20

Electrical input data

Specification item	Value	Unit	Condition
Rated input voltage range	220...240	V _{ac}	Performance range
Rated input voltage	230	V _{ac}	
Rated input frequency	50...60	Hz	Rated range
Rated input current	0.19	A	@ rated output power @ rated input voltage
Rated input power	44.0	W	@ rated output power @ rated input voltage
Power factor	0.98		@maximum output power @ rated input voltage
Total harmonic distortion	20	%	@ rated output power @ rated input voltage
Efficiency	90.0	%	@ maximum output power @ rated input voltage @ max. Uoutput
Rated input voltage DC	186...250	V _{dc}	Performane range; EOFi = 60%
Rated input current DC	0.11...0.14	A _{dc}	Performance range
Input voltage AC	198...264	V _{ac}	Operational range
Input frequency AC	47.5...63	Hz	Performance range
Input voltage DC	168...275	V _{dc}	Operational range
Standby Power (W)	< 0.50	W	
Isolation input to output	No		

Electrical output data

Specification item	Value	Unit	Condition
Regulation method	Constant Current		
Output voltage	60...120	V _{dc}	
Output voltage max.	250	V	Maximum output voltage (rms)
Output current	100...350	mA	Via dipswitches:
Min output current	10	mA	
Output current tolerance ±	5	%	@Iout range 200...350mA
Output current tolerance ±	7	%	@Iout range 100...200mA
Output current ripple LF	≤ 5	%	Ripple = peak / average, < 3kHz, ≤6% @ DC input
Output current ripple HF	≤ 15	%	
Output P _{st} ^{LM}	≤ 0.6		In entire voltage range for each choice of output current
Output SVM	≤ 0.3		In entire voltage range for each choice of output current
Output power	12.0...40.0	W	Performance range: 12...40W, THD < 20% @ 17...40W
Number of output channels	1		

Control interfaces

Specification item	Value	Unit	Condition
Control method	DALI		Output current can be set via dip switches
Dimming range	5...100	%	Default range

Wiring and Connections

Specification item	Value	Unit	Type
Input wire cross-section	0.5...1.5 / 20...16	mm ² / AWG	WAGO744, solid wire
Input wire strip length	8...9	mm	
Output wire cross-section	0.5...1.5 / 20...16	mm ² / AWG	WAGO744, solid wire
Output wire strip length	8...9	mm	
Maximum cable length	2	m	CISPR15: between driver and LED module


pin1	pin2	setting	Io
off	off	0	200mA
off	on	1	250mA
on	off	2	300mA
on	on	3	350mA

Isolation

Insulation per IEC61347-1	Input	Output	DALI	Housing
Input	-	No	Basic	Basic
Output	No	-	Basic	Basic
DALI	Basic	Basic	-	Basic
Housing	Basic	Basic	Basic	-

Dimensions and weight

Specification item	Value	Unit	Tolerance (mm)
Length (A1)	210	mm	± 0.3
Mounting hole distance (A2)	198.5	mm	± 0.3
Width (B1)	30	mm	± 0.5
Height (C1)	21	mm	± 0.5
Mounting hole diameter (D1)	4.1	mm	± 0.2
Mounting hole diameter (D2)	4.1	mm	± 0.2
Weight	140	gram	
Housing color	White		




Operational temperatures and humidity

Specification item	Value	Unit	Condition
Ambient temperature	-25...+50	°C	Higher ambient temperature allowed as long as Tcase-max is not exceeded
Tcase-max	80	°C	Maximum temperature measured at T _{case} -point
Tcase-life	70	°C	Measured at T _{case} -point
Maximum housing temperature	110	°C	In case of a failure, inherent by design
Relative humidity	10...90	%	Non-condensing

Lifetime

Specification item	Value	Unit	Condition
Driver lifetime	50,000	hours	Measured temperature at Tcase-point is Tcase-max. Maximum failures = 10%
Driver lifetime	100,000	hours	Measured temperature at Tcase-point is Tcase-max -10 degrees. Maximum failures = 10%



Maximum failures = 10%

Storage temperature and humidity

Specification item	Value	Unit	Condition
Ambient temperature	-25...+85	°C	
Relative humidity	5...95	%	Non-condensing

Programmable features

Specification item	Available	Default setting	Condition
Set Adjustable Output Current (AOC)	Yes	OFF	Programmable via MultiOne; AOC enable overrides DipSwitch
DipSwitch	Yes	Setting 0: 200mA, see wiring	Set the output current via the dipswitch; for output current, configurable via MultiOne
Adjustable Light Output (ALO)	Yes	OFF	
Constant Light Output (CLO)	Yes	OFF	
Min Dim Level (%)	Yes	5 %	
DC emergency (DCemDim)	Yes	ON	max emergency level:60%
OEM Write Protection (OWP)	Yes	OFF	
Luminaire Info (DALI part 251)	Yes		
Luminaire maintenance (DALI part 253)	Yes		

Non-programmable features


Specification item	Value		Condition
Open load protection	Yes		Automatic recovering
Short circuit protection	Yes		Automatic recovering
Over power protection	Yes		Automatic recovering
Hot wiring	No		
Suitable for fixtures with protection class	I		per IEC60598
Output Overvoltage Detection	Yes		
Energy metering (DALI part 252)	Yes		
Diagnostics (DALI part 253)	Yes		
Touch & Dim (TD)	No		

Inrush current

Specification item	Value	Unit	Condition
Inrush current	20	A	Input voltage 230V
Inrush peak width	209	μs	Input voltage 230V, measured at 50% height
Drivers / MCB 16A type B @230V AC	≤ 29	pcs	Input voltage 230V

Please refer to the driver design in guide if you use other MCB-types.

If several mini circuit breakers are used directly side-by-side (without distance pieces)
a correction factor of 80% has to be applied to the rated current



Driver touch current / protective conductor current / earth leakage current


Specification item	Value	Unit	Condition
Typical Protective Conductor Current (ins. Class I)	0.7	mA rms	Acc. IEC60598-1. LED module contribution not included

Surge immunity


Specification item	Value	Unit	Condition
Mains surge immunity (diff. mode)	1	kV	L- N Acc. IEC61000-4-5. 2 Ohm, 1.2/50us, 8/20us
Mains surge immunity (comm. mode)	2	kV	L/N - PE Acc. IEC61000-4-5. 12 Ohm, 1.2/50us, 8/20us
Control surge immunity (diff. mode)	0.8	kV	DA - DA Acc. IEC61000-4-5. 40 Ohm, 1.2/50us, 8/20us
Control surge immunity (comm. mode)	2	kV	DA/DA- PE, Acc. IEC61000-4-5. 12 Ohm, 1.2/50us,8/20us

Application Info (Approbation)


Specification item	Value
Approval marks and Certifications	CB / CCC / CE / DALI 2 / EAC / EL / ENEC / RCM / UA / UKCA
Ingress Protection classification (IP)	20
Application	Indoor Linear
Mounting Type	Built-in




Type	Output current (mA)	Min. output voltage (V)	Max. output voltage (V)	Max. output power (W)
Xitanium 40W 0.1-0.35A 120V DALI DS 230V	100	120	120	12
Xitanium 40W 0.1-0.35A 120V DALI DS 230V	150	80	120	18
Xitanium 40W 0.1-0.35A 120V DALI DS 230V	200	60	120	24
Xitanium 40W 0.1-0.35A 120V DALI DS 230V	250	60	120	30
Xitanium 40W 0.1-0.35A 120V DALI DS 230V	300	60	120	36
Xitanium 40W 0.1-0.35A 120V DALI DS 230V	350	60	114	40



Efficiency versus output power



THD versus output power



©2025 Signify Holding, IBRS 10461, 5600 VB, NL. All rights reserved.
UK importer address: Signify Commercial UK Limited, 2 Guildford Business Park GU2 8XG, UK

The information provided herein is subject to change without notice. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify.

Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V. All other trademarks are owned by Signify Holding or their respective owners.

Date of release: September 12, 2025 v0

www.philips.com/oem