



MASTER LED tube EM/Mains T8 with Recycled Plastic

MAS LEDtube 1500mm HO 16.7W 830 T8 EELC

MASTER, LEDtube, T8, EM/Mains, 59-1/16 inch, 16.7 W, 58W TL-D, 3000 K, 2900 lm, CRI 80, 75000 hour(s)

MASTER, LEDtube, T8, EM/Mains, 59-1/16 inch, 16.7 W, LED alternative to 58W TL-D, 3000 K, 2900 lm, CRI 80, 75000 hour(s), 173 lm/W, EEL C, G13 Rotatable end-cap, Beam angle 160 degree(s), Plastic, 40 %, 1500 mm, RGO, SDCM 6, PF 0.9, IP20, SVM 0.1, PstLM 0.1

Product data

General Information	
Cap-Base	G13 Rotatable end-cap
Nominal lifetime	75,000 hour(s)
Switching Cycle	200,000
Lighting Technology	LEDtube
Flux measurement reference	Sphere
Warranty period	5 years

Light Technical	
Color Code	830 [CCT of 3000K]
Beam Angle (Nom)	160 degree(s)
Luminous Flux	2,900 lm
Color Designation	White (WH)
Correlated Color Temperature (Nom)	3000 K

Luminous Efficacy (rated) (Nom)	173 lm/W
Color Consistency	<6
Color rendering index (CRI)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %
Photobiological safety according to EN 62471	RG0

Operating and Electrical	
Input Frequency	50 to 60 Hz
Power Consumption	16.7 W
Lamp Current (Max)	84 mA
Lamp Current (Min)	70 mA
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.9

MASTER LED tube EM/Mains T8 with Recycled Plastic

Voltage (Nom)	220-240 V
LED alternative to fluorescent lamp power	58W TL-D
Inrush current at mains	7.7
Max. lamp no. on MCB B type 10A – Mains	90
Max. lamp no. on MCB B type 10A – EM ballast without Compensation Capacitor.	90
Max. lamp no. on MCB B type 10A – EM ballast with Compensation Capacitor.	10
Max. lamp no. on MCB B type 16A – Mains	150
Max. lamp no. on MCB B type 16A – EM ballast without Compensation Capacitor.	150
Max. lamp no. on MCB B type 16A – EM ballast with Compensation Capacitor.	16
Ballast Compatibility	EM/Mains

Temperature

T-Case Maximum (Nom)	122 °F
----------------------	--------

Controls and Dimming

Dimmable	No
----------	----

Mechanical and Housing

Bulb Finish	Frosted
Bulb Material	Plastic
Product Length	59-1/16 inch
Bulb Shape	T8
Net Weight (Piece)	0.584 lb

Approval and Application

Energy Efficiency Class	C
Energy Saving Product	Yes
Approval Marks	RoHS compliance CE marking KEMA Keur certificate ENEC certificate

Energy Consumption kWh/1000 h	17 kWh
EPREL Registration Number	2571907
CE mark	Yes
EU RoHS compliant	Yes
LED Innovations	UltraEfficient
Flickering value (PstLM) - Flickering value as per EN 61000-3-3	0.1
Stroboscopic effect visibility measure (SVM)	0.1
Ambient temperature range	-4 to +113 °F
Post-consumer recycled plastic material ratio	40 %

Application Conditions

can it be used in closed luminaires	Yes
Wireless Technology	Not applicable


Sustainability Data

Sustainability rating	Signify Circle
Product non-virgin material ratio	25.8 %

Product Data

Order product name	MAS LEDtube 1500mm HO 16.7W 830 T8 EELC
Full product name	MAS LEDtube 1500mm HO 16.7W 830 T8 EELC
Full product code	872016938811600
Order code	929004242702
Material Nr. (12NC)	929004242702
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8720169388116
Numerator - Packs per outer box	10
EAN/UPC - Case	8720169388123


Dimensional drawing




Product	D1	D2	A1	A2	A3
MAS LEDtube 1500mm HO 16.7W 830 T8 EELC	1-1/16 inch	1-1/8 inch	59-1/16 inch	59-3/8 inch	59-5/8 inch

MASTER LED tube EM/Mains T8 with Recycled Plastic


Photometric data



General uniform lighting - MAS LEDtube 1500mm HO 16.7W 830 T8 EELC




Spectral Power Distribution Colour - MAS LEDtube 1500mm HO 16.7W 830 T8 EELC




Light Distribution Diagram - MAS LEDtube 1500mm HO 16.7W 830 T8 EELC

Lifetime




Lumen Maintenance Diagram - MAS LEDtube 1500mm HO 16.7W 830 T8 EELC




Life Expectancy Diagram

MASTER LED tube EM/Mains T8 with Recycled Plastic


Lifetime



Lumen Maintenance Diagram - MAS LEDtube 1500mm HO 16.7W 830 T8
EELC



Life Expectancy Diagram



Life Expectancy Diagram

