



MASTER LED tube EM/Mains T8 with Recycled Plastic

MAS LEDtube 600mm HO 7.6W865 T8

MASTER, LEDtube, T8, EM/Mains, 23-5/8 inch, 7.6 W, 18W TL-D, 6500 K, 1150 lm, CRI 80, 75000 hour(s)

MASTER, LEDtube, T8, EM/Mains, 23-5/8 inch, 7.6 W, LED alternative to 18W TL-D, 6500 K, 1150 lm, CRI 80, 75000 hour(s), 151 lm/W, EEL D, G13 Rotatable end-cap, Beam angle 160 degree(s), Plastic, 40 %, 600 mm, RG0, SDCM 6, PF 0.9, IP20, SVM 0.1, PstLM 0.1

Product data

General Information	
Cap-Base	G13 Rotatable end-cap
Nominal lifetime	75,000 hour(s)
Switching Cycle	200,000
Lighting Technology	LEDtube
Flux measurement reference	Sphere
Warranty period	5 years
Light Technical	
Color Code	865 [CCT of 6500K]
Beam Angle (Nom)	160 degree(s)
Luminous Flux	1,150 lm
Color Designation	Cool Daylight
Correlated Color Temperature (Nom)	6500 K

Luminous Efficacy (rated) (Nom)	151 lm/W
Color Consistency	<6
Color rendering index (CRI)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %
Photobiological safety according to EN 62471	RG0
Operating and Electrical	
Input Frequency	50 to 60 Hz
Power Consumption	7.6 W
Lamp Current (Max)	40 mA
Lamp Current (Min)	30 mA
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.9

MASTER LED tube EM/Mains T8 with Recycled Plastic

Voltage (Nom)	220-240 V
LED alternative to fluorescent lamp power	18W TL-D
Inrush current at mains	7
Max. lamp no. on MCB B type 10A – Mains	105
Max. lamp no. on MCB B type 10A – EM ballast without Compensation Capacitor.	125
Max. lamp no. on MCB B type 10A – EM ballast with Compensation Capacitor.	30
Max. lamp no. on MCB B type 16A – Mains	170
Max. lamp no. on MCB B type 16A – EM ballast without Compensation Capacitor.	290
Max. lamp no. on MCB B type 16A – EM ballast with Compensation Capacitor.	49
Ballast Compatibility	EM/Mains

Temperature

T-Case Maximum (Nom)	122 °F
----------------------	--------

Controls and Dimming

Dimmable	No
----------	----

Mechanical and Housing

Bulb Finish	Frosted
Bulb Material	Plastic
Product Length	23-5/8 inch
Bulb Shape	T8
Net Weight (Piece)	0.209 lb

Approval and Application

Energy Efficiency Class	D
Energy Saving Product	Yes
Approval Marks	RoHS compliance CE marking KEMA Keur certificate ENEC certificate

Energy Consumption kWh/1000 h	8 kWh
EPREL Registration Number	2571908
CE mark	Yes
EU RoHS compliant	Yes
Flickering value (PstLM) - Flickering value as per EN 61000-3-3	0.1
Stroboscopic effect visibility measure (SVM)	0.1
Ambient temperature range	-4 to +113 °F
Post-consumer recycled plastic material ratio	40 %

Application Conditions

can it be used in closed luminaires	Yes
Wireless Technology	Not applicable


Sustainability Data

Product non-virgin material ratio	40.9 %
-----------------------------------	--------

Product Data

Order product name	MAS LEDtube 600mm HO 7.6W865 T8
Full product name	MAS LEDtube 600mm HO 7.6W865 T8
Full product code	872110304419800
Order code	929004260402
Material Nr. (12NC)	929004260402
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8721103044198
Numerator - Packs per outer box	10
EAN/UPC - Case	8721103044204



Dimensional drawing



Product	D1	D2	A1	A2	A3
MAS LEDtube 600mm HO 7.6W865 T8	1-1/16 inch	1-1/8 inch	23-1/4 inch	23-1/2 inch	23-13/16 inch


MASTER LED tube EM/Mains T8 with Recycled Plastic

Photometric data




General uniform lighting - MAS LEDtube 600mm HO 7.6W865 T8

Light Distribution Diagram - MAS LEDtube 600mm HO 7.6W865 T8




Spectral Power Distribution Colour - MAS LEDtube 600mm HO 7.6W865 T8

Lifetime





Lumen Maintenance Diagram - MAS LEDtube 600mm HO 7.6W865 T8



Life Expectancy Diagram


MASTER LED tube EM/Mains T8 with Recycled Plastic

Lifetime



Lumen Maintenance Diagram - MAS LEDtube 600mm HO 7.6W865 T8

Life Expectancy Diagram



Life Expectancy Diagram

