

PHILIPS

Xitanium

LED driver



Datasheet

Xitanium Round Shape Highbay LED Drivers

Xi RHB 120W 0.30-0.50A DS TWE 129S

9290 048 53901

Xitanium Round Shape High Bay LED Drivers are designed to deliver highly reliable and efficient LED drivers in industrial applications.

The key features of Xitanium Round Shape High Bay LED Drivers are Adjustable Output Current (AOC) with DipSwitch.

DipSwitch enables a simple and fast way to set Output current of the drivers. The TWE family can operate on input voltage 100-277Vac and ensure 100% performance from 120-277Vac.

Features

- Adjustable Output Current (AOC) via DipSwitch
- Input voltage range: 100-277Vac
- Surge protection: 4/6kV (DM/CM)
- 50,000 hours lifetime @Tc life
- IP65
- High efficiency up to 94.5%

Benefits

- Enables flexibility in the application and SKU reduction
- Low maintenance cost and peace of mind in extreme conditions
- Enable high efficiency to luminaire and save energy
- Enables more application possibilities

Application

- Highbay industrial lighting
- Warehouse lighting

Logistical data

Specification item	Value
Product name	Xi RHB 120W 0.30-0.50A DS TWE 129S
Logistic code 12NC	9290 048 53901
Pieces per box	12
Weight	555 gram

Electrical input data

Specification item	Value	Unit	Condition
Rated input voltage range	120...277	V _{ac}	Performance range
Rated input voltage	230	V _{ac}	
Rated input frequency	50...60	Hz	Performance range
Rated input current	0.57	A	@ rated output power @ rated input voltage
Max. input current	1.1	A	@ rated output power @ minimum performance input voltage
Rated input power	127.0	W	@ rated output power @ rated input voltage
Power factor	0.95		@ rated output power @ rated input voltage
Total harmonic distortion	10	%	@ rated output power @ rated input voltage
Efficiency	94.5	%	@ rated output power @ rated input voltage @max. U _{out}
Input voltage AC	100...305	V _{ac}	Operational range
Input frequency AC	47...63	Hz	Operational range

Electrical output data

Specification item	Value	Unit	Condition
Regulation method	Constant Current		
Output voltage	200...300	V _{dc}	
Output voltage max.	380	V	Maximum output voltage (rms)
Output current	300 / 400 / 500	mA	
Output current tolerance ±	8	%	@full load
Output current ripple LF	≤ 5	%	Ripple = peak / average, < 3kHz
Output current ripple HF	≤ 30	%	
Output P _{st} ^{LM}	≤ 0.3		In entire operating window
Output SVM	≤ 0.1		In entire operating window
Output power	60.0...120.0	W	
Rated output power	120.0	W	
Load regulation	≤ 5	%	

Control interfaces

Specification item	Value	Unit	Condition
Control method	Fixed		

Wiring and Connections


Specification item	Value	Unit	Type
Input wire cross-section	1	mm ²	3x 1.0mm2 stranded wires
Output wire cross-section	1	mm ²	2x 1.0mm2 stranded wires
Maximum cable length	2	m	Total length of wiring including LED module, one way

Isolation

Insulation per IEC61347-1	Mains	Output	PE
Mains	-	Non	Basic
Output	Non	-	Basic
PE	Basic	Basic	-

Dimensions and weight

Specification item	Value	Unit	Tolerance (mm)
Length (A1)	129	mm	
Mounting hole distance (A2)	113	mm	
Length (A3)	113	mm	
Length (A4)	113	mm	
Width (B1)	20	mm	
Height (C1)	59	mm	
Height (C2)	40	mm	
Mounting hole diameter (D1)	6.5	mm	
Mounting hole diameter (D2)	14	mm	
Input cable length (E1)	200	mm	
Output cable length (E2)	150	mm	
Weight	555	gram	




Operational temperatures and humidity

Specification item	Value	Unit	Condition
Ambient temperature	-40...+60 -40...+50	°C	Ta≤60°C @ Vin=202...277V Ta≤50°C @ Vin=120...202V
Tcase-max	90	°C	Maximum temperature measured at T _{case} -point
Tcase-life	85 78	°C	Tc=85°C @ Vin=230V, measured at T _c -point Tc=78°C @ Vin=120V, measured at T _c -point
Relative humidity	10...90	%	Non-condensing

Lifetime

Specification item	Value	Unit	Condition
Driver lifetime	50,000	hours	Measured temperature at Tcase-point is 85°C, Vin 230V. Maximum failures = 10%



Maximum failures = 10%

Storage temperature and humidity

Specification item	Value	Unit	Condition
Ambient temperature	-40...+80	°C	
Relative humidity	5...95	%	Non-condensing

Programmable features

Specification item	Available	Default setting	Condition
Set Adjustable Output Current (AOC)	DipSwitch	500 mA	

Non-programmable features


Specification item	Value		Condition
Open load protection	Yes		Automatic recovering
Short circuit protection	Yes		Automatic recovering
Over power protection	No		
Hot wiring	No		
Suitable for fixtures with protection class	I		per IEC60598
Overtemperature protection	Yes		Automatic recovering

Inrush current

Specification item	Value	Unit	Condition
Inrush current	74	A	Input voltage 230V
Inrush peak width	91	μ s	Input voltage 230V, measured at 50% height
Drivers / MCB 16A type B @ 230V AC	≤ 15	pcs	Input voltage 230V

Please refer to the driver design in guide if you use other MCB-types.

If several mini circuit breakers are used directly side-by-side (without distance pieces)
a correction factor of 80% has to be applied to the rated current



Driver touch current / protective conductor current / earth leakage current

Specification item	Value	Unit	Condition
Typical Protective Conductor Current (ins. Class I)	1	mA rms	Acc. IEC60598-1. LED module contribution not included

Surge immunity


Specification item	Value	Unit	Condition
Mains surge immunity (diff. mode)	4	kV	Acc. IEC61000-4-5. 2 Ohm, 1.2/50us, 8/20us
Mains surge immunity (comm. mode)	6	kV	Acc. IEC61000-4-5. 12 Ohm, 1.2/50us, 8/20us

Application Info (Approbation)


Specification item	Value
Approval marks and Certifications	CB / CCC / CE / ENEC / RCM / UKCA
Ingress Protection classification (IP)	65
Mounting Type	Independent

Graphs


Operating window




Load versus input voltage




Power factor versus output power



Efficiency versus output power



THD versus output power



©2026 Signify Holding, IBRS 10461, 5600 VB, NL. All rights reserved.
UK importer address: Signify Commercial UK Limited, 2 Guildford Business Park GU2 8XG, UK

The information provided herein is subject to change without notice. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify.

Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V. All other trademarks are owned by Signify Holding or their respective owners.

Date of release: January 16, 2026 v1

www.philips.com/oem