



High intensity reflector lamp

This Philips pressed-glass reflector bulb is designed to use indoors and outdoors, wherever blown-bulb reflector lamps would be too vulnerable. Choose between narrow (spot) and wide (flood) beam angles.

Special purpose lighting

For specific applications

Highlights

For specific applications



Philips special purpose incandescent light bulbs are meant to be used for specific applications. Light bulbs for general home lighting are available in the Philips halogen, energy-saving, and LED ranges.

Specifications

Bulb characteristics

Shape: ReflectorSocket: E27Dimmable: Yes

Bulb dimensions

Height: 137 mmWidth: 123 mm

Durability

Average life (at 2.7 hrs/day): 2 year(s)
Number of switch cycles: 8,000
Nominal lifetime: 2,000

Light characteristics

Application: Accent light
Beam angle: 10 degree(s)
Color rendering index (CRI): 100
Warm-up time to 60% light: instant full light s

• Correlated Color Temperature (Nom): 2700

Power

· Power Factor (Fraction): 1

Power consumption

Voltage: 24 VWattage: 120 W

Power Consumption: 120.0 WEnergy Consumption kWh/1000 h: 127

Rated values

· Rated lifetime: 2,000

Technical specifications

Dimmable: YesCap-Base: E27

Packaging dimensions & weight

• EAN/UPC - product: 8711500380739

Gross weight: 356.4 gHeight: 14.1 cmLength: 11.1 cmWidth: 11.1 cm

· Net weight: 319 g



Issue date: 2025-11-12 Version: 0.664 © 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips