

PHILIPS

Bulb 8W A60S E27
3000K NonDim

LED

3000K

770lm

15000h

8718699651633



A light bulb like no other

State-of-the-art LED light bulb providing a general lighting solution for daily indoor activities. You will save on energy costs immediately and reduce the frequency of bulb replacements, without compromising on the quality of your lighting.

Choose for a sustainable solution

- You can trust what the Philips packaging is saying.
- Contains no mercury

High quality LED light that lasts for decades

- Reduced glare. Increased comfort.

Highlights

No UV or IR

The beam of light is free of infra-red meaning no heat is radiated, and no ultra-violet light means that fabric and items under this light won't fade.

Contains no mercury



No mercury allows for non-hazardous waste disposal, so this characteristic provides a simple way to make your current space more sustainable.

EyeComfort with Interlaced optics

Interlaced optics technology enhances the overall lighting experience in your every-day life. Imprinted with 3D patterns to help diffuse light, the micro-lens technology produce an even distribution of light which reduces glare significantly. This illumination is not only a soft and uniform light which brings more comfort to your eyes, but it also cleverly redistributes light for less glaring illumination in the lit area.

Specifications

Bulb characteristics

- Intended use: Indoor
- Lamp shape: Non directional bulb
- Socket: E27
- Bulb Finish: Frosted
- Dimmable: No
- Bulb Material: Plastic

Durability

- Number of switch cycles: 50,000
- Ambient temperature range: -20 to +45 °C
- Nominal lifetime: 25,000

Environmental

- Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

Extra feature/accessory incl.

- LED integrated: Yes

Light characteristics

- Beam angle: 200
- Color rendering index (CRI): 90
- Color temperature: 3000 K
- Nominal luminous flux: 910 lm
- Warm-up time to 60% light: 0.5 s
- Color Code: 930 | CCT of 3000K
- Correlated Color Temperature (Nom): 3000
- Luminous Flux: 910 lm
- Luminous Efficacy (rated) (Nom): 113

Miscellaneous

- EyeComfort: Yes
- LED Innovations: EyeComfort

Other characteristics

- EU RoHS compliant: Yes

Packaging information

- EAN: 8718699651633
- EOC: 871869965163300
- Product title: LEDBulb 8W E27 930 230V 1PF/6 AU

Power

- Power Factor (Fraction): 0.5

Power consumption

- Power factor: 0.5
- Voltage: AC 220-240 V
- Wattage equivalent: 76
- Power: 8

Product dimensions and weight

- Overall height: 110 mm
- Overall length: 110 mm
- Overall width: 60 mm

Rated values

- Rated lifetime: 15,000

Technical specifications

- Frequency: 50-60
- Diameter: 60 mm
- Bulb technology: LED
- Dimmable: No
- Cap-Base: E27

The bulb

- Software upgradable: No

What's supported

- Compatible with Effects: No
- Defined support period: Not applicable
- Compatible operating systems: Not applicable
- Communication protocol: Not applicable
- Compatibility with 3rd party systems: Not applicable

Packaging dimensions & weight

- EAN/UPC - product: 8718699651633
- Net weight: 0.06 kg
- Gross weight: 0.08 kg
- Height: 13.7 cm
- Length: 6.1 cm
- Width: 6.1 cm



Issue date: 2026-05-13
Version: 0.245

© 2026 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com