



Spot 50W PAR16 GU10

Put the spotlight on your comfort and well-being! These smart spots have the standard GU10 shape that you know and love, but their real glass lenses bring an extra touch of elegance. And they offer you something that's anything but standard: tunable white light for all your needs and moods. Schedule cool white light when you need to get things done, or cozy warm white light when you want to kick back and relax—whatever lets you live your best, most comfortable home life. All this plus control via your voice, the WiZ remote, or the WiZ app whether you're home or away. WiZ GU10 spots connect using your existing Wi-Fi, no there's no additional hardware, networking, or setup required.

PRODUCT HIGHLIGHTS

- Tunable white smart bulb
- Up to 345 lumens
- Easy plug and play
- Control with app or voice

EAN: 8720169076747 wizconnected.com





Smart lighting functionalities easy to set up

Enjoy the benefits of smart features instantly, just by connecting your WiZ light to your Wi-Fi network. Control lights easily when you're away from home and scheduling lights to go on and off automatically. No need to install additional hardware such as hub or gateway!



Control with any Matter smart home platform

This product is Matter certified, allowing easy control through Google Home, Amazon Alexa, Apple Home, or any other Matter-based smart home platform of your choice.



Light that fits in any standard fixture

Compact shape that fits perfectly into any spot and recessed light fixture.



Control your smart lights from anywhere

No need to worry if lights were left on while no one's home. Simply turn them off from wherever you are, with your smartphone.



Create the perfect ambience for all your activities

Our classic glass GU10 lamp gives you something special: tunable white LED light for all your moods and activities. Schedule cool light when you need to focus, or cozy light when you want to relax—or simply select from preset modes such as Focus and Relax.



Create even light distribution for the entire

Enjoy a pleasant light balance in a room with this ceiling light. Its design is especially made to distribute light uniformly and provide soft, bright light throughout the room.

EAN: 8720169076747 wizconnected.com



SPECIFICATIONS

BULB CHARACTERISTICS

Intended use: Indoor Lamp shape: PAR16 Socket: GU10 Type of glass: Clear Dimmable: Yes

BULB DIMENSIONS

Weight: 0.05 kg

DURABILITY

Average life (at 2.7 hrs/day): 15 year(s) Lumen maintenance factor: 70% Number of switch cycles: 50,000 Nominal lifetime: 15.000

LIGHT CHARACTERISTICS

Beam angle: 36 degree(s)
Color consistency: 6 SDCM
Color rendering index (CRI): ≥90
Color temperature: 2700-6500 K
Light Color Category: Tunable white
Nominal luminous flux: 345 Im

Starting time: <0.5 s

Warm-up time to 60% light: instant

full light

Luminous Efficacy (rated) (Nom): 73

Im/W

OTHER CHARACTERISTICS

Lamp current: 40 mA

PACKAGING INFORMATION

EAN: 8720169076747 EOC: 872016907674700

Product title: Wi-Fi BLE 50W GU10

GLASS 927-65 TW 1PF/6

POWER CONSUMPTION

Power factor: 0.48
Voltage: AC 220-240 V
Wattage equivalent: 50 W
Energy Efficiency Label (EEL): F
Power Consumption: 4.7 W
Energy Consumption kWh/1000 h: 5

PRODUCT DIMENSIONS AND WEIGHT

Overall height: 55 mm Overall length: 55 mm Overall width: 50 mm

RATED VALUES

Rated lifetime: 15,000 Rated luminous flux: 345 lm Rated peak intensity: 550 cd

Rated power: 4.7 W

TECHNICAL SPECIFICATIONS

Frequency: 50-60

EPREL Registration Number: 1877834 Flux measurement reference: Narrow

Cone

WHAT'S SUPPORTED

Compatible with Effects: Yes

WiFi: Wireless G

Defined support period: Minimum of 60 months after introduction date Max. number of accessories: 9999 Communication protocol: Bluetooth

WiFi (2.4GHz)

PACKAGING DIMENSIONS & WEIGHT

EAN/UPC - product: 8720169076747

Net weight: 0.05 kg Gross weight: 0.09 kg

Height: 16 cm Length: 7 cm Width: 7 cm

Signify

© 2025 Signify Holding. All rights reserved. The information provided herein is subject to change, without notice. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. All trademarks are owned by Signify Holding or their respective owners.

EAN: 8720169076747 wizconnected.com