



Find what you need, right now!

Use the table below to find the product most commonly used for the given application. Don't see what you need? Visit www.bodine.com for a complete selection or call 1-888-BODINE-8 or email bodinetech@signify.com if you need help.



Order Code
(Click for product page)

Combo Exit Signs – FirstLink Connected

	Red lettering, white housing, up to 76' spacing	BCA2RWFL1
	Green lettering, white housing, up to 76' spacing	BCA2GWFL1





Exit Signs – FirstLink Connected

	Red lettering, white housing, single or double faced	BXARWFL1
	Green lettering, white housing, single or double faced	BXAGWFL1




Unit Equipment – FirstLink Connected

	2 Head, LED, 180 lumens, up to 40' spacing	BUA1WFL1
	2 Head, LED, 520 lumens, up to 76' spacing	BUA2WFL1



For LED Center Basket Troffers, LED Strip fixtures:

Installed inside fixture:

	10 W EM driver, Class 2 output, linear, FirstLink connected	BSL10T4UAK55PKFLI2
	10 W EM driver, Class 2 output, linear, selectable self-test	BSL10T3UAK55PKI2
	10VA inverter, up to 50VA w/0-10V dim load	ELIS10



Installed outside of or remote from fixture:

14 W EM driver, Class 2 output w/conduit (14W)	BSL14B2UAK55C111
10 W EM driver, Class 2 w/conduit	BSL310C2WM
10VA inverter w/conduit, up to 50VA w/0-10V dim load	ELIS10C



For LED Panels:

10 W EM driver, Class 2 w/conduit	BSL310C2WM
10VA inverter w/conduit, up to 50VA w/0-10V dim load	ELIS10C
25VA inverter w/conduit, up to 200 W w/0-10V dim load	ELIS25J1UK50C1AD11





For LED HighBays:

25VA inverter w/conduit, up to 200 W w/0-10V dim load	ELIS25J1UK50C1AD11
50VA inverter w/conduit, up to 320 W w/0-10V dim load	ELIS50J2UK50C1AD11



Distributor Quick Reference


For Retrofit, Type B TLEDs:

	1000 Lumens Kit (driver+LED module)	BLK1000T3UK55TS1	
	1000 Lumens Kit (driver+LED module) (w/FirstLink)	BLK1000T3UK55FL1	
	25VA inverter w/conduit, up to 200 W w/0-10V dim load	ELIS25J1UK50C1AD11	
	12 W inverter, for <u>phase cut dimmable</u> TLEDs up to 15 W	BTB15D	


For Retrofit, Type A TLEDs:

	1000 Lumens Kit (driver+LED module)	BLK1000T3UK55TS1	
	1000 Lumens Kit (driver+LED module) (w/FirstLink)	BLK1000T3UK55FL1	
	1 lamp, linear, up to 16.5 W	B50CT	


For LED Downlights:

	10VA inverter w/conduit, up to 50VA w/0-10V dim load	ELIS10C	
	6 W Class 2 output, bottom stud mount	BSL06M5UAK55BSI1	

For Fluorescent troffers:

	1 or 2 lamps, T5, T8, 4-pin compact, 1400 lumens max	B50	
	1 lamp, 18-42 W 4-pin CFL, 750 lumens max	B94CGUM	

Emergency Lighting Mini-Inverters - Useful for providing high emergency power to large or multiple luminaires.

	100VA output, 120-277VAC in/out, up to 400VA w/0-10V dim load	ELIS100	
	250VA output, 120-277VAC in/out, up to 800VA w/0-10V dim load	ELIS250I2UO30ADI2	
	400VA output, 120-277VAC in/out	ELIS400CEC	
	400VA output, 120-277VAC in/out, up to 800VA w/0-10V dim load	ELIS400I2UO30ADI2	



Products marked with the FirstLink logo have Bodine's FirstLink capabilities.

Though fully functional self-testing emergency lighting products on their own, connecting these products to the free FirstLink application allows for all test data to be wirelessly collected. The FirstLink application also allow you to control your emergency lights, like initiating a test manually and changing the testing time and date. Visit www.bodine.com/firstlink for more.

Not finding what you need? Contact us!

For a broader range of products, including extended runtime, high voltage, and for cold temperature applications, find them on the web at www.bodine.com, or, contact Bodine's support team..

Call or e-mail: 1-888-BODINE-8 / Bodinetech@Signify.com

