

Since
1894

BEAUTIFUL LIGHT, BUILT
TO PERFORM

 MAZDA



GREAT LIGHT SOLID DESIGN

There's an art to creating a quality lighting scheme that exceeds your customers' expectations - without going over their budget. Now you can master it beautifully with MAZDA's portfolio of LED lamps and luminaires.

QUALITY WHEN IT COUNTS

The MAZDA name has been trusted for quality and reliability since 1894. Our solid lighting solutions are built on decades of experience in lighting. From retail and residential projects to commercial and industrial installations, they have been developed to meet the challenging requirements of a wide range of lighting applications.

We've designed our range using the very latest LED technology, from classic bulbs and elegant candles to hand-working tubes and directional spots. The MAZDA portfolio now also offers

indoor and outdoor luminaires to meet your customer's needs. So you can promise your customers excellent performance and efficiency from their lighting installation, with instant energy savings.

They'll love the light quality too. With a choice of lumens, color temperatures and beam angles, our high quality LED solutions create the perfect ambience for every space. Light that's designed to create a great first impression, with value that lasts.

MASTERING LIGHT SINCE 1894.

MAZDA has been trusted for quality and reliability since 1894. Our solid lighting solutions are built on decades of experience in lighting:

- Engineered for performance
- Up to 35,000 hours reliable lifetime
- Superb light quality
- Save up to 85% energy



CONTENTS

LUMINAIRES

Indoor luminaires



Outdoor luminaires



LAMPS

LED Bulbs



LED Candles & Lustres



LED Spots



LED Tubes



LED High-bay lamps





LUMINAIRES

LUMINAIRES

Indoor
luminaires



Outdoor
luminaires



LAMPS

LED Bulbs



LED Candles & Lustres



LED Spots



LED Tubes



LED High-bay lamps



INDOOR LUMINAIRES

FOR INSTANT ENERGY SAVINGS

LED Batten

Most popular batten type of 1200mm, non-dimmable, 3000lm, neutral white

light and with IP20 rating. Ideal for general lighting and storage areas.



LED Downlights

Energy efficient luminaires with a robust design typically used for general lighting in residential and retail applications. Comes in 1300 and 2200 lumen options and in a choice of 3 color temperatures from warm white to cool daylight for recessed version. Comes in 950 and 1900 lumen for surface mounted version.



LED High-bay

Nicely designed High-bay luminaire with sturdy die-casting housing and special glass cover with unique textured design to cut glare.



LED Panels

Energy saving square LED panel for general application areas, available in 5 non-dimmable types (1200 and 3200 lumen) and including an office compliant version.



LED Spots

Our LED spots come with a slim design that fits most ceiling types. Available in 4 types, from 180-280 lumen and a choice of 2 color temperatures (warm white and cool white light).




LED Wallmounts

4 types of non-dimmable wallmount luminaires, available in neutral white light, 960-1400 lm, round and oval style. Typical applications include corridors, public entrance areas and staircases. Silver trim and motion sensor included.



LED Waterproof

A robust choice for all industrial applications. Comes in 1700, 3400 and 5400 lumen, neutral white light and with IP65 rating.



INDOOR LUMINAIRES

FOR INSTANT ENERGY SAVINGS

80
CRI

220-240 Vac

20,000h



LED BATTEN



Product type	Lumen output	Energy consumption	Efficiency	Color temperature	Operating temperature range	IP / IK	Power factor	Safety Class	Certifications	Lifetime	12NC	EAN1
	lm	W	[Lm/W]	K	°C					hrs		
MAZDA BN007C LED30S/840 PSU L1200	3000	30	100	4000	-20 to +35	IP20	0,9	I	CE	20.000	911401800480	8710163338040

80
CRI

220-240 Vac

25,000 or 35,000h



LED DOWNLIGHTS



Product type	Lumen output	Energy consumption	Efficiency	Color temperature	Operating temperature range	IP / IK	Power factor	Safety Class	Certifications	Lifetime	12NC	EAN1
	lm	W	[Lm/W]	K	°C					hrs		
MZD DN020B LED13/830 14W 220-240V WH	1300	14	92	3000	-20 to +40	IP20 / IK02	0,51	II	CE	35.000	929002668302	3139188163645
MZD DN020B LED13/840 14W 220-240V WH	1300	14	92	4000	-20 to +40	IP20 / IK02	0,51	II	CE	35.000	929002668402	3139188163669
MZD DN020B LED13/865 14W 220-240V WH	1300	14	92	6500	-20 to +40	IP20 / IK02	0,51	II	CE	35.000	929002668502	3139188163683
MZD DN020B LED22/830 22.5W 220-240V WH	2200	22,5	97	3000	-20 to +40	IP20 / IK02	0,51	II	CE	35.000	929002668602	3139188163706
MZD DN020B LED22/840 22.5W 220-240V WH	2200	22,5	97	4000	-20 to +40	IP20 / IK02	0,51	II	CE	35.000	929002668702	3139188163720
MZD DN020B LED22/865 22.5W 220-240V WH	2200	22,5	97	6500	-20 to +40	IP20 / IK02	0,51	II	CE	35.000	929002668802	3139188163744

80
CRI

220-240 Vac

35,000h



LED HIGH-BAY



Product type	Lumen output	Energy consumption	Efficiency	Color temperature	Operating temperature range	IP / IK	Power factor	Safety Class	Certifications	Lifetime	12NC	EAN1
	lm	W	[Lm/W]	K	°C					hrs		
MAZDA BY007P LED150S/840 PSU WB	15000	150	100	4000	-20 to +45	IP65 / IK06	0,95	I	CE	35.000	911401841582	8719514527829
MAZDA BY007P LED200S/840 PSU WB	20000	200	100	4000	-20 to +45	IP65 / IK06	0,95	I	CE	35.000	911401841682	8719514527836

INDOOR LUMINAIRES

FOR INSTANT ENERGY SAVINGS

80
CRI


220-240 Vac


35,000h


non dimmable

LED PANELS



Product type	Lumen output	Energy consumption	Efficiency	Color temperature	Operating temperature range	IP / IK	Power factor	Safety Class	Certifications	Lifetime	12NC	EAN1
	lm	W	[Lm/W]	K	°C					hrs		
MAZDA RC007B LED32S/840 PSU W60L60 NOC	3200	36	88	4000	-10 to +45	IP20	0,9	II	CE	35.000	911401801280	8710163340180
MAZDA RC007B LED12S/840 PSU W30L30 NOC	1200	15	88	4000	-10 to +45	IP20	0,9	II	CE	35.000	911401801380	8710163340197
MAZDA RC007C LED32S/840 PSU W60L60 NOC FR	3200	36	88	4000	-10 to +45	IP20	0,9	II	CE	35.000	911401800281	8710163364704
MAZDA RC007C LED32S/840 PSU W60L60 OC FR	3200	36	88	4000	-10 to +45	IP20	0,9	II	CE	35.000	911401800381	8710163364711
MAZDA RC008C LED32S/840 PSU W62L62 NOC	3200	36	88	4000	-10 to +45	IP20	0,9	II	CE	35.000	911401859581	8719514507401

80
CRI


220-240 Vac


35,000h


non dimmable

LED SPOTS



Product type	Lumen output	Energy consumption	Efficiency	Color temperature	Operating temperature range	IP / IK	Power factor	Safety Class	Certifications	Lifetime	12NC	EAN1
	lm	W	[Lm/W]	K	°C					hrs		
MZD SL252 EC RD 070 3W 27K W HV 06	180	3	60	2700	-20 to +40	IP20 / IK02	>0,5	II	CE	15.000	929002222432	3139188164000
MZD SL252 EC RD 070 3W 40K W HV 06	185	3	61	4000	-20 to +40	IP20 / IK02	>0,5	II	CE	15.000	929002222532	3139188164024
MZD SL252 EC RD 070 5W 27K W HV 06	270	5	54	2700	-20 to +40	IP20 / IK02	>0,5	II	CE	15.000	929002222632	3139188164048
MZD SL252 EC RD 070 5W 40K W HV 06	280	5	56	4000	-20 to +40	IP20 / IK02	>0,5	II	CE	15.000	929002222732	3139188164062

INDOOR LUMINAIRES

FOR INSTANT ENERGY SAVINGS

70

CRI

80

CRI

220-240 Vac

20,000 or 35,000h

non dimmable

LED WALLMOUNTS



Product type	Lumen output	Energy consumption	Efficiency	Color temperature	Operating temperature range	IP / IK	Power factor	Safety Class	Certifications	Lifetime	12NC	EAN1
	lm	W	[Lm/W]	K	°C					hrs		
MAZDA WL007C LED14S/740 PSU OVL WH	1400	15	90	4000	-20 to +40	IP65 / IK06	0,9	II	CE	20.000	911401800880	8710163338088
MAZDA WL007C LED13S/740 PSU RND MDU WH	1300	15	85	4000	-20 to +40	IP54 / IK06	0,9	II	CE	20.000	911401800780	8710163338071
MAZDA WL007C LED10S/840 PSU RND WH G2	960	12	80	4000	-30 to +35	IP54 / IK06	0,5	II	CE	35.000	911401800081	871016336456899
MAZDA WL007C LED16S/840 PSU RND WH G2	1600	20	80	4000	-30 to +35	IP54 / IK06	0,5	II	CE	35.000	911401800181	871016336457599

LED WATERPROOF



80

CRI

220-240 Vac

35,000h

non dimmable

Product type	Lumen output	Energy consumption	Efficiency	Color temperature	Operating temperature range	IP / IK	Power factor	Safety Class	Certifications	Lifetime	12NC	EAN1
	lm	W	[Lm/W]	K	°C					hrs		
MAZDA WT007C LED17S/840 PSU L600	1700	17	90	4000	-20 to +35	IP65 / IK06	0,9	II	CE	35.000	911401800980	8710163338774
MAZDA WT007C LED34S/840 PSU L1200	3400	34	90	4000	-20 to +35	IP65 / IK06	0,9	II	CE	35.000	911401800580	8710163338057
MAZDA WT007C LED54S/840 PSU L1500	5400	54	90	4000	-20 to +35	IP65 / IK06	0,9	II	CE	35.000	911401800680	8710163338064

LUMINAIRES

Indoor
luminaires



Outdoor
luminaires



LAMPS

LED Bulbs



LED Candles & Lustres



LED Spots



LED Tubes



LED High-bay lamps



OUTDOOR LUMINAIRES

FOR INSTANT ENERGY SAVINGS

LED Floodlight

Highly versatile range of robust floodlights designed to meet diverse application requirements, including building facades, parking spaces and indoor industrial workspaces. Available from 800-17000 lumen in warm white, cool white and cool daylight and with IP65 rating.




OUTDOOR LUMINAIRES

FOR INSTANT ENERGY SAVINGS

LED FLOODLIGHTS



Product type	Lumen output	Energy consumption	Efficiency	Color temperature	Operating temperature range	IP / IK	Power factor	Safety Class	Certifications	Lifetime	12NC	EAN1
	lm	W	[Lm/W]	K	°C					hrs		
MAZDA BVP008 10W 3000K	900	10	85	3000	-40 to +50	IP65 / IK06	0,9	I	CE	35.000	911401810683	8719514533288
MAZDA BVP008 20W 3000K	1800	20	85	3000	-40 to +50	IP65 / IK06	0,9	I	CE	35.000	911401811683	8719514533271
MAZDA BVP008 50W 3000K	4500	50	85	3000	-40 to +50	IP65 / IK06	0,9	I	CE	35.000	911401814683	8719514533257
MAZDA BVP008 100W 3000K	9000	100	85	3000	-40 to +50	IP65 / IK06	0,9	I	CE	35.000	911401816683	8719514533240
MAZDA BVP008 150W 3000K	13500	150	80	3000	-40 to +50	IP65 / IK06	0,9	I	CE	35.000	911401817683	8719514533233
MAZDA BVP008 10W 4000K	950	10	80	4000	-40 to +50	IP65 / IK06	0,9	I	CE	35.000	911401820683	8719514533226
MAZDA BVP008 20W 4000K	1900	20	80	4000	-40 to +50	IP65 / IK06	0,9	I	CE	35.000	911401821683	8719514533219
MAZDA BVP008 30W 4000K	2850	30	80	4000	-40 to +50	IP65 / IK06	0,9	I	CE	35.000	911401823683	8719514533202
MAZDA BVP008 50W 4000K	4750	50	85	4000	-40 to +50	IP65 / IK06	0,9	I	CE	35.000	911401824683	8719514533196
MAZDA BVP008 100W 4000K	9500	100	85	4000	-40 to +50	IP65 / IK06	0,9	I	CE	35.000	911401826683	8719514533189
MAZDA BVP008 150W 4000K	14250	150	85	4000	-40 to +50	IP65 / IK06	0,9	I	CE	35.000	911401827683	8719514533172
MAZDA BVP008 20W 3000K MDU	1800	20	85	3000	-40 to +50	IP65 / IK06	0,9	I	CE	35.000	911401876083	8719514534568
MAZDA BVP008 20W 4000K MDU	1900	20	85	4000	-40 to +50	IP65 / IK06	0,9	I	CE	35.000	911401876183	8719514534551
MAZDA BVP008 50W 3000K MDU	4500	50	85	3000	-40 to +50	IP65 / IK06	0,9	I	CE	35.000	911401876683	8719514534544
MAZDA BVP008 50W 4000K MDU	4750	50	85	4000	-40 to +50	IP65 / IK06	0,9	I	CE	35.000	911401876783	8719514534537
MAZDA BVP008 10W 6500K	950	10	85	6500	-40 to +50	IP65 / IK06	0,9	I	CE	35.000	911401830683	8719514536449
MAZDA BVP008 20W 6500K	1900	20	85	6500	-40 to +50	IP65 / IK06	0,9	I	CE	35.000	911401831683	8719514536432
MAZDA BVP008 30W 6500K	2850	30	85	6500	-40 to +50	IP65 / IK06	0,9	I	CE	35.000	911401833683	8719514536425
MAZDA BVP008 50W 6500K	4750	50	85	6500	-40 to +50	IP65 / IK06	0,9	I	CE	35.000	911401834683	8719514536418
MAZDA BVP008 100W 6500K	9500	100	85	6500	-40 to +50	IP65 / IK06	0,9	I	CE	35.000	911401836683	8719514536401
MAZDA BVP008 200W 6500K	19000	200	85	6500	-40 to +50	IP65 / IK06	0,9	I	CE	35.000	911401838683	8719514536395



LAMPS

LUMINAIRES

Indoor
luminaires



Outdoor
luminaires



LAMPS

LED Bulbs



LED Candles & Lustres



LED Spots



LED Tubes



LED High-bay lamps



LED BULBS

FOR INSTANT ENERGY SAVINGS

LED Bulbs

An extensive range of non-dimmable LED bulbs that provide instant brightness in a classic design. Available with E27 fitting, 470-1521 lumen, in clear and frosted version and in 3 color temperatures from warm white to cool daylight.



A60 frosted



A60 clear glass



A60 frosted glass



A67 frosted glass

LED BULBS

FOR INSTANT ENERGY SAVINGS

80
CRI

220-240 Vac

ON
OFF
up to 30,000x

non dimmable

Product type	Lumen output	Energy consumption	Lifetime	Efficiency	Color temperature	Operating temperature range	Power factor	Certifications	Dimensions	12NC	EAN1	EEL
	lm	W	hrs	[Lm/W]	K	°C			mm			
MZD LED 40W A60 E27 827 FR ND 1CT/6	470	4.9	15000	95	2700	-20 to +45	0.53	CE	60 x 107	929003540232	8710163540511	F A G
MZD LED 40W A60 E27 827 FR ND 2CT/5	470	4.9	15000	95	2700	-20 to +45	0.53	CE	60 x 107	929003540233	8710163540771	F A G
MZD LED 40W A60 E27 840 FR ND 1CT/6	470	4.9	15000	95	4000	-20 to +45	0.54	CE	60 x 108	929003564132	8710163540535	F A G
MZD LED 40W A60 E27 840 FR ND 2CT/5	470	4.9	15000	95	4000	-20 to +45	0.54	CE	60 x 108	929003564133	8710163540757	F A G
MZD LED 40W A60 E27 865 FR ND 1CT/6	470	4.9	15000	95	6500	-20 to +45	0.5	CE	60 x 107	929003604232	8710163540559	F A G
MZD LED 60W A60 E27 827 FR ND 1CT/6	806	8	15000	100	2700	-20 to +45	0.54	CE	60 x 108	929002306232	8710163540573	F A G
MZD LED 60W A60 E27 827 FR ND 2CT/5	806	8	15000	100	2700	-20 to +45	0.54	CE	60 x 108	929002306243	8710163540818	F A G
MZD LED 60W A60 E27 840 FR ND 1CT/6	806	8	15000	100	4000	-20 to +45	0.54	CE	60 x 108	929002306332	8710163540597	F A G
MZD LED 60W A60 E27 840 FR ND 2CT/5	806	8	15000	100	4000	-20 to +45	0.54	CE	60 x 108	929002306333	8710163540795	F A G
MZD LED 60W A60 E27 865 FR ND 1CT/6	806	8	15000	100	6500	-20 to +45	0.54	CE	60 x 108	929002306432	8710163540610	F A G
MZD LED 60W A60 B22 827 FR ND 1CT/6	806	8	15000	100	2700	-20 to +45	0.55	CE	60 x 105	929002310232	8710163540658	F A G
MZD LED 60W A60 E27 827 FR ND 10CT/2*	806	8	15000	100	2700	-20 to +45	0.54	CE	60 x 108	929002306223	8710163541297	F A G
MZD LED 75W A60 E27 827 FR ND 1CT/6 G3	1055	10	15000	105	2700	-20 to +45	0.54	CE	60 x 108	929002306532	8710163540931	F A G
MZD LED 75W A60 E27 840 FR ND 1CT/6 G3	1055	10	15000	105	4000	-20 to +45	0.54	CE	60 x 108	929002306632	8710163540955	F A G
MZD LED 75W A60 E27 CDL FR ND 1CT/6 G3	1055	10	15000	105	6500	-20 to +45	0.54	CE	60 x 108	929002306732	8710163540917	F A G
MZD LED 100W A60 E27 WW FR ND 1CT/6	1521	13	15000	117	2700	-20 to +45	0.54	CE	60 x 120	929002306832	8710163540450	E A G
MZD LED 100W A60 E27 CW FR ND 1CT/6 G3	1521	13	15000	117	4000	-20 to +45	0.54	CE	60 x 120	929002306932	8710163540634	E A G
MZD LED 100W A60 E27 CDL FR ND 1CT/6 G3	1521	13	15000	117	6500	-20 to +45	0.54	CE	60 x 120	929002307032	8710163540474	E A G

* Multipack

LED BULBS

FOR INSTANT ENERGY SAVINGS

80
CRI

⚡
220-240 Vac

ON
OFF
up to 20,000x

⚠
non dimmable

Product type	Lumen output	Energy consumption	Lifetime	Efficiency	Color temperature	Operating temperature range	Power factor	Certifications	Dimensions	12NC	EAN1	EEL
	lm	W	hrs	[Lm/W]	K	°C			mm			
MZD LEDCLA 40W A60 E27 827 CL ND 1CT/10	470	4.3	15000	109	2700	-20 to +45	0.52	CE	60 x 104	929001890032	3139188163768	F A G
MZD LEDCLA 40W A60 E27 840 CL ND 1CT/10	470	4.3	15000	109	4000	-20 to +45	0.52	CE	60 x 104	929002214432	3139188163782	F A G
MZD LEDCLA 60W A60 E27 827 CL ND 1CT/10	806	7	15000	115	2700	-20 to +45	0.52	CE	60 x 104	929003033932	8710163541617	E A G
MZD LEDCLA 60W A60 E27 840 CL ND 1CT/10	806	7	15000	115	4000	-20 to +45	0.52	CE	60 x 104	929003035632	8710163541570	E A G
MZD LEDCLA 75W A60 E27 827 CL ND 1CT/10	1055	8.5	15000	124	2700	-20 to +45	0.56	CE	60 x 104	929003033832	8710163541556	E A G
MZD LEDCLA 75W A60 E27 840 CL ND 1CT/10	1055	8.5	15000	124	4000	-20 to +45	0.56	CE	60 x 104	929003035732	8710163541532	E A G
MZD LEDCLA 100W A60 E27 827 CL ND 1CT/10	1521	10.5	15000	144	2700	-20 to +45	0.52	CE	60 x 104	929002026132	8710163540498	D A G
MZD LEDClassic 100W A60 E27 CWCLND1CT/10	1521	10.5	15000	144	4000	-20 to +45	0.5	CE	60 x 104	929002026232	8710163541594	D A G

Product type	Lumen output	Energy consumption	Lifetime	Efficiency	Color temperature	Operating temperature range	Power factor	Certifications	Dimensions	12NC	EAN1	EEL
	lm	W	hrs	[Lm/W]	K	°C			mm			
MZD LEDCLA 60W A60 E27 827 FR ND 1CT/10	806	7	15000	115	2700	-20 to +45	0.52	CE	60 x 104	929003033332	8710163541938	E A G
MZD LEDCLA 60W A60 E27 840 FR ND 1CT/10	806	7	15000	115	4000	-20 to +45	0.52	CE	60 x 104	929003033632	8710163541952	E A G
MZD LEDCLA 75W A60 E27 827 FR ND 1CT/10	1055	8.5	15000	124	2700	-20 to +45	0.56	CE	60 x 104	929003033432	8710163541976	E A G
MZD LEDCLA 75W A60 E27 840 FR ND 1CT/10	1055	8.5	15000	124	4000	-20 to +45	0.56	CE	60 x 104	929003033532	8710163541990	E A G
MZD LEDCLA 100W A60 E27 827 FR ND 1CT/10	1521	10.5	15000	144	2700	-20 to +45	0.52	CE	60 x 104	929002026432	8710163542010	D A G
MZD LEDCLA 100W A60 E27 840 FR ND 1CT/10	1521	10.5	15000	144	4000	-20 to +45	0.52	CE	60 x 104	929002026532	8710163542034	D A G
MZD LEDCLA 120W A67 E27 827 FR ND 1CT/10	2000	13	15000	153	2700	-20 to +45	0.51	CE	70 x 121	929002371832	8710163542133	D A G
MZD LEDCLA 120W A67 E27 840 FR ND 1CT/10	2000	13	15000	153	4000	-20 to +45	0.51	CE	70 x 121	929002371932	8710163542157	D A G

LED BULBS

FOR INSTANT ENERGY SAVINGS

80
CRI

⚡
220-240 Vac

ON
OFF
up to 20,000x

⏻
Dimmable



Product type	Lumen output	Energy consumption	Lifetime	Efficiency	Color temperature	Operating temperature range	Power factor	Certifications	Dimensions	12NC	EAN1	EEL
	lm	W	hrs	[Lm/W]	K	°C			mm			
MZD LEDCLA 60W E27 827 A60 CL D 1CT/10	806	7.2	15000	111	2700	-20 to +45	0.7	CE	60 x 105	929003034632	8710163542393	E A++ G
MZD LEDCLA 100W A60 E27 827 CL D 1CT/10	1521	11.5	15000	132	2700	-20 to +45	0.7	CE	60 x 105	929002428832	8710163542416	E A++ G
MZD LEDCLA 60W E27 827 A60 FR D 1CT/10	806	7.2	15000	111	2700	-20 to +45	0.7	CE	60 x 104	929003034732	8710163542355	E A++ G
MZD LEDCLA 100W A60 E27 827 FR D 1CT/10	1521	11.5	15000	132	2700	-20 to +45	0.7	CE	60 x 104	929002429432	8710163542379	E A++ G

LUMINAIRES

Indoor
luminaires



Outdoor
luminaires



LAMPS

LED Bulbs



LED Candles & Lustres



LED Spots



LED Tubes



LED High-bay lamps



LED CANDLE & LUSTRE

FOR INSTANT ENERGY SAVINGS

LED Candles & Lustres

Elegant energy-saving lamps for a wide range of applications. An extensive range of non-dimmable candles and lustres, available in 250, 470 and 806 lumen, in clear and frosted version and in 3 color temperatures from warm white to cool daylight.



B35 frosted



B35 clear glass



P45 E27 frosted



P45 E14 frosted



B35 frosted glass



P45 clear glass



P45 frosted glass

LED CANDLE & LUSTRE

DESIGNED FOR ATMOSPHERE

80
CRI

⚡
220-240 Vac

ON
OFF
up to 30,000x

⚠
non dimmable



Product type	Lumen output	Energy consumption	Lifetime	Efficiency	Color temperature	Operating temperature range	Power factor	Certifications	Dimensions	12NC	EAN1	EEL
	lm	W	hrs	[Lm/W]	K	°C			mm			
MZD LED 25W E14 827 B35 FR ND 1CT/10	250	3	15000	83	2700	-20 to +45	0.47	CE	35x106	929002966832	8710163541372	G
MZD LED 25W B35 E14 CW FR ND 1CT/10 G3	250	3	15000	83	4000	-20 to +45	0.47	CE	35x106	929002967432	8710163541433	G
MZD LED 25W B35 E14 CDL FR ND 1CT/10 G3	250	3	15000	83	6500	-20 to +45	0.47	CE	35x106	929003041332	8710163541631	G
MZD LED 40W B35 E14 WW FR ND 1CT/10	470	4.9	15000	95	2700	-20 to +45	0.51	CE	35x106	929003541132	8710163541396	F
MZD LED 40W B35 E14 CW FR ND 1CT/10	470	4.9	15000	95	4000	-20 to +45	0.5	CE	35x106	929003604032	8710163541419	F
MZD LED 40W B35 E14 CDL FR ND 1CT/10 G3	470	4.9	15000	95	6500	-20 to +45	0.5	CE	35x106	929003604132	8710163541457	F
MZD LED 60W B35 E14 827 ND 1CT/10	806	8	15000	100	2700	-20 to +45	0.54	CE	38x114	929002972532	8710163541310	F
MZD LED 60W B35 E14 840 ND 1CT/10	806	8	15000	100	4000	-20 to +45	0.54	CE	38x114	929002972732	8710163541334	F
MZD LED 60W B35 E14 865 ND 1CT/10	806	8	15000	100	6500	-20 to +45	0.54	CE	38x114	929002972932	8710163541358	F



Product type	Lumen output	Energy consumption	Lifetime	Efficiency	Color temperature	Operating temperature range	Power factor	Certifications	Dimensions	12NC	EAN1	EEL
	lm	W	hrs	[Lm/W]	K	°C			mm			
MZD LED 25W E14 827 P45 FR ND 1CT/10	250	2.8	15000	89	2700	-20 to +45	0.41	CE	45x88	929002967132	8710163542539	F
MZD LED 25W E27 827 P45 FR ND 1CT/10	250	2.8	15000	89	2700	-20 to +45	0.41	CE	45x87	929002966932	8710163542553	F
MZD LED 40W P45 E14 WW FR ND 1CT/10	470	4.9	15000	85	2700	-20 to +45	0.5	CE	45x84	929003540532	8710163543222	F
MZD LED 40W P45 E27 WW FR ND 1CT/10	470	4.9	15000	85	2700	-20 to +45	0.5	CE	45x79	929003540632	8710163543000	F
MZD LED 40W P45 E14 CW FR ND 1CT/10	470	4.9	15000	85	4000	-20 to +45	0.5	CE	45x84	929003540732	8710163543024	F
MZD LED 40W P45 E27 CW FR ND 1CT/10	470	4.9	15000	85	4000	-20 to +45	0.5	CE	45x79	929003540832	8710163543048	F
MZD LED 40W P45 E14 CDL FR ND 1CT/10 G3	470	4.9	15000	94	6500	-20 to +45	0.5	CE	45x82	929003540932	8710163543062	F
MZD LED 40W P45 E27 CDL FR ND 1CT/10 G3	470	4.9	15000	94	6500	-20 to +45	0.5	CE	45x77	929003541032	8710163543086	F



LED CANDLE & LUSTRE

DESIGNED FOR ATMOSPHERE

80
CRI

220-240 Vac

ON
OFF
up to 20,000x

non dimmable



Product type	Lumen output	Energy consumption	Lifetime	Efficiency	Color temperature	Operating temperature range	Power factor	Certifications	Dimensions	12NC	EAN1	EEL
	lm	W	hrs	[Lm/W]	K	°C			mm			
MZD LEDCLA 40W P45 E14 827 FR ND 1CT/10	470	4.3	15000	109	2700	-20 to +45	0.51	CE	45x80	929001345532	8710163542058	F A G
MZD LEDCLA 40W P45 E14 840 FR ND 1CT/10	470	4.3	15000	109	4000	-20 to +45	0.51	CE	45x80	929002269432	8710163542072	F A G
MZD LEDCLA 25W P45 E14 827 CL ND 1CT/10	250	2	15000	125	2700	-20 to +45	0.5	CE	45x80	929001238632	3139188163881	E A G
MZD LEDCLA 25W P45 E14 840 CL ND 1CT/10	250	2	15000	125	4000	-20 to +45	0.5	CE	45x80	929002215132	3139188164109	E A G
MZD LEDCLA 40W P45 E14 827 CL ND 1CT/10	470	4.3	15000	109	2700	-20 to +45	0.52	CE	45x80	929001890432	3139188163904	F A G
MZD LEDCLA 40W P45 E14 840 CL ND 1CT/10	470	4.3	15000	109	4000	-20 to +45	0.52	CE	45x80	929002214632	3139188163928	F A G



Product type	Lumen output	Energy consumption	Lifetime	Efficiency	Color temperature	Operating temperature range	Power factor	Certifications	Dimensions	12NC	EAN1	EEL
	lm	W	hrs	[Lm/W]	K	°C			mm			
MZD LEDCLA 40W B35 E14 827 FR ND 1CT/10	470	4.3	15000	109	2700	-20 to +45	0.51	CE	35 x 97	929001345332	8710163542096	F A G
MZD LEDCLA 40W B35 E14 840 FR ND 1CT/10	470	4.3	15000	109	4000	-20 to +45	0.51	CE	35 x 97	929002269332	8710163542119	F A G
MZD LEDCLA 25W B35 E14 827 CL ND 1CT/10	250	2	15000	125	2700	-20 to +45	0.52	CE	35 x 97	929001238332	3139188163942	E A G
MZD LEDCLA 25W B35 E14 840 CL ND 1CT/10	250	2	15000	125	4000	-20 to +45	0.5	CE	35 x 97	929002215232	3139188164123	E A G
MZD LEDCLA 40W B35 E14 827 CL ND 1CT/10	470	4.3	15000	109	2700	-20 to +45	0.52	CE	35 x 97	929001889732	3139188163966	F A G
MZD LEDCLA 40W B35 E14 840 CL ND 1CT/10	470	4.3	15000	109	4000	-20 to +45	0.52	CE	35 x 97	929002214932	3139188163980	F A G
MZD LEDCLA 60W B35 E14 827 CL ND 1CT/10	806	6.5	15000	124	2700	-20 to +45	0.52	CE	35 x 97	929003035932	8710163541754	E A G
MZD LEDCLA 60W B35 E14 840 CL ND 1CT/10	806	6.5	15000	124	4000	-20 to +45	0.52	CE	35 x 97	929003036032	8710163541778	E A G

LUMINAIRES

Indoor
luminaires



Outdoor
luminaires



LAMPS

LED Bulbs



LED Candles & Lustres



LED Spots



LED Tubes



LED High-bay lamps



LED SPOTS

FOR INSTANT ENERGY SAVINGS

LED Spots

Our LED Spots are ideal for creating lighting accents. Come in 2 versions: GU10 and GU5.3, with various lumen packages, color temperatures and beam options.



GU10



GU5.3

LED SPOTS

SPOTLIGHT ON STYLE

80
CRI

⚡
220-240 Vac

ON
OFF
up to 30,000x

⚠
non dimmable



Product type	Energy consumption	Beam angle	Lifetime	Color temperature	Operating temperature range	Lumen output	Efficiency	Power factor	Certifications	Dimensions	12NC	EAN1	EEL
	W		hrs	K	°C	lm	[Lm/W]			mm			
MZD LED 50W GU10 827 36D ND 1CT/10	4.7	36	15000	2700	-20 to +45	380	80	0.4	CE	50x56	929003038632	8710163541495	F A ↑ G
MZD LED 50W GU10 840 36D ND 1CT/10	4.7	36	15000	4000	-20 to +45	440	93	0.4	CE	50x56	929003038332	8710163541471	E A ↑ G
MZD LED 50W GU10 827 36D ND 10CT/6	4.7	36	15000	2700	-20 to +45	345	73	0.53	CE	50x54	929001250443	8710163541273	G A ↑ G
MZD LED 50W GU10 830 60D ND 1CT/10	4.7	60	15000	3000	-20 to +45	345	73	0.53	CE	50x54	929001912232	3139188161276	F A ↑ G
MZD LED 50W GU10 840 60D ND 1CT/10	4.7	60	15000	4000	-20 to +45	360	76	0.53	CE	50x54	929001912332	3139188161290	F A ↑ G
MZD LED 65W GU10 827 36D ND 1CT/10	4.9	36	15000	2700	-20 to +45	460	93	0.4	CE	50x56	929003038832	8710163541877	E A ↑ G
MZD LED 65W GU10 840 36D ND 1CT/10	4.9	36	15000	4000	-20 to +45	460	93	0.4	CE	50x56	929001371232	3139188161658	E A ↑ G
MZD LED 500lm GU10 827 120D ND 1CT/10	4.9	120	15000	2700	-20 to +45	500	102	0.4	CE	50x58	929001372032	3139188161719	F A ↑ G
MZD LED 500lm GU10 840 120D ND 1CT/10	4.9	120	15000	4000	-20 to +45	500	102	0.4	CE	50x58	929001358632	3139188161696	F A ↑ G
MZD LED 500lm GU10 865 120D ND 1CT/10	4.9	120	15000	6500	-20 to +45	500	102	0.4	CE	50x58	929001372132	3139188161733	F A ↑ G
MZD LED 720lm GU10 830 120D ND 1CT/10	7	120	15000	3000	-20 to +45	720	102	0.52	CE	50x58	929002093332	3139188163584	F A ↑ G
MZD LED 720lm GU10 840 120D ND 1CT/10	7	120	15000	4000	-20 to +45	720	102	0.52	CE	50x58	929002093432	3139188163607	F A ↑ G
MZD LED 720lm GU10 865 120D ND 1CT/10	7	120	15000	6500	-20 to +45	720	102	0.52	CE	50x58	929002093532	3139188163621	F A ↑ G

LED SPOTS

SPOTLIGHT ON STYLE

80
CRI

⚡
220-240 Vac

ON
OFF
up to 30,000x

⚠
non dimmable



Product type	Energy consumption	Beam angle	Lifetime	Color temperature	Operating temperature range	Lumen output	Efficiency	Power factor	Certifications	Dimensions	12NC	EAN1	EEL
	W		hrs	K	°C	lm	[Lm/W]			mm			
MZD LED 50W GU5.3 827 12V 36D ND 1CT/10	6.5	36	15000	2700	-20 to +45	621	95	0.5	CE	50x45	929002404732	8710163540719	F A ↑ G
MZD LED 50W GU5.3 840 12V 36D ND 1CT/10	6.5	36	15000	4000	-20 to +45	621	95	0.5	CE	50x45	929002404832	8710163540733	F A ↑ G
MZD LED 50W GU5.3 830 12V 60D ND 1CT/10	6.5	60	15000	3000	-20 to +45	621	95	0.5	CE	50x45	929002404532	8710163540672	F A ↑ G
MZD LED 50W GU5.3 840 12V 60D ND 1CT/10	6.5	60	15000	4000	-20 to +45	621	95	0.5	CE	50x45	929002404632	8710163540696	F A ↑ G

LUMINAIRES

Indoor luminaires



Outdoor luminaires



LAMPS

LED Bulbs



LED Candles & Lustres



LED Spots



LED Tubes



LED High-bay lamps



LED TUBES

FOR INSTANT ENERGY SAVINGS

LED Tubes

Our LED tubes provide high quality light to illuminate any space, saving energy up to 55%. Range consists of T8 in 600, 1200, 1500mm in a choice of 3 color temperatures (white, cool white and cool daylight).



T8 Tube

LED TUBES

FOR INSTANT ENERGY SAVINGS

80
CRI

⚡
220-240 Vac

ON
OFF
200,000x

⚠
non dimmable

T8 TUBE



Product type	Lamp type	Energy consumption	Beam angle	Lifetime	Color temperature	Operating temperature range	Lumen output	Efficiency		Certifications	Input current	Frequency	Dimensions	12NC	EAN1	EEL
		W		hrs	K	°C	lm	[Lm/W]								
MZD LEDtube 600mm 8W 840	T8	8	240	30000	4000	-20 to +45	800	100	0.9	CE	46	50/60	604h/27,80ø	929003547632	8710163543284	F A G
MZD LEDtube 600mm 8W 865	T8	8	240	30000	6500	-20 to +45	800	100	0.9	CE	46	50/60	604h/27,80ø	929003547732	8710163543307	F A G
MZD LEDtube 1200mm 15.5W 840	T8	15.5	240	30000	4000	-20 to +45	1800	116	0.9	CE	84	50/60	1213,60h/27,80ø	929003519932	8710163542430	E A G
MZD LEDtube 1200mm 15.5W 865	T8	15.5	240	30000	6500	-20 to +45	1800	116	0.9	CE	84	50/60	1213,60h/27,80ø	929003520032	8710163542454	E A G
MZD LEDtube 1500mm 20W 840	T8	20	240	30000	4000	-20 to +45	2200	110	0.9	CE	105	50/60	1514,20h/27,80ø	929003547832	8710163543321	E A G
MZD LEDtube 1500mm 20W 865	T8	20	240	30000	6500	-20 to +45	2200	110	0.9	CE	105	50/60	1514,20h/27,80ø	929003547932	8710163543345	E A G
MZD LEDtube 1200mm UO 21.5W 830	T8	21.5	240	30000	3000	-20 to +45	2250	104	0.9	CE	105	50/60	1214h/28ø	929003650702	8710163543888	F A G
MZD LEDtube 1200mm UO 21.5W 840	T8	21.5	240	30000	4000	-20 to +45	2400	111	0.9	CE	105	50/60	1214h/28ø	929003635902	8710163543741	E A G
MZD LEDtube 1200mm UO 21.5W 865	T8	21.5	240	30000	6500	-20 to +45	2400	111	0.9	CE	105	50/60	1214h/28ø	929003636002	8710163543765	E A G
MZD LEDtube 1500mm UO 31.5W 830	T8	31.5	240	30000	3000	-20 to +45	3320	105	0.9	CE	135	50/60	1514h/28ø	929003650802	8710163543901	F A G
MZD LEDtube 1500mm UO 31.5W 840	T8	31.5	240	30000	4000	-20 to +45	3500	111	0.9	CE	135	50/60	1514h/28ø	929003636102	8710163543789	E A G
MZD LEDtube 1500mm UO 31.5W 865	T8	31.5	240	30000	6500	-20 to +45	3500	111	0.9	CE	135	50/60	1514h/28ø	929003636202	8710163543802	E A G

LUMINAIRES

Indoor luminaires



Outdoor luminaires



LAMPS

LED Bulbs



LED Candles & Lustres



LED Spots



LED Tubes



LED High-bay lamps



LED HIGH-BAY LAMPS

FOR INSTANT ENERGY SAVINGS

LED High-bay

Quick and easy solution to replace conventional HID/CFLi lamps in industrial applications for immediate energy savings.



LED HIGH-BAY LAMPS

FOR INSTANT ENERGY SAVINGS

80
CRI

⚡
220-240 Vac

ON
OFF
50,000x

⚠
non dimmable

LED HIGH_BAY LAMPS

Product type	Lamp type	Energy consumption	Beam angle	Lifetime	Color temperature	Operating temperature range	Lumen output	Efficiency	Power factor	Certifications	Input current	Frequency	Dimensions	12NC	EAN1	EEL
		W		hrs	K	°C	lm	[Lm/W]								
MZD LED 20W E27 840 HB G3 1CT/6	T shape	20	150	10000	4000	-20 to +45	2700	135	>0.5	CE	170	50/60	139h/80ø	929002453432	8710163540856	D A G
MZD LED 35W E27 840 HB G3 1CT/6	T shape	35	180	10000	4000	-20 to +45	5000	142	>0.9	CE	178	50/60	193h/118ø	929002453632	8710163540894	D A G



MAZDA | I.B.R.S. / C.C.R.I. Numéro 10461 | 5600 VB Eindhoven, the Netherlands | WWW.MAZDALIGHTING.COM

© 2021 Signify Holding. All rights reserved. The information provided herein is subject to change, without notice. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify.

All trademarks are owned by Signify Holding or their respective owners.

 **MAZDA**