



CoreLine recessed

RC136B 43S/840 WIA W60L60 OC

CoreLine recessed, 31 W, 600x600 mm, 4300 lm, 4000 K, Wireless, Interact Ready, UGR19

Philips CoreLine recessed delivers on the CoreLine promise of innovative, easy-to-use, high-quality luminaires. It's a high-quality recessed LED that's designed to replace existing recessed luminaires with T8 or T5 technology. This CoreLine family also features an innovative new choice of multiple lumen outputs in one single luminaire, called MultiLumen. Instant energy savings and a longer lifetime, make this an environmentally-friendly and cost-saving solution. With a quick-connector or Wieland feature, CoreLine RC136B recessed luminaires are quick and easy to install. Also available within the range are Interact Ready luminaires with integrated wireless communications, which are fully compatible with Interact gateways, sensors and software.

Warnings and Safety

- The product is IPX0 & as such is not protected against water ingress & as such we strongly recommend that The environment in which The luminaire is to be installed is suitably checked
- If the above advice is not taken and the luminaires are subject to water ingress, Philips / Signify cannot guarantee safe failure & product warranty will become void

Product data

General Information			
Light source replaceable	No	Warranty period	5 years
Number of gear units	1 unit	Flammability mark	For mounting on normally flammable surfaces
Driver included	Yes	ENEC mark	ENEC mark
Connectivity	Interact Ready	Glow-wire test	Temperature 650 °C, duration 30 s
Lighting Technology	LED	EU RoHS compliant	Yes
Value ladder	Performance		
CE mark	Yes		

CoreLine recessed

Light Technical	
Luminous Flux	4,300 lm
Saturated Red (R9)	<50
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	140 lm/W
Color rendering index (CRI)	≥80
Flickering value (PstLM)	1
Stroboscopic effect value (SVM)	0.4
Light source color	840 neutral white
Optic type	Beam angle 84°
Luminaire light beam spread	84°
Unified glare rating CEN	19

Operating and Electrical	
Input Voltage	220-240 V
Line Frequency	50 or 60 Hz
Inrush current	4.9 A
Inrush time	0.056 ms
Power Consumption	31 W
Power Factor (Fraction)	0.9
Connection	Connection unit 3-pole
Cable	Cable with connector 3-pole
Number of products on MCB of 16 A type B	24

Temperature	
Ambient temperature range	-10 to +40 °C

Controls and Dimming	
Dimmable	Yes
Driver/power unit/transformer	Wireless driver Interact System ready
Control interface	Wireless
Constant light output	No

Mechanical and Housing	
Housing Material	Steel
Reflector material	Polycarbonate
Optic material	Polycarbonate
Optical cover material	Polymethyl methacrylate
Fixation material	-
Housing Color	White
Optical cover finish	Microprismatic lens
Overall length	597 mm
Overall width	597 mm

Overall height	44 mm
Dimensions (Height x Width x Depth)	44 x 597 x 597 mm

Approval and Application	
Ingress protection code	IP20/44 [Finger-protected; wire-protected, splash-proof]
Mech. impact protection code	IK03 [0.3 J]
Sustainability rating	-
Protection class IEC	Safety class II
Photobiological risk	Photobiological risk group 0 @200mm to EN62778

Initial Performance (IEC Compliant)	
Luminous flux tolerance	+/-10%
Initial chromaticity	(0.38, 0.38) SDCM ≤3
Power consumption tolerance	+/-10%

Over Time Performance (IEC Compliant)	
Control gear failure rate at median useful life	5 %
50000 h	
Lumen maintenance at median useful life*	L85
50000 h	
Lumen maintenance at median useful life*	L70
100000 h	

Application Conditions	
Performance ambient temperature Tq	25 °C
Maximum dim level	1%
Suitable for random switching	Yes

Product Data	
Order product name	RC136B 43S/840 WIA W60L60 OC
Full product name	RC136B 43S/840 WIA W60L60 OC
Full product code	871951451505500
Order code	911401896781
Material Nr. (12NC)	911401896781
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8719514515055
Numerator - Packs per outer box	1
EAN/UPC - Case	8719514515055

CoreLine recessed

Dimensional drawing

