



## CoreLine Panel

### SMI36V 43S/840 WIA W20LI50 OC ELP3

CoreLine surface-mounted, 32.5 W, 1500x200 mm, 4300 lm, 4000K, Wireless, Interact Ready, UGR19, Self-test 3h emergency

#### Product data

##### General Information

Luminous flux (system)	4300 lm
Emergency output	294 lm
Luminaire efficacy	132 lm/W
Luminous flux tolerance	+/- 10%
Light source colour	4000K [neutral white]
Init. Colour rendering index	> 80
Initial chromaticity	(0.38, 0.38) SDCM≤3
Unified glare (UGR)	19 [office compliant]
Beam angle	84°
Installation	Surface mounted
Connection type	3 or 4 pole connection
Emergency	ELP [Self-test 3h emergency]
Battery type	LiFePO4
Ambient temperature range	0 to +40 °C

##### Controls and Dimming

Driver	WIA [Wireless driver Interact System-ready]
Dimming	Yes

##### Mechanical and housing

Housing material	Steel
Colour	White
IP / IK rating	IP20/44 IK03 (0.3J)
Dimensions (L x W x H)	69 x 200 x 1200 mm

##### Operating and Electrical

Mains supply	230 – 240V / 50-60Hz
Power consumption	32.5 W
Power Factor (Fraction)	0.9
Power consumption tolerance	+/- 10%
Safety class	II

##### Over Time Performance

Control gear failure rate at median useful life 50000 h	5 %
Lumen maintenance at median useful life* 50000 h	L85
Lumen maintenance at median useful life* 100000 h	L70

##### Product data

Order code	821350000017
Product name	SMI36V 43S/840 WIA W20LI50 OC ELP3

##### Dimensions

