



# CoreLine Fastset, surface-mounted

SM155C 48S/830\_840 WIA TW3 PI5 L1160

CoreLine Fastset, surface-mounted, 34 W, L1160 mm, 4800 lm, 3000 K, 4000 K, Wireless, Interact Ready

Philips CoreLine FastSet is a 1:1 energy-efficient LED replacement for conventional indoor surface-mounted lights. With identical lumen packages to fluorescent lighting, there's no need to make new lighting calculations for retrofit projects – thanks to the all-in-one design, you can switch between correlated color temperatures (CCT) and lumen package in the same luminaire to suit your exact needs. Installation of these surface-mounted LED lights is fast and flexible too with a choice of simple through-wiring, or cable entry from the side or back of the luminaire. That means CoreLine FastSet indoor surface-mounted lights are easy to mount as a standalone fixture, directly to the surface-mounted or using brackets. You can also create a line of light due to straight end-caps with head to head mounting. It is also easy to connect them to other CoreLine Fastset luminaires to create harmonious lines of light. Should you require it, accessories are also available to adapt the CoreLine fixtures for suspended mounting. As you'd expect from Philips, safety is designed into every CoreLine FastSet luminaire. Not only are the IP44 and IK06 rated to protect against accidental impact, the captive safety pins on the luminaire cover also prevents it from falling. Interact Ready options are available for smart lighting applications. So with CoreLine FastSet surface-mounted LED lights, you have the perfect solution for high circulation areas such as hallways and staircase lighting.

## Product data

General Information		Driver included	
Number of gear units	1 unit	Feed-through wiring	Feed-through wiring 3-phase

## CoreLine Fastset, surface-mounted

Connectivity	Interact Ready
Value ladder	Performance
CE mark	CE mark
Warranty period	5 years
Flammability mark	For mounting on normally flammable surfaces
ENEC mark	ENEC mark
Glow-wire test	Temperature 650 °C, duration 30 s
EU RoHS compliant	Yes

### Light Technical

Luminous Flux	4.800 lm
Saturated Red (R9)	<50
Correlated Color Temperature (Nom)	3000 4000 K
Luminous Efficacy (rated) (Nom)	133 lm/W
Color rendering index (CRI)	80
Flickering value (PstLM)	1
Stroboscopic effect value (SVM)	0.4
Light source color	Multi Color Temperature
Optic type	Opal
Luminaire light beam spread	110°
Unified glare rating CEN	25

### Operating and Electrical

Input Voltage	220 to 240 V
Line Frequency	50 or 60 Hz
Inrush current	17 A
Inrush time	0.14 ms
Power Consumption	34 W
Power Factor (Fraction)	0.95
Connection	Push-in connector 5-pole
Cable	-
Number of products on MCB of 16 A type B	25

### Temperature

Ambient temperature range	-20 °C to 45 °C
---------------------------	-----------------

### Controls and Dimming

Dimmable	Yes
Driver/power unit/transformer	Wireless driver Interact System ready
Control interface	Wireless
Constant light output	No

### Mechanical and Housing

Housing Material	Steel
Reflector material	Steel
Optic material	Polycarbonate
Optical cover material	Polycarbonate

Fixation material	-
Housing Color	White RAL 9003
Optical cover finish	Opal
Overall length	1,160 mm
Overall width	163 mm
Overall height	67 mm
Dimensions (Height x Width x Depth)	67 x 163 x 1160 mm

### Approval and Application

Ingress protection code	IP44 [Wire-protected, splash-proof]
Mech. impact protection code	IK08 [5 J vandal-protected]
Sustainability rating	-
Protection class IEC	Safety class I
Photobiological risk	Photobiological risk group 0 @ 200mm to EN62471
Photobiological risk specification	0.2 m

### Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Initial chromaticity	(0.38,0.38)SDCM<3;(0.44,0.40)SDCM<3
Power consumption tolerance	+/-10%

### Over Time Performance (IEC Compliant)

Control gear failure rate at median useful life 50000 h	5 %
Lumen maintenance at median useful life* 50000 h	L80
Lumen maintenance at median useful life* 100000 h	L65

### Application Conditions

Performance ambient temperature Tq	25 °C
Maximum dim level	10%
Suitable for random switching	Yes

### Product Data

Order product name	SM155C 48S/830_840 WIA TW3 PI5 L1160
Full product name	SM155C 48S/830_840 WIA TW3 PI5 L1160
Full product code	872016975070899
Order code	911401803287
Material Nr. (12NC)	911401803287
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8720169750708
Numerator - Packs per outer box	4
EAN/UPC - Case	8720169750753

CoreLine Fastset, surface-mounted

Dimensional drawing

