



Coreline Slim Batten

BN126C LED22S/840 PSU L600

Coreline Slim Batten, 21 W, 2200 lm, 4000 K

The new Philips Coreline slim batten offers exceptional value. It is Perfect for your everyday lighting installations. Available in 3 standard sizes, and 2 CCTs to provide flexibility to customer.

Product data

General Information	
Light source engine type	LED
CE mark	CE mark
Light Technical	
Luminous Flux	2,200 lm
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	104 lm/W
Color rendering index (CRI)	>80
Light source color	840 neutral white
Optical cover type	Polycarbonate Diffuser
Operating and Electrical	
Input Voltage	220 to 240 V
Line Frequency	50 or 60 Hz
Power Consumption	21 W
Power Factor (Fraction)	0.9
Number of products on MCB of 16 A type B	80

Temperature	
Ambient temperature range	-20 to +40 °C
Controls and Dimming	
Dimmable	No
Control interface	-
Mechanical and Housing	
Housing Material	Steel
Optical cover material	Polycarbonate
Housing Color	White RAL 9003
Optical cover finish	Opal
Overall length	65 mm
Overall width	65 mm
Overall height	600 mm
Dimensions (Height x Width x Depth)	600 x 65 x 65 mm
Approval and Application	
Ingress protection code	IP20/40 [Finger-protected, Emitting surface]
Mech. impact protection code	IK04 [0.5 J standard plus]

Coreline Slim Batten

Protection class IEC	Safety class I
Initial Performance (IEC Compliant)	
Luminous flux tolerance	+/-10%
Power consumption tolerance	+/-10%
Product Data	
Order product name	BN126C LED22S/840 PSU L600
Full product name	BN126C LED22S/840 PSU L600

Full product code	692382863851199
Order code	911401898780
Material Nr. (12NC)	911401898780
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	6923828638511
Numerator - Packs per outer box	8
EAN/UPC - Case	6923828638573

Dimensional drawing

