



# CoreLine Waterproof

## WT120C G2 LED19S/840 PSD L600

CoreLine Waterproof, 16.5 W, L600 mm, 1900 lm, 4000 K, DALI, Wide beam, Frosted, IP65, IK08, TW1-ready

CoreLine waterproof delivers on the CoreLine promise of innovative, easy-to-use and high-quality luminaires. With its slim and stylish design, it retains the product architecture that the range is well-known and appreciated for. Installation is quick and easy, all thanks to its efficient design. CoreLine waterproof provides better wide-beam light distribution for straightforward and effective lighting. A direct replacement for traditional waterproof luminaires with fluorescent lamps ranging from 18W up to 58W, it delivers significant energy savings. Interact Ready luminaires with integrated wireless communications are also available in the CoreLine waterproof range, ready to be used with Interact connected lighting system.

### Warnings and Safety

- UV radiation will damage the material over time resulting in loss of waterproof sealing and IP66 rating.
- Do not install the luminaire in locations where it will be exposed to direct sunlight.

### Product data

General Information		
Lamp family code	LED19S [LED module, system flux 1900 lm]	
Light source replaceable	No	
Number of gear units	1 unit	
Driver included	Yes	
Feed-through wiring	Simple Connection and removable cover available for feed-through wiring 1-phase (internal wiring is not included)	
Remarks	*-Per Lighting Europe guidance paper "Evaluating performance of LED based luminaires - January 2018": statistically there is no relevant difference in lumen maintenance between B50 and for example B10. Therefore, the median useful life (B50) value also represents the B10 value.	
		Service tag
		Yes
		Product family code
		WT130C [Coreline Waterproof G2 LSC]
		Lighting Technology
		LED
		Value ladder
		Performance
		CE mark
		CE mark
		Warranty period
		5 years
		Flammability mark
		For mounting on easily flammable surfaces

# CoreLine Waterproof

ENEC mark	ENEC mark
Glow-wire test	Temperature 850 °C, duration 30 s
EU RoHS compliant	Yes

## Light Technical

Luminous Flux	1,900 lm
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (rated) (Nom)	115 lm/W
Color rendering index (CRI)	>80
Flickering value (PstLM)	1
Stroboscopic effect value (SVM)	1.6
Light source color	840 neutral white
Optic type	Wide beam
Luminaire light beam spread	105°
Unified glare rating CEN	25

## Operating and Electrical

Input Voltage	220 to 240 V
Line Frequency	50 or 60 Hz
Inrush current	19.4 A
Inrush time	0.2 ms
Power Consumption	16.5 W
Power Factor (Fraction)	0.9
Connection	Push-in connector 5-pole
Cable	-
Number of products on MCB of 16 A type B	30

## Temperature

Ambient temperature range	-20 to +35 °C
---------------------------	---------------

## Controls and Dimming

Dimmable	Yes
Driver/power unit/transformer	Power supply unit with DALI interface
Control interface	DALI
Constant light output	No

## Mechanical and Housing

Housing Material	Polycarbonate
Reflector material	Steel
Optic material	Polycarbonate
Optical cover material	Polycarbonate
Fixation material	Stainless steel
Housing Color	Gray

Optical cover finish	Frosted
Overall length	665 mm
Overall width	80 mm
Overall height	76 mm
Dimensions (Height x Width x Depth)	76 x 80 x 665 mm

## Approval and Application

Ingress protection code	IP65 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK08 [5 J vandal-protected]
Sustainability rating	-
Protection class IEC	Safety class I
Photobiological risk	Photobiological risk group 0 @200mm to EN62778

## Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Initial chromaticity	(0.38,0.38)SDCM<=3
Power consumption tolerance	+/-10%

## Over Time Performance (IEC Compliant)

Control gear failure rate at median useful life 50000 h	5 %
Lumen maintenance at median useful life* 50000 h	85
Lumen maintenance at median useful life* 100000 h	70

## Application Conditions

Performance ambient temperature Tq	25 °C
Maximum dim level	1%
Suitable for random switching	Not applicable

## Product Data

Order product name	WT120C G2 LED19S/840 PSD L600
Full product name	WT120C G2 LED19S/840 PSD L600
Full product code	871869688306800
Order code	910505100038
Material Nr. (12NC)	910505100038
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	8718696883068
Numerator - Packs per outer box	1
EAN/UPC - Case	8718696883068

CoreLine Waterproof

Dimensional drawing

