



# CoreLine Highbay Gen5

## BY122X G5 LED300S/840 SIA WB H4

CoreLine Highbay Gen5, 203 W, 30000 lm, 4000 K, Wireless, Interact Ready, Wide beam, H4, IP65, IK05

CoreLine Highbay Gen5 delivers on the CoreLine promise of innovative, easy-to-use and high-quality luminaires. A reliable, highly efficient luminaire with a very long-lifetime, it delivers great savings on energy and requires less maintenance. At the same time, CoreLine Highbay is very easy to handle. The luminaire can be installed on your existing grid and the electrical connection is a straightforward task, with no need to open the luminaire and an external IP65 connector. With a choice of two beam angles: narrow and wide beam, you can adjust your lighting plan to suit your exact needs. This range also includes Interact Ready luminaires with integrated wireless communications and integrated movement and daylight sensors. So CoreLine Highbay Gen5 is ready to be used with any Interact connected lighting system.

### Product data

General Information	
Light source replaceable	No
Number of gear units	Unit
Driver included	Yes
Connectivity	Interact Ready
Lighting Technology	LED
Embedded control	Sensor SNH (R) 210
CE mark	Yes
Warranty period	5 years

Flammability mark	For mounting on normally flammable surfaces
ENEC mark	ENEC mark
Glow-wire test	Temperature 650 °C, duration 30 s
EU RoHS compliant	Yes
Light Technical	
Luminous Flux	30,000 lm
Saturated Red (R9)	<50
Correlated Colour Temperature	4000 K

## CoreLine Highbay Gen5

Luminous efficacy (rated) (nom.)	148 lm/W
Colour rendering index (CRI)	>80
Flickering value (PstLM)	0.5
Stroboscopic effect	1
Light source colour	840 neutral white
Optic type	Wide beam
Luminaire light beam spread	85° x 85°
Unified Glare Rating (CEN)	25

### Operating and Electrical

Input Voltage	220 to 240 V
Line Frequency	50 or 60 Hz
Inrush current	5.1 A
Inrush time	760 ms
Power Consumption	203 W
Power Factor (Fraction)	0.95
Connection	Connection unit 3-pole
Cable	Cable 0.3 m with connector 3-pole
Number of products on MCB of 16 A type B	6

### Temperature

Ambient temperature range	-30 to +50 °C
---------------------------	---------------

### Controls and Dimming

Dimmable	Yes
Driver/power unit/transformer	Sensor-ready driver Interact System-ready
Control interface	Wireless
Constant light output	No

### Mechanical and Housing

Housing material	Aluminium die-cast
Reflector material	-
Optic material	Polycarbonate
Optical cover/lens material	Polycarbonate
Fixation material	-
Housing Colour	Grey
Optical cover/lens finish	Clear
Overall length	530 mm
Overall height	126 mm
Overall diameter	393 mm

### Approval and Application

Ingress protection code	IP65 [Dust penetration-protected, jet-proof]
Mech. impact protection code	IK05 [0.7 J]
Sustainability rating	-
Protection class IEC	Safety class I
Photobiological risk	Photobiological risk group 1 @200mm to EN62778
Photobiological risk specification	18.2 m

### Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
Initial chromaticity	(0.385, 0.380) SDCM<5
Power consumption tolerance	+/-10%

### Over Time Performance (IEC Compliant)

Control gear failure rate at median useful life 50,000 h	5 %
Control gear failure rate at median useful life 100,000 h	10 %
Lumen maintenance at median useful life* 50,000 h	L85
Lumen maintenance at median useful life* 100,000 h	L75

### Application Conditions

Performance ambient temperature Tq	35 °C
Maximum dim level	1%
Suitable for random switching	Yes

### Product Data

Order product name	BY122X G5 LED300S/840 SIA WB H4
Full product name	BY122X G5 LED300S/840 SIA WB H4
Full EOC	871951495605600
Order code	95605600
Material no. (12 NC)	911401633108
SAP numerator – quantity per pack	1
EAN/UPC – Product/Case	8719514956056
Numerator – packs per outer box	1
EAN/UPC - Case	8719514956056

## CoreLine Highbay Gen5

### Dimensional drawing

