



## Philips GreenPower LED Interlighting 3.1 & 3.2

Length	<b>2.0 m</b> 1.95 m • 76.7 in	<b>2.5 m</b> 2.42 m • 95.3 in	Input voltage	200V – 400V	IP rating	IP66
Width	6.5 cm • 2.6 in	6.5 cm • 2.6 in	Beam angle	Bi-directional 120°	Ambient operating temp	0° C Min. • 40° C Max 40° F Min. • 104° F Max
Height	7.6 cm • 3.0 in	7.6 cm • 3.0 in	L90	36,000 hrs	Frequency	50/60 Hz
Weight	2.2 kg • 4.9 lb	2.5 kg • 5.5 lb	L70	50,000 hrs	Power factor	> 0.90
			Warranty	5 year limited	Total harmonic distortion	<10%
			UL/CSA rated	Damp/wet		

### 3.1 High Output (HO) 200V – 400V

Description	12 NC	Power (W)	Amps 208V	Amps 240V	Amps 277V	Amps 347V	Photon Flux $\mu\text{mol/s}$	Efficacy $\mu\text{mol/J}$
GPL IL 300 DRB L250 200-400V G3.1 S NA	9290 021 00154	92	0.44	0.38	0.33	0.26	300	3.3
GPL IL 240 DRB L200 200-400V G3.1 S NA	9290 021 00155	74	0.36	0.31	0.27	0.21	240	3.2

### 3.2 Extra High Output (EHO) 277V – 400V

Description	12 NC	Power (W)	Amps 277V	Amps 347V	Photon Flux $\mu\text{mol/s}$	Efficacy $\mu\text{mol/J}$
GPL IL 440 DRB L250 277-400V 3.2S NA	9290 021 00644	126	0.46	0.36	440	3.5
GPL IL 350 DRB L200 277-400V 3.2S NA	9290 021 00646	100	0.36	0.29	350	3.5