

PHILIPS

Lighting



DigiStreet Medium

BGP762 LED-HB/740 II DM10 9000 lm


Introduction

Developed with the aim of becoming your long-term partner, the system-ready architecture of DigiStreet enables you to enjoy the benefits of connected lighting systems today and also gets the city ready for the innovations to come! Its two sockets enable you to connect directly to the Philips CityTouch system and it is also prepared to connect you to the future innovations of IoT. Next to this, each individual luminaire is uniquely identifiable, thanks to the Philips Service tag application. With a simple scan of a QR code, placed on the inside of the mast door, you gain instant access to the luminaire configuration, making maintenance and programming operations faster and easier, no matter what stage of the luminaire's lifetime. DigiStreet is also equipped with dedicated light recipes that: 1) maintain optimal ecosystems for bats or 2) preserve a dark night sky.

Product Information

Product Family Code	BGP762
Mechanical and Housing	
Housing Material	Aluminium die-cast
Fixation material	Stainless steel
Ingress protection code	IP66
Mech. impact protection code	IK09
Corrosion resistance	500 hours Salt Spray Test for standard version, 1.000 hours. Salt Spray Test optional Marine Salt Protection (MSP)
Certification	
CE mark	CE mark
ENEC mark	ENEC mark
RoHS mark	-
WEEE mark	-
Protection class IEC	II
Service	
Warranty period	5 years
Serviceability	Class A, the luminaire is equipped with serviceable parts (when applicable): LED board, driver, control units, surge-protection device, optics, front cover and mechanical parts
Light source replaceable	Yes
Operating ambient temperature range Tamb	-40 to +50 °C
Performance ambient temperature (Tq)	25 °C
L-Value	L90
Lifetime	100000 h
Surge protection	6KV in Common or Differential mode as standard, 10KV with optional Surge Protector Device (SPD)

Dimensional drawing(s) - mm



Light technical Report

Drivers

Description	Xi FP 150W 0.2-0.7A SNLDAE 230V S240 sXt
12NC	929002128606
Number of driver(s)	1
Number of driver per MCB 16A	8
Inrush current	53 A
Inrush time	300 μ s
Input Voltage	220V-240V
Input Frequency	50/60 Hz
Current	205 mA
System power (minimum)	51 W
System power (maximum)	51 W
System power (average)	51 W
Power consumption tolerance	+/-10%
Power Factor (100%)	0.97
Power Factor (50%)	0.92
Connectivity	No connectivity
Dimming	No dimming

Light engine


Light source engine type	LED
Number of LED	80
Initial LED luminaire efficacy (source)	176 lm/W
Initial LED luminaire efficacy (system)	161 lm/W
Light source colour	740 (Neutral White)
Init. colour Rendering Index	70
Init. CRI tolerance	+/-2
Init. Corr. colour Temperature	4000 K
Initial tolerance	+/- 180 K (5 SDCM)
End of life tolerance	+/- 255 K
Initial luminous flux (source)	9000 lm
Luminous flux tolerance	+/-7%
Initial luminous flux (system)	8217 lm
Photobiological risk	Risk group 0 (exempt) according to EN IEC 62471

Optics


Optical configuration	DM10
LOR	0.91
ULR at tilt=0°	0.00%
G* at tilt=0°	G*3
Imax (at 90° and above)	0 cd/klm
CIE code	39 73 97 100 91

Photometric Graphs

Polar intensity diagram




Utilisation factor curve and luminance yield diagram Relative isolux diagram



Horizontal Illuminance $\triangle 0^\circ$

H (m)	E_{max} (lux)
4.0	133
6.0	59
8.0	33

M.F. = 1.0



Lab Information & Certification

Lab Information

Test standards

EN 13032-4:2015	Light and lighting. Measurement and presentation of photometric data of lamps and luminaires. Part 4: LED lamps, modules and luminaires
EN 13032-1:2014	Light and lighting. Measurement and presentation of photometric data of lamps and luminaires. Part 1: Measurement and file format
IEC 62717:2014+AMD1:2015	LED modules for general lighting - performance requirements
IES LM-79-08	IES Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products
IEC / EN 62722-1:2014	Luminaire performance - Part 1: General requirements
IEC / EN 62722-2-1:2014	Luminaire performance - Part 2-1: Particular requirements for LED luminaires

Test equipment

LMT GO-DS 2000 Goniometer (C/G)	<input type="checkbox"/>
Yokogawa WT3000 power analyzer	<input type="checkbox"/>
Chroma 6415 programmable AC source	<input type="checkbox"/>
Agilent 6675A system DC power supply	<input type="checkbox"/>
Integrating sphere U-101-A	<input type="checkbox"/>
EM TEST NetWave3 AC/DC source	<input type="checkbox"/>
FLUKE Norma 4000 power analyzer	<input type="checkbox"/>
Sonopan L-100 luxmeter	<input type="checkbox"/>
Gigahertz X1-3 hazard lightmeter	<input type="checkbox"/>
Gigahertz XD-45-HB-4 Head	<input type="checkbox"/>
Gigahertz XD-45-HUV-4 head	<input type="checkbox"/>

MEASUREMENT UNCERTAINTIES

Type of test	Uncertainties
Luminous flux	+/- 2.2 %
Power	+/- 0.5 %
Imax	+/- 2.2 %
Beam angle of Imax	+/- 0.1°
Ambient temperature 0-50°C	+/- 0.1°C

.....
Signed-off by
Dariusz Pierzchanowski

DISCLAIMER: This photometry report is compiled based on real measurement done in Signify Laboratories during development and release of new products and calculation data pulled from PPS web-based tool and internal data. The values present in this report may differ from real values measured for specific product, but not more than +/-10 % on power and +/- 7% on lumen.

Certification



APPENDIX TO CERTIFICATE

SMT/CTF-3/0001/3/2018

Supervised Manufacturers' Testing SMT Customer's Testing Facility CTF - Stage 3

List of products

for which the Laboratory of Quality Philips Lighting Poland Sp. z o.o. Pila O/Kętrzyn
is authorized to perform testing
for ITE PREDOM Division as a certification body in the framework
ENEC an CCA agreements and IECEE CB Scheme

CATEGORY	PRODUCTS*)	STANDARDS**)		
		For ENEC and CCA	For IECEE CB Scheme	For national certification
LITE	Fixed general purpose luminaires	EN 60598-1 EN 60598-2-1	IEC 60598-1 IEC 60598-2-1	EN 60598-1 EN 60598-2-1
LITE	Recessed luminaires	EN 60598-1 EN 60598-2-2	IEC 60598-1 IEC 60598-2-2	EN 60598-1 EN 60598-2-2
LITE	Luminaires for road and street lighting	EN 60598-1 EN 60598-2-3	IEC 60598-1 IEC 60598-2-3	EN 60598-1 EN 60598-2-3
LITE	Floodlights	EN 60598-1 EN 60598-2-5	IEC 60598-1 IEC 60598-2-5	EN 60598-1 EN 60598-2-5
LITE	Luminaires for emergency lighting	EN 60598-1 EN 60598-2-22	IEC 60598-1 IEC 60598-2-22	EN 60598-1 EN 60598-2-22
LITE	Luminaires with limited surface temperatures	EN 60598-1 EN 60598-2-24	IEC 60598-1 IEC 60598-2-24	EN 60598-1 EN 60598-2-24
LITE	LED modules for general lighting	EN 62031	IEC 62031	EN 62031
LITE (ENEC+)	LED modules for general lighting	EPRS 001/ IEC 62717	-	-
LITE (ENEC+)	Luminaires	EPRS 002 / IEC 62722-1	-	-
LITE (ENEC+)	LED Luminaires	EPRS 003/ IEC 62722-2-1	-	-
LITE	Lamp and luminaires	-	-	EN 13032-1
LITE	Lamp and luminaires	-	-	EN 13032-2
LITE	Lamp and luminaires	-	-	EN 13032-3
LITE	LED lamps, modules and luminaires	-	-	EN 13032-4
LITE	Solid-State Lighting Products	-	-	LM-79

*) - Name and address of manufacturing place of the products: Philips Lighting Poland Sp. z o.o. Pila, ul. Koszaka 150, O/Kętrzyn ul. Chrobrego 8, 11-400 Kętrzyn, Poland

**) - newest edition of the standards/documents

Manager of Certification Office
ITE PREDOM Division

Joanna Walczak- Zlotkowska

Deputy Director of ITE PREDOM Division

Aleksander Piotrowski

Warsaw, 2018-11-28



Instytut Technologii Elektronowej Oddział PREDOM
Institute of Electron Technology PREDOM Division
ul. Krakowiaków 53, 02-255 WARSZAWA, POLSKA - POLAND

POLSKIE CENTRUM AKREDYTACJI
POLISH CENTRE FOR ACCREDITATION



Sygnatariusz EA MLA
EA MLA Signatory

CERTYFIKAT AKREDYTACJI
LABORATORIUM BADAWCZEGO
ACCREDITATION CERTIFICATE OF TESTING LABORATORY
Nr AB 003

Potwierdza się, że: / This is to confirm that:

INSTYTUT TECHNOLOGII ELEKTRONOWEJ
Al. Lotników 32/46, 02-668 Warszawa
INSTYTUT TECHNOLOGII ELEKTRONOWEJ ODDZIAŁ PREDOM
LABORATORIUM BADAWCZE
ul. Krakowiaków 53, 02-255 Warszawa

spełnia wymagania normy PN-EN ISO/IEC 17025:2005
meets requirements of the PN-EN ISO/IEC 17025:2005 standard

Akredytowana działalność jest określona w Zakresie Akredytacji Nr AB 003
Accredited activity is defined in the Scope of Accreditation No AB 003

Akredytacja pozostaje w mocy pod warunkiem przestrzegania
wymagań jednostki akredytującej określonych w kontrakcie Nr AB 003
This accreditation remains in force provided the Laboratory observes
the requirements of Accreditation Body defined in the Contract No AB 003

Akredytacji udzielono dnia 27.04.1993 r.
Accreditation was granted on 27.04.1993



DYREKTOR
POLSKIEGO CENTRUM AKREDYTACJI


LUCYNA OLBORSKA

Warszawa, 10 grudnia 2018 roku

Intensity Table

FORMAT=PHILLUM
VERSION=2.0
STATUS=R
MCCOD=LVE16B3230
DATE=2018-01-04
TXTS="L-TUNE 2022-08-10"
ORIG=WLD
BRAND=PHILIPS
FAMILY=DigiStreet Medium
FAMCOD=BGP762
HOUSING=BGP762 T25
OPTICS=DM10
BLID=-
LAMP=LED-HB 9000 lm-4S L90@100kh
LAFLUX=9000
NLPS=1
LAMPVOL=740
INPW=51
INVO=230
GEOTYPE=3
GEOL1=0.107
GEOL2=0.361
GEOL3=0.792
OPTTYPE=3
OPTL1=0
OPTL2=0.313
OPTL3=0.285
SURF76=0.022
SURF85=0.008
PTYP=C
BANGLE=0.0
TLME=0.0
LUBA=1000
CORR=1
SYMCON=4
SYMPANE=2
NCON=64
NPLA=73
CONA= 0 2.5 5 7.5 10 12.5 15 17.5 20 22.5 25 27.5 30 32.5 35 37.5 40 42.5 45 46 47 48 49 50 51 52 53 54 55 56
57 58 59 60 61 62 63 64 65 66 67 68 69 70 71 72 73 74 75 76 77 78 79 80 81 82 83 84 85 86 87 88 89 90
PLANA= 90 92.5 95 97.5 100 102.5 105 107.5 110 112.5 115 117.5 120 122.5 125 127.5 130 132.5 135 137.5 140
142.5 145 147.5 150 152.5 155 157.5 160 162.5 165 167.5 170 172.5 175 177.5 180 182.5 185 187.5 190 192.5 195
197.5 200 202.5 205 207.5 210 212.5 215 217.5 220 222.5 225 227.5 230 232.5 235 237.5 240 242.5 245 247.5 250
252.5 255 257.5 260 262.5 265 267.5 270
ITABLE= 218.1 225.2 232.5 239.5 246.8 253.9 260.3 266 271.5 276.6 279.9 282.3 284.7 287.5 289.7 291.4 293.3
294.1 292.3 290.7 286.7 282.6 270.9 259.2 237.3 215.4 187.2 159 130.9 102.9 82.4 61.9 51.8 44.9 40.7 37.9
35.3 33.1 31.1 29.3 27.2 24.7 22.5 21 20.5 20 18 15.4 13.1 11.3 9.9 8.6 7.4 6.2 5.1 4 2.9 2 1.2 0.6 0.3 0.1 0
0
218.1 225.1 232.4 239.4 246.6 253.8 260.2 265.9 271.4 276.6 280 282.4 284.8 287.6 289.8 291.4 293.3 294 292.2
290.6 286.7 282.6 271.7 260.7 239.5 218.2 190.2 162.1 134 106 84.4 62.8 52.2 44.7 40.2 37.3 34.7 32.5 30.7
29.5 28.1 25.9 23.6 21.8 20.8 19.9 18 15.7 13.4 11.7 10.2 8.8 7.6 6.4 5.3 4.2 3.1 2.1 1.3 0.7 0.3 0.1 0 0
218.1 224.9 232.3 239.4 246.6 253.7 260.3 266.1 271.6 276.9 280.6 283 285.4 288.2 290.5 292.1 293.8 294.3
292.5 291.1 287.6 284 274.9 265.8 246.6 227.4 200.4 173.5 144.6 115.9 92 68.1 55.2 46.6 40.9 37.5 34.9 32.5
30.8 29.3 28.1 26.3 24.1 22.3 21.3 20.2 18.6 16.4 14.2 12.4 10.7 9.4 8 6.8 5.7 4.6 3.5 2.5 1.6 0.9 0.4 0.1 0 0
218.1 224.9 232.3 239.3 246.4 253.6 260.1 265.8 271.2 276.5 280.1 282.4 284.7 287.5 289.6 290.9 292.1 292.3
290.4 289 285.4 281.6 272.2 262.7 243.1 223.5 196.5 169.5 141.1 112.7 89.3 66 53.5 45.1 39.6 36.2 33.6 31.5
29.8 28.5 27.4 25.6 23.8 22.3 21 19.4 17.6 15.7 13.7 12 10.4 9 7.8 6.6 5.5 4.3 3.3 2.2 1.4 0.8 0.3 0.1 0 0
218.1 224.8 232.2 239.2 246.3 253.4 260 265.9 271.3 276.7 280.5 283 285.4 287.9 290 291.1 292.3 292.8 291.7
290.7 287.8 284.8 277.4 269.9 253.2 236.6 211.3 186.1 157.3 128.6 102.4 76.3 59.9 49.5 42.4 37.9 35.1 32.7
30.7 29.2 28.1 26.8 24.9 23.3 21.7 20 18.2 16.3 14.5 12.7 11.1 9.6 8.2 7 5.9 4.7 3.7 2.6 1.7 1 0.5 0.2 0 0
218.1 224.8 232.1 239.1 246.1 253.2 259.8 265.5 270.9 276.3 280.1 282.5 284.6 287 289 290.1 291.3 292.2 291.4
290.5 287.8 284.9 277.8 270.6 254.2 237.8 212.8 187.9 159.3 130.6 104.1 77.6 60.6 49.7 42.5 37.9 34.9 32.6
30.6 29 27.9 26.6 24.8 23.1 21.2 19.2 17.5 15.8 14 12.3 10.7 9.1 7.8 6.5 5.5 4.3 3.3 2.3 1.5 0.8 0.4 0.1 0 0
218.1 224.7 231.9 238.8 245.8 252.9 259.6 265.4 270.8 276.2 280.3 282.9 284.9 287.2 289.4 290.8 292.1 293.2
293.2 292.7 290.7 288.6 283.2 277.9 264.8 251.8 229.7 207.6 179.6 151.5 122.9 94.3 72.4 57.7 48 41.5 37.4
34.3 32.1 30 28.5 27.4 26.1 24.2 22.1 20 18.2 16.5 14.6 13 11.4 9.8 8.3 6.9 5.8 4.7 3.7 2.7 1.8 1 0.5 0.2 0 0
218.1 224.6 231.8 238.7 245.6 252.6 259.3 265.1 270.4 275.7 279.8 282.4 284.4 286.6 288.7 290.2 291.4 292.7
293.2 293 291.2 289.5 284.7 280 268.3 256.6 235.9 215.1 187.8 160.5 131.6 102.6 79.4 62.5 51.4 43.7 38.7 35.1
32.4 30.1 28.4 27.3 26.2 24.1 21.8 19.5 17.6 16.1 14.2 12.5 11 9.4 7.9 6.5 5.4 4.3 3.4 2.4 1.5 0.8 0.4 0.1 0 0
218.1 224.5 231.6 238.4 245.2 252.2 258.9 264.7 270.1 275.3 279.6 282.5 284.6 286.6 288.7 290.5 292 293.8
295.3 295.7 294.9 294.2 291.4 288.5 280.5 272.5 256.2 239.7 215.1 190.3 161 131.7 103.7 80.9 64 51.9 43.9
38.4 34.7 32.2 30 28.3 27.2 25.7 23.2 20.7 18.5 16.7 15.1 13.3 11.6 10 8.5 7 5.8 4.6 3.7 2.8 1.8 1.1 0.5 0.2
0 0
218.1 224.4 231.4 238.2 244.8 251.9 258.5 264.3 269.7 274.6 279 282.1 284 285.9 288 290.1 292 294.5 297.4
298.6 298.8 299.1 297.1 294.9 288.4 281.8 267.5 253 229.9 206.8 177.4 148 118.1 91.2 71.4 56.5 47 40.7 36.2
33.2 30.8 28.8 27.6 26 23.3 20.6 18.3 16.5 14.8 13 11.2 9.7 8.2 6.7 5.4 4.2 3.3 2.5 1.6 0.9 0.4 0.1 0 0
218.1 224.3 231.2 237.9 244.4 251.4 258 263.7 269.1 274 278.5 281.8 283.9 285.9 288.2 290.8 293.4 297 301
302.6 303.5 304.3 303.4 302.5 298.4 294.2 283.8 273.4 254.1 234.7 207.2 179.6 148.4 118.5 93.3 73 57.9 48
41.5 37.1 33.8 31.2 29.1 27.4 25.2 22.3 19.7 17.4 15.4 13.7 12 10.2 8.7 7.3 5.9 4.6 3.6 2.8 1.9 1.1 0.5 0.2 0
0
218.1 224.2 230.9 237.5 244 250.9 257.5 263.2 268.5 273.3 277.7 281.1 283.3 285.4 288.1 291.5 295.2 299.2
303.4 305.1 306.1 307.2 306.6 306.1 302.6 299.2 290.6 282 265.6 249.1 224.1 199.2 169 137.8 109.4 85.2 66.9

23.1 21.8 20.5 19.1 17.6 16.2 14.7 13.3 11.9 10.5 9 7.6 6.2 4.9 3.7 2.7 1.8 1.1 0.6 0.3 0.2 0
 218.1 211.9 206.3 200.9 195.8 191.8 189.2 187.5 185.4 182.4 179 174.6 167.2 152.3 132.5 110.8 88 67.5 54.1
 50.5 48.7 46.8 45.4 44 42.8 41.6 40.6 39.5 38.5 37.4 36.3 35.1 33.9 32.9 31.8 30.8 29.9 28.9 27.9 26.7 25.6
 24.5 23.3 22 20.7 19.3 17.9 16.5 15.1 13.5 12.2 10.8 9.3 7.8 6.4 5.2 3.9 2.8 1.8 1.2 0.6 0.3 0.2 0
 218.1 211.9 206.2 200.6 195.6 191.7 189.2 187.6 185.6 182.6 179.2 174.6 166.6 150.7 130.3 108.4 85.5 65.6
 53.2 50 48.2 46.5 45.1 43.7 42.5 41.4 40.3 39.2 38.2 37.1 36.1 34.9 33.8 32.8 31.8 30.9 29.9 28.9 27.8 26.6
 25.4 24.1 22.9 21.7 20.3 18.9 17.5 16 14.5 13.1 11.7 10.3 8.8 7.3 6 4.6 3.4 2.3 1.6 1 0.5 0.3 0.2 0
 218.1 211.9 206.2 200.6 195.5 191.5 189 187.3 185.3 182.4 179 174.6 166.7 151 130.9 109.2 86.2 66 53.4 50.2
 48.4 46.6 45.2 43.7 42.6 41.4 40.4 39.4 38.3 37.3 36.3 35.2 34.1 33.2 32.2 31.2 30.3 29.2 28.2 26.9 25.7 24.4
 23.1 21.8 20.4 19 17.5 16.1 14.5 13.1 11.7 10.4 8.9 7.4 6.1 4.7 3.5 2.5 1.7 1.1 0.6 0.3 0.2 0
 218.1 211.8 206 200.5 195.4 191.6 189.2 187.6 185.5 182.6 179.3 174.6 166.1 149.5 128.9 106.9 83.9 64.3 52.7
 49.8 48.1 46.5 45.1 43.6 42.5 41.4 40.3 39.3 38.3 37.2 36.2 35.2 34.2 33.2 32.3 31.3 30.3 29.2 28 26.8 25.5
 24.2 22.8 21.5 20 18.5 17 15.5 13.9 12.5 11.1 9.7 8.1 6.8 5.5 4.2 3.1 2.2 1.5 0.9 0.5 0.3 0.2 0
 218.1 211.8 206 200.4 195.3 191.3 188.9 187.2 185.2 182.3 179.1 174.7 166.5 150.5 130.3 108.5 85.4 65.4 53.1
 50.1 48.4 46.7 45.3 43.8 42.6 41.5 40.4 39.4 38.4 37.4 36.4 35.5 34.4 33.5 32.5 31.6 30.6 29.5 28.3 27.1 25.8
 24.4 23.1 21.7 20.3 18.8 17.2 15.7 14.1 12.5 11.2 9.8 8.3 6.9 5.6 4.4 3.3 2.4 1.6 1.1 0.6 0.3 0.2 0
 218.1 211.8 206.1 200.4 195.3 191.2 188.7 187.1 185.2 182.3 179.1 174.8 167.1 151.5 131.3 109.5 86.8 66.4
 53.6 50.3 48.6 46.9 45.5 44 42.8 41.7 40.6 39.6 38.6 37.6 36.6 35.6 34.6 33.6 32.7 31.8 30.8 29.7 28.5 27.3
 26 24.6 23.3 21.9 20.5 19 17.5 16 14.4 12.8 11.4 10 8.6 7.2 5.9 4.5 3.5 2.6 1.8 1.2 0.7 0.3 0.2 0

