



Specification Sheet


UID8480 Zigbee Green Power switch

- No wiring and power connections required so easy to install.
- Low mechanical force required to operate the device (typically less than 8 Newton).
- Indoor distance that can be covered is typically 10m. for line-of-sight installations. When there are walls this will be reduced depending on the type and thickness of the walls.

UID8480

- Provides switch and scene selection functionality.
- Wireless communication based on the ZigBee Pro standard (IEEE 802.15.4, WPAN). There is no need to connect to any electrical power supply as the device is battery powered.
- When a button is pressed, or released, a message is sent including a unique 32 bit identifier which prevents interferences with other devices.
- Briefly pressing the rocker either switches lights On or Off or selects a predefined scene.
- The device is Interact ready and can be easily linked to a wireless standalone or connected lighting system.
- The devices are easy to install and use. Additional information can be found in the appropriate installation instructions.

Dimensional drawing



Specifications

Communication

Wireless	Zigbee PRO Green Power IEEE 802.15.4 WPAN			
Data rate	250 kbps			
Carrier frequency	2.4 GHz			

Transmission distances (typical values)*

Indoor (plasterboard)	10 m (33 ft); max. 3 walls
Indoor reinforced concrete	7 m (23 ft); max 1 wall/ ceiling

Physical

Dimensions (H x W x D)	81 x 81 x 14 mm (3.19 x 3.19 x 0.55 in)
Weight	0.098 kg (0.22 lb)
Housing	Polycarbonate
Color	White (similar to RAL9000)
Lifetime	>50,000 actuations

Environment

Temperature (operating)	-25 to 65 °C (-13 to 149 °F)
Relative humidity (operating)	0% to 95% (non-condensing)
Temperature (storage and transport)	-25 to 65 °C (-13 to 149 °F)
Relative humidity (storage and transport)	0% to 95% (non-condensing)

* distance is largely influenced by the wall/ceiling material andthe angle that the transmitted signal is intersecting with. Note:fire-safety walls, elevator shafts and so on are considered asshielding.

Compliances and approvals

Protection rating	IP20			
Electromagnetic compatibility (EMC)	EN 61000-6-2:2005 EN 61000-6-4:2007+A1:2011			
Quality standard	ISO9001			
Environmental standard	ISO14001, CE2522			
Restriction of Hazardous Substances (RoHS)	2011/65/EU Annex 2015/863/EU			
Wireless				
Radio Equipment Directive	RED 2014/53/EU			
Electronic compatibility and radio spectrum matters (ERM)	EN 301489-1:V2.2.0 EN 301489-17:V3.2.0			
Wideband transmission systems	ETSI EN 300 328: V1.8.1			



Packing data

Туре	Dimensions Qty		Material	Weight	Weight	
_				net	gross	
Single pack	205 x 95 x 95 mm (80.7 x 37.4 x 37.4 in)	10	Cardboard	0.6 kg (1.3 lb)	0.7 kg (1.5 lb)	

Ordering data

Туре	MOQ	Ordering number	EAN1	EAN2	EOC
UID8480/10 ZGP Switch Scene recall 4B	10	9137 010 55803	8719514 273801	8719514 273818	273801 00

© 2020 Signify Holding. All rights reserved. Specifications are subject to change without notice. No representation or warranty as to the accuracy or completeness of the information included herein is given and any liability for any action in reliance thereon is disclaimed. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V. All other trademarks are owned by Signify Holding or their respective owners.

