

Recommended transformer compatibility list for Low Voltage lamps For non-dimmable systems only

х-у	Transformer is compatible with x - y lamp	
	Transformer is compatible but will not work according Philips claimed specifications under all conditions	This document is for information purposes and must be treated as
	Transformer is not compatible and therefore will not comply to Philips claimed specifications.	recommendation. Signify attempted to provide best results, results are
N.A.	Transformer lamp combination not applicable/relevant	generated in lab conditions and might contain faults
TRD	Transformer Jamn combination not tested	

				LED spots					
				MAS LED ExpertColor 10,8-50W 9xx AR111 xD 9290030432 9290030433 9290030434 9290030435 9290030436 9290030437	MAS LED ExpertColor 14.8-75W 9xx AR111 xxD 9290030426 9290030427 9290030428 9290030429 9290030430 9290030431	MAS LEDspotLV D 20-100W 927 AR111 24D 9290020503 9290020504 9290020505 9290020506 9290020507 9290020508	LED 4.6 - 35W MR16 WW 60D D RF 1PF/12 9290024941	MAS LED spot VLE D 5.8-35W MR16 9xx - xxD 9290024925 9290024926 9290024927 9290024928 9290024929 9290024930	MAS LEDspotLV DimTone 5.8-35W MR16 36D 9290024931
				Drorenalis	Dromals.	Dominalis.	Dominalis Dominalis	num Drevals	Ommubis
	Brand / type	Watt	LED Watt						
	Philips Primaline 70	20-70	20-70	1	1	1	1-4	1-3	1-3
	OSRAM Halotronic HTM 70 (new type)	20-70	4-14	1	1	1	1-4	1-3	1-3
	Philips Certaline 60	20-60	4-12	1	1	1	1-4	1-3	1-3
	SEET STE 70VA 7429	20-70	4-14	1	1	N.A.	1-2	1-2	1-2
	TRIDONIC SPEEDY TE-0050 C101	20-50	4-10	1	N.A.	N.A.	1-2	1	1
70W	TCI PICO WOLF 60	10-60	4-12	1	N.A.	N.A.		2	2
Transformer 50-70W	Vossloh Schwabe EST 60/12.635	10-60	4-12	1	N.A.	N.A.	1-2	1-2	1-2
rmer	RELCO ICE60 PFS TH 60W	10-60	4-12	1	N.A.	N.A.	1-2	1-2	1-2
nsfo	RELCO MINI ICE RN1650 70W	20-70	4-14	1	1	N.A.	1-2	1-2	1-2
Tra	Varilight YT50L	0-50	0-10	1	1	1	1-4	1-3	1-2
	Varilight YT70L	0-70	0-14	1	1	1	1-4	1-3	1-3
	TRIDONIC SPEEDY TE-0070	20-70	4-14	1	1	N.A.	2	1, 2	2
	Vossloh Schwabe EST 70/12.380	20-70	4-14	1	1	N.A.	1-2	1, 2	1-2
	Radiant XE060/03	20-50	4-10	1	N.A.	N.A.	1-2	1	1
	OSRAM ET-P 60	20-60	4-12		N.A.	N.A.			
	Philips Primaline 105	35-105	7-20	1	1	1	1-4	1-4	1-4
	OSRAM Halotronic HTM 105	35-105	7-20	1	1	1	1-4	1-4	1-4
	Philips Certaline 105	35-105	7-20	1	1	1	1-4	1-4	1-4
5W	Tridonic speedy TE-0105 C101	35-105	7-20	2	2	2	2 - 4	2 - 3	2 - 3
er 10	RELCO ICE 105 PFS TH	20-105	4-20	1 - 2	1	1	1 - 4	1-3	1-3
form	Vossloh Schwabe EST 105	20-105	4-20	1-2	1	1	1 - 4	1-3	1-3
Transformer 105W	Varilight YT105L	0-105	0-20	1-2	1	1	1 - 4	1-3	1-3
_	IBL lighting UK 4106.00 105W	35-105	7-20	1-2	1	1	1 - 4	1-3	1-3
	TCI Pico Wolf 105	20-105	4-20	1-2	1	1	1 - 4	1-3	2 - 3
	GIRA tronic trafo	20-105	4-20	1-2	1	1	1 - 4	1-3	1-3
		1	1						
	Philips Primaline 150	50-150	10-30	1-2	1-2	1	1-4	1-4	1-6
Mo	Philips certaline 150	50-150	10-30	1-2	1-2	1	2-4	2-4	1-6
0-16	Relco ICE 150	50-150	10-30	2	2	1	2 - 6	2-5	2 - 5
Transformer 150-160W	Relco ICE 160 PFS TH	100-160		2	2	2	3 - 6	4 - 5	4 - 5
form	TCI (DIAG) T150 (WX150)	30-150	6-30	2	3	1	2 - 6	2-5	2 - 5
Frans	OSRAM HTM 150	50-150	10-30	1-2	1-2	1	2-4	2-4	2-6
	SEET HA-150 code 7431	50-150	10-30	1-3	1-2		2 - 6	2-5	2 - 5
	Varilight YT150	0-150	0-30	1-3	1-2	1	1 - 6	1 - 5	1 - 5
3	RELCO ICE 200 PFS TH	100-200	20-40	2 - 4	2	2	4 - 8	4 - 6	4 - 6
-250	SEET HA 210 code 7432	50-210	10-42	1 - 4	2	1-2	2 - 8	2 - 6	2 - 6
-210-	TCI W210	50-210	10-42	2 - 4	2	1-2	3 - 8	3 - 6	3 - 6
rmer	RELCO ICE 250 PFS TH	100-250	20-50	4 - 5	2 - 3	2		4 - 8	4 - 8
Transformer 210-250W	VARILIGHT YT 250	0-250	0-50	1 - 5	1 - 3	1-2	1 - 10	1 - 8	1 - 8
Tra	TCI W250	50-250	10-50	2 - 5	1 - 3	1-2	4 - 10	4 - 8	4 - 8





Recommended transformer compatibility list for Low Voltage lamps For non-dimmable systems only

KEY

X	х-у	Transformer is compatible with x - y lamp			
		Transformer is compatible but will not work according Philips claimed specifications under all conditions	This document is for information purposes and must be treated as		
		Transformer is not compatible and therefore will not comply to Philips claimed specifications.	recommendation. Signify attempted to provide best results, results are		
N	N.A.	Transformer lamp combination not applicable/relevant	generated in lab conditions and might contain faults		
T.	B.D.	Transformer lamp combination not tested			

				MAS LED SPOT VLE D 7.5-50W MR16 9xx - xxD 9290024932 9290024933 9290024934 9290024935 9290024936 9290024937	MAS LEDspotLV D 7.5-50W 9xx MR16 xxD 9290024919 9290024920 9290024921 9290024922 9290024923 9290024924	MAS LED ExpertColor 6.7-35W MR16 9xx - xxD 9290030785, 9290030786 9290030787, 9290030788 9290030789, 9290030790 9290030791, 9290030792 9290030793, 9290030794 9290030795, 9290030796	MAS LED ExpertColor 7.5-43W MR16 9xx - xxD 9290030797 9290030798 9290030799 9290030800 9290030801 9290030802	MAS LEDspotLV 3.5-20W 827 MR11 24D 9290030870	CorePro LED spot ND 2.9-20W MR16 827 36D 9290024945
				model (Dimnate)	Orrentale	Domalde	Commable		11 11 man
	Brand / type	Watt	LED Watt						
	Philips Primaline 70	20-70	20-70	1-2	1	1 - 2	1	1 - 4	1-5
	OSRAM Halotronic HTM 70 (new type)	20-70	4-14	1-2	1	1	1	1 - 4	1 - 5
	Philips Certaline 60	20-60	4-12	1-2	1	1	1	1 - 4	1 - 4
	SEET STE 70VA 7429	20-70	4-14	1	1	1 - 2	1	2 - 4	2 - 4
	TRIDONIC SPEEDY TE-0050 C101	20-50	4-10	1	1	1	1	2 - 4	
Transformer 50-70W	TCI PICO WOLF 60	10-60	4-12	2			2	2 - 4	
- 20-	Vossloh Schwabe EST 60/12.635	10-60	4-12	1	1	1-2	1	2 - 4	4
ıme	RELCO ICE60 PFS TH 60W	10-60	4-12	1	1	1-2	1	2 - 4	2 - 4
ansfo	RELCO MINI ICE RN1650 70W	20-70	4-14		1	1-2	1	2 - 4	2 - 4
Ë	Varilight YT50L	0-50	0-10	1	1	N.A.	N.A.	1 - 4	1-3
	Varilight YT70L	0-70	0-14	1	1	1	1	1 - 4	1 - 4
	TRIDONIC SPEEDY TE-0070	20-70	4-14	2	1	2	2	2 - 4	
	Vossloh Schwabe EST 70/12.380	20-70	4-14	1-2	1	1-2	1	2 - 4	2 - 4
	Radiant XE060/03	20-50	4-10	1	1	1	1	2 - 4	2 - 4
	OSRAM ET-P 60	20-60	4-12						3 - 4
	Philips Primaline 105	35-105	7-20	1-3	1 - 2	1 - 2	1-2	1 - 5	1 - 10
	OSRAM Halotronic HTM 105	35-105	7-20	1-3	1-2	1 - 2	1 - 2	1 - 5	1-5
	Philips Certaline 105	35-105	7-20	1-3	1-2	1 - 2	1 - 2	1 - 5	1 - 10
05W	Tridonic speedy TE-0105 C101	35-105	7-20	2	1 - 2	2 - 3	2	3 - 5	2 - 5
Transformer 105W	RELCO ICE 105 PFS TH	20-105	4-20	1-2	1-2	1-3	1-2	2 - 5	
ısforı	Vossloh Schwabe EST 105	20-105	4-20	1-2	1-2	1-3	1-2	2 - 5	2 - 5
Tra	Varilight YT105L	0-105	0-20	1 - 2	1-2	1 - 3	1-2	1 - 5	1-5
	IBL lighting UK 4106.00 105W	35-105	7-20	1 - 2	1 - 2	1 - 3	1-2	2 - 5	2 - 5
	TCI Pico Wolf 105	20-105	4-20	1 - 2	1-2	1-3	1-2	2 - 5	2 - 5
	GIRA tronic trafo	20-105	4-20	1-2	1 - 2	1 - 3	1 - 2	2 - 5	2 - 5
	Philips Primaline 150	50-150	10-30	1-4	1-3	1-3	1-3	1-5	1-5
>	Philips certaline 150	50-150	10-30	1-4	1-3	1 - 3	1-3	2 - 5	1-5
Transformer 150-160W	Relco ICE 150	50-150	10-30	2 - 3	2 - 3	3 - 5	2 - 3	4 - 8	3 - 8
150-	Relco ICE 160 PFS TH	100-160	20-32	3	3	3 - 5	3	5 - 8	
rme	TCI (DIAG) T150 (WX150)	30-150	6-30	2 - 3	2 - 3	2 - 5	2 - 3	2 - 8	2 - 8
ansfo	OSRAM HTM 150	50-150	10-30	2-4	1-3	1-2	1-9		1 - 10
Ĕ	SEET HA-150 code 7431	50-150	10-30	1-3	1-3	2 - 5	1-3	3 - 8	3 - 8
	Varilight YT150	0-150	0-30	1 - 3	1 - 3	1 - 5	1-3	1 - 8	1 - 8
_	RELCO ICE 200 PFS TH	100-200	20-40	3 - 5	3 - 5	4 - 6	3 - 5	7 - 11	
50W	SEET HA 210 code 7432	50-210	10-42	1-5	1-5	2 - 6	1-5	3 - 11	3 - 11
210-2	TCI W210	50-210	10-42	3 - 5	2 - 5	2 - 6	2 - 5	5 - 11	
mer,	RELCO ICE 250 PFS TH	100-250	_	4 - 6	4 - 6	4 - 8	4 - 6	6 - 14	
Transformer 210-250W	VARILIGHT YT 250	0-250	0-50	1 - 6	1 - 6	1 - 8	1-6	1 - 14	1 - 12
Tra	TCI W250	50-250	_	2 - 6	2 - 6	4 - 8	2 - 6	4 - 14	3 - 12

www.philips.com/ledlamps





Recommended transformer compatibility list for Low Voltage lamps For non-dimmable systems only

_			
	х-у	Transformer is compatible with x - y lamp	
		Transformer is compatible but will not work according Philips claimed specifications under all conditions	This document is for information purposes and must be treated as
		Transformer is not compatible and therefore will not comply to Philips claimed specifications.	recommendation. Signify attempted to provide best results, results are
	N.A.	Transformer lamp combination not applicable/relevant	generated in lab conditions and might contain faults
	T.B.D.	Transformer lamp combination not tested	

				LED spots						
		CorePro LED spot TorePro LED spot CorePro LED spot Post of spot CorePro LED spot Post of spot				CorePro LEDspot 14-100W 830 AR111 40D 9290029652				
				11 11						
	Brand / type	Watt	LED Watt							
	Philips Primaline 70	20-70	20-70	1-3	1-3	1-2	1	1		
	OSRAM Halotronic HTM 70 (new type)	20-70	4-14	1 - 3	1 - 3	1 - 2	1	1		
	Philips Certaline 60	20-60	4-12	1-3	1-3	1 - 2	1	1		
	SEET STE 70VA 7429	20-70	4-14	2 - 4	2 - 4	1	1	1		
	TRIDONIC SPEEDY TE-0050 C101	20-50	4-10	2 - 4	2 - 4	1	1	N.A.		
Mo	TCI PICO WOLF 60	10-60	4-12	2 - 4	2 - 4	2	2	N.A.		
50-7	Vossloh Schwabe EST 60/12.635	10-60	4-12	2 - 4	2 - 4		1	N.A.		
mer	RELCO ICE60 PFS TH 60W	10-60	4-12	2 - 4	2 - 4	1	1	N.A.		
Transformer 50-70W	RELCO MINI ICE RN1650 70W	20-70	4-14	2 - 4	2 - 4	2	1	1		
Trail	Varilight YT50L	0-50	0-10	1 - 3	1 - 3	1-2	1	1		
	Varilight YT70L	0-70	0-14	1 - 3	1-3	1-2	1	1		
	TRIDONIC SPEEDY TE-0070	20-70	4-14		3 - 4	2	1	1		
	Vossloh Schwabe EST 70/12.380	20-70	4-14	2 - 4	2 - 4	1	1	1		
	Radiant XE060/03	20-50	4-10	2 - 4	2 - 4	1	1	N.A.		
	OSRAM ET-P 60	20-60	4-12	2 - 4	2 - 4			N.A.		
	Philips Primaline 105	35-105	7-20	1-5	1-5	1-3	1-2	1		
	OSRAM Halotronic HTM 105	35-105	7-20	1-5	1-5	1-3	1-2	1		
	Philips Certaline 105	35-105	7-20	1-5	1-5	1-3	1-2	1		
>	Tridonic speedy TE-0105 C101	35-105	7-20	2 - 5	2 - 4	2	2			
r 105	RELCO ICE 105 PFS TH	20-105	4-20	2 - 5	2 - 4	1 - 2	1 - 2	1		
Transformer 105W	Vossloh Schwabe EST 105	20-105	4-20	2 - 5	2 - 4	1 - 2	1-2	1		
ansfe	Varilight YT105L	0-105	0-20	1-5	1 - 4	1 - 2	1-2	1		
Ĕ	IBL lighting UK 4106.00 105W	35-105	7-20	2 - 5	2 - 4	1-2	1-2	1		
	TCI Pico Wolf 105	20-105	4-20	2 - 5	2 - 4	1 - 2	1-2	1		
	GIRA tronic trafo	20-105	4-20	2 - 5	2 - 4	1 - 2	1-2	1		
	OINA HOURE HAID	20-105	4-20	2 - 3	2-4	1.5 Z	1-2	'		
	Philips Primaline 150	50-150	10-30	1 - 3	1 - 3	1-3	1-3	1 - 2		
MOS	Philips certaline 150	50-150	10-30	1-7	1-7	1-3	1-3	1-2		
-160	Relco ICE 150	50-150	10-30	3 - 8	3 - 4	3	2	2		
Transformer 150-16	Relco ICE 160 PFS TH	100-160	20-32	5 - 8	4	3				
orme	TCI (DIAG) T150 (WX150)	30-150	6-30	2 - 8	2 - 4	2 - 3	1 - 2	1 - 2		
ansf	OSRAM HTM 150	50-150	10-30	1 - 5	1 - 5					
Ė	SEET HA-150 code 7431	50-150	10-30	3 - 8	3 - 4	1-3	1-3	1-2		
	Varilight YT150	0-150	0-30	1 - 8	1 - 4	1-3	1-3	1-2		
	RELCO ICE 200 PFS TH	100-200	20-40	5 - 8	4	3 - 5	2 - 4			
150W	SEET HA 210 code 7432	50-210	10-42	3 - 8	3 - 4	2-5	1-4	2		
2.10-2	TCI W210	50-210	10-42	3 - 8	3 - 4	2 - 5	2 - 4	2		
mer 2	RELCO ICE 250 PFS TH	100-250			4	5 - 6	5			
Transformer 210-250W	VARILIGHT YT 250	0-250	0-50	1 - 8	1-4	1-6	1-5	1-3		
Tran	TCI W250	50-250	10-50	3 - 8	3 - 4	3 - 6	2-5	2-3		
	10, 17250	30 230	10 30		3 4	<u> </u>	2 3	2 3		





Recommended transformer compatibility list for Low Voltage lamps For non-dimmable systems only

_			
	х-у	Transformer is compatible with x - y lamp	
		Transformer is compatible but will not work according Philips claimed specifications under all conditions	This document is for information purposes and must be treated as
		Transformer is not compatible and therefore will not comply to Philips claimed specifications.	recommendation. Signify attempted to provide best results, results are
	N.A.	Transformer lamp combination not applicable/relevant	generated in lab conditions and might contain faults
	T.B.D.	Transformer lamp combination not tested	

				LED spots					
				Master LEDspot Dimtone MR16 7 - 50W 9290020589	Master LED ExpertColor MR16 D 6.5 - 35W 9290013417 Master LED ExpertColor MR16 D 7.5 - 43W 9290013860	Master LEDspot D 8-50W MR16 9290018815	Master LEDspot DimTone MR16 5-35W 9290019047	Master LEDspot VLE D 7-50W MR16 9290019034	
				11	Commanda	(nonata)		ment Domoda	
	Brand / type	Watt	LED Watt						
	Philips Primaline 70	20-70	20-70						
	OSRAM Halotronic HTM 70 (new type)	20-70	4-14	1	1	1	1 - 2	1	
	Philips Certaline 60	20-60	4-12	1	1	1	1 - 2	1	
	SEET STE 70VA 7429	20-70	4-14	1	1	1	1-2	1	
	TRIDONIC SPEEDY TE-0050 C101	20-50	4-10	1	1	1	1-2	1	
Mo	TCI PICO WOLF 60	10-60	4-12				2		
20-7	Vossloh Schwabe EST 60/12.635	10-60	4-12	1	1	1	1-2	1	
mer	RELCO ICE60 PFS TH 60W	10-60	4-12	1	1	1	1	1	
Transformer 50-70W	RELCO MINI ICE RN1650 70W	20-70	4-14			1		1	
Trai	Varilight YT50L	0-50	0-10	1	1	1	1-2	1	
	Varilight YT70L	0-70	0-14	1	1	1	1-2	1	
	TRIDONIC SPEEDY TE-0070	20-70	4-14		1	1	2	1	
	Vossloh Schwabe EST 70/12.380	20-70	4-14	1	1	1	2	1	
	Radiant XE060/03	20-50	4-10	1	1	1	1-2	1	
	OSRAM ET-P 60	20-60	4-12	1	1	1		1	
	Philips Primaline 105	35-105	7-20	1-2	1-2	1-2	2 - 4	1 - 2	
	OSRAM Halotronic HTM 105	35-105	7-20	1-2	1-2	1-2	2 - 4	1 - 2	
	Philips Certaline 105	35-105	7-20	2	1-2	1-2	3 - 4	1 - 2	
×	Tridonic speedy TE-0105 C101	35-105	7-20	2	2	2	3 - 4	2	
r 105	RELCO ICE 105 PFS TH	20-105	4-20	2	2	2	3 - 4	1-2	
Transformer 105W	Vossloh Schwabe EST 105	20-105	4-20	1-2	1-2	1-2	2 - 4	1 - 2	
ansf	Varilight YT105L	0-105	0-20	1-2	1-2	1-2	1-4	1-2	
F	IBL lighting UK 4106.00 105W	35-105	7-20	2	2	1-2	2 - 4	2	
	TCI Pico Wolf 105	20-105	4-20	2	1-2	1-2	1-4	2	
	GIRA tronic trafo	20-105	4-20	2	2	1-2	1-4	1-2	
	S. S. Golden and								
	Philips Primaline 150	50-150	10-30	1 - 3	1 - 3	1 - 3	2 - 6	1-3	
WC	Philips certaline 150	50-150	10-30	1 - 3	1 - 3	1 - 3	3 - 6	1-3	
)-16(Relco ICE 150	50-150	10-30	3	3	3	3 - 6	1 - 3	
Transformer 150-160W	Relco ICE 160 PFS TH		20-32			3	4 - 6	3	
orme	TCI (DIAG) T150 (WX150)	30-150	6-30	2 - 3	2 - 3	2 - 3	4 - 6	1-3	
ransf	OSRAM HTM 150	50-150	10-30	2 - 3	2 - 3	2 - 3	2 - 6	2 - 3	
F	SEET HA-150 code 7431	50-150	10-30	1-3	1-3	1-3	2 - 6	1-3	
	Varilight YT150	0-150	0-30	1-3	1-3	1-3	1 - 6	1-3	
-	RELCO ICE 200 PFS TH	100-200	20-40	3 - 4	4	2 - 4	4 - 8	3 - 4	
2500.	SEET HA 210 code 7432	50-210	10-42	2 - 4	2 - 4	2 - 4	4 - 8	1-4	
210-	TCI W210	50-210	10-42	3 - 4	2 - 4	2 - 4	4 - 8	3 - 4	
mer	RELCO ICE 250 PFS TH	_	20-50		4 - 5			3 - 4	
Transformer 210-250W	VARILIGHT YT 250	0-250	0-50	1-5	1-5	1-5	1 - 8	1-5	
Trar	TCI W250	50-250		3 - 5	2 - 5	2 - 5	4 - 8	2 - 5	
		30 230	1.0 30	<u> </u>			, 0		





Recommended transformer compatibility list for Low Voltage lamps For non-dimmable systems only

х-у	Transformer is compatible with x - y lamp				
	Transformer is compatible but will not work according Philips claimed specifications under all conditions	This document is for information purposes and must be treated as recommendation. Signify attempted to provide best results, results are			
	Transformer is not compatible and therefore will not comply to Philips claimed specifications.				
N.A.	Transformer lamp combination not applicable/relevant	generated in lab conditions and might contain faults			
T.B.D.	Transformer lamp combination not tested				

			LED spots					
		Master LEDspot Expertcolor 11-50W AR111 40° D 9290022388	Master LEDspot Expertcolor 15-75W AR111 40' D 9290022390	Corepro LEDspot ND 3 - 20W MR16 9290013440	Corepro LEDspot ND 5 - 35W MR16 9290013443			
	. -	Dmulio	Drivnable	record	The state of the s			
Brand / type		D Watt						
Philips Primaline 70		-70						
OSRAM Halotronic HTM 70 (new type			1	1-3	1-2			
Philips Certaline 60	20-60 4-1		N.A.	1-3	1-2			
SEET STE 70VA 7429	20-70 4-1		1	1-3	1-2			
TRIDONIC SPEEDY TE-0050 C101	20-50 4-1		N.A.		2			
TCI PICO WOLF 60	10-60 4-1		N.A.					
TCI PICO WOLF 60 Vossloh Schwabe EST 60/12.635 RELCO ICE60 PFS TH 60W RELCO MINI ICE RN1650 70W Varilight YT50L	10-60 4-1		N.A.	1-3	1-2			
RELCO ICE60 PFS TH 60W	10-60 4-1		N.A.	1-3	1-2			
RELCO MINI ICE RN1650 70W	20-70 4-1		1					
	0-50 0-1		N.A.	1-2	1			
Varilight YT70L	0-70 0-1		1	1-3	1-2			
TRIDONIC SPEEDY TE-0070	20-70 4-1							
Vossloh Schwabe EST 70/12.380	20-70 4-1		1	1-3	1-2			
Radiant XE060/03	20-50 4-1		N.A.	1-2	1			
OSRAM ET-P 60	20-60 4-1	1	N.A.	1-3	1			
Philips Primaline 105	35-105 7-2	20 1 - 2	1	2 - 5	1-3			
OSRAM Halotronic HTM 105	35-105 7-2	20 1 - 2	1	2 - 5	1-3			
Philips Certaline 105	35-105 7-2	20 1 - 2	1	2 - 5	1-3			
	35-105 7-2	20 2		2 - 5	1-3			
RELCO ICE 105 PFS TH	20-105 4-2	20 1 - 2	1		1-3			
Tridonic speedy TE-0105 C101 RELCO ICE 105 PFS TH Vossloh Schwabe EST 105 Varilight YT105L	20-105 4-2		1	1-5	1-3			
Varilight YT105L	0-105 0-2		1	1-5	1-3			
IBL lighting UK 4106.00 105W	35-105 7-2		1	2 - 5	1-3			
TCI Pico Wolf 105	20-105 4-2		1	2 - 5	1-3			
GIRA tronic trafo	20-105 4-2		1		1-3			
City troine train	20 103 1 2		·		1 3			
Philips Primaline 150	50-150 10-	-30 1 - 2	1-2	3 - 7	2 - 4			
Philips certaline 150	50-150 10-		1-2	3 - 7	2 - 4			
Relco ICE 150	50-150 10-		2	3 - 7	2 - 4			
Relco ICE 150 Relco ICE 160 PFS TH TCI (DIAG) T150 (WX150) OSRAM HTM 150 SEET HAJ50 code 7431	100-160 20		2					
TCI (DIAG) T150 (WX150)	30-150 6-3	1-2	1-2	2 - 7	1 - 4			
OSRAM HTM 150	50-150 10-	-30 1 - 2	1-2	3 - 7	3 - 4			
SEET HA-150 code 7431	50-150 10-	-30 1 - 3	1 - 2	4 - 7	2 - 4			
Varilight YT150	0-150 0-3	30 1-3	1 - 2	1 - 7	1 - 4			
RELCO ICE 200 PFS TH	100-200 20	-40 2 - 4	2					
SEET HA 210 code 7432	50-210 10-		2					
TCI W210	50-210 10-		2	5 - 10	2 - 6			
RELCO ICE 250 PFS TH			2	3-10	2-0			
VADILICAT VE 250	100-250 20-		1-3	1 10	1.7			
SEET HA 210 code 7432 TCI W210 RELCO ICE 250 PFS TH VARILIGHT YT 250	0-250 0-9			1 - 10	1-7			
F TCI W250	50-250 10-	-50 2 - 5	2 - 3	3 - 10	2 - 7			





Recommended transformer compatibility list for Low Voltage lamps For non-dimmable systems only

х-у	Transformer is compatible with x - y lamp				
	Transformer is compatible but will not work according Philips claimed specifications under all conditions	This document is for information purposes and must be treated as recommendation. Signify attempted to provide best results, results are			
	Transformer is not compatible and therefore will not comply to Philips claimed specifications.				
N.A.	Transformer lamp combination not applicable/relevant	generated in lab conditions and might contain faults			
T.B.D.	Transformer lamp combination not tested	-			

				LED spots					
				Corepro LEDspot ND 7 - 50W MR16 GU5,3 9290019049	CorePro LED spot 2.3-20W ND 827 MR11 36'D 9290020664	MAS LED ExpertColor 6.7-35W MR16 927 60D 9290030785	MAS LEDspotLV 3.5-20W 827 MR11 24D 9290030870		
					noon II	Direnable			
	Brand / type	Watt	LED Watt						
	Philips Primaline 70	20-70	20-70	1 - 2	1 - 4	1	4		
	OSRAM Halotronic HTM 70 (new type)	20-70	4-14	1	2 - 6	1	4		
	Philips Certaline 60	20-60	4-12	1	2 - 5	1	4		
	SEET STE 70VA 7429	20-70	4-14	1	2 - 6				
	TRIDONIC SPEEDY TE-0050 C101	20-50	4-10						
70W	TCI PICO WOLF 60	10-60	4-12						
Transformer 50-70W	Vossloh Schwabe EST 60/12.635	10-60	4-12		1 - 5				
orme	RELCO ICE60 PFS TH 60W	10-60	4-12	1	1-5				
ansfc	RELCO MINI ICE RN1650 70W	20-70	4-14		2-6				
Ĕ	Varilight YT50L	0-50	0-10	1	1 - 4	1	4		
	Varilight YT70L	0-70	0-14	1-2	1-6	1	4		
	TRIDONIC SPEEDY TE-0070	20-70	4-14						
	Vossloh Schwabe EST 70/12.380	20-70	4-14	1	2- 6				
	Radiant XE060/03	20-50	4-10	1	2 - 5				
	OSRAM ET-P 60	20-60	4-12	1					
	Philips Primaline 105	35-105	7-20	1-3	4 - 9	2	5		
	OSRAM Halotronic HTM 105	35-105	7-20	1-3	4 - 9	2	5		
	Philips Certaline 105	35-105	7-20	1-3	4 - 9	2	5		
)5W	Tridonic speedy TE-0105 C101	35-105	7-20	2					
Transformer 105W	RELCO ICE 105 PFS TH	20-105	4-20						
sforn	Vossloh Schwabe EST 105	20-105	4-20	1-2	2 - 9				
Tran	Varilight YT105L	0-105	0-20	1-2	1-9				
	IBL lighting UK 4106.00 105W	35-105	7-20	1-2	4 - 9				
	TCI Pico Wolf 105	20-105	4-20	1 - 2					
	GIRA tronic trafo	20-105	4-20	1-2	2 - 9				
	Philips Primaline 150	50-150	10-30	2 - 4	5 - 10	4	5		
	Philips certaline 150	50-150	10-30	2 - 4	5 - 10	4	5		
M091	Relco ICE 150	50-150			5 - 10	·			
150-1	Relco ICE 160 PFS TH	100-160							
Transformer 150-160W	TCI (DIAG) T150 (WX150)	30-150	6-30	2 - 3	3 - 10				
nsfor	OSRAM HTM 150	50-150	10-30	2 - 4	5 - 10	4	5		
Tra	SEET HA-150 code 7431	50-150	10-30		5 - 10				
	Varilight YT150	0-150	0-30	1-3	1 - 10				
	-								
MOS	RELCO ICE 200 PFS TH	100-200							
0-25	SEET HA 210 code 7432	50-210	10-42		5 - 10				
ler 21	TCI W210	50-210	10-42		5 - 10				
form	RELCO ICE 250 PFS TH	100-250			1.40				
Transformer 210-250W	VARILIGHT YT 250	0-250	0-50	1 - 5	1 - 10				
	TCI W250	50-250	10-50		5 - 10				





Recommended transformer compatibility list for Low Voltage lamps For non-dimmable systems only

х-у	Transformer is compatible with x - y lamp				
	Transformer is compatible but will not work according Philips claimed specifications under all conditions	This document is for information purposes and must be treated as			
	Transformer is not compatible and therefore will not comply to Philips claimed specifications.	recommendation. Signify attempted to provide best results, results are			
N.A.	Transformer lamp combination not applicable/relevant	generated in lab conditions and might contain faults			
T.B.D.	Transformer lamp combination not tested	-			

						LED spots		
				LED 10W G4 WW 12V ND 9290023888 LED 10W G4 WH 12V ND 9290023889	LED 20W G4 WW 12V ND 9290023890 LED 20W G4 WH 12V RF ND 9290023891	LED 28W G4 WW 12V ND 9290023892	CorePro LEDcapsule LV 2.1-20W G4 827 D 9290023894	LED 20W GY6.35 WW 12V ND 9290023897 LED 20W GY6.35 WH 12V RF ND 9290023898
	Brand / type	Watt	LED Watt					
	Philips Primaline 70	20-70	20-70	1-10	1-10	1-5	2-9	1-10
	OSRAM Halotronic HTM 70 (new type)	20-70	4-14	1-10	1-10	1-5	3 - 8	1-10
	Philips Certaline 60	20-60	4-12	1-10	1-10	1-4	3 - 8	1-10
	SEET STE 70VA 7429	20-70	4-14	1-10	1-10	1-5	3 - 8	1-10
	TRIDONIC SPEEDY TE-0050 C101	20-50	4-10					
No.	TCI PICO WOLF 60	10-60	4-12					
50-70W	Vossloh Schwabe EST 60/12.635	10-60	4-12					
	RELCO ICE60 PFS TH 60W	10-60	4-12					
Transformer	RELCO MINI ICE RN1650 70W	20-70	4-14					
Trar	Varilight YT5OL	0-50	0-10	1-10	1-10	1-10	1-10	1-10
	Varilight YT70L	0-70	0-14	1-10	1-10	1-10	3 - 8	1-10
	TRIDONIC SPEEDY TE-0070	20-70	4-14	1-10	1-10	1-10	3 - 8	1-10
	Vossloh Schwabe EST 70/12.380	20-70	4-14					
	Radiant XE060/03	20-50	4-10					
	OSRAM ET-P 60	20-60	4-12					
	Philips Primaline 105	35-105	7-20	1-10	1-10	1-2	2-9	1-10
	OSRAM Halotronic HTM 105	35-105	7-20	1-10	1-10	1-2	3 - 8	1-10
>	Philips Certaline 105	35-105	7-20	1-10	1-8	1-4, 6-10	3 - 8	1-8, 10
Transformer 105W	Tridonic speedy TE-0105 C101	35-105	7-20	1-10	1-10	1-5	3 - 8	1-10
m er	RELCO ICE 105 PFS TH	20-105	4-20					
nnsfo	Vossloh Schwabe EST 105	20-105	4-20					
Ē	Varilight YT105L	0-105	0-20					
	IBL lighting UK 4106.00 105W	35-105	7-20					
	TCI Pico Wolf 105	20-105	4-20					
	GIRA tronic trafo	20-105	4-20					
	Philips Primaline 150	50-150	10-30	1-10	1-6	1-4	2-9	1-6
>	Philips certaline 150	50-150	10-30	1-10	1-6	1-4	4 - 8	1-6
160	Relco ICE 150	50-150	10-30	1-10	1-10	1-5	3 - 8	1-10
Transformer 150-160W	Relco ICE 160 PFS TH	100-160	20-32					
rmer	TCI (DIAG) T150 (WX150)	30-150	6-30					
nsfo	OSRAM HTM 150	50-150	10-30	1-2	1-10	1-10	2-9	1-10
Tra	SEET HA-150 code 7431	50-150	10-30	1-2	1-2	1-10	3 - 8	1-10
	Varilight YT150	0-150	0-30					
	DEI 60 165 000 DE6	100	20.45					
MO	RELCO ICE 200 PFS TH	100-200						
0-25	SEET HA 210 code 7432	50-210	10-42					
er 21	TCI W210	50-210	10-42					
form	RELCO ICE 250 PFS TH	100-250						
Transformer 210-250W	VARILIGHT YT 250	0-250	0-50					
	TCI W250	50-250	10-50					





Recommended Low Voltage Dimmer compatibility list - LED Lamps

KEY

#	Transformer - dimmer combination is compatible with # of lamp(s) and minimum dimming level is below 30% AND maximum dimming level is at least 80%.	
#	Transformer - dimmer combination is compatible with # of lamp(s) and minimum dimming level is between 30% (inclusive) and 50% AND maximum level is above or equal to 70%.	This document is for information purposes and must be treated as
	Transformer is not compatible.	recommendation. Signify attempted to provide best results, results are
	Transformer lamp combination not applicable	generated in lab conditions and might contain faults
	Transformer lamp combination not tested	



MAS LEDspotLV D 7.5-50W 9xx MR16 xxD 9290024919, 9290024920, 9290024921, 9290024922, 9290024923, 9290024924

C+-1i 150			Varilight			Tridonic			
Certaline 60 Certaline 105 Certaline 150 Primaline 70 Primaline 105 Primaline 150		YT50	YT70	HTM 70	HTM 105	HTM 150	VIPER		
50 - 150W	20-70W	35-105W	50 - 150W	0 - 50W	0 - 70W	20 - 70W	35 - 105W	50 - 150W	20 - 60W
	50 - 150W	50 - 150W 20-70W	50 - 150W 20-70W 35-105W	50 - 150W 20-70W 35-105W 50 - 150W	50 - 150W 20-70W 35-105W 50 - 150W 0 - 50W	50 - 150W 20-70W 35-105W 50 - 150W 0 - 50W 0 - 70W	50 - 150W 20-70W 35-105W 50 - 150W 0 - 50W 0 - 70W 20 - 70W	50 - 150W 20-70W 35-105W 50 - 150W 0 - 50W 0 - 70W 20 - 70W 35 - 105W	50 - 150W 20-70W 35-105W 50 - 150W 0 - 50W 0 - 70W 20 - 70W 35 - 105W 50 - 150W

Brand	Model	Load												
Busch Jaeger	6513 U-102, TE	2 - 100W	1	1	1	1	2	1-3	1	1	1		2 - 3	1
Busch Jaeger	6523 UR-103, TE	2-100W, LE 2-400W, TE	1	1	1	1	1	1	1	1	1	1	1	1
Doyle & Tratt (Varilight)	HQ3W	60-400W	1		1-3			1 - 2			1	1 - 2		
Schneider (Elko)	SBD200LED (CCTEL10501) (S520512: 4-400VA)	4-40W, LE 4-200W, TE		2	2 - 3	1	1-2	1	1	1	1	1-2	2	1
Merten Schneider	MEG5300-0001 (CCT99100), TE		1	1	1		1	1	1	1	1	1	1	1
Legrand	BTN4411N, LE BTNT4411 BTL4411N	5 - 75VA	1	1-2	1	1	1	2-3	1	1	1	1-2	2 - 3	
Legrand	752060	5 - 75VA	1	2	2		1	1	1	1	1	1	2	1
Gira	245000, TE	20 - 60W LE & TE	1	1	1	1	1	1	1	1	1	1	1	1
Gira INSTA	5401 00, TE	20 - 100W LE & TE	1	1	1	1	1	1-2	1	1	1	1	1	1





Recommended Low Voltage Dimmer compatibility list - LED Lamps

KEY

#	Transformer - dimmer combination is compatible with # of lamp(s) and minimum dimming level is below 30% AND maximum dimming level is at least 80%.	
#	Transformer - dimmer combination is compatible with # of lamp(s) and minimum dimming level is between 30% (inclusive) and 50% AND maximum level is above or equal to 70%.	This document is for information purposes and must be treated as recommendation. Signify attempted to provide best results, results are
	Transformer is not compatible.	
	Transformer lamp combination not applicable	generated in lab conditions and might contain faults
	To of markets and his big and had	



MAS LED spot VLE D 5.8-35W MR16 9xx-xxD 9290024925, 9290024926, 9290024927, 9290024928, 9290024929, 9290024930

	Ph	ilips		Var	rilight		Tridonic		
Certaline 105	Primaline 70	Primaline 105	Primaline 150	YT50	YT70	HTM 70	HTM 105	HTM 150	VIPER
35 - 150W	20-70W	35 - 105W	50 - 150W	0 - 50W	0 - 70W	20 - 70W	35 - 105W	50 - 150W	20 - 60W

Brand	Model	Load										
Doyle & Tratt (Varilight)	HQ3W	60-400W	1	2	2	1	1	1		1		
Schneider (Elko)	SBD200LED (CCTEL10501) (S520512: 4-400VA) SBD200LED (MEG5134-0000)	4-40W, LE 4-200W, TE	1-2	2	2	1	1	1	1	1		1
Merten Schneider	MEG5300-0001 (CCT99100), TE	4 - 20VA, LE 4 - 100VA, TE	1-2			1	1	1	1	1		
Busch-Jaeger	6523 U-102, TE	2 - 100W	1	2	2	1	1	1	1	1		
Busch Jaeger	6523 UR-103, TE	2-100W, LE 2-400W, TE	1-2		2	1	1	1	1	1	2	1
Legrand	BTN4411N, TE BTNT4411 BTL4411N	5 - 75VA	1-2			1	1	1	1	1		
Legrand	752060	5 - 75VA	1		2	1	1	1	1	1	2	
Gira	245000, TE	20 - 60W LE & TE		2	2	1	1	1	1	1	2	1
Gira INSTA	5401 00, TE	20 - 100W LE & TE	1	2	2	1	1	1	1	1	2	1





Recommended Low Voltage Dimmer compatibility list - LED Lamps

KEY

#	Transformer - dimmer combination is compatible with # of lamp(s) and minimum dimming level is below 30% AND maximum dimming level is at least 80%.	
#	Transformer - dimmer combination is compatible with # of lamp(s) and minimum dimming level is between 30% (inclusive) and 50% AND maximum level is above or equal to 70%.	This document is for information purposes and must be treated as
	Transformer is not compatible.	recommendation. Signify attempted to provide best results, results are
	Transformer lamp combination not applicable	generated in lab conditions and might contain faults
	Transformer lawn combination not tested	



MAS LED SPOT VLE D 7.5-50W MR16 9xx-xxD 9290024932, 9290024933, 9290024934, 9290024935, 9290024936, 9290024937

	Transformer									
	Phi	ilips		Vari	Varilight OSRAM			Tridonic		
Certaline 105	Primaline 70	Primaline 105	Primaline 150	YT50	YT50 YT70		HTM 105	HTM 150	VIPER	
35-105W	20-70W	35 - 105W	50 - 150W	0 - 50W	0 - 70W	20 - 70W	35 - 105W	50 - 150W	20 - 60W	

Bra	and	Model	Load										
Do	yle & Tratt (Varilight)	HQ3W	60-400W	1	2	2	2	1	1		1		
Sch	nneider (Elko)	SBD200LED (CCTEL10501) (S520512: 4-400VA) SBD200LED (MEG5134-0000)	4-40W, LE 4-200W, TE	1-2	2	2	2	1	1	1	1		1
Me	erten Schneider	MEG5300-0001 (CCT99100), TE	4 - 20VA, LE 4 - 100VA, TE	1-2			2	1	1	1	1		
Bu:	sch-Jaeger	6523 U-102, TE	2 - 100W	1	2	2	2	1	1		1		
Bu:	sch Jaeger	6523 UR-103, TE	2-100W, LE 2-400W, TE	1-2		2	2	1	1	1	1	2	1
Leg	grand	BTN4411N, TE BTNT4411 BTL4411N	5 - 75VA				2	1	1	1	1		
Leg	grand	752060	5 - 75VA	1-2		2	2	1	1	1	1	2	1
Gir	a	245000, TE	20 - 60W LE & TE		2	2	2	1	1	1	1	2	1
Gir	a INSTA	5401 00, TE	20 - 100W LE & TE	1-2	2	2	2	1	1	1	1	2	1





Recommended Low Voltage Dimmer compatibility list - LED Lamps


KEY

#	Transformer - dimmer combination is compatible with # of lamp(s) and minimum dimming level is below 30% AND maximum dimming level is at least 80%.	
#	Transformer - dimmer combination is compatible with # of lamp(s) and minimum dimming level is between 30% (inclusive) and 50% AND maximum level is above or equal to 70%.	This document is for information purposes and must be treated as
	Transformer is not compatible.	recommendation. Signify attempted to provide best results, results are
	Transformer lamp combination not applicable	generated in lab conditions and might contain faults
	Transformer lamp combination not tested	



MAS LED ExpertColor 6.7-35W MR16 9xx-xxD 9290030785, 9290030786, 9290030787, 9290030788, 9290030789, 9290030790, 9290030791, 9290030792, 9290030793, 9290030794, 9290030795, 9290030796

	Transformer												
		Phi	lips		Var	ilight		Tridonic					
Certaline 60	Certaline 105	Certaline 150	Primaline 70	Primaline 105	Primaline 150	YT50	YT70	HTM 70	HTM 105	HTM 150	VIPER		
20-60W	35-105W	50-150W	20-70W	35-105W	50-150W	0-50W	0-70W	20-70W	35-105W	50-150W	20-60W		







Recommended Low Voltage Dimmer compatibility list - LED Lamps

KEY

#	Transformer - dimmer combination is compatible with # of lamp(s) and minimum dimming level is below 30% AND maximum dimming level is at least 80%.				
#	Transformer - dimmer combination is compatible with # of lamp(s) and minimum dimming level is between 30% (inclusive) and 50% AND maximum level is above or equal to 70%.	This document is for information purposes and must be treated as			
	Transformer is not compatible.	recommendation. Signify attempted to provide best results, results are			
	Transformer lamp combination not applicable	generated in lab conditions and might contain faults			
	To of markets and his big and had				



MAS LEDspotLV DimTone 5.8-35W MR16 36D 9290024931

	Transformer											
	Ph	ilips		Varilight			OSRAM	Tridonic				
Certaline 105	Primaline 70	Primaline 105	Primaline 150	YT50	YT70	HTM 70	HTM 105	HTM 150	VIPER			
35-105W	20-70W	35 - 105W	50 - 150W	0 - 50W	0 - 70W	20 - 70W	35 - 105W	50 - 150W	20 - 60W			

Brand	Model	Load										
Doyle & Tratt (Varilight)	HQ3W	60-400W	1	1	1	1		1		1		
Schneider (Elko)	SBD200LED (CCTEL10501) (S520512: 4-400VA) SBD200LED (MEG5134-0000)	4-40W, LE 4-200W, TE	2	1-2	1	2	1	1	1	1	2	1
Merten Schneider	MEG5300-0001 (CCT99100), TE	4 - 20VA, LE 4 - 100VA, TE	2			2	1	1	1	1		1
Busch-Jaeger	6523 U-102, TE	2 - 100W	1	1	1-2	1	1	1	1	1	2	1
Busch Jaeger	6523 UR-103, TE	2-100W, LE 2-400W, TE	2	1	1	1-2	1	1	1	1	2	1
Legrand	BTN4411N, TE BTNT4411 BTL4411N	5 - 75VA				2	1	1	1	1		2
Legrand	752060	5 - 75VA	1	1	1 - 2	1	1	1	1	1	2	1
Gira	245000, TE	20 - 60W LE & TE										
Gira INSTA	5401 00, TE	20 - 100W LE & TE	1	1	1	1	1	1	1	1	2	





Recommended Low Voltage Dimmer compatibility list - LED Lamps

KEY

#	Transformer - dimmer combination is compatible with # of lamp(s) and minimum dimming level is below 30% AND maximum dimming level is at least 80%.				
#	Transformer - dimmer combination is compatible with # of lamp(s) and minimum dimming level is between 30% (inclusive) and 50% AND maximum level is above or equal to 70%.	This document is for information purposes and must be treated as			
	Transformer is not compatible.	recommendation. Signify attempted to provide best results, results are			
	Transformer lamp combination not applicable	generated in lab conditions and might contain faults			
	To of markets and his big and had				



LED 4.6 - 35W MR16 WW 60D D RF 9290024941

	Transformer												
	Ph	ilips		Var	Varilight OSRAM				Tridonic				
Certaline 105	Primaline 70	Primaline 105	Primaline 150	YT50	YT70	HTM 70	HTM 105	HTM 150	VIPER				
35-105W	20-70W	35 - 105W	50 - 150W	0 - 50W	0 - 70W	20 - 70W	35 - 105W	50 - 150W	20 - 60W				

Brand	Model											
Doyle & Tratt (Varilight)	HQ3W	60-400W	2	1	1	2		1	1	1	2	1
Schneider (Elko)	SBD200LED (CCTEL10501) (S520512: 4-400VA) SBD200LED (MEG5134-0000)	4-40W, LE 4-200W, TE	1	2	2		1	1	1	1	2	1
Merten Schneider	MEG5300-0001 (CCT99100), TE	4 - 20VA, LE 4 - 100VA, TE	2			2	1	1	1	1		
Busch-Jaeger	6523 U-102, TE	2 - 100W	1	1	1-2	1	1	1	1	1		1
Busch Jaeger	6523 UR-103, TE	2-100W, LE 2-400W, TE	2		2	2	1	1	1	1		1
Legrand	BTN4411N, TE BTNT4411 BTL4411N	5 - 75VA	2			2	1	1	1	1		2
Legrand	752060	5 - 75VA	1 - 2	2	1-2	1	1	1	1	1	2	1
Gira	245000, TE	20 - 60W LE & TE										
Gira INSTA	5401 00, TE	20 - 100W LE & TE	1	1	1	1	1	1	1	1	2	1





Recommended Low Voltage Dimmer compatibility list - LED Lamps

KEY

#	Transformer - dimmer combination is compatible with # of lamp(s) and minimum dimming level is below 30% AND maximum dimming level is at least 80%.	
#	Transformer - dimmer combination is compatible with # of lamp(s) and minimum dimming level is between 30% (inclusive) and 50% AND maximum level is above or equal to 70%.	This document is for information purposes and must be treated as
	Transformer is not compatible.	recommendation. Signify attempted to provide best results, results are
	Transformer lamp combination not applicable	generated in lab conditions and might contain faults
	To a few values and in the state of the stat	



MAS LED ExpertColor 7.5-43W MR16 9xx-xxD 9290030797, 9290030798, 9290030799, 9290030800, 9290030801, 9290030802

		Transformer										
			Philips			Vari	light		Tridonic			
Certaline 60	Certaline 105	Certaline 150	Primaline 70	Primaline 105	Primaline 150	YT50	YT70	HTM 70	HTM 105	HTM 150	VIPER	
20-60W	35-105W	50-150W	20-70W	35 - 105W	50 - 150W	0 - 50W	0 - 70W	20 - 70W	35 - 105W	50 - 150W	20 - 60W	

Brand	Model													
Busch Jaeger	6513 U-102	2 - 100W	1	1	1	1	1	1		1		1	1	1
Busch Jaeger	6523 UR-103	2-100W, LE 2-400W, TE	1	1	1	1	1	1		1	1	1	1	1
Doyle & Tratt (Varilight)	HQ3W	60-400W			1			1			1	1		1
Schneider (Elko)	SBD200LED (CCTEL10501) (S520512: 4-400VA)	4-40W, LE 4-200W, TE		2	2	1	1-2	1	1	1	1	1	1	1
Merten Schneider	MEG5300-0001 (CCT99100)	4 - 20VA, LE 4 - 100VA, TE	1	1	1	1	1	1		1	1	1	1	1
Legrand	BTN4411N BTNT4411 BTL4411N	5 - 75VA		1-2	1-3	1	1-2	1-3		1	1	2		1
Legrand	752060	5 - 75VA		2	2	1	1-2	1		1	1	1	1	1
Gira	245000	20 - 60W LE & TE		1	1	1	1	1		1	1	1	1	1
Gira INSTA	5401 00	20 - 100W LE & TE	1	1	1	1	1	1	1	1	1	1	1	1





Recommended Low Voltage Dimmer compatibility list - LED Lamps

KEY

# Transformer - dimmer combination is compatible with # of lamp(s) and minimum dimming level is below 30% AND maximum dimming level is at least 80%.	
# Transformer - dimmer combination is compatible with # of lamp(s) and minimum dimming level is between 30% (inclusive) and 50% AND maximum level is above or equal to 70%.	This document is for information purposes and must be treated as
Transformer is not compatible.	recommendation. Signify attempted to provide best results, results are
Transformer lamp combination not applicable	generated in lab conditions and might contain faults
Transformer lamp combination not tested	



Master LEDspot Expertcolor 11-50W AR111 9290022388

	Transformer										
		Ph	ilips		Vari	ilight		Tridonic			
Certaline 60	Certaline 105	Certaline 150	Primaline 105	Primaline 150	YT50	YT70	HTM 70	HTM 105	HTM 150	VIPER	
20-60W	35-105W	50-150W	35 - 105W	50 - 150W	0 - 50W	0 - 70W	20 - 70W	35 - 105W	50 - 150W	20 - 60W	

	Brand	Model	
	Busch Jaeger	6513 U-102	2 - 100W
	Gira	1176	50 - 420W
	Merten (Schneider)	5771	20 - 315W
	Doyle & Tratt (Varilight)	HQ3W	60-400W
Dimmer	Insta Group (Berker)	283010	60 - 400W
Ē	Insta Group (Berker/ Insta)	286710/51190	20 - 360W
	Legrand	67081	40 - 300W
	Legrand	67082	40 - 600W
	Legrand (Bticino)	L4407	60 - 250W
	Schneider Electric	315GLE	20 - 315W

1	1-2	1-2	1 - 2	1-2	1	1		1-2	1-2	
					1	1		1 - 2		
1	1 - 2	1 - 2	1 - 2	1-2	1	1	1	1 - 2	1-2	1
					1			1 - 2		
			1 - 2	1-2	1	1		1 - 2	1-2	1
1	1-2	1-2	1 - 2	1-2	1	1		1 - 2	1-2	1



Master LEDspot Expertcolor 15-75W 9290022390

	Transformer											
		Phi	lips		Varil	light	OSRAM			Tridonic		
Certaline 60	Certaline 105	Certaline 150	Primaline 105	Primaline 150	YT50	YT70	HTM 70	HTM 105	HTM 150	VIPER		
20-60W	35-105W	50-150W	35 - 105W	50 - 150W	0 - 50W	0 - 70W	20 - 70W	35 - 105W	50 - 150W	20 - 60W		

Brand	Model	
Busch Jaeger	6513 U-102	2 - 100W
Gira	1176	50 - 420W
Merten (Schneider)	5771	20 - 315W
Doyle & Tratt (Varilight)	HQ3W	60-400W
Insta Group (Berker)	283010	60 - 400W
Insta Group (Berker/ Insta)	286710/51190	20 - 360W
Legrand	67081	40 - 300W
Legrand	67082	40 - 600W
Legrand (Bticino)	L4407	60 - 250W
Schneider Electric	315GLE	20 - 315W

	1	2			1	1	1	1	1
					1	1	1		1
	1	1-2	1	1-2	1	1	1	1-2	1
					1		1	2	1
			1	1-2	1	1	1	1-2	1
		1-2		1	1	1	1	2	1





Recommended Low Voltage Dimmer compatibility list - LED Lamps

KEY

#	Transformer - dimmer combination is compatible with # of lamp(s) and minimum dimming level is below 30% AND maximum dimming level is at least 80%.	
#	Transformer - dimmer combination is compatible with # of lamp(s) and minimum dimming level is between 30% (inclusive) and 50% AND maximum level is above or equal to 70%.	This document is for information purposes and must be treated as
	Transformer is not compatible.	recommendation. Signify attempted to provide best results, results are
	Transformer lamp combination not applicable	generated in lab conditions and might contain faults



MAS LEDspotLV D 20-100W 927 AR111 24D 9290020503, 9290020504 9290020505, 9290020506 9290020507, 9290020508

					Trans	former				
		Ph	ilips		Var	ilight	OSRAM			Tridonic
Certaline 60	Certaline 105	Primaline 70	Primaline 105	Primaline 150	YT50	YT70	HTM 70	HTM 105	HTM 150	VIPER
20-60W	35-105W	20-70W	35 - 105W	50 - 150W	0 - 50W	0 - 70W	20 - 70W	35 - 105W	50 - 150W	20 - 60W

	Brand	Model											
	Doyle & Tratt (Varilight)	HQ3W	60-400W	1	1	1	1		1	1	1	1	1
	Schneider (Elko)	SBD200LED (CCTEL10501) (S520512: 4-400VA) SBD200LED (MEG5134-0000)	4-40W, LE 4-200W, TE	1	1	1	1	1	1	1	1	2	1
	Merten Schneider	MEG5300-0001 (CCT99100), TE	4 - 20VA, LE 4 - 100VA, TE	1	2		2	1	1	1	1	2	1
힅	Busch-Jaeger	6523 U-102, TE	2 - 100W	1	1	1	1	1	1	1	1	1	1
Dimr	Busch Jaeger	6523 UR-103, TE	2-100W, LE 2-400W, TE	1	1 - 2	1	1	1	1	1	1	2	1
	Legrand	BTN4411N, TE BTNT4411 BTL4411N	5 - 75VA	1	2		1	1	1	1	1	1	1
	Legrand	752060	5 - 75VA	1	1		1	1	1	1	1	1-2	1
	Gira	245000, TE	20 - 60W LE & TE										
	Gira INSTA	5401 00, TE	20 - 100W LE & TE	1	1-2	1	1	1	1	1	1		1





Recommended Low Voltage Dimmer compatibility list - LED Lamps

KEY

#	Transformer - dimmer combination is compatible with # of lamp(s) and minimum dimming level is below 30% AND maximum dimming level is at least 80%.	
#	Transformer - dimmer combination is compatible with # of lamp(s) and minimum dimming level is between 30% (inclusive) and 50% AND maximum level is above or equal to 70%.	This document is for information purposes and must be treated as
	Transformer is not compatible.	recommendation. Signify attempted to provide best results, results are
	Transformer lamp combination not applicable	generated in lab conditions and might contain faults
	Transformer lawn combination not tested	



MAS LED ExpertColor 10,8-50W 9xx AR111 xD 9290030432, 9290030433 9290030434, 9290030435 9290030436, 9290030437

		Transformer											
		Ph	ilips		Vari	light	OSRAM			Tridonic			
Certaline 60	Certaline 105	Primaline 70	Primaline 105	Primaline 150	YT50	YT70	HTM 70	HTM 105	HTM 150	VIPER			
20-60W	35-105W	20-70W	35 - 105W	50 - 150W	0 - 50W	0 - 70W	20 - 70W	35 - 105W	50 - 150W	20 - 60W			

	Brand	Model											
	Doyle & Tratt (Varilight)	HQ3W	60-400W	1-2	1	1-2	1			1	1	1-2	1-2
	Schneider (Elko)	SBD200LED (CCTEL10501) (S520512: 4-400VA) SBD200LED (MEG5134-0000)	4-40W, LE 4-200W, TE	1-2	1-2	1-2	1	1	1	1	1	2	1-2
	Merten Schneider	MEG5300-0001 (CCT99100), TE	4 - 20VA, LE 4 - 100VA, TE	1 - 2	2			1		1	1	2	1-2
ımer	Busch-Jaeger	6523 U-102, TE	2 - 100W	1-2	1-2	1-2	1	1	1	1	1	2	1-2
Dim	Busch Jaeger	6523 UR-103, TE	2-100W, LE 2-400W, TE	1-2	1 - 2	1 - 2		1	1	1	1	2	1-2
	Legrand	BTN4411N, TE BTNT4411 BTL4411N	5 - 75VA	2				1	1	1	1		2
	Legrand	752060	5 - 75VA	1-2	1-2	1-2	1	1	1	1	1		1 - 2
	Gira	245000, TE	20 - 60W LE & TE										
	Gira INSTA	5401 00, TE	20 - 100W LE & TE	1-2	1-2	1-2	1	1	1	1	1		1 - 2





Recommended Low Voltage Dimmer compatibility list - LED Lamps

KEY

#	Transformer - dimmer combination is compatible with # of lamp(s) and minimum dimming level is below 30% AND maximum dimming level is at least 80%.		
#	Transformer - dimmer combination is compatible with # of lamp(s) and minimum dimming level is between 30% (inclusive) and 50% AND maximum level is above or equal to 70%.	This document is for information purposes and must be treated as	
	Transformer is not compatible.	recommendation. Signify attempted to provide best results, results are	
	Transformer lamp combination not applicable	generated in lab conditions and might contain faults	
	To a factor of the state of the state of	_	



MAS LED ExpertColor 14.8-75W 9xx AR111 xxD 9290030426, 9290030427 9290030428, 9290030429 9290030430, 9290030431

					Trans	former				
		Phi	ilips		Vari	light		OSRAM		Tridonic
Certaline 60	Certaline 105	Primaline 70	Primaline 105	Primaline 150	YT50	YT70	HTM 70	HTM 105	HTM 150	VIPER
20-60W	35-105W	20-70W	35 - 105W	50 - 150W	0 - 50W	0 - 70W	20 - 70W	35 - 105W	50 - 150W	20 - 60W

	Brand	Model											
	Doyle & Tratt (Varilight)	HQ3W	60-400W	1	1	1				1	1	1	1
	Schneider (Elko)	SBD200LED (CCTEL10501) (S520512: 4-400VA) SBD200LED (MEG5134-0000)	4-40W, LE 4-200W, TE	1	1	1	1	1	1	1	1	2	1
	Merten Schneider	MEG5300-0001 (CCT99100), TE	4 - 20VA, LE 4 - 100VA, TE	1	2		2	1	1	1	1	2	2
ımer	Busch-Jaeger	6523 U-102, TE	2 - 100W	1	1	1	1	1	1	1	1	2	1
Ä	Busch Jaeger	6523 UR-103, TE	2-100W, LE 2-400W, TE	1	1 - 2	1	1	1	1			2	
	Legrand	BTN4411N, TE BTNT4411 BTL4411N	5 - 75VA	1			1	1	1	1	1	2	1
	Legrand	752060	5 - 75VA	1	1	1	1	1	1	1	1	1 - 2	1
	Gira	245000, TE	20 - 60W LE & TE										
	Gira INSTA	5401 00, TE	20 - 100W LE & TE	1	1	1	1	1	1	1	1	2	1





Recommended Low Voltage Dimmer compatibility list - LED Lamps

KEY


#	Transformer - dimmer combination is compatible with # of lamp(s) and minimum dimming level is below 30% AND maximum dimming level is at least 80%.	
#	Transformer - dimmer combination is compatible with # of lamp(s) and minimum dimming level is between 30% (inclusive) and 50% AND maximum level is above or equal to 70%.	This document is for information purposes and must be treated as
	Transformer is not compatible.	recommendation. Signify attempted to provide best results, results are
	Transformer lamp combination not applicable	generated in lab conditions and might contain faults
	Transformer lamp combination not tested	



Master LEDspot D 8-50W 9290018815

						Trans	former					
		Phi	lips		Vari	light				OSRAM		Tridonic
Certaline 60	Certaline 105	Certaline 150	Primaline 105	Primaline 150	YT50	YT70			HTM 70	HTM 105	HTM 150	VIPER

	Brand	Model	
	Busch Jaeger	6513 U-102	2 - 100W
	Gira	1176	50 - 420W
	Merten (Schneider)	5771	20 - 315W
	Doyle & Tratt (Varilight)	HQ3W	60-400W
Dimmer	Insta Group (Berker)	283010	60 - 400W
E	Insta Group (Berker/ Insta)	286710/51190	20 - 360W
	Legrand	67081	40 - 300W
	Legrand	67082	40 - 600W
	Legrand	67084	40 - 300W
	Legrand (Bticino)	ART5364	
	Legrand (Bticino)	L4407	60 - 250W
	Schneider Electric	315GLE	20 - 315W





Master LEDspot DimTone 5-35W MR16 9290019047

						Transformer					
		Phi	lips		Vari	ilight	ELT		OSRAM		Tridonic
Certaline 60	Certaline 105	Certaline 150	Primaline 105	Primaline 150	YT50	YT70	TCE 6/23-E	HTM 70	HTM 105	HTM 150	VIPER



1	1	1		1	1	1	1	1	1	1	1
1		1	1	1	1	1	1	1	1	1	1
1	1	1	1	1	1	1	1	1	1	1	1
											1
1	1	1	1	1	1	1		1	1	1	
1	1	1	1	1	1	1	1	1	1	1	1
											1
											1
1		1		1	1	1		1	1		1
1	1	1	1	1	1	1		1	1		1





Tridonic

20 - 60W

Recommended Low Voltage Dimmer compatibility list - LED Lamps

KEY

#	Transformer - dimmer combination is compatible with # of lamp(s) and minimum dimming level is below 30% AND maximum dimming level is at least 80%.	
#	Transformer - dimmer combination is compatible with # of lamp(s) and minimum dimming level is between 30% (inclusive) and 50% AND maximum level is above or equal to 70%.	This document is for information purposes and must be treated as
	Transformer is not compatible.	recommendation. Signify attempted to provide best results, results are
	Transformer lamp combination not applicable	generated in lab conditions and might contain faults
	To a factor of the state of the state of	_



Master LEDspot Dimtone 7 - 50W MR16 9290020589

						Trans	former					
			Philips			Vari	ilight	ELT		OSRAM		Tridonic
Certaline 60	Certaline 105	Certaline 150	Primaline 70	Primaline 105	Primaline 150	YT50	YT70	TCE 6/23-E	HTM 70	HTM 105	HTM 150	VIPER
20-60W	35-105W	50-150W	20-70W	35 - 105W	50 - 150W	0 - 50W	0 - 70W	0-70W	20 - 70W	35 - 105W	50 - 150W	20 - 60W

	Brand	Model	
	Busch Jaeger	6513 U-102	2 - 100W
	Gira	1176	50 - 420W
	Merten (Schneider)	5771	20 - 315W
	Doyle & Tratt (Varilight)	HQ3W	60-400W
à	Insta Group (Berker)	283010	60 - 400W
Dimmer	Insta Group (Berker/ Insta)	286710/51190	20 - 360W
^	Legrand	67081	40 - 300W
	Legrand	67082	40 - 600W
	Legrand	67084	40 - 300W
	Legrand (Bticino)	L4407	60 - 250W
	Schneider Electric	315GLE	20 - 315W

_												
	1	1	1	1	1	1	1	1	1	1	1	1
	1	1	1	1	1		1	1	1	1	1	1
	1	1	1	1	1	1	1	1	1	1	1	1
												1
	1	1	1	1	1		1	1		1	1	1
	1	1	1	1	1	1	1	1	1	1	1	1
												1
												1
		1	1							1	1	1
	1	1	1	1	1	1	1	1	1	1	1	1

YT50

0 - 50W

0 - 70W

ELT

TCE 6/23-E



Master LED ExpertColor D 6.5 - 35W D 7.5 - 43W MR16 9290013417, 9290013860

	9290013417, 92	290013000										
Brand	Model		-									
Busch Jaeger	6513 U-102	2 - 100W	1	1	1	1	1	1	1	1 1	1 1 1	1 1 1 1
Gira	1176	50 - 420W	1	1	1	1		1	1	1 1	1 1 1	1 1 1 1
Merten (Schneider)	5771	20 - 315W	1	1	1	1	1	1	1	1 1	1 1 1	1 1 1 1
Doyle & Tratt (Varilight)	HQ3W	60-400W	1	1	1	1	1				1	1
Insta Group (Berker)	283010	60 - 400W	1	1	1	1	1	1	1	1	1 1	1 1 1
Insta Group (Berker/ Insta	a) 286710/51190	20 - 360W	1	1	1	1	1	1	1	1 1	1 1 1	1 1 1 1
Legrand	67081	40 - 300W	1	1	1		1	1	1	1 1	1 1	1 1 1
Legrand	67082	40 - 600W	1	1	1		1	1	1	1	1	1 1
Legrand	67084	40 - 300W	1	1	1	1	1	1	1	1 1	1 1 1	1 1 1 1
Legrand (Bticino)	L4407	60 - 250W										
Schneider Electric	315GLF	20 - 315W	1	1	1	1		1	1	1	1	1

50 - 150W

35 - 105W



OSRAM

HTM 150

50 - 150W

HTM 105

35 - 105W

20-60W

35-105W

50-150W



Recommended Low Voltage Dimmer compatibility list - LED Lamps

#	Transformer - dimmer combination is compatible with # of lamp(s) and minimum dimming level is below 30% AND maximum dimming level is at least 80%.			
#	Transformer - dimmer combination is compatible with # of lamp(s) and minimum dimming level is between 30% (inclusive) and 50% AND maximum level is above or equal to 70%.			
	Transformer is not compatible.	recommendation. Signify attempted to provide best results, results are		
	Transformer lamp combination not applicable	generated in lab conditions and might contain faults		
	To of markets and his big and had			

			Transformer											
	Master LEDspot Dimtone 7 - 50W MR16 9290020589			Philips			Varilight		ELT	OSRAM			Tridonic	
			Certaline 60	Certaline 105	Certaline 150	Primaline 105	Primaline 150	YT50	YT70	TCE 6/23-E	HTM 70	HTM 105	HTM 150	VIPER
PHILIPS			20-60W	35-105W	50-150W	35 - 105W	50 - 150W	0 - 50W	0 - 70W		20 - 70W	35 - 105W	50 - 150W	20 - 60W
Brand	Model													
Busch Jaeger	6513 U-102	2 - 100W	1		1		1	1	1	1	1	1	1	1
Gira	1176	50 - 420W	1					1	1	1				1
Merten (Schneider)	5771	20 - 315W	1	1	1		1	1	1	1	1	1	1	1
Doyle & Tratt (Varilight)	HQ3W	60-400W	1		1			1	1		1	1		
Insta Group (Berker)	283010	60 - 400W	1		1			1	1		1	1		1
Insta Group (Berker/ Insta)	286710/51190	20 - 360W	1	1	1		1	1	1		1	1		1
Legrand	67081	40 - 300W												
Legrand	67082	40 - 600W												
Legrand	67084	40 - 300W						1	1		1	1		1
Legrand (Bticino)	L4407	60 - 250W												
Schneider Electric	315GLE	20 - 315W					1	1	1		1	1		1



DISCLAIMERS

- Transfomers and dimmers are tested with the number of LED light sources mentioned in the tables above. A number of LED light sources outside the listed range may result in less optimal behavior. Although not specifically tested, some combination of dimmers and transformers can be loaded with more light sources than specified in this document.
- #1a) Most (non-LED dedicated) dimmers and or transformers can be loaded with LED light sources up to 20% of dimmer/transformer specified maximum power. Example: Dimmer 400W -> 20% = 80W, which means that e.g. up to 16 pcs 5W LED light sources can be connected.
- #1b) LED dimmers/transformers can be loaded up to the specified maximum dimmer/transformer power (Wattage).
- #2) Always study the packaging of LED light sources if these can be used in combination with occupancy motion sensors.#3) "Dimming range" color indications and criteria (all percentages relate to the LED light source full power):
- Green cell: minimum dimming level is below 30% AND maximum level at least 80% Yellow cell: minimum dimming level is between 30% (inclusive) and 50% AND maximum level is above or equal to 70%.

Red cell: not compatible.

Grey cell: the dimmer-transformer-LED light source combination is not applicable. White cell: no data available.

- #4) Various dimmer suppliers offer "active loads" to optimize dimming performance in case of light source-dimmer system issues. (e.g. Busch Jaeger Compensator 6596).
- This list is based on measurements performed in a lab environment at nominal mains voltage, different mains voltages may result in a different dimming range.
- #6) Dimmer and or transformer manufacturers may change the technical design of their dimmer/transformer without informing Philips. Such changes may affect the performance when used in combination with LED light sources.
 #7) In general Philips / Signify dimmable LED light sources can be dimmed with any type of dimmer (type R, RL, RC or RLC).
- Mixed loads may give unexpected dimming behavior or even result in defects, for which Philips cannot be held responsible.
- #9) LED light source are dimmable across the indicated dimming range, but may exhibit minor flickering at distinct dim settings.
- #10) The information contained here is believed to be accurate at the time it was published, but is provided "AS IS"



© 2021 Signify Holding. All rights reserved. The information provided herein is subject to change, without notice. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Specifically mentioned products, materials and or tools from third parties are only indicative and reference to these products, materials and or tools does not necessarily mean they are endorsed by Signify.