



Type A



PAR



BR



Candle



G25 / ST19
Miscellaneous

Contents

Type A lamps 1 – 13

PAR lamps 14 – 25

BR lamps 26 – 30

Candles 31 – 36

Misc. (G25, ST19) 37 – 45

Type A lamps

Number of bulbs

							
		14A19/COR/927/FR/P/E26/DIM/T20 14A19/COR/930/FR/P/E26/DIM/T20 14A19/COR/940/FR/P/E26/DIM/T20 14A19/COR/950/FR/P/E26/DIM/T20	14A19/MAS/927-22/FR/P/E26/T20	12.2A19/COR/927/FR/P/E26/DIM/T20 12.2A19/COR/930/FR/P/E26/DIM/T20 12.2A19/COR/940/FR/P/E26/DIM/T20 12.2A19/COR/950/FR/P/E26/DIM/T20	12.2A19/MAS/927-22/FR/P/E26/T20	8.8A19/COR/927/FR/P/E26/DIM/T20 8.8A19/COR/930/FR/P/E26/DIM/T20 8.8A19/COR/940/FR/P/E26/DIM/T20 8.8A19/COR/950/FR/P/E26/DIM/T20	8.8A19/MAS/927-22/FR/P/E26/T20
Dimmer Company	Model No.	9290037846 (588681) 9290037847 (588673) 9290037848 (588665) 9290037849 (588657)	9290037845 (588780)	9290023852 (561035) 9290023853 (561043) 9290023854 (561050) 9290022852 (560994)	9290022854 (561000)	9290020363 (550459) 9290020362 (550442) 9290020361 (550434) 9290020323 (545897)	9290019409 (479444)
Leviton	6602	1-10	1-10	1-13	1-13	1-17	1-17
Leviton	6631	1-10	1-10	1-13	1-13	1-17	1-17
Leviton	6633	1-10	1-10	1-13	1-13	1-17	1-17
Leviton	6672	1-10	1-10	1-13	1-13	1-17	1-17
Leviton	6674	1-10	1-10	1-13	1-13	1-17	1-17
Leviton	6615P	1-5	1-5	NR	NR	2-9	2-9
Leviton	DSE06	1-10	1-10	1-13	1-13	1-17	1-17
Leviton	DSL06	1-10	1-10	1-13	1-13	1-17	1-17
Leviton	DSM10	1-10	1-10	1-13	1-13	1-17	1-17
Leviton	IPI06	1-10	1-10	1-13	1-13	1-17	1-17
Leviton	IPL06	1-10	1-10	1-13	1-13	1-17	1-17
Leviton	VPI06	1-10	1-10	1-13	2-13	1-17	1-17
Lutron	AYCL-153P	1-10	1-10	1-13	1-10	1-17	1-17
Lutron	CTCL-153P	1-10	1-10	1-13	1-13	1-17	1-17
Lutron	CTCL-153PDH	1-10	1-10	11-13	1-13	1-17	1-17
Lutron	DV-600P	1-10	1-10	1-13	1-13	1-17	1-17
Lutron	DV-600PR	1-10	1-10	1-13	1-13	1-17	1-17
Lutron	DVCL-153P	1-10	1-10	1-13	1-13	1-17	1-17
Lutron	DVCL-253P	1-10	1-10	1-13	1-13	1-17	1-17
Lutron	DVELV-300P	1-5	1-5	1-6	1-6	1-9	1-9
Lutron	DVRP-253P	1-10	1-10	1-13	1-13	1-17	1-17
Lutron	LGCL-153P	1-10	1-10	1-13	1-13	1-17	1-17
Lutron	MACL-153M	1-10	1-10	1-13	1-13	1-17	1-17
Lutron	MAELV-600	1-10	1-10	1-13	1-13	1-17	1-17
Lutron	MALV-600	2-10	2-10	NR	NR	NR	NR
Lutron	MRF2-6ND-120	1-10	1-10	1-13	1-13	1-17	1-17
Lutron	NTCL-250	1-10	1-10	1-13	1-13	1-17	1-17
Lutron	PD-5NE	1-10	1-10	1-13	1-13	1-17	1-17
Lutron	PD-6WCL	1-10	1-10	1-13	1-13	1-17	1-17
Lutron	RRD-3LD	1-5	1-5	1-6	1-6	1-9	1-9
Lutron	RRD-6NA	1-10	1-10	1-13	1-13	1-17	1-17
Lutron	S-600P	1-10	2-10	1-13	1-13	1-17	1-17
Lutron	SCL-153P	1-3	1-3	1-3	1-3	1-4	1-4
Lutron	SCL-153PR	1-3	1-3	1-3	1-3	1-4	1-4
Lutron	SELV-300P	1-5	1-5	1-6	1-6	1-9	1-9
Lutron	SLV-600P	1-8	1-8	1-9	1-9	1-13	1-13
Lutron	TGCL-153PH	1-10	1-10	1-13	1-13	1-17	1-17
Cooper	RI061-VW-K2	1-10	1-10	1-13	1-13	1-17	1-17
Eaton	DAL06P	1-10	1-10	1-13	1-13	1-17	1-17
Legrand	HCL453P	1-10	1-10	1-13	1-13	1-17	1-17
Sensors							
Lutron	MSCL-OP153M	1-10	1-10	1-13	1-13	1-17	1-17
Lutron	MSCL-OP153MH	1-10	1-10	1-13	1-13	1-17	1-17
Lutron	MS-OPS2H	1-10	1-10	1-13	1-13	1-17	1-17
Panel Modules							
Lutron	GP (Harrier) Card	NR	1-10	1-13	2-13	NR	NR
Lutron	HW-RPM-4A-120	1-10	1-10	1-13	1-13	1-17	1-17
Lutron	HW-RPM-4U-120	1-10	1-10	1-13	1-13	1-17	1-17
Lutron	LP-RPM-4U-120	1-10	1-10	1-13	1-13	1-17	1-17

KEY (May exhibit one or several of the described parameters within the group)

Best	No flicker above 10% Full Light Output, good dimming range. Possible minor pop-on.
OK	No flicker above 20% Full Light Output and/or minor flicker which is hard to find at one specific point above 20%. Some limit of dim-range. Relatively high pop-on position reducing mechanical range.
NR	Use of this dimmer/lamp combination not recommended for the quantity of lamps indicated (# or range) or at all (X).
	Lamp not yet tested with this dimmer, compatibility unknown.

¹ Audible noise may be observed when used with this dimmer, depending on the application.² This dimmer has low end trim adjustment that may be used for optimal performance.

WG = Warm Glow AF = Air Flux DS = Diamond Spark CC = Clear Classic DC = Die Cast DW = Direct White SO = Single Optic

Type A lamps

Number of bulbs

											
			5A19/COR/927/FR/P/E26/DIM/T20 5A19/PER/950/P/E26/DIM T20 5A19/PER/940/P/E26/DIM T20 5A19/PER/930/P/E26/DIM T20	5A19/MAS/927-22/FR/P/E26/T20	14A19/PER/8xx/FR/P/E26/D 4/4CT	11A19/CNG/8xx/FR/P/E26/D 4/4CT					
Dimmer Company	Model No.		9290020357 (550400) 9290020360 (550426) 9290020359 (547042) 9290020358 (550418)	9290019407 (479428)	9290035853 (581868) 9290035853 (371179) 9290035853 (589754) 9290035853 (133611)	9290035852 (581835) 9290035852 (589747) 9290035851 (581827) 9290035851 (589739)	9290035850 (581801) 9290035850 (371161) 9290035850 (589721) 9290035850 (130211)	9290037520 (587733) 9290037520 (371112) 9290037520 (589713) 9290037519 (587725)	9290037519 (589705) 9290037518 (587717) 9290037518 (589697) 9290037519 (587709)	9290037517 (371104) 9290037517 (589689)	
Leviton	6602	Professional Channel	1-20	1-20		1-10			1-13		
Leviton	6631		2-20	1-20		1-10			1-13		
Leviton	6633		1-20	1-20		1-10			1-13		
Leviton	6672		1-20	1-20		1-10			1-13		
Leviton	6674		1-20	1-20		1-10			1-13		
Leviton	6615P		2-14	2-14		1-5			1-7		
Leviton	DSE06		1-20	1-20		1-10			1-13		
Leviton	DSL06		1-20	1-20		1-10			1-13		
Leviton	DSM10		2-20	2-20		1-10			1-13		
Leviton	IPI06		1-20	1-20		1-10			1-13		
Leviton	IPL06		1-20	1-20		1-10			1-13		
Leviton	VPI06		1-20	2-20		1-10			1-13		
Lutron	AYCL-153P		1-20	1-20		1-10			1-13		
Lutron	CTCL-153P		1-20	1-20		1-10			1-13		
Lutron	CTCL-153PDH		1-20	1-20		NR			NR		
Lutron	DV-600P		1-20	1-20		1-10			1-13		
Lutron	DV-600PR		1-20	1-20		1-10			1-13		
Lutron	DVCL-153P		1-20	1-20		1-10			1-13		
Lutron	DVCL-253P		1-20	1-20		1-10			1-13		
Lutron	DVELV-300P		1-20	1-15		1-10			1-7		
Lutron	DVRP-253P		1-20	1-20		1-10			1-13		
Lutron	LGCL-153P		1-20	1-20		NR			NR		
Lutron	MACL-153M		1-20	1-20		1-10			1-13		
Lutron	MAELV-600		1-20	1-20		1-10			1-13		
Lutron	MALV-600		NR	NR		NR			NR		
Lutron	MRF2-6ND-120		1-20	1-20		1-10			1-13		
Lutron	NTCL-250		1-20	1-20		1-10			1-13		
Lutron	PD-5NE		1-20	1-20		1-10			1-13		
Lutron	PD-6WCL		1-10	1-5		1-10			1-13		
Lutron	RRD-3LD		1-14	1-20		1-5			1-7		
Lutron	RRD-6NA		1-20	1-20		1-10			1-13		
Lutron	S-600P		1-20	1-20		1-10			1-13		
Lutron	SCL-153P		1-5	1-5		1-3			1-3		
Lutron	SCL-153PR		1-5	1-5		1-3			1-3		
Lutron	SELV-300P		1-10	1-10		1-5			1-7		
Lutron	SLV-600P		1-20	1-20		1-8			1-10		
Lutron	TGCL-153PH		1-10	1-20		1-10			1-13		
Cooper	RI061-VW-K2		1-20	3-20		1-10			1-13		
Eaton	DAL06P		1-20	2-20		1-10			1-13		
Legrand	HCL453P		1-20	1-20		1-10			1-13		
Sensors											
Lutron	MSCL-OP153M		1-20	1-20		1-10			1-13		
Lutron	MSCL-OP153MH		1-20	1-20		1-10			1-13		
Lutron	MS-OPS2H		1-20	1-20		1-10			1-13		
Panel Modules											
Lutron	GP (Harrier) Card		NR	NR		1-10			1-13		
Lutron	HW-RPM-4A-120		1-20	1-20		1-10			1-13		
Lutron	HW-RPM-4U-120		1-20	1-20		1-10			1-13		
Lutron	LP-RPM-4U-120		1-20	1-20		1-10			1-13		

KEY (May exhibit one or several of the described parameters within the group)

Best	No flicker above 10% Full Light Output, good dimming range. Possible minor pop-on.
OK	No flicker above 20% Full Light Output and/or minor flicker which is hard to find at one specific point above 20%. Some limit of dim-range. Relatively high pop-on position reducing mechanical range.
NR	Use of this dimmer/lamp combination not recommended for the quantity of lamps indicated (# or range) or at all (X).
	Lamp not yet tested with this dimmer, compatibility unknown.

¹ Audible noise may be observed when used with this dimmer, depending on the application.² This dimmer has low end trim adjustment that may be used for optimal performance.

Type A lamps

Number of bulbs

										
			8A19/PER/8xx/FR/P/E26/D 4/4CT	5A19/CNG/8xx/FR/P/E26/D 4/4CT	12A19/LED/9xx/FR/Glass/E26/DIM 1FB T20	9.5A19/LED/9xx/FR/Glass/E26/DIM 1FB T20				
			9290035849 (581777) 9290035849 (588079) 9290035848 (589671) 9290035748 (588061) 9290035748 (589663)	9290035796 (581785) 9290035796 (588053) 9290035796 (344960) 9290035796 (589655) 9290035796 (130195) 9290035796 (130203)	9290035795 (581751) 9290035795 (588046) 9290035795 (344952) 9290035795 (589648) 9290035795 (127886) 9290035795 (130187)	9290037512 (587691) 9290037512 (344945) 9290037512 (589630) 9290037511 (587683)	9290037511 (589622) 9290037510 (587675) 9290037510 (589614) 9290037509 (587667)	9290037509 (344937) 9290037509 (589606)	9290034984 (578633) 9290034983 (578625) 9290034982 (578617)	9290034981 (578609) 9290034980 (578591) 9290034979 (578583)
Dimmer Company	Model No.	Professional Channel	1-17	1-30	1-11	1-17				
Leviton	6602		1-17	1-30	1-11	1-17				
Leviton	6631		1-17	1-30	1-11	1-17				
Leviton	6633		1-17	1-30	1-11	1-17				
Leviton	6672		1-17	1-30	1-11	1-17				
Leviton	6674		1-17	1-30	1-11	1-17				
Leviton	6615P		1-9	1-15	NR	NR				
Leviton	DSE06		1-17	1-30	1-20	1-20				
Leviton	DSL06		1-17	1-30	NR	NR				
Leviton	DSM10		1-17	1-30	1-20	1-20				
Leviton	IPI06		1-17	1-30	1-11	1-17				
Leviton	IPL06		1-17	1-30	1-11	1-17				
Leviton	VPI06		1-17	1-30	1-11	1-17				
Lutron	AYCL-153P		1-17	1-30	1-11	NR				
Lutron	CTCL-153P		1-17	1-30	1-11	1-17				
Lutron	CTCL-153PDH		NR	NR	1-11	1-17				
Lutron	DV-600P		1-17	1-30	1-11	1-17				
Lutron	DV-600PR		1-17	1-30	1-11	1-17				
Lutron	DVCL-153P		1-17	1-30	1-11	1-17				
Lutron	DVCL-253P		1-17	1-30	1-19	NR				
Lutron	DVELV-300P		1-9	1-15	NR	NR				
Lutron	DVRP-253P		1-17	1-30	1-19	1-20				
Lutron	LGCL-153P		NR	NR	1-11	1-17				
Lutron	MACL-153M		1-17	1-30	1-11	1-17				
Lutron	MAELV-600		1-17	1-30	1-11	1-17				
Lutron	MALV-600		NR	NR	NR	NR				
Lutron	MRF2-6ND-120		1-17	1-30	1-11	1-17				
Lutron	NTCL-250		1-17	1-30	1-19	NR				
Lutron	PD-5NE		1-17	1-30	1-19	1-20				
Lutron	PD-6WCL		1-17	1-30	NR	NR				
Lutron	RRD-3LD		1-9	1-15	1-11	1-17				
Lutron	RRD-6NA		1-17	1-30	1-11	1-17				
Lutron	S-600P		1-17	1-30	1-11	1-17				
Lutron	SCL-153P		1-4	1-8	1-3	1-4				
Lutron	SCL-153PR		1-4	1-8	1-3	1-4				
Lutron	SELV-300P		1-9	1-15	1-6	1-8				
Lutron	SLV-600P		1-13	1-20	1-8	1-13				
Lutron	TGCL-153PH		1-17	1-30	1-11	1-17				
Cooper	RI061-VW-K2		1-17	1-30	1-11	1-17				
Eaton	DAL06P		1-17	1-30	1-20	1-20				
Legrand	HCL453P		1-17	1-30	1-20	1-20				
Sensors										
Lutron	MSCL-OP153M		1-17	1-30	NR	NR				
Lutron	MSCL-OP153MH		1-17	1-30	NR	NR				
Lutron	MS-OPS2H		1-17	1-30	1-5	1-7				
Panel Modules										
Lutron	GP (Harrier) Card		1-17	1-30	NR	NR				
Lutron	HW-RPM-4A-120		1-17	1-30	1-20	1-20				
Lutron	HW-RPM-4U-120		1-17	1-30	1-20	1-20				
Lutron	LP-RPM-4U-120		1-17	1-30	1-20	1-20				

KEY (May exhibit one or several of the described parameters within the group)

Best	No flicker above 10% Full Light Output, good dimming range. Possible minor pop-on.
OK	No flicker above 20% Full Light Output and/or minor flicker which is hard to find at one specific point above 20%. Some limit of dim-range. Relatively high pop-on position reducing mechanical range.
NR	Use of this dimmer/lamp combination not recommended for the quantity of lamps indicated (# or range) or at all (X).
	Lamp not yet tested with this dimmer, compatibility unknown.

¹ Audible noise may be observed when used with this dimmer, depending on the application.² This dimmer has low end trim adjustment that may be used for optimal performance.

WG = Warm Glow AF = Air Flux DS = Diamond Spark CC = Clear Classic DC = Die Cast DW = Direct White SO = Single Optic

Type A lamps

Number of bulbs

								
			8A19/LED/9xx/FR/Glass/E26/ DIM 1FB T20	5A19/LED/9xx/FR/Glass/E26/ DIM 1FB T20	6.6A15/PER/UD50/CL/G/E26/ DIM 2PF T20	8A19/PER/UD/FR/G/E26/WGD 4/ 2PF T20	5A15/PER/UD/CL/G/E12-E26/ WGD 6/2PF T20	
Dimmer Company	Model No.		9290034978 (578641) 9290034977 (578575) 9290034976 (578567)	9290034975 (578559) 9290034974 (578542) 9290034973 (578534)	9290030845 (573402)	9290030832 (573436) 9290030832 (574897) 9290030832 (574871)	9290030832 (574889) 9290030832 (576116) 9290029865 (564385) 9290029865 (575043)	
Leviton	6602	Professional Channel	1-10	1-10	1-20	1-10	1-10	
Leviton	6631		1-10	1-10	1-20	1-10	1-10	
Leviton	6633		1-10	1-10	1-20	1-10	1-10	
Leviton	6672		1-10	1-10	1-20	1-10	1-10	
Leviton	6674		1-10	1-10	1-20	1-10	1-10	
Leviton	6615P		NR	NR	NR	NR	NR	
Leviton	DSE06		1-10	1-10	1-20	1-10	1-10	
Leviton	DSL06		1-10	1-10	1-20	1-10	1-10	
Leviton	DSM10		1-10	1-10	1-20	1-10	1-10	
Leviton	IPI06		1-10	1-10	1-20	1-10	1-10	
Leviton	IPL06		1-10	1-10	1-20	1-10	1-10	
Leviton	VPI06		1-10	1-10	1-20	1-10	1-10	
Lutron	AYCL-153P		1-11	1-11	1-20	1-11	1-11	
Lutron	CTCL-153P		1-10	1-10	1-20	1-10	1-10	
Lutron	CTCL-153PDH		1-10	1-10	1-20	1-10	1-10	
Lutron	DV-600P		1-10	1-10	1-20	1-10	1-10	
Lutron	DV-600PR		1-10	1-10	1-20	1-10	1-10	
Lutron	DVCL-153P		1-10	1-10	1-20	1-10	1-10	
Lutron	DVCL-253P		1-20	1-20	1-20	1-20	1-20	
Lutron	DVELV-300P		NR	NR	NR	NR	NR	
Lutron	DVRP-253P		1-20	1-20	1-20	1-20	1-20	
Lutron	LGCL-153P		1-10	1-10	1-20	1-10	1-10	
Lutron	MACL-153M		1-10	1-10	1-20	1-10	1-10	
Lutron	MAELV-600		1-10	1-10	1-20	1-10	1-10	
Lutron	MALV-600		NR	NR	NR	NR	NR	
Lutron	MRF2-6ND-120		1-10	1-10	1-20	1-10	1-10	
Lutron	NTCL-250		1-20	1-20	1-20	1-20	1-20	
Lutron	PD-5NE		1-10	1-10	1-20	1-10	1-10	
Lutron	PD-6WCL		1-10	1-10	1-20	1-10	1-10	
Lutron	RRD-3LD		1-10	1-10	1-11	1-10	1-10	
Lutron	RRD-6NA		1-10	1-10	1-20	1-10	1-10	
Lutron	S-600P		1-10	1-10	1-20	1-10	1-10	
Lutron	SCL-153P		1-8	1-8	1-6	1-8	1-8	
Lutron	SCL-153PR		1-8	1-8	1-6	1-8	1-8	
Lutron	SELV-300P		1-10	1-10	1-11	1-10	1-10	
Lutron	SLV-600P		1-10	1-10	1-17	1-10	1-10	
Lutron	TGCL-153PH		1-10	1-10	1-20	1-10	1-10	
Cooper	RI061-VW-K2		1-10	1-10	1-20	1-10	1-10	
Eaton	DAL06P		1-10	1-10	1-20	1-10	1-10	
Legrand	HCL453P		1-10	1-10	1-20	1-10	1-10	
Sensors								
Lutron	MSCL-OP153M		1-10	1-10	1-20	1-10	1-10	
Lutron	MSCL-OP153MH		1-10	1-10	1-20	1-10	1-10	
Lutron	MS-OPS2H		1-10	1-10	1-20	1-10	1-10	
Panel Modules								
Lutron	GP (Harrier) Card		NR	NR	NR	NR	NR	
Lutron	HW-RPM-4A-120		1-20	1-20	1-20	1-20	1-20	
Lutron	HW-RPM-4U-120		1-20	1-20	1-20	1-20	1-20	
Lutron	LP-RPM-4U-120		1-20	1-20	1-20	1-20	1-20	

KEY (May exhibit one or several of the described parameters within the group)

Best	No flicker above 10% Full Light Output, good dimming range. Possible minor pop-on.
OK	No flicker above 20% Full Light Output and/or minor flicker which is hard to find at one specific point above 20%. Some limit of dim-range. Relatively high pop-on position reducing mechanical range.
NR	Use of this dimmer/lamp combination not recommended for the quantity of lamps indicated (# or range) or at all (X).
	Lamp not yet tested with this dimmer, compatibility unknown.

¹ Audible noise may be observed when used with this dimmer, depending on the application.² This dimmer has low end trim adjustment that may be used for optimal performance.

Type A lamps

Number of bulbs

Type A lamps Number of bulbs									
			19W (100W Eq) A21	15W (75W Eq) A21	16A19/PER/9xx/P/E26/DIM 6/1FB T20	29A21/PER/8xx/FR/P/E26/WG/HO 4/1PF	16A21/PER/930/P/GU24/DIM 6/1FB T20	8.8A19/PER/930/P/GU24/DIM 6/1FB T20	
Dimmer Company	Model No.		9290002596A (451906)	9290002595A (453159) 9290002595A (451898)	9290023857 (561456) 9290023856 (561076) 9290023855 (561068) 9290022853 (561019)	9290023431 (571505) 9290023430 (571497)	9290023276 (558684)	9290023275 (557686) 9290023275 (557660)	
Leviton	6602	Professional Channel			1-9	1-5	1-9	1-17	
Leviton	6631				1-9	1-5	1-9	1-17	
Leviton	6633				1-9	1-5	1-9	1-17	
Leviton	6672				1-9	1-5	1-9	1-17	
Leviton	6674		NR	NR	1-9	1-5	1-9	1-17	
Leviton	6615P		1-3	1-4		1-3	1-5	NR	
Leviton	DSE06						1-19	1-20	
Leviton	DSL06				1-9	1-10	1-19	1-20	
Leviton	DSM10						1-20	1-20	
Leviton	IPI06		NR	1-8	NR	1-5	1-9	1-17	
Leviton	IPL06				1-9	1-5	1-9	1-17	
Leviton	VPI06						1-9	1-17	
Lutron	AYCL-153P				1-9		1-9	1-17	
Lutron	CTCL-153P				1-9		1-9	1-17	
Lutron	CTCL-153PDH						1-9	NR	
Lutron	DV-600P		1-6	1-8	1-9	1-5	1-9	1-17	
Lutron	DV-600PR						1-9	1-17	
Lutron	DVCL-153P				1-9		1-9	1-17	
Lutron	DVCL-253P						1-16	1-20	
Lutron	DVELV-300P		1-3	1-4	1-9	1-3	1-5	1-9	
Lutron	DVRP-253P						1-16	1-20	
Lutron	LGCL-153P						1-9	1-17	
Lutron	MACL-153M		1-6	1-8	1-9	1-5	1-9	1-17	
Lutron	MAELV-600						1-20	1-20	
Lutron	MALV-600						NR	NR	
Lutron	MRF2-6ND-120		1-6	1-8	1-9	1-5	1-9	1-17	
Lutron	NTCL-250				1-9		1-16	1-20	
Lutron	PD-5NE						1-16	1-20	
Lutron	PD-6WCL				1-9	1-5	1-9	1-17	
Lutron	RRD-3LD						1-5	1-9	
Lutron	RRD-6NA		1-7	1-8	1-9	1-5	1-9	1-17	
Lutron	S-600P						1-9	1-17	
Lutron	SCL-153P		1-6		1-9		1-2	1-4	
Lutron	SCL-153PR						1-2	1-4	
Lutron	SELV-300P						1-5	1-9	
Lutron	SLV-600P		1-4	1-6*	1-7	1-4	1-7	1-13	
Lutron	TGCL-153PH						1-9	1-17	
Cooper	RI061-VW-K2						1-9	1-17	
Eaton	DAL06P						1-19	1-20	
Legrand	HCL453P						1-20	1-20	
Sensors									
Lutron	MSCL-OP153M		1-6	1-8	1-9	1-5	1-9	1-17	
Lutron	MSCL-OP153MH		1-6		1-9	1-5	1-9	1-17	
Lutron	MS-OPS2H						1-9	1-17	
Panel Modules									
Lutron	GP (Harrier) Card		1-12		1-9		NR	NR	
Lutron	HW-RPM-4A-120		1-17				1-19	1-20	
Lutron	HW-RPM-4U-120		1-17				1-20	1-20	
Lutron	LP-RPM-4U-120		1-17				1-20	1-20	

KEY (May exhibit one or several of the described parameters within the group)

Best	No flicker above 10% Full Light Output, good dimming range. Possible minor pop-on.
OK	No flicker above 20% Full Light Output and/or minor flicker which is hard to find at one specific point above 20%. Some limit of dim-range. Relatively high pop-on position reducing mechanical range.
NR	Use of this dimmer/lamp combination not recommended for the quantity of lamps indicated (# or range) or at all (X).
	Lamp not yet tested with this dimmer, compatibility unknown.

1 Audible noise may be observed when used with this dimmer, depending on the application.
2 This dimmer has low end trim adjustment that may be used for optimal performance.

WG = Warm Glow AF = Air Flux DS = Diamond Spark CC = Clear Classic DC = Die Cast DW = Direct White SO = Single Optic

Type A lamps

Number of bulbs

Type A lamps Number of bulbs								
			16A19/PER/927-22/P/E26/ WG 6/1FB T20	5.5A15/PER/927-922/CL/G/ E26/WGX1FB	3.8A15/PER/927-922/CL/G/E26/ WGX1FB T20	3.8A15/PER/927-922/CL/G/E12/ WGX1FB T20	16W (100W Eq) A21 T20, P024994, 2019Q2	12.2W (75W Eq) A21 T20, P0024994, 2019Q2
Dimmer Company	Model No.		9290022855 (561027)	9290022086 (549402)	9290022083 (549386)	9290022081 (549378)	9290020371 (550525) 9290020370 (547125) 9290020369 (550517) 9290020368 (550509)	9290020367 (550491) 9290020366 (547091) 9290020365 (550483) 9290020364 (550475)
Leviton	6602	Professional Channel	1-9	1-10	1-10	1-10	1-9	1-12
Leviton	6631		1-9	1-10	1-10	1-10		
Leviton	6633		1-9	1-10	2-10	2-10	1-9	1-12
Leviton	6672		1-9	1-10	1-10	1-10	1-9	1-12
Leviton	6674		1-9	1-10	1-10	1-10		
Leviton	6615P			NR	NR	NR	1-5	1-6
Leviton	DSE06			1-10				
Leviton	DSL06		1-9	1-10	1-10	1-10		
Leviton	DSM10			1-10				
Leviton	IPI06		NR	1-10	2-10	2-10	1-9	1-12
Leviton	IPL06		1-9	1-10	1-10	1-10		
Leviton	VPI06			1-10				
Lutron	AYCL-153P		1-9	1-11				
Lutron	CTCL-153P		1-9	1-10				
Lutron	CTCL-153PDH			1-10				
Lutron	DV-600P		1-9	1-10	1-10	1-10	1-9	1-12
Lutron	DV-600PR			1-10				
Lutron	DVCL-153P		1-9	1-10				
Lutron	DVCL-253P			1-20				
Lutron	DVELV-300P		1-9	NR	1-10	1-10	1-5	1-6
Lutron	DVRP-253P			1-20				
Lutron	LGCL-153P			1-10				
Lutron	MACL-153M		1-9	1-10	1-10	1-10	1-9	1-12
Lutron	MAELV-600			1-10				
Lutron	MALV-600			NR				
Lutron	MRF2-6ND-120		1-9	1-10	1-10	1-10	1-9	1-12
Lutron	NTCL-250		1-9	1-20				
Lutron	PD-5NE			1-10				
Lutron	PD-6WCL		1-9	1-10	1-10	1-10	1-9	1-12
Lutron	RRD-3LD			1-10				
Lutron	RRD-6NA		1-9	1-10			1-9	1-12
Lutron	S-600P			1-10				
Lutron	SCL-153P		1-9	1-8				
Lutron	SCL-153PR			1-8				
Lutron	SELV-300P			1-10				
Lutron	SLV-600P		1-7	1-10	1-10	1-10	1-7	1-9
Lutron	TGCL-153PH			1-10				
Cooper	RI061-VW-K2			1-10				
Eaton	DAL06P			1-10				
Legrand	HCL453P			1-10				
Sensors								
Lutron	MSCL-OP153M		1-9	1-10	1-10	1-10	1-9	1-12
Lutron	MSCL-OP153MH		1-9	1-10	1-10	1-10		
Lutron	MS-OPS2H			1-10				
Panel Modules								
Lutron	GP (Harrier) Card		1-9	NR				
Lutron	HW-RPM-4A-120			1-20				
Lutron	HW-RPM-4U-120			1-20				
Lutron	LP-RPM-4U-120			1-20				

KEY (May exhibit one or several of the described parameters within the group)

Best	No flicker above 10% Full Light Output, good dimming range. Possible minor pop-on.
OK	No flicker above 20% Full Light Output and/or minor flicker which is hard to find at one specific point above 20%. Some limit of dim-range. Relatively high pop-on position reducing mechanical range.
NR	Use of this dimmer/lamp combination not recommended for the quantity of lamps indicated (# or range) or at all (X).
	Lamp not yet tested with this dimmer, compatibility unknown.

¹ Audible noise may be observed when used with this dimmer, depending on the application.² This dimmer has low end trim adjustment that may be used for optimal performance.

Type A lamps

Number of bulbs

Type A lamps Number of bulbs									
			16W A21 WG & CG bulb	12W (75W Eq) WG & CG T20, P0022267, 2019Q1 WG, 2019Q2 CG	8A19/PER/927-922/CL/G/E26/WGX 1FB T20	8W WG A19 filament	5.5W (40W Eq)A19	12W (75W Eq) A21	
Dimmer Company	Model No.		9290020073A 9290020073 9290019413A 9290019413	9290020072 9290019411 (479469)	9290019696 (549493)	9290019334 (536920)	9290018669 (532985) 9290018371 (479428) 9290018362 (479436) 9290018361 (479840)	9290018668 (532993) 9290018367 (479477)	
Leviton	6602	Professional Channel	1-9	1-10	1-10	1-10	1-15	1-13	
Leviton	6631				1-10				
Leviton	6633		1-9	1-10	1-10	1-10	1-15	1-13	
Leviton	6672		1-9	1-10	1-10	1-10	1-15	1-13	
Leviton	6674				1-10				
Leviton	6615P		NR	3-6	NR	1-9	1-14	1-6	
Leviton	DSE06				1-10				
Leviton	DSL06				1-10				
Leviton	DSM10				1-10				
Leviton	IPI06		1-9	1-10	1-10	1-10	1-15	1-13	
Leviton	IPL06				1-10				
Leviton	VPI06				1-10				
Lutron	AYCL-153P				1-11				
Lutron	CTCL-153P				1-10				
Lutron	CTCL-153PDH				1-10				
Lutron	DV-600P		1-9	1-10	1-10	1-10	1-15	1-13	
Lutron	DV-600PR				1-10				
Lutron	DVCL-153P				1-10				
Lutron	DVCL-253P				1-20				
Lutron	DVELV-300P		1-5	1-6	NR	1-10	1-15	1-6	
Lutron	DVRP-253P				1-20				
Lutron	LGCL-153P				1-10				
Lutron	MACL-153M		1-9	1-10	1-10	1-10	1-15	1-13	
Lutron	MAELV-600				1-10				
Lutron	MALV-600				NR				
Lutron	MRF2-6ND-120		1-9	1-10	1-10	1-3	1-15	1-13	
Lutron	NTCL-250				1-20				
Lutron	PD-5NE				1-10				
Lutron	PD-6WCL		1-9	1-10	1-10	1-10	1-15	1-13	
Lutron	RRD-3LD				1-10				
Lutron	RRD-6NA		1-9	1-10	1-10	1-10	1-15	1-13	
Lutron	S-600P				1-10				
Lutron	SCL-153P				1-8				
Lutron	SCL-153PR				1-8				
Lutron	SELV-300P				1-10				
Lutron	SLV-600P		1-7	1-9	1-10	1-10	1-5	1-9	
Lutron	TGCL-153PH				1-10				
Cooper	RI061-VW-K2				1-10				
Eaton	DAL06P				1-10				
Legrand	HCL453P				1-10				
Sensors									
Lutron	MSCL-OP153M		1-9	1-10	1-10	1-10	1-15	1-13	
Lutron	MSCL-OP153MH				1-10	1-10	1-15	1-13	
Lutron	MS-OPS2H				1-10	1-10	1-15	1-13	
Panel Modules									
Lutron	GP (Harrier) Card				NR	1-10	1-15	1-15	
Lutron	HW-RPM-4A-120				1-20	1-10	1-15	1-15	
Lutron	HW-RPM-4U-120				1-20	1-10	1-15	1-15	
Lutron	LP-RPM-4U-120				1-20	1-10	1-15	1-15	

KEY (May exhibit one or several of the described parameters within the group)

Best	No flicker above 10% Full Light Output, good dimming range. Possible minor pop-on.
OK	No flicker above 20% Full Light Output and/or minor flicker which is hard to find at one specific point above 20%. Some limit of dim-range. Relatively high pop-on position reducing mechanical range.
NR	Use of this dimmer/lamp combination not recommended for the quantity of lamps indicated (# or range) or at all (X).
	Lamp not yet tested with this dimmer, compatibility unknown.

¹ Audible noise may be observed when used with this dimmer, depending on the application.² This dimmer has low end trim adjustment that may be used for optimal performance.

WG = Warm Glow AF = Air Flux DS = Diamond Spark CC = Clear Classic DC = Die Cast DW = Direct White SO = Single Optic

Type A lamps

Number of bulbs

Type A lamps									
Number of bulbs			16A21/PER/827-22/P/E26/WG	9.5W (60W Eq) A19 WG	16W (100W Eq) A21	9.5W (60W Eq) A19	4.5W (60W Eq) A19	5.5W (40W Eq)A15 Clear WG	
Dimmer Company	Model No.		9290018377 9290018377A (479485) 9290018377A (479535) 9290018377A (479402)	9290018373 (479444)	9290018370 (479493) 9290018369 (479899) 9290018368 (479881)	9290018365 (479451) 9290018364 (479865) 9290018363 (479857)	9290012741 (466243) 9290012739 (466227)	9290012150 (462529)	
Leviton	6602	Professional Channel	1-3	1-15	1-9	1-15	1-33	1-25	
Leviton	6631								
Leviton	6633		1-3	1-15	1-9	1-15	1-33	1-25	
Leviton	6672		1-3	1-15	1-9	1-15	1-33	1-25	
Leviton	6674						1-10		
Leviton	6615P		1-3	1-8	1-5	NR	1-17	1-13	
Leviton	DSE06								
Leviton	DSL06								
Leviton	DSM10								
Leviton	IPI06		1-3	1-15	1-9	NR	1-33	1-25	
Leviton	IPL06								
Leviton	VPI06								
Lutron	AYCL-153P								
Lutron	CTCL-153P								
Lutron	CTCL-153PDH								
Lutron	DV-600P		1-3	1-15	1-9	1-15	1-33	1-25	
Lutron	DV-600PR								
Lutron	DVCL-153P								
Lutron	DVCL-253P								
Lutron	DVELV-300P		1-3	1-8	1-9	1-15	1-17	1-13	
Lutron	DVRP-253P								
Lutron	LGCL-153P								
Lutron	MACL-153M		1-3	1-15	1-9	1-15	1-33	1-25	
Lutron	MAELV-600								
Lutron	MALV-600								
Lutron	MRF2-6ND-120		1-3	1-15	1-9	1-15	1-33	1-25	
Lutron	NTCL-250								
Lutron	PD-5NE								
Lutron	PD-6WCL		1-3	1-15	1-9	1-15	NR	NR	
Lutron	RRD-3LD								
Lutron	RRD-6NA		1-3	1-15	1-9	1-15	1-15	NR	
Lutron	S-600P								
Lutron	SCL-153P								
Lutron	SCL-153PR								
Lutron	SELV-300P								
Lutron	SLV-600P		1-3	1-15	1-7	1-8	1-25	1-19	
Lutron	TGCL-153PH								
Cooper	RI061-VW-K2								
Eaton	DAL06P								
Legrand	HCL453P								
Sensors									
Lutron	MSCL-OP153M		1-3	1-15	1-9	1-15	1-33	1-25	
Lutron	MSCL-OP153MH			1-15	1-9	1-15	1-33	1-25	
Lutron	MS-OPS2H			1-15	1-9	1-15	1-33	1-25	
Panel Modules									
Lutron	GP (Harrier) Card			1-15	1-15	1-15	1-33	1-25	
Lutron	HW-RPM-4A-120			1-15	1-15	1-15	1-33		
Lutron	HW-RPM-4U-120			1-15	1-15	1-15	1-33		
Lutron	LP-RPM-4U-120			1-15	1-15	1-15	1-33		

KEY (May exhibit one or several of the described parameters within the group)

Best	No flicker above 10% Full Light Output, good dimming range. Possible minor pop-on.
OK	No flicker above 20% Full Light Output and/or minor flicker which is hard to find at one specific point above 20%. Some limit of dim-range. Relatively high pop-on position reducing mechanical range.
NR	Use of this dimmer/lamp combination not recommended for the quantity of lamps indicated (# or range) or at all (X).
	Lamp not yet tested with this dimmer, compatibility unknown.

¹ Audible noise may be observed when used with this dimmer, depending on the application.² This dimmer has low end trim adjustment that may be used for optimal performance.

Type A lamps

Number of bulbs

Type A lamps								
Number of bulbs			9.5W A19 2700K Core	9W (60W Eq) A19 5000K core	9W (60W Eq) A19 3000K	9.5W A19 2200K-2700K	14W (75W Eq) A21 WG	
Dimmer Company	Model No.		9290012006 (461269) 9290012006 (461226) 9290012006 (461194) 9290012006 (461228) 9290012006 (461210) 9290012006 (461251) 9290012006 (461244) 9290012006 (461236)	9290011970 (461327) 9290011970 (461350) 9290011970 (455881) 9290011970 (462259) 9290011970 (461368) 9290011970 (461335)	9290011969 (459057) 9290011969 (462234) 9290011969 (462242)	9290011840	9290011839 (459065) 9290011839 (459073) 9290011839 (459081) 9290011839 (459099)	
Leviton	6602	Professional Channel	1-15	1-17	1-15	1-15	1-11	
Leviton	6631							
Leviton	6633		1-15	1-17	1-15	1-15	1-11	
Leviton	6672		1-15	1-17	1-15	1-15	1-11	
Leviton	6674		1-15	1-3	1-15	1-15	1-11	
Leviton	6615P		1-8	1-8	1-8	1-5	1-5	
Leviton	DSE06							
Leviton	DSL06							
Leviton	DSM10							
Leviton	IPI06		1-15	1-17	1-15	1-15	1-11	
Leviton	IPL06							
Leviton	VPI06							
Lutron	AYCL-153P							
Lutron	CTCL-153P							
Lutron	CTCL-153PDH							
Lutron	DV-600P		1-15	1-17	1-15	1-15	1-11	
Lutron	DV-600PR							
Lutron	DVCL-153P							
Lutron	DVCL-253P							
Lutron	DVELV-300P		1-8	1-8	1-8	1-5	1-5	
Lutron	DVRP-253P							
Lutron	LGCL-153P							
Lutron	MACL-153M		1-15	1-3	1-15	NR	1-11	
Lutron	MAELV-600							
Lutron	MALV-600							
Lutron	MRF2-6ND-120		1-15	1-17	1-15	1-15	1-11	
Lutron	NTCL-250							
Lutron	PD-5NE							
Lutron	PD-6WCL		1-15	1-17	1-15	1-15	1-11	
Lutron	RRD-3LD							
Lutron	RRD-6NA		1-15	1-3	1-15	1-15	1-11	
Lutron	S-600P							
Lutron	SCL-153P							
Lutron	SCL-153PR							
Lutron	SELV-300P							
Lutron	SLV-600P		1-15	1-13	1-15	1-11	1-11	
Lutron	TGCL-153PH							
Cooper	RI061-VW-K2							
Eaton	DAL06P							
Legrand	HCL453P							
Sensors								
Lutron	MSCL-OP153M		1-15	1-3	1-15	NR	1-11	
Lutron	MSCL-OP153MH		1-15	1-17	1-15	1-15	1-11	
Lutron	MS-OPS2H		1-15	1-17	1-15	1-15	1-11	
Panel Modules								
Lutron	GP (Harrier) Card		1-15	1-17	1-15	1-15	1-23	
Lutron	HW-RPM-4A-120		1-15	1-17	1-15	1-15	1-23	
Lutron	HW-RPM-4U-120		1-15	1-17	1-15	1-15	1-23	
Lutron	LP-RPM-4U-120		1-15	1-17	1-15	1-15	1-23	

KEY (May exhibit one or several of the described parameters within the group)

Best	No flicker above 10% Full Light Output, good dimming range. Possible minor pop-on.
OK	No flicker above 20% Full Light Output and/or minor flicker which is hard to find at one specific point above 20%. Some limit of dim-range. Relatively high pop-on position reducing mechanical range.
NR	Use of this dimmer/lamp combination not recommended for the quantity of lamps indicated (# or range) or at all (X).
	Lamp not yet tested with this dimmer, compatibility unknown.

¹ Audible noise may be observed when used with this dimmer, depending on the application.² This dimmer has low end trim adjustment that may be used for optimal performance.

WG = Warm Glow AF = Air Flux DS = Diamond Spark CC = Clear Classic DC = Die Cast DW = Direct White SO = Single Optic

Type A lamps

Number of bulbs

Type A lamps Number of bulbs									
			7W (40W Eq) A15 CC WG	7W (40W Eq) A19 CC WG	18W (100W Eq) A21 WG	6W (40 Eq) A19	6.5W (40W Eq) A19 WG		
Dimmer Company	Model No.		9290011818 (458760)	9290011815 (458737)	9290011741 (459107) 9290011741 (459115) 9290011741 (459123) 9290011741 (459131)	9290011348 (455808) 9290011348 (455782) 9290011348 (455790)	9290011178 (453209) 9290011178 (453274) 9290011178 (454058)	9290011347 (455774) 9290011347 (455766) 9290011347 (455741)	9290011176 (453316) 9290011176 (453183)
Leviton	6602	Professional Channel	1-21	1-21	1-8	1-12	1-23		
Leviton	6631								
Leviton	6633		1-21	1-21	1-8	1-12	1-23		
Leviton	6672		1-21	1-21	1-8	1-12	1-23		
Leviton	6674		1-21	1-21	1-8	1-12	1-23		
Leviton	6615P		1-11	1-11	1-8	1-12	1-7		
Leviton	DSE06								
Leviton	DSL06								
Leviton	DSM10								
Leviton	IPI06		1-21	1-21	1-8	1-12	1-23		
Leviton	IPL06								
Leviton	VPI06								
Lutron	AYCL-153P								
Lutron	CTCL-153P								
Lutron	CTCL-153PDH								
Lutron	DV-600P		1-21	1-21	1-8	1-12	1-23		
Lutron	DV-600PR								
Lutron	DVCL-153P								
Lutron	DVCL-253P								
Lutron	DVELV-300P		1-11	1-11	1-8	1-12	1-7		
Lutron	DVRP-253P								
Lutron	LGCL-153P								
Lutron	MACL-153M		1-21	1-21	1-8	1-12	1-23		
Lutron	MAELV-600								
Lutron	MALV-600								
Lutron	MRF2-6ND-120		1-15	1-15	1-8	1-12	1-23		
Lutron	NTCL-250								
Lutron	PD-5NE								
Lutron	PD-6WCL		1-21	1-21	1-8	1-12	1-23		
Lutron	RRD-3LD								
Lutron	RRD-6NA		NR	NR	1-8	1-12	1-23		
Lutron	S-600P								
Lutron	SCL-153P								
Lutron	SCL-153PR								
Lutron	SELV-300P								
Lutron	SLV-600P		1-16	1-16	1-8	1-12	1-10		
Lutron	TGCL-153PH								
Cooper	RI061-VW-K2								
Eaton	DAL06P								
Legrand	HCL453P								
Sensors									
Lutron	MSCL-OP153M		1-21	1-21	1-8	1-12	1-23		
Lutron	MSCL-OP153MH				1-8	1-12	1-23		
Lutron	MS-OPS2H		1-21	1-21	1-8	1-12	1-23		
Panel Modules									
Lutron	GP (Harrier) Card		1-21	1-21	1-22				
Lutron	HW-RPM-4A-120		1-21	1-21	1-22				
Lutron	HW-RPM-4U-120		1-21	1-21	1-22				
Lutron	LP-RPM-4U-120		1-21	1-21	1-22				

KEY (May exhibit one or several of the described parameters within the group)

Best	No flicker above 10% Full Light Output, good dimming range. Possible minor pop-on.
OK	No flicker above 20% Full Light Output and/or minor flicker which is hard to find at one specific point above 20%. Some limit of dim-range. Relatively high pop-on position reducing mechanical range.
NR	Use of this dimmer/lamp combination not recommended for the quantity of lamps indicated (# or range) or at all (X).
	Lamp not yet tested with this dimmer, compatibility unknown.

¹ Audible noise may be observed when used with this dimmer, depending on the application.² This dimmer has low end trim adjustment that may be used for optimal performance.

Type A lamps

Number of bulbs

Type A lamps Number of bulbs									
			9W (60W Eq) A19 5000K	9.5W A19 WG	10.5W (60W Eq) A19 Slim style	8W A19 Slim Style	11W (60W Eq) A19 Sultan		
Dimmer Company	Model No.		9290011346 (455881) 9290011346 (455907) 9290011346 (455899)	9290011346 (455873) 9290011177 (453282) 9290011177 (453241)	9290011345 (455824) 9290011345 (455865) 9290011345 (455857) 9290011345 (455840)	9290011345 (455831) 9290011345 (455832) 9290011345 (455816)	9290002709 (433235) 9290002709 (433151) 9290002707 (433227) 9290002707 (433144)	9290002706 (433219) 9290002706 (433136) 9290002704 (433201) 9290002704 (433128)	9290002296 (425264)
Leviton	6602	Professional Channel	1-15	1-15					
Leviton	6631								
Leviton	6633		1-15	1-15					
Leviton	6672		1-15	1-15					
Leviton	6674		1-15	1-15	1-14	1-18	1-4		
Leviton	6615P		1-8	1-8	1-5	1-8	1-4		
Leviton	DSE06								
Leviton	DSL06								
Leviton	DSM10								
Leviton	IPI06		1-15	1-15	1-14	1-18	NR		
Leviton	IPL06								
Leviton	VPI06								
Lutron	AYCL-153P						1-5		
Lutron	CTCL-153P						1-5		
Lutron	CTCL-153PDH								
Lutron	DV-600P		1-15	1-15	1-14	1-18	1-4		
Lutron	DV-600PR								
Lutron	DVCL-153P								
Lutron	DVCL-253P						1-5		
Lutron	DVELV-300P		1-8	1-8	1-5	1-8	1-6		
Lutron	DVRP-253P								
Lutron	LGCL-153P								
Lutron	MACL-153M		1-15	1-15	1-14	1-18	1-13		
Lutron	MAELV-600								
Lutron	MALV-600								
Lutron	MRF2-6ND-120		1-15	1-15	1-14	1-18	1-13		
Lutron	NTCL-250						1-5		
Lutron	PD-5NE								
Lutron	PD-6WCL		1-15	1-15					
Lutron	RRD-3LD								
Lutron	RRD-6NA		1-15	1-15	1-14	1-18	1-13		
Lutron	S-600P								
Lutron	SCL-153P				1-14	1-18	1-13		
Lutron	SCL-153PR								
Lutron	SELV-300P								
Lutron	SLV-600P		1-15	1-15	1-8	1-11	1-13		
Lutron	TGCL-153PH								
Cooper	RI061-VW-K2						1-2		
Eaton	DAL06P								
Legrand	HCL453P								
Sensors									
Lutron	MSCL-OP153M		1-15	1-15	1-14	1-18	1-13		
Lutron	MSCL-OP153MH		1-15	1-15					
Lutron	MS-OPS2H		1-15	1-15					
Panel Modules									
Lutron	GP (Harrier) Card			1-19					
Lutron	HW-RPM-4A-120								
Lutron	HW-RPM-4U-120								
Lutron	LP-RPM-4U-120								

KEY (May exhibit one or several of the described parameters within the group)

Best	No flicker above 10% Full Light Output, good dimming range. Possible minor pop-on.
OK	No flicker above 20% Full Light Output and/or minor flicker which is hard to find at one specific point above 20%. Some limit of dim-range. Relatively high pop-on position reducing mechanical range.
NR	Use of this dimmer/lamp combination not recommended for the quantity of lamps indicated (# or range) or at all (X).
	Lamp not yet tested with this dimmer, compatibility unknown.

¹ Audible noise may be observed when used with this dimmer, depending on the application.² This dimmer has low end trim adjustment that may be used for optimal performance.

WG = Warm Glow AF = Air Flux DS = Diamond Spark CC = Clear Classic DC = Die Cast DW = Direct White SO = Single Optic

Type A lamps

Number of bulbs

Type A lamps									
Number of bulbs			22W (100W Eq) A21	11W (60W Eq) A19 Sultan	8W (40W Eq) A19 Sultan	17W (75W Eq) A21 Prince	7W (40W Eq) A15 CC WG	7W (40W Eq) A19 CC WG	
Dimmer Company	Model No.		9290002290 (423525) 9290002290 (424432)	9290002268 (429258)	9290002267 (423483) 9290002267 (424374) 9290002267 (429266)	9290002018 (422220) 17E26A21D (418590)	9290011818 (458778)	9290011815 (458745)	
Leviton	6602	Professional Channel					1-21	1-21	
Leviton	6631								
Leviton	6633						1-21	1-21	
Leviton	6672						1-21	1-21	
Leviton	6674		NR	1-4	NR	1-8	1-21	1-21	
Leviton	6615P		NR	1-4	1-9	1-4	1-11	1-11	
Leviton	DSE06								
Leviton	DSL06								
Leviton	DSM10								
Leviton	IPI06		1-6	NR	1-9	1-8	1-21	1-21	
Leviton	IPL06								
Leviton	VPI06								
Lutron	AYCL-153P			1-5		1-8			
Lutron	CTCL-153P			1-5		1-8			
Lutron	CTCL-153PDH								
Lutron	DV-600P		NR	1-4	1-6	1-8	1-21	1-21	
Lutron	DV-600PR								
Lutron	DVCL-153P								
Lutron	DVCL-253P			1-5		1-8			
Lutron	DVELV-300P		NR	1-6	1-9	1-4	1-11	1-11	
Lutron	DVRP-253P								
Lutron	LGCL-153P								
Lutron	MACL-153M		1-6	1-13	1-12	1-8	1-21	1-21	
Lutron	MAELV-600		1-6						
Lutron	MALV-600								
Lutron	MRF2-6ND-120		1-6	1-13	1-12	1-8	1-15	1-15	
Lutron	NTCL-250			1-5		1-8			
Lutron	PD-5NE								
Lutron	PD-6WCL						1-21	1-21	
Lutron	RRD-3LD								
Lutron	RRD-6NA		1-6	1-13	1-13	1-8	NR	NR	
Lutron	S-600P					1-8			
Lutron	SCL-153P			1-13	1-18				
Lutron	SCL-153PR								
Lutron	SELV-300P		1-6			1-8			
Lutron	SLV-600P		1-6	1-13	1-12	1-4	1-16	1-16	
Lutron	TGCL-153PH								
Cooper	RI061-VW-K2		NR	1-2					
Eaton	DAL06P								
Legrand	HCL453P								
Sensors									
Lutron	MSCL-OP153M		1-6	1-13	1-12	1-8	1-21	1-21	
Lutron	MSCL-OP153MH				1-18				
Lutron	MS-OPS2H				1-18		1-21	1-21	
Panel Modules									
Lutron	GP (Harrier) Card						1-21	1-21	
Lutron	HW-RPM-4A-120						1-21	1-21	
Lutron	HW-RPM-4U-120						1-21	1-21	
Lutron	LP-RPM-4U-120						1-21	1-21	

KEY (May exhibit one or several of the described parameters within the group)

Best	No flicker above 10% Full Light Output, good dimming range. Possible minor pop-on.
OK	No flicker above 20% Full Light Output and/or minor flicker which is hard to find at one specific point above 20%. Some limit of dim-range. Relatively high pop-on position reducing mechanical range.
NR	Use of this dimmer/lamp combination not recommended for the quantity of lamps indicated (# or range) or at all (X).
	Lamp not yet tested with this dimmer, compatibility unknown.

¹ Audible noise may be observed when used with this dimmer, depending on the application.² This dimmer has low end trim adjustment that may be used for optimal performance.

Type A lamps

Number of bulbs

					
		10W A19 L Prize	8W(40W Eq)A19Remote Phosphor	12.5W(60W Eq)A19 Remote Phosphor	8W A19
Dimmer Company	Model No.	420075	414839	409946	409938
Leviton	6602				
Leviton	6631				NR
Leviton	6633				
Leviton	6672				
Leviton	6674	1	1-4	1-12	1-14
Leviton	6615P	1-4	NR	1-12	NR
Leviton	DSE06				
Leviton	DSL06				
Leviton	DSM10				
Leviton	IPI06	1-2	NR	1-12	1-16
Leviton	IPL06				
Leviton	VPI06				
Lutron	AYCL-153P				1-4
Lutron	CTCL-153P				1-4
Lutron	CTCL-153PDH				
Lutron	DV-600P	1-4	NR	1-8	1-16
Lutron	DV-600PR				
Lutron	DVCL-153P				
Lutron	DVCL-253P				1-4
Lutron	DVELV-300P	1-5	1-18	1-12	1-9
Lutron	DVRP-253P				
Lutron	LGCL-153P				
Lutron	MACL-153M	1-9	NR	1-12	NR
Lutron	MAELV-600				1-16
Lutron	MALV-600				NR
Lutron	MRF2-6ND-120	1-11	NR	1-12	NR
Lutron	NTCL-250				1-4
Lutron	PD-5NE				
Lutron	PD-6WCL				
Lutron	RRD-3LD				
Lutron	RRD-6NA	1-9	1-16	1-12	1-16
Lutron	S-600P	NR	NR		
Lutron	SCL-153P		1-8		
Lutron	SCL-153PR				
Lutron	SELV-300P				
Lutron	SLV-600P	1-4	NR	NR	1-16
Lutron	TGCL-153PH				
Cooper	RI061-VW-K2	NR	1-4		1-16
Eaton	DAL06P				
Legrand	HCL453P				
Sensors					
Lutron	MSCL-OP153M	1-9	NR	1-12	NR
Lutron	MSCL-OP153MH				
Lutron	MS-OPS2H				
Panel Modules					
Lutron	GP (Harrier) Card				
Lutron	HW-RPM-4A-120				
Lutron	HW-RPM-4U-120				
Lutron	LP-RPM-4U-120				

KEY (May exhibit one or several of the described parameters within the group)

Best	No flicker above 10% Full Light Output, good dimming range. Possible minor pop-on.
OK	No flicker above 20% Full Light Output and/or minor flicker which is hard to find at one specific point above 20%. Some limit of dim-range. Relatively high pop-on position reducing mechanical range.
NR	Use of this dimmer/lamp combination not recommended for the quantity of lamps indicated (# or range) or at all (X).
	Lamp not yet tested with this dimmer, compatibility unknown.

¹ Audible noise may be observed when used with this dimmer, depending on the application.² This dimmer has low end trim adjustment that may be used for optimal performance.

WG = Warm Glow AF = Air Flux DS = Diamond Spark CC = Clear Classic DC = Die Cast DW = Direct White SO = Single Optic

PAR lamps

Number of bulbs

									
			6PAR38/90W/UE/930/40D/D/G/ULW/E26/T20	4GU10/LED/930/F35/DIM/G/120V T20 10/1	4GU10/LED/927-22/F35/G/WG/T20 10/1	10PAR30S-L/EXPERTCOLOR/Fxx/9xx/P/D/T/JA8	10PAR30S-L/EXPERTCOLOR RETAIL/Fxx-Sxx/9xx/D		
Dimmer Company	Model No.		9290037408 (586446)	9290020555 (468140)	9290020553 (471565)	9290045790 (590216) 9290037558 (587642) 9290037557 (587634)	9290037556 (587626) 9290037555 (587618) 9290037554 (587600)	9290037553 (587592) 9290037552 (587584) 9290037551 (587576)	9290037550 (587568) 9290037549 (587550) 9290037548 (587543)
Leviton	6602	Professional Channel	1-20	1-20	1-20		1-15	1-15	
Leviton	6631		1-20	1-20	1-20		1-15	1-15	
Leviton	6633		1-20	1-20	1-20		1-15	1-15	
Leviton	6672		1-20	1-20	1-20		1-15	1-15	
Leviton	6674		1-20	1-20	1-20		1-15	1-15	
Leviton	6615P		2-20	NR	NR		1-8	1-8	
Leviton	DSE06		1-20	1-20	1-20		1-20	1-20	
Leviton	DSL06		1-20	1-20	1-20		1-20	1-20	
Leviton	DSM10		1-20	1-20	1-20		1-20	1-20	
Leviton	IPI06		1-20	1-20	1-20		1-15	1-15	
Leviton	IPL06		1-20	1-20	1-20		1-15	1-15	
Leviton	VPI06		1-20	1-20	NR		1-15	1-15	
Lutron	AYCL-153P		1-20	1-20	1-20		1-15	1-15	
Lutron	CTCL-153P		1-20	1-20	1-20		1-15	1-15	
Lutron	CTCL-153PDH		1-20	NR	1-20		1-15	1-15	
Lutron	DV-600P		1-20	1-20	1-20		1-15	1-15	
Lutron	DV-600PR		1-20	1-20	1-20		1-15	1-15	
Lutron	DVCL-153P		1-20	1-20	1-20		1-15	1-15	
Lutron	DVCL-253P		1-20	1-20	1-20		1-15	1-15	
Lutron	DVELV-300P		1-10	1-20	1-20		1-8	1-8	
Lutron	DVRP-253P		1-20	NR	NR		1-20	1-20	
Lutron	LGCL-153P		1-20	1-20	1-20		1-15	1-15	
Lutron	MACL-153M		1-20	1-20	1-20		1-15	1-15	
Lutron	MAELV-600		1-20	1-20	1-20		1-20	1-20	
Lutron	MALV-600		4-18	NR	NR		NR	NR	
Lutron	MRF2-6ND-120		1-20	1-20	1-20		1-15	1-15	
Lutron	NTCL-250		1-20	1-20	1-20		1-15	1-15	
Lutron	PD-5NE		1-18	1-20	NR		1-20	1-20	
Lutron	PD-6WCL		1-20	1-20	1-20		1-15	1-15	
Lutron	RRD-3LD		1-13	1-20	1-19		1-8	1-8	
Lutron	RRD-6NA		1-20	1-20	1-20		1-15	1-15	
Lutron	S-600P		1-20	1-20	1-20		1-15	1-15	
Lutron	SCL-153P		1-20	1-20	1-20		1-15	1-15	
Lutron	SCL-153PR		1-5	1-9	1-9		1-3	1-3	
Lutron	SELV-300P		1-20	1-19	1-20		1-8	1-8	
Lutron	SLV-600P		1-20	1-20	1-20		1-10	1-10	
Lutron	TGCL-153PH		1-20	1-20	1-20		1-15	1-15	
Eaton	RI061-VW-K2		1-20	1-20	1-20		1-15	1-15	
Eaton	DAL06P		1-20	1-20	1-20		1-20	1-20	
Legrand	HCL453P		1-3	1-20	NR		1-20	1-20	
Sensors									
Lutron	MSCL-OP153M		1-20	1-20	NR		1-15	1-15	
Lutron	MSCL-OP153MH		1-20	1-20	1-20		1-10	1-10	
Lutron	MS-OPS2H		1-18	1-20	1-20		1-15	1-15	
Panel Modules									
Lutron	GP (Harrier) Card		1-18	NR	NR		1-20	1-20	
Lutron	HW-RPM-4A-120		1-18	1-20	1-20		1-20	1-20	
Lutron	HW-RPM-4U-120		1-18	1-20	1-20		1-20	1-20	
Lutron	LP-RPM-4U-120		1-18	1-20	1-20		1-20	1-20	

KEY (May exhibit one or several of the described parameters within the group)	
Best	No flicker above 10% Full Light Output, good dimming range. Possible minor pop-on.
OK	No flicker above 20% Full Light Output and/or minor flicker which is hard to find at one specific point above 20%. Some limit of dim-range. Relatively high pop-on position reducing mechanical range.
NR	Use of this dimmer/lamp combination not recommended for the quantity of lamps indicated (# or range) or at all (X).
	Lamp not yet tested with this dimmer, compatibility unknown.

¹ Audible noise may be observed when used with this dimmer, depending on the application.

² This dimmer has low end trim adjustment that may be used for optimal performance.

WG = Warm Glow AF = Air Flux DS = Diamond Spark CC = Clear Classic DC = Die Cast DW = Direct White SO = Single Optic

PAR lamps

Number of bulbs

											
		14PAR38/EXPERTCOLOR/Fxx-Sxx/ 9xx/P/D/T20/JA8		14PAR38/EXPERTCOLOR RETAIL/ Fxx-Sxx/9xx/P/D		8.5PAR30S/COR/9xx/Fxx/D/P/ULW/ T20 6/1FB		8.5PAR30L/COR/9xx/Fxx/D/P/ULW/ T20 6/1FB		5.5PAR20/COR/Fxx/9xx/DIM/P/ T20 6/1FB	
Dimmer Company	Model No.	9290037547 (587535) 9290037544 (587501) 9290037546 (587527) 9290037543 (587493) 9290037545 (587519) 9290037542 (587485)		9290037541 (587477) 9290037540 (587469) 9290037539 (587451) 9290037538 (587444)		9290037537 (587436) 9290037536 (587428) 9290037392 (586347) 9290037391 (586339)		9290037535 (587410) 9290037534 (587402) 9290037387 (586297) 9290037384 (586263)		9290037398 (586404) 9290037397 (586396) 9290037396 (586388) 9290037395 (586370)	
Leviton	6602	1-10		1-10		1-20		1-20		1-20	
Leviton	6631	1-10		1-10		1-20		1-20		1-20	
Leviton	6633	1-10		1-10		1-20		1-20		1-20	
Leviton	6672	1-10		1-10		1-20		1-20		1-20	
Leviton	6674	1-10		1-10		1-20		1-20		1-20	
Leviton	6615P	1-5		1-5		NR		NR		1-14	
Leviton	DSE06	1-20		1-20		1-20		1-20		1-20	
Leviton	DSL06	1-20		1-20		1-20		1-20		1-20	
Leviton	DSM10	1-20		1-20		1-20		1-20		1-20	
Leviton	IPI06	1-10		1-10		1-20		1-20		1-20	
Leviton	IPL06	1-10		1-10		1-20		1-20		1-20	
Leviton	VPI06	1-10		1-10		1-20		1-20		1-20	
Lutron	AYCL-153P	1-10		1-10		1-20		1-20		1-20	
Lutron	CTCL-153P	1-10		1-10		1-20		1-20		1-20	
Lutron	CTCL-153PDH	1-10		1-10		1-20		1-20		1-20	
Lutron	DV-600P	1-20		1-20		1-20		1-20		1-20	
Lutron	DV-600PR	1-10		1-10		1-20		1-20		1-20	
Lutron	DVCL-153P	1-10		1-10		1-20		1-20		1-20	
Lutron	DVCL-253P	1-10		1-10		1-20		1-20		1-20	
Lutron	DVELV-300P	1-5		1-5		1-20		1-20		1-20	
Lutron	DVRP-253P	1-15		1-15		1-20		1-20		1-20	
Lutron	LGCL-153P	1-10		1-10		1-20		1-20		1-20	
Lutron	MACL-153M	1-10		1-10		1-20		1-20		1-20	
Lutron	MAELV-600	1-20		1-20		1-20		1-20		1-20	
Lutron	MALV-600	1-15		1-15		NR		NR		NR	
Lutron	MRF2-6ND-120	1-10									

PAR lamps

Number of bulbs

								
			5.5PAR20/COR/Fxx/927-922/ DIM/P/ T20 6/1FB	10PAR38/COR/9xx/Fxx/DIM/P/ ULW/T20 6/1FB	13PAR38/COR/9xx/Fxx/DIM/P/ULW/T20 6/1FB	27PAR38TrueF 8xx Fxx DIM 120V-277V 6/1FB	33PAR38/PER/8xx/Sxx-Fxx/ DIM/120V 6/1FB	
Dimmer Company	Model No.		9290037394 (586362) 9290037393 (586354)	9290037383 (586255) 9290037380 (586222) 9290037382 (586248) 9290037379 (586214) 9290037381 (586230)	9290037378 (586206) 9290037377 (586198) 9290037376 (586180) 9290037372 (586149) 9290037375 (586172) 9290037371 (586131)	9290037374 (586164) 9290037373 (586156) 9290037370 (586123) 9290037369 (586115)	9290030636 (569731) 9290030635 (569723)	9290019208-Phase out 9290019197 (534636) 9290019196 (534628) 9290019169 (534610) 9290019168 (534602)
Leviton	6602	Professional Channel	1-20	1-15	1-20	NR	1-5	
Leviton	6631		1-20	1-15	1-20	NR	1-5	
Leviton	6633		1-20	1-15	1-20	NR	1-5	
Leviton	6672		1-20	1-15	1-20	NR	1-5	
Leviton	6674		1-20	1-15	1-20	NR	1-5	
Leviton	6615P		NR	1-8	1-14	1-3	1-2	
Leviton	DSE06		1-20	1-20	1-20	1-5	1-5	
Leviton	DSL06		1-20	1-20	1-20	NR	1-5	
Leviton	DSM10		1-20	1-20	1-20	NR	1-5	
Leviton	IPI06		1-20	1-15	1-20	NR	1-5	
Leviton	IPL06		1-20	1-15	1-20	NR	1-5	
Leviton	VPI06		1-20	1-15	1-20	NR	1-5	
Lutron	AYCL-153P		1-20	1-15	1-10	NR	1-5	
Lutron	CTCL-153P		1-20	1-15	1-10	NR	1-5	
Lutron	CTCL-153PDH		1-20	1-15	1-20	NR	NR	
Lutron	DV-600P		1-20	1-15	1-20	NR	1-5	
Lutron	DV-600PR		1-20	1-15	1-20	NR	1-5	
Lutron	DVCL-153P		1-20	1-15	1-20	NR	1-5	
Lutron	DVCL-253P		1-20	1-15	1-10	NR	1-5	
Lutron	DVELV-300P		1-20	1-8	1-20	1-3	1-2	
Lutron	DVRP-253P		1-20	1-20	1-20	1-5	1-5	
Lutron	LGCL-153P		1-20	1-15	1-20	NR	NR	
Lutron	MACL-153M		1-20	1-15	1-20	NR	1-5	
Lutron	MAELV-600		1-20	1-20	1-20	NR	1-5	
Lutron	MALV-600		NR	NR	NR	NR	1-5	
Lutron	MRF2-6ND-120		NR	NR	NR	NR	1-5	
Lutron	NTCL-250		1-20	1-15	1-10	NR	1-5	
Lutron	PD-5NE		1-20	1-20	1-19	NR	1-5	
Lutron	PD-6WCL		1-20	1-15	1-20	NR	1-5	
Lutron	RRD-3LD		1-20	1-8	1-6	NR	1-2	
Lutron	RRD-6NA		1-20	1-15	1-20	NR	1-5	
Lutron	S-600P		1-20	1-15	1-20	NR	1-5	
Lutron	SCL-153P		1-20	1-15	1-10	NR	1	
Lutron	SCL-153PR		1-7	1-4	1-20	NR	1	
Lutron	SELV-300P		1-14	1-8	1-20	1-3	1-2	
Lutron	SLV-600P		1-20	1-11	1-8	NR	1-3	
Lutron	TGCL-153PH		1-20	1-15	1-20	NR	1-5	
Eaton	RI061-VW-K2		1-20	1-15	1-20	NR	1-5	
Eaton	DAL06P		1-20	1-20	1-20	NR	1-5	
Legrand	HCL453P		1-20	1-20	1-20	NR	1-5	
Sensors								
Lutron	MSCL-OP153M		1-20	1-15	1-20	NR	1-5	
Lutron	MSCL-OP153MH		NR	NR	NR	NR	1-5	
Lutron	MS-OPS2H		1-20	1-15	1-12	1-5	1-5	
Panel Modules								
Lutron	GP (Harrier) Card		NR	NR	NR	NR	NR	
Lutron	HW-RPM-4A-120		1-20	1-20	1-20	NR	1-5	
Lutron	HW-RPM-4U-120		1-20	1-20	1-20	NR	1-5	
Lutron	LP-RPM-4U-120		1-20	1-20	1-20	NR	1-5	

KEY (May exhibit one or several of the described parameters within the group)

Best	No flicker above 10% Full Light Output, good dimming range. Possible minor pop-on.
OK	No flicker above 20% Full Light Output and/or minor flicker which is hard to find at one specific point above 20%. Some limit of dim-range. Relatively high pop-on position reducing mechanical range.
NR	Use of this dimmer/lamp combination not recommended for the quantity of lamps indicated (# or range) or at all (X).
	Lamp not yet tested with this dimmer, compatibility unknown.

¹ Audible noise may be observed when used with this dimmer, depending on the application.² This dimmer has low end trim adjustment that may be used for optimal performance.

PAR lamps

Number of bulbs

									
			9.4PAR30S/COR/935/F25/DIM/ 120V/T20 6/1FB	14PAR38/COR/9xx/F25/DIM/ 120V/T20 6/1FB	14PAR38/COR/930/F25/D/P/B/ ULW/T20 6/1FB	13PAR38/LED/950/F25/DIM/GULW/ T20 6/1FB	10PAR38/LED/9xx/Fxx/DIM/GULW/ T20 6/1FB		
Dimmer Company	Model No.		9290034669 (577759)	9290034668 (577742) 9290034667 (577734)	9290031338 (576470)	9290030303 (567818) 9290030300 (567792) 9290030299 (567784)	9290030298 (567776) 9290030296 (567768) 9290030295 (567750)	9290030293 (567917) 9290030292 (567933) 9290030290 (567891) 9290030289 (567883)	9290030288 (567875) 9290030287 (567925) 9290030286 (567867) 9290030285 (567859)
Leviton	6602	Professional Channel	1-10	1-10	1-5				
Leviton	6631		1-10	1-10					
Leviton	6633		1-10	1-10	1-5	1-10	1-15		
Leviton	6672		1-10	1-10	1-5				
Leviton	6674		1-10	1-10		1-10	1-15		
Leviton	6615P		NR	NR	1-5				
Leviton	DSE06								
Leviton	DSL06		1-10	1-10		1-10	1-15		
Leviton	DSM10								
Leviton	IPI06		NR	NR	1-5	1-10	1-15		
Leviton	IPL06		1-10	1-10					
Leviton	VPI06								
Lutron	AYCL-153P		1-10	1-10		1-10	1-15		
Lutron	CTCL-153P		1-10	1-10		1-10	1-15		
Lutron	CTCL-153PDH								
Lutron	DV-600P		1-10	1-10	1-5	1-10	1-15		
Lutron	DV-600PR								
Lutron	DVCL-153P		1-10	1-10		1-10	1-15		
Lutron	DVCL-253P		1-10	1-10		1-10	1-15		
Lutron	DVELV-300P				1-5	1-5	1-8		
Lutron	DVRP-253P								
Lutron	LGCL-153P								
Lutron	MACL-153M		1-10	1-10	1-5				
Lutron	MAELV-600								
Lutron	MALV-600								
Lutron	MRF2-6ND-120		1-10	1-10	1-5	1-10	1-15		
Lutron	NTCL-250		1-10	1-10		1-10	1-15		
Lutron	PD-5NE								
Lutron	PD-6WCL		1-10	1-10	1-5				
Lutron	RRD-3LD								
Lutron	RRD-6NA								
Lutron	S-600P								
Lutron	SCL-153P		1-10	1-10		1-10	1-15		
Lutron	SCL-153PR								
Lutron	SELV-300P								
Lutron	SLV-600P		1-10	1-8	1-5	1-8	1-10		
Lutron	TGCL-153PH								
Eaton	RI061-VW-K2								
Eaton	DAL06P								
Legrand	HCL453P								
Sensors									
Lutron	MSCL-OP153M		1-10	1-10	1-5				
Lutron	MSCL-OP153MH		1-10	1-10		1-10	1-15		
Lutron	MS-OPS2H								
Panel Modules									
Lutron	GP (Harrier) Card								
Lutron	HW-RPM-4A-120								
Lutron	HW-RPM-4U-120					#VALUE!			
Lutron	LP-RPM-4U-120								

KEY (May exhibit one or several of the described parameters within the group)

Best	No flicker above 10% Full Light Output, good dimming range. Possible minor pop-on.
OK	No flicker above 20% Full Light Output and/or minor flicker which is hard to find at one specific point above 20%. Some limit of dim-range. Relatively high pop-on position reducing mechanical range.
NR	Use of this dimmer/lamp combination not recommended for the quantity of lamps indicated (# or range) or at all (X).
	Lamp not yet tested with this dimmer, compatibility unknown.

¹ Audible noise may be observed when used with this dimmer, depending on the application.² This dimmer has low end trim adjustment that may be used for optimal performance.

WG = Warm Glow AF = Air Flux DS = Diamond Spark CC = Clear Classic DC = Die Cast DW = Direct White SO = Single Optic

PAR lamps

Number of bulbs

								
			PAR38 13W JA8	8.5PAR30S/LED/9xx/F25/DIM/GULW/T20 6/1FB	8.5PAR30L/LED/9xx/Fxx/DIM/GULW/T20 6/1FB	5.5PAR20/LED/F40/9xx/DIM/G/T20 6/1FB	5.5PAR20/LED/F25/927-922/DIM/G/T20 6/1FB	
Dimmer Company	Model No.		9290030297 (567834) 9290030302 (567842)	9290030282 (568055) 9290030278 (568014) 9290030277 (568006)	9290030280 (568030) 9290030279 (568022) 9290030274 (567999) 9290030272 (567973)	9290030265 (568097) 9290030261 (568063)	9290030263 (568105)	
Leviton	6602	Professional Channel						
Leviton	6631							
Leviton	6633		1-10	1-15	1-15	1-20	1-20	
Leviton	6672							
Leviton	6674		1-10	1-15	1-15	1-20	1-20	
Leviton	6615P							
Leviton	DSE06							
Leviton	DSL06		1-10	1-15	1-15	1-20	1-20	
Leviton	DSM10							
Leviton	IPI06		1-10	1-15	1-15	1-20	1-20	
Leviton	IPL06							
Leviton	VPI06							
Lutron	AYCL-153P		1-10	1-15	1-15	1-20	1-20	
Lutron	CTCL-153P		1-10	1-15	1-15	1-20	1-20	
Lutron	CTCL-153PDH							
Lutron	DV-600P		1-10	1-15	1-15	1-20	1-20	
Lutron	DV-600PR							
Lutron	DVCL-153P		1-10	1-15	1-15	1-20	1-20	
Lutron	DVCL-253P		1-10	1-15	1-15	1-20	1-20	
Lutron	DVELV-300P		1-5	1-8	1-8	1-10	1-10	
Lutron	DVRP-253P							
Lutron	LGCL-153P							
Lutron	MACL-153M							
Lutron	MAELV-600							
Lutron	MALV-600							
Lutron	MRF2-6ND-120		1-10	1-15	1-15	1-20	1-20	
Lutron	NTCL-250		1-10	1-15	1-15	1-20	1-20	
Lutron	PD-5NE							
Lutron	PD-6WCL							
Lutron	RRD-3LD							
Lutron	RRD-6NA							
Lutron	S-600P							
Lutron	SCL-153P		1-10	1-15	1-15	1-20	1-20	
Lutron	SCL-153PR							
Lutron	SELV-300P							
Lutron	SLV-600P		1-8	1-10	1-10	1-15	1-15	
Lutron	TGCL-153PH							
Eaton	RI061-VW-K2							
Eaton	DAL06P							
Legrand	HCL453P							
Sensors								
Lutron	MSCL-OP153M							
Lutron	MSCL-OP153MH		1-10	1-15	1-15	1-20	1-20	
Lutron	MS-OPS2H							
Panel Modules								
Lutron	GP (Harrier) Card							
Lutron	HW-RPM-4A-120							
Lutron	HW-RPM-4U-120							
Lutron	LP-RPM-4U-120							

KEY (May exhibit one or several of the described parameters within the group)

Best	No flicker above 10% Full Light Output, good dimming range. Possible minor pop-on.
OK	No flicker above 20% Full Light Output and/or minor flicker which is hard to find at one specific point above 20%. Some limit of dim-range. Relatively high pop-on position reducing mechanical range.
NR	Use of this dimmer/lamp combination not recommended for the quantity of lamps indicated (# or range) or at all (X).
	Lamp not yet tested with this dimmer, compatibility unknown.

¹ Audible noise may be observed when used with this dimmer, depending on the application.² This dimmer has low end trim adjustment that may be used for optimal performance.

PAR lamps

Number of bulbs

													
			PAR20 5.5W JA8	17W PAR38 SO/Expert color, 14WPAR38 T20, 10W PAR38 T20				12W PAR30L Expert color, 9.4W PAR30L & PAR30S T20			12W PAR30S AF SO/ Expert color		
Dimmer Company	Model No.		9290030262 (568071)	9290022383 (551895) 9290022382 (551887) 9290020451 (546937) 9290020450 (546929)	9290019092 (546937) 9290019091 (546929) 9290018538 (546950) 9290018537 (546945)	9290013698 (471797) 9290013398 (470864) 9290013394 (470823) 9290011138 (435420)	9290011137 (435412) 9290011135 (435396) 9290011131 (435354)	9290020457 (546993) 9290020456 (546985) 9290020455 (546977) 9290020454 (546969)	9290013412 (470988) 9290013411 (470970) 9290013410 (470962) 9290013409 (470954)	9290012858 (471052) 9290012857 (471045) 9290012856 (471037)	9290013697 (471789) 9290013407 (470930) 9290013406 (470922) 9290013402 (478989)	9290012862 (471094) 9290011129 (435339) 9290011126 (435305)	9290011123 (435271) 9290011122 (435263) 9290011125 (435297)
Leviton	6602	Professional Channel		1-8				1-8			1-12		
Leviton	6631												
Leviton	6633		1-20	1-8				1-8			1-8		
Leviton	6672			1-8				1-8			1-8		
Leviton	6674		1-20					1-8			1-8		
Leviton	6615P			1-4				1-5			1-4		
Leviton	DSE06												
Leviton	DSL06		1-20					1-8			1-8		
Leviton	DSM10												
Leviton	IPI06		1-20	1-8				1-8			1-8		
Leviton	IPL06												
Leviton	VPI06												
Lutron	AYCL-153P		1-20										
Lutron	CTCL-153P		1-20										
Lutron	CTCL-153PDH												
Lutron	DV-600P		1-20	1-8				1-8			1-12		
Lutron	DV-600PR												
Lutron	DVCL-153P		1-20										
Lutron	DVCL-253P		1-20										
Lutron	DVELV-300P		1-10	1-4				1-5			1-4		
Lutron	DVRP-253P												
Lutron	LGCL-153P												
Lutron	MACL-153M			1-8				1-8			1-12		
Lutron	MAELV-600												
Lutron	MALV-600												
Lutron	MRF2-6ND-120		1-20	1-8				1-8			1-8		
Lutron	NTCL-250		1-20										
Lutron	PD-5NE												
Lutron	PD-6WCL			1-8				1-8			1-12		
Lutron	RRD-3LD												
Lutron	RRD-6NA							1-8			1-8		
Lutron	S-600P												
Lutron	SCL-153P		1-20										
Lutron	SCL-153PR												
Lutron	SELV-300P												
Lutron	SLV-600P		1-15	1-5				1-8			1-8		
Lutron	TGCL-153PH												
Eaton	RI061-VW-K2												
Eaton	DAL06P												
Legrand	HCL453P												
Sensors													
Lutron	MSCL-OP153M			1-8				1-8			1-12		
Lutron	MSCL-OP153MH		1-20	1-8				1-8			1-8		
Lutron	MS-OPS2H			1-8				1-8			1-8		
Panel Modules													
Lutron	GP (Harrier) Card			1-8									
Lutron	HW-RPM-4A-120												
Lutron	HW-RPM-4U-120												
Lutron	LP-RPM-4U-120												

KEY (May exhibit one or several of the described parameters within the group)

Best	No flicker above 10% Full Light Output, good dimming range. Possible minor pop-on.
OK	No flicker above 20% Full Light Output and/or minor flicker which is hard to find at one specific point above 20%. Some limit of dim-range. Relatively high pop-on position reducing mechanical range.
NR	Use of this dimmer/lamp combination not recommended for the quantity of lamps indicated (# or range) or at all (X).
	Lamp not yet tested with this dimmer, compatibility unknown.

¹ Audible noise may be observed when used with this dimmer, depending on the application.² This dimmer has low end trim adjustment that may be used for optimal performance.

WG = Warm Glow AF = Air Flux DS = Diamond Spark CC = Clear Classic DC = Die Cast DW = Direct White SO = Single Optic

PAR lamps

Number of bulbs

PAR lamps Number of bulbs								
			14PAR38/COR/930/F25-F40/DIM/ 120V T20 6/1FB	8.5PAR20/PER/9xx/Fxx/DIM/EC/ 120V 6/1FB	12PAR30S/EXPERTCOLOR/F25/ 9xx/DIM	17PAR38/EXPERTCOLOR/F40/ 9xx/DIM	17PAR38/EXPERTCOLOR RETAIL/ S8/9xx/DIM	
Dimmer Company	Model No.		9290020453 (546950) 9290020452 (546945)	9290019225 (535336) 9290019224 (535328) 9290019223 (535310) 9290019222 (535300)	9290019221 (535294) 9290019220 (535286) 9290019219 (535278) 9290019218 (535260)	9290013408 (470948) 9290013404 (470914) 9290013403 (470906)	9290013401 (470880) 9290013400 (470872) 9290013396 (470849)	9290013395 (470831) 9290012855 (471029) 9290012852 (470996) 9290012854 (471011)
Leviton	6602	Professional Channel	1-8	5-15	1-12	1-8	1-8	
Leviton	6631							
Leviton	6633		1-8	1-15	1-8	1-8	1-8	
Leviton	6672		1-8	1-15	1-8	1-8	1-8	
Leviton	6674			1-15	1-8			
Leviton	6615P		1-4	1-8	1-4	1-4	1-4	
Leviton	DSE06							
Leviton	DSL06			1-15	1-8			
Leviton	DSM10							
Leviton	IPI06		1-8	1-15	1-8	1-8	1-8	
Leviton	IPL06							
Leviton	VPI06							
Lutron	AYCL-153P			1-3				
Lutron	CTCL-153P			1-3				
Lutron	CTCL-153PDH							
Lutron	DV-600P		1-8	1-15	1-12	1-8	1-8	
Lutron	DV-600PR							
Lutron	DVCL-153P			1-3				
Lutron	DVCL-253P			1-3				
Lutron	DVELV-300P		1-4	1-8	1-4	1-4	1-4	
Lutron	DVRP-253P							
Lutron	LGCL-153P							
Lutron	MACL-153M		1-8	1-15	1-12	1-8	1-8	
Lutron	MAELV-600							
Lutron	MALV-600							
Lutron	MRF2-6ND-120		1-8	1-15	1-8	1-8	1-8	
Lutron	NTCL-250			1-3				
Lutron	PD-5NE							
Lutron	PD-6WCL		1-8	1-15	1-12	1-8	1-8	
Lutron	RRD-3LD							
Lutron	RRD-6NA			1-15	1-8			
Lutron	S-600P							
Lutron	SCL-153P			1-3				
Lutron	SCL-153PR							
Lutron	SELV-300P							
Lutron	SLV-600P		1-5	1-13	1-8	1-5	1-5	
Lutron	TGCL-153PH							
Eaton	RI061-VW-K2							
Eaton	DAL06P							
Legrand	HCL453P							
Sensors								
Lutron	MSCL-OP153M		1-8	1-15	1-12	1-8	1-8	
Lutron	MSCL-OP153MH		1-8	1-15	1-8	1-8	1-8	
Lutron	MS-OPS2H		1-8	1-15	1-8	1-8	1-8	
Panel Modules								
Lutron	GP (Harrier) Card		1-8	1-15		1-8	1-8	
Lutron	HW-RPM-4A-120			1-15				
Lutron	HW-RPM-4U-120			1-15				
Lutron	LP-RPM-4U-120			1-15				

KEY (May exhibit one or several of the described parameters within the group)

Best	No flicker above 10% Full Light Output, good dimming range. Possible minor pop-on.
OK	No flicker above 20% Full Light Output and/or minor flicker which is hard to find at one specific point above 20%. Some limit of dim-range. Relatively high pop-on position reducing mechanical range.
NR	Use of this dimmer/lamp combination not recommended for the quantity of lamps indicated (# or range) or at all (X).
	Lamp not yet tested with this dimmer, compatibility unknown.

¹ Audible noise may be observed when used with this dimmer, depending on the application.² This dimmer has low end trim adjustment that may be used for optimal performance.

PAR lamps
Number of bulbs

PAR lamps													
Number of bulbs				120V Gen2 Glass PAR30L 10-75W	120V Gen2 Glass PAR30S 10-75W	120V Gen2 Glass PAR38 12-90W	120V Gen2 Glass PAR38 14-120W						
Dimmer Company	Model No.			9290013224 (471359) 9290013224 (471318) 9290013223 (529750) 9290013221 (529743)	9290013220 (529735) 9290013218 (529727) 9290013216 (529719) 9290013215 (529701)	9290013213 (471334) 9290013212 (529818) 9290013210 (529800) 9290013209 (529792)	9290013207 (529784) 9290013205 (529776) 9290013204 (529768)	9290013203 (529693) 9290013202 (529685) 9290013201 (474700) 9290013200 (529677)	9290013199 (529669) 9290013198 (529651) 9290013197 (529644) 9290013196 (474692)	9290013195 (529636) 9290013194 (529628)	9290013192 (529610) 9290013191 (529602) 9290013190 (474684) 9290013189 (529594)	9290013188 (529552) 9290013187 (529545) 9290013186 (529537) 9290013185 (474676)	9290013184 (529529) 9290013183 (529503)
Leviton	6602	Professional Channel		1-15	1-15	1-11	1-10						
Leviton	6631												
Leviton	6633			1-15	1-15	1-11	1-10						
Leviton	6672			1-15	1-15	1-11	1-10						
Leviton	6674												
Leviton	6615P			1-8	1-8	1-5	1-5						
Leviton	DSE06												
Leviton	DSL06												
Leviton	DSM10												
Leviton	IPI06			1-15	1-15	1-11	1-10						
Leviton	IPL06												
Leviton	VPI06												
Lutron	AYCL-153P			NR	NR	1-5	NR						
Lutron	CTCL-153P			NR	NR	1-5	NR						
Lutron	CTCL-153PDH												
Lutron	DV-600P			1-15	1-15	1-11	1-10						
Lutron	DV-600PR												
Lutron	DVCL-153P			NR	NR	1-5	NR						
Lutron	DVCL-253P			NR	NR	1-5	NR						
Lutron	DVELV-300P			1-8	1-8	1-5	1-5						
Lutron	DVRP-253P												
Lutron	LGCL-153P												
Lutron	MACL-153M			1-15	1-15	1-11	1-10						
Lutron	MAELV-600												
Lutron	MALV-600												
Lutron	MRF2-6ND-120			1-15	1-15	1-11	1-5						
Lutron	NTCL-250			NR	NR	1-5	NR						
Lutron	PD-5NE												
Lutron	PD-6WCL			1-15	1-15	1-11	1-10						
Lutron	RRD-3LD												
Lutron	RRD-6NA			1-2	1-2	1-3	1-10						
Lutron	S-600P						1-8						
Lutron	SCL-153P			NR	NR	1-5	NR						
Lutron	SCL-153PR												
Lutron	SELV-300P												
Lutron	SLV-600P			1-11	1-11	1-8							
Lutron	TGCL-153PH												
Eaton	RI061-VW-K2												
Eaton	DAL06P												
Legrand	HCL453P												
Sensors													
Lutron	MSCL-OP153M			1-15	1-15	1-11	1-10						
Lutron	MSCL-OP153MH			1-15	1-15	1-11	1-5						
Lutron	MS-OPS2H			1-15	1-15	1-11	1-10						
Panel Modules													
Lutron	GP (Harrier) Card			1-15	1-15	1-14	1-10						
Lutron	HW-RPM-4A-120			1-15	1-15	1-2	1-10						
Lutron	HW-RPM-4U-120			1-15	1-15	1-2	1-10						
Lutron	LP-RPM-4U-120			1-15	1-15	1-2	1-10						

KEY (May exhibit one or several of the described parameters within the group)

Best	No flicker above 10% Full Light Output, good dimming range. Possible minor pop-on.
OK	No flicker above 20% Full Light Output and/or minor flicker which is hard to find at one specific point above 20%. Some limit of dim-range. Relatively high pop-on position reducing mechanical range.
NR	Use of this dimmer/lamp combination not recommended for the quantity of lamps indicated (# or range) or at all (X).
	Lamp not yet tested with this dimmer, compatibility unknown.

¹ Audible noise may be observed when used with this dimmer, depending on the application.

² This dimmer has low end trim adjustment that may be used for optimal performance.

WG = Warm Glow AF = Air Flux DS = Diamond Spark CC = Clear Classic DC = Die Cast DW = Direct White SO = Single Optic

PAR lamps

Number of bulbs

PAR lamps Number of bulbs										
			7W PAR16L ES	7W PAR20 WG Glass	7W PAR20 Glass	12W Glass PAR30		13.5W PAR38 GLASS		
Dimmer Company	Model No.		9290013181 (475434)	9290013173 (471136) 9290013172 (471102)	9290013170 (471151) 9290013169 (471144) 9290013167 (471128) 9290013165 (471110)	9290012954 (467928) 9290012952 (467902) 9290012950 (467894)	9290012949 (467886) 9290012948 (467878) 9290012946 (467860)	9290012944 (467845) 9290012942 (467837) 9290012940 (467811)	9290012927 (468025) 9290012927 (468009) 9290012926 (467803) 9290012920 (467753) 9290012923 (468199)	9290012922 (467779) 9290012921 (467761) 9290012920 (467753)
Leviton	6602	Professional Channel	1-15	1-15	1-16	NR	NR			
Leviton	6631									
Leviton	6633		1-15	1-15	1-16	1-13	NR			
Leviton	6672		1-15	1-15	1-16	NR	1-11			
Leviton	6674					NR	NR			
Leviton	6615P		1-10	1-10	1-10	2-5	1-5			
Leviton	DSE06									
Leviton	DSL06					NR	NR			
Leviton	DSM10									
Leviton	IPI06		1-15	1-15	1-16	1-13	1-11			
Leviton	IPL06									
Leviton	VPI06									
Lutron	AYCL-153P		8G	1-15	3					
Lutron	CTCL-153P		8G	1-15	3					
Lutron	CTCL-153PDH									
Lutron	DV-600P		1-15	1-15	1-16	1-13	1-11			
Lutron	DV-600PR									
Lutron	DVCL-153P		8G	1-15	3					
Lutron	DVCL-253P		8G	1-15	3					
Lutron	DVELV-300P		1-10	1-15	1-10	1-5	1-5			
Lutron	DVRP-253P									
Lutron	LGCL-153P									
Lutron	MACL-153M		1-15	1-15	1-16	NR	NR			
Lutron	MAELV-600									
Lutron	MALV-600									
Lutron	MRF2-6ND-120		1-15	1-15	1-16	NR	NR			
Lutron	NTCL-250		8G	1-15	3					
Lutron	PD-5NE									
Lutron	PD-6WCL		1-15	1-15	1-16	NR	NR			
Lutron	RRD-3LD									
Lutron	RRD-6NA			1-15	1-16	NR	NR			
Lutron	S-600P		1-15							
Lutron	SCL-153P		8G	1-15	3					
Lutron	SCL-153PR									
Lutron	SELV-300P									
Lutron	SLV-600P		1-15	1-15	1-16	1-9	1-8			
Lutron	TGCL-153PH									
Eaton	RI061-VW-K2									
Eaton	DAL06P									
Legrand	HCL453P									
Sensors										
Lutron	MSCL-OP153M		1-15	1-15	1-16	NR	NR			
Lutron	MSCL-OP153MH		1-15	1-15	1-16	NR	NR			
Lutron	MS-OPS2H		1-15	1-15	1-16	1-13	1-11			
Panel Modules										
Lutron	GP (Harrier) Card		1-15	1-15	1-16	NR	NR			
Lutron	HW-RPM-4A-120		1-15	1-15	1-16	NR	NR			
Lutron	HW-RPM-4U-120		1-15	1-15	1-16	NR	NR			
Lutron	LP-RPM-4U-120		1-15	1-15	1-16	NR	NR			

KEY (May exhibit one or several of the described parameters within the group)

Best	No flicker above 10% Full Light Output, good dimming range. Possible minor pop-on.
OK	No flicker above 20% Full Light Output and/or minor flicker which is hard to find at one specific point above 20%. Some limit of dim-range. Relatively high pop-on position reducing mechanical range.
NR	Use of this dimmer/lamp combination not recommended for the quantity of lamps indicated (# or range) or at all (X).
	Lamp not yet tested with this dimmer, compatibility unknown.

¹ Audible noise may be observed when used with this dimmer, depending on the application.

² This dimmer has low end trim adjustment that may be used for optimal performance.

WG = Warm Glow AF = Air Flux DS = Diamond Spark CC = Clear Classic DC = Die Cast DW = Direct White SO = Single Optic

PAR lamps

Number of bulbs

								
			16W PAR38 Glass	12PAR30S/EXPERTCOLOR RETAIL /F40/930/DIM	7W PAR16S/PAR16L 500lm	8W PAR30L	6W PAR20	
Dimmer Company	Model No.		9290012919 (467984) 9290012915 (468181) 9290012919 (467944) 9290012914 (467712) 9290012918 (467746) 9290012913 (467704)	9290012861 (471086) 9290012860 (471078) 9290012859 (471060)	9290012457 (465005) 9290012456 (464999) 9290012457 (465039) 9290012454 (464981) 9290012456 (465021)	9290012391 (463737) 9290012391 (463752)	9290012260 (463711) 9290012254 (463687) 9290012253 (463679) 9290012251 (463653) 9290012259 (463703) 9290012254 (463612) 9290012253 (463604) 9290012250 (463646) 9290012255 (463695) 9290012254 (463851) 9290012253 (463844) 9290012247 (463729) 9290012254 (463620) 9290012254 (463794) 9290012252 (463661)	
Leviton	6602	Professional Channel	1-9	1-12	1-20	1-15	1-15	
Leviton	6631							
Leviton	6633		1-9	1-8	1-20	1-15	1-15	
Leviton	6672		1-9	1-8	1-20	1-15	1-15	
Leviton	6674		1-9	1-8	NR	1-15	1-15	
Leviton	6615P		2-5	1-4	1-10	1-8	1-15	
Leviton	DSE06							
Leviton	DSL06		1-9	1-8	NR	1-15	1-15	
Leviton	DSM10							
Leviton	IPI06		1-9	1-8	1-20	1-15	1-15	
Leviton	IPL06							
Leviton	VPI06							
Lutron	AYCL-153P							
Lutron	CTCL-153P							
Lutron	CTCL-153PDH							
Lutron	DV-600P		1-9	1-12	1-20	1-15	1-15	
Lutron	DV-600PR							
Lutron	DVCL-153P							
Lutron	DVCL-253P							
Lutron	DVELV-300P		1-5	1-4	1-10	1-8	NR	
Lutron	DVRP-253P							
Lutron	LGCL-153P							
Lutron	MACL-153M		NR	1-12	NR	1-15	1-15	
Lutron	MAELV-600							
Lutron	MALV-600							
Lutron	MRF2-6ND-120		NR	1-8	NR	1-15	1-15	
Lutron	NTCL-250							
Lutron	PD-5NE							
Lutron	PD-6WCL		NR	1-12		1-15	1-15	
Lutron	RRD-3LD							
Lutron	RRD-6NA		1-9	1-8	NR	1-15	1-15	
Lutron	S-600P							
Lutron	SCL-153P							
Lutron	SCL-153PR							
Lutron	SELV-300P							
Lutron	SLV-600P		1-7	1-8	1-16	1-10	NR	
Lutron	TGCL-153PH							
Eaton	RI061-VW-K2							
Eaton	DAL06P							
Legrand	HCL453P							
Sensors								
Lutron	MSCL-OP153M		NR	1-12	NR	1-15	1-15	
Lutron	MSCL-OP153MH		NR	1-8	NR	1-15	1-15	
Lutron	MS-OPS2H		1-9	1-8	1-20	1-15	1-15	
Panel Modules								
Lutron	GP (Harrier) Card		1-10		NR	1-15		
Lutron	HW-RPM-4A-120		1-10		NR	1-15		
Lutron	HW-RPM-4U-120		1-10		NR	1-15		
Lutron	LP-RPM-4U-120		1-10		NR	1-15		

KEY (May exhibit one or several of the described parameters within the group)

Best	No flicker above 10% Full Light Output, good dimming range. Possible minor pop-on.
OK	No flicker above 20% Full Light Output and/or minor flicker which is hard to find at one specific point above 20%. Some limit of dim-range. Relatively high pop-on position reducing mechanical range.
NR	Use of this dimmer/lamp combination not recommended for the quantity of lamps indicated (# or range) or at all (X).
	Lamp not yet tested with this dimmer, compatibility unknown.

¹ Audible noise may be observed when used with this dimmer, depending on the application.² This dimmer has low end trim adjustment that may be used for optimal performance.

WG = Warm Glow AF = Air Flux DS = Diamond Spark CC = Clear Classic DC = Die Cast DW = Direct White SO = Single Optic

PAR lamps

Number of bulbs

PAR lamps Number of bulbs										
			6W (50W Eq) PAR20 SO	12W PAR38 SO		7W PAR16-GU10	6W PAR20 AF		12.5W PAR30L SO AF	
Dimmer Company	Model No.		9290012256 (463638) 9290012256 (463869)	9290011835 (460121) 9290011835 (460089) 9290011835 (461046) 9290011835 (460097)	9290011834 (460063) 9290011834 (460055) 9290011834 (460105) 9290011834 (460071)	929001172505 (457663)	9290011487 (456269) 9290011452 (456111) 9290011451 (456103) 9290011450 (456095)	9290011449 (456087) 9290011449 (458893) 9290011448 (456079) 9290011448 (458927)	9290011448 (458919) 9290011447 (456061) 9290011446 (456053) 9290011445 (456046)	9290011327 (454702) 9290011325 (454686) 9290011324 (454678)
Leviton	6602	Professional Channel	1-15	1-14	NR	1-20	1-8			
Leviton	6631									
Leviton	6633		1-15	NR	2-16	1-20	1-8			
Leviton	6672		1-15	1-14	2-16	1-20	1-8			
Leviton	6674		1-15		2-13	1-20	1-8			
Leviton	6615P		1-15	1-7	NR	1-10	1-5			
Leviton	DSE06									
Leviton	DSL06		1-15		2-13	1-20	1-8			
Leviton	DSM10									
Leviton	IPI06		1-15	1-14	NR	1-20	1-8			
Leviton	IPL06									
Leviton	VPI06									
Lutron	AYCL-153P									
Lutron	CTCL-153P									
Lutron	CTCL-153PDH									
Lutron	DV-600P		1-15	1-14	2-16	1-20	1-8			
Lutron	DV-600PR									
Lutron	DVCL-153P									
Lutron	DVCL-253P									
Lutron	DVELV-300P		NR	1-7	1-8	1-10	1-5			
Lutron	DVRP-253P									
Lutron	LGCL-153P									
Lutron	MACL-153M		1-15	NR	2-20	1-20	1-8			
Lutron	MAELV-600									
Lutron	MALV-600									
Lutron	MRF2-6ND-120		1-15	NR	2-16	NR	1-8			
Lutron	NTCL-250									
Lutron	PD-5NE									
Lutron	PD-6WCL		1-15	NR	2-16	NR	1-8			
Lutron	RRD-3LD									
Lutron	RRD-6NA		1-15	NR	2-16	1-20	1-8			
Lutron	S-600P									
Lutron	SCL-153P									
Lutron	SCL-153PR									
Lutron	SELV-300P									
Lutron	SLV-600P		NR	1-10	2-12	1-20	1-8			
Lutron	TGCL-153PH									
Eaton	RI061-VW-K2									
Eaton	DAL06P									
Legrand	HCL453P									
Sensors										
Lutron	MSCL-OP153M		1-15	NR	2-20	1-20	1-8			
Lutron	MSCL-OP153MH		1-15	NR	2-20	1-20	1-8			
Lutron	MS-OPS2H		1-15	1-15	2-20	1-20	1-8			
Panel Modules										
Lutron	GP (Harrier) Card			1-15	2-20	1-20				
Lutron	HW-RPM-4A-120			1-15	2-20	1-20				
Lutron	HW-RPM-4U-120			1-15	2-20	1-20				
Lutron	LP-RPM-4U-120			1-15	2-20	1-20				

KEY (May exhibit one or several of the described parameters within the group)

Best	No flicker above 10% Full Light Output, good dimming range. Possible minor pop-on.
OK	No flicker above 20% Full Light Output and/or minor flicker which is hard to find at one specific point above 20%. Some limit of dim-range. Relatively high pop-on position reducing mechanical range.
NR	Use of this dimmer/lamp combination not recommended for the quantity of lamps indicated (# or range) or at all (X).
	Lamp not yet tested with this dimmer, compatibility unknown.

¹ Audible noise may be observed when used with this dimmer, depending on the application.

² This dimmer has low end trim adjustment that may be used for optimal performance.

PAR lamps

Number of bulbs

							
			13W PAR38 SO	4.5W PAR16-GU10	10.5W PAR30L AF	15W PAR38	
Dimmer Company	Model No.		9290011322 (454751) 9290011321 (454744) 9290011320 (454736) 9290011319 (454728)	9290011288 (454363) 9290011288 (455378) 9290011288 (454405) 9290011288 (458034) 9290011288 (454389)	9290011114 (452656) 9290011113 (452615) 9290011114 (452623) 9290011113 (434984) 9290011114 (434992)	9290011111 (453431)	
Leviton	6602	Professional Channel	1-8	1-15		1-8	
Leviton	6631						
Leviton	6633		1-8	1-8		1-8	
Leviton	6672		1-8	1-15		1-8	
Leviton	6674		1-8	1-15	1-7	1-8	
Leviton	6615P		1-5	1-12	1-6	1-4	
Leviton	DSE06						
Leviton	DSL06		1-8	1-15	1-7	1-8	
Leviton	DSM10						
Leviton	IPI06		1-8	1-15	1-7	1-8	
Leviton	IPL06						
Leviton	VPI06						
Lutron	AYCL-153P						
Lutron	CTCL-153P						
Lutron	CTCL-153PDH						
Lutron	DV-600P		1-8	1-15	1-7	1-8	
Lutron	DV-600PR						
Lutron	DVCL-153P						
Lutron	DVCL-253P						
Lutron	DVELV-300P		1-5	1-12	1-6	1-4	
Lutron	DVRP-253P						
Lutron	LGCL-153P						
Lutron	MACL-153M		1-8	NR	1-7	1-8	
Lutron	MAELV-600						
Lutron	MALV-600						
Lutron	MRF2-6ND-120		1-8	1-15	1-7	1-8	
Lutron	NTCL-250						
Lutron	PD-5NE						
Lutron	PD-6WCL		1-8	1-11			
Lutron	RRD-3LD						
Lutron	RRD-6NA		1-8	1-15	1-7	1-8	
Lutron	S-600P						
Lutron	SCL-153P						
Lutron	SCL-153PR						
Lutron	SELV-300P						
Lutron	SLV-600P		NR	1-15	1-7	1-8	
Lutron	TGCL-153PH						
Eaton	RI061-VW-K2						
Eaton	DAL06P						
Legrand	HCL453P						
Sensors							
Lutron	MSCL-OP153M		1-8	NR	1-7	1-8	
Lutron	MSCL-OP153MH		1-8	1-15			
Lutron	MS-OPS2H		1-4	1-15			
Panel Modules							
Lutron	GP (Harrier) Card						
Lutron	HW-RPM-4A-120						
Lutron	HW-RPM-4U-120						
Lutron	LP-RPM-4U-120						

KEY (May exhibit one or several of the described parameters within the group)

Best	No flicker above 10% Full Light Output, good dimming range. Possible minor pop-on.
OK	No flicker above 20% Full Light Output and/or minor flicker which is hard to find at one specific point above 20%. Some limit of dim-range. Relatively high pop-on position reducing mechanical range.
NR	Use of this dimmer/lamp combination not recommended for the quantity of lamps indicated (# or range) or at all (X).
	Lamp not yet tested with this dimmer, compatibility unknown.

¹ Audible noise may be observed when used with this dimmer, depending on the application.

² This dimmer has low end trim adjustment that may be used for optimal performance.

BR lamps

Number of bulbs

									
			7.2BR30/MAS/922-27/P/E26/WG 6/1FB	8.8BR30/CNG/8xx/FR/P/E26/ DIM/120V 6/1CT	13.3BR40/PER/9xx/P/E26/ DIM 6/1CT T20	13.3BR40/PER/927-22/P/E26/ WG 6/1CT T20	P0027894 BR40 T20	15BR30/PER/927/P/E26/WG/ HO/T20 4/1PF	
Dimmer Company	Model No.		9790020069 9290018703 (457044)	9290036201 (583617) 9290036200 (583609) 9290036199 (583591) 9290036198 (583583)	9290034775 (577882) 9290034774 (577874) 9290034773 (577866) 9290034772 (577858)	9290034771 (577841)	9290023515 (558056) 9290023512 (558049)	9290023514 (571471)	
Leviton	6602	Professional Channel	1-20	1-17	2-11	1-11	1-8	1-10	
Leviton	6631		1-20	1-17	1-11	1-11	1-8	1-10	
Leviton	6633		1-20	1-17	1-11	1-11	1-8	1-10	
Leviton	6672		1-20	1-17	1-11	1-11	1-8	1-10	
Leviton	6674		2-20	2-17	1-11	1-11	1-8	1-10	
Leviton	6615P		1-10	NR	2-6	2-6	1-4	1-5	
Leviton	DSE06		1-20	1-17	1-20	1-20		1-20	
Leviton	DSL06		2-20	2-17	1-20	1-20	1-16	1-20	
Leviton	DSM10		1-20	1-17	1-20	1-20		1-20	
Leviton	IPI06		1-20	1-17	1-11	1-11	1-8	1-10	
Leviton	IPL06		2-20	2-17	1-11	1-11	1-8	1-10	
Leviton	VPI06		1-20	1-17	1-11	1-11		1-10	
Lutron	AYCL-153P		1-20	1-17	1-11	1-11		1-10	
Lutron	CTCL-153P		1-20	1-17	1-11	1-11		1-10	
Lutron	CTCL-153PDH		NR	NR	NR	NR		NR	
Lutron	DV-600P		1-20	1-17	1-11	1-11	1-8	1-10	
Lutron	DV-600PR		1-20	1-17	1-11	1-11		1-10	
Lutron	DVCL-153P		1-20	1-17	1-11	1-11	1-8	1-10	
Lutron	DVCL-253P		1-20	1-17	1-19	1-19		1-17	
Lutron	DVELV-300P		1-10	1-9	1-6	1-6	1-4	1-5	
Lutron	DVRP-253P		1-20	1-17	1-19	1-19		1-17	
Lutron	LGCL-153P		1-20	1-17	1-11	1-11		1-10	
Lutron	MACL-153M		1-20	1-17	1-11	1-11	1-8	1-10	
Lutron	MAELV-600		1-20	1-17	1-20	1-20		1-20	
Lutron	MALV-600		NR	NR	1	1		1-10	
Lutron	MRF2-6ND-120		1-20	1-17	1-11	1-11	1-8	1-10	
Lutron	NTCL-250		1-20	1-17	1-19	1-19		1-17	
Lutron	PD-5NE		1-20	1-17	1-19	1-19		1-17	
Lutron	PD-6WCL		1-20	1-17	1-11	1-11	1-8	1-10	
Lutron	RRD-3LD		1-10	1-9	1-6	1-6		1-5	
Lutron	RRD-6NA		1-20	1-17	1-11	1-11		1-10	
Lutron	S-600P		1-20	1-17	1-11	1-11		1-10	
Lutron	SCL-153P		1-5	1-4	1-3	1-3		1-3	
Lutron	SCL-153PR		1-5	1-4	1-3	1-3		1-3	
Lutron	SELV-300P		1-10	1-9	1-6	1-6		1-5	
Lutron	SLV-600P		1-16	1-13	1-8	1-8	1-6	1-8	
Lutron	TGCL-153PH		1-20	1-17	1-11	1-11		1-10	
Cooper	RI061-VW-K2		1-20	1-17	1-11	1-11		1-10	
Eaton	DAL06P		1-20	1-17	1-20	1-20		1-20	
Legrand	HCL453P		1-20	1-17	1-20	1-20		1-20	
Sensors									
Lutron	MSCL-OP153M		1-20	1-17	1-11	1-11	1-8	1-10	
Lutron	MSCL-OP153MH		1-20	1-17	1-11	1-11	1-8	1-10	
Lutron	MS-OPS2H		1-20	1-17	1-11	1-11		1-10	
Panel Modules									
Lutron	GP (Harrier) Card		NR	NR	NR	NR		1-20	
Lutron	HW-RPM-4A-120		1-20	1-17	1-20	1-20		1-20	
Lutron	HW-RPM-4U-120		1-20	1-17	1-20	1-20		1-20	
Lutron	LP-RPM-4U-120		1-20	1-17	1-20	1-20		1-20	

KEY (May exhibit one or several of the described parameters within the group)

Best	No flicker above 10% Full Light Output, good dimming range. Possible minor pop-on.
OK	No flicker above 20% Full Light Output and/or minor flicker which is hard to find at one specific point above 20%. Some limit of dim-range. Relatively high pop-on position reducing mechanical range.
NR	Use of this dimmer/lamp combination not recommended for the quantity of lamps indicated (# or range) or at all (X).
	Lamp not yet tested with this dimmer, compatibility unknown.

¹ Audible noise may be observed when used with this dimmer, depending on the application.² This dimmer has low end trim adjustment that may be used for optimal performance.

WG = Warm Glow AF = Air Flux DS = Diamond Spark CC = Clear Classic DC = Die Cast DW = Direct White SO = Single Optic

BR lamps

Number of bulbs

									
			15BR30/PER/950/P/E26/D/HO/ T20 4/1PF	BR40, P0025038, 2019Q2	7.2BR30/COR/9xx/P/E26/ DIM 6/1FB T20	5R20/PER/950/P/E26/ DIM 6/1FB T20	P0025038 BR40	5R20/PER/927/P/E26/ DIM 6/1FB T20	
Dimmer Company	Model No.		9290023513 (571463)	9290022042 (548115) 9290020356 (547430) 9290020355 (547422)	9290022041 (548107) 9290022041 (571364) 9290020923 (553891) 9290020923 (576579)	9290020923 (576587) 9290020322 (545913) 9290020321 (545905)	9290022040 (548123)	9290020924 (553909)	9290020922 (553883)
Leviton	6602	Professional Channel	1-10	1-18	1-20	1-20	1-18	1-20	
Leviton	6631		1-10		1-20	1-20		1-20	
Leviton	6633		1-10	1-18	1-20	1-20	1-18	1-20	
Leviton	6672		1-10	1-18	1-20	1-20	1-18	1-20	
Leviton	6674		1-10		2-20	2-20		2-20	
Leviton	6615P		1-5	1-9	1-10	1-15	1-9	1-15	
Leviton	DSE06		1-20		1-20	1-20		1-20	
Leviton	DSL06		1-20		2-20	2-20		2-20	
Leviton	DSM10		1-20		1-20	1-20		1-20	
Leviton	IPI06		1-10	1-18	1-20	1-20	1-18	1-20	
Leviton	IPL06		1-10		2-20	2-20		2-20	
Leviton	VPI06		1-10		1-20	1-20		1-20	
Lutron	AYCL-153P		1-10		1-20	1-20		1-20	
Lutron	CTCL-153P		1-10		1-20	1-20		1-20	
Lutron	CTCL-153PDH		NR		NR	NR		NR	
Lutron	DV-600P		1-10	1-18	1-20	1-20	1-18	1-20	
Lutron	DV-600PR		1-10		1-20	1-20		1-20	
Lutron	DVCL-153P		1-10		1-20	1-20		1-20	
Lutron	DVCL-253P		1-17		1-20	1-20		1-20	
Lutron	DVELV-300P		1-5	1-9	1-10	1-15	1-9	1-15	
Lutron	DVRP-253P		1-17		1-20	1-20		1-20	
Lutron	LGCL-153P		1-10		1-20	1-20		1-20	
Lutron	MACL-153M		1-10	1-18	1-20	1-20	1-18	1-20	
Lutron	MAELV-600		1-20		1-20	1-20		1-20	
Lutron	MALV-600		1-10		NR	NR		NR	
Lutron	MRF2-6ND-120		1-10	1-18	1-20	1-20	1-18	1-20	
Lutron	NTCL-250		1-17		1-20	1-20		1-20	
Lutron	PD-5NE		1-17		1-20	1-20		1-20	
Lutron	PD-6WCL		1-10	1-18	1-20	1-20	1-18	1-20	
Lutron	RRD-3LD		1-5		1-10	1-15		1-15	
Lutron	RRD-6NA		1-10		1-20	1-20		1-20	
Lutron	S-600P		1-10		1-20	1-20		1-20	
Lutron	SCL-153P		1-3		1-5	1-8		1-8	
Lutron	SCL-153PR		1-3		1-5	1-8		1-8	
Lutron	SELV-300P		1-5		1-10	1-15		1-15	
Lutron	SLV-600P		1-8	1-13	1-16	1-20	1-13	1-20	
Lutron	TGCL-153PH		1-10		1-20	1-20		1-20	
Cooper	RI061-VW-K2		1-10		1-20	1-20		1-20	
Eaton	DAL06P		1-20		1-20	1-20		1-20	
Legrand	HCL453P		1-20		1-20	1-20		1-20	
Sensors									
Lutron	MSCL-OP153M		1-10	1-18	1-20	1-20	1-18	1-20	
Lutron	MSCL-OP153MH		1-10		1-20	1-20		1-20	
Lutron	MS-OPS2H		1-10		1-20	1-20		1-20	
Panel Modules									
Lutron	GP (Harrier) Card		1-20		NR	NR		NR	
Lutron	HW-RPM-4A-120		1-20		1-20	1-20		1-20	
Lutron	HW-RPM-4U-120		1-20		1-20	1-20		1-20	
Lutron	LP-RPM-4U-120		1-20		1-20	1-20		1-20	

KEY (May exhibit one or several of the described parameters within the group)

Best	No flicker above 10% Full Light Output, good dimming range. Possible minor pop-on.
OK	No flicker above 20% Full Light Output and/or minor flicker which is hard to find at one specific point above 20%. Some limit of dim-range. Relatively high pop-on position reducing mechanical range.
NR	Use of this dimmer/lamp combination not recommended for the quantity of lamps indicated (# or range) or at all (X).
	Lamp not yet tested with this dimmer, compatibility unknown.

¹ Audible noise may be observed when used with this dimmer, depending on the application.
² This dimmer has low end trim adjustment that may be used for optimal performance.

WG = Warm Glow AF = Air Flux DS = Diamond Spark CC = Clear Classic DC = Die Cast DW = Direct White SO = Single Optic

BR lamps

Number of bulbs

							
		BR20, P0025038, 2019Q2	8.8W BR40 WG & CG, P0020365, 2018Q4	5R20/MAS/927-22/P/E26/ WG 6/1FB T20	9W BR30	9W BR30	9W (65W Eq) BR40 WG
Dimmer Company	Model No.	9290020354 (547414) 9290020353 (547406)	9290020092 9290020091 (457010)	9290020090 9290020089 (456979)	9290012137 (461855) 9290011944 (464180)	9290011749 (458109) 9290011749 (465286) 9290011749 (464198) 9290011749 (462143) 9290011749 (465229)	9290011558 (457010) 9290011558 (457002) 9290011558 (457028)
Leviton	6602	1-20	1-18	1-20	NR	1-5	1-16
Leviton	6631			1-20			
Leviton	6633	1-20	1-18	1-20	NR	1-4	1-16
Leviton	6672	1-20	1-18	1-20	1-8	1-8	1-16
Leviton	6674			2-20	1-8	1-8	1-16
Leviton	6615P	1-16	1-9	1-15	1-8	1-8	1-8
Leviton	DSE06			1-20			
Leviton	DSL06			2-20			
Leviton	DSM10			1-20			
Leviton	IPI06	1-20	1-18	1-20	1-5	1-5	1-16
Leviton	IPL06			2-20			
Leviton	VPI06			1-20			
Lutron	AYCL-153P			1-20			
Lutron	CTCL-153P			1-20			
Lutron	CTCL-153PDH			NR			
Lutron	DV-600P	1-20	1-18	1-20	1-8	1-8	1-16
Lutron	DV-600PR			1-20			
Lutron	DVCL-153P			1-20			
Lutron	DVCL-253P			1-20			
Lutron	DVELV-300P	1-16	1-9	1-15	1-8	1-8	1-8
Lutron	DVRP-253P			1-20			
Lutron	LGCL-153P			1-20			
Lutron	MACL-153M	1-20	1-18	1-20	1-8	1-8	1-16
Lutron	MAELV-600			1-20			
Lutron	MALV-600			NR			
Lutron	MRF2-6ND-120	1-20	1-18	1-20	1-8	1-8	1-16
Lutron	NTCL-250			1-20			
Lutron	PD-5NE			1-20			
Lutron	PD-6WCL	1-20	1-18	1-20	1-8	1-8	1-16
Lutron	RRD-3LD			1-15			
Lutron	RRD-6NA			1-20	1-8	1-8	1-16
Lutron	S-600P			1-20			
Lutron	SCL-153P			1-8			
Lutron	SCL-153PR			1-8			
Lutron	SELV-300P			1-15			
Lutron	SLV-600P	1-20	1-13	1-20	1-8	1-8	1-12
Lutron	TGCL-153PH			1-20			
Cooper	RI061-VW-K2			1-20			
Eaton	DAL06P			1-20			
Legrand	HCL453P			1-20			
Sensors							
Lutron	MSCL-OP153M	1-20	1-18	1-20	1-8	1-8	1-16
Lutron	MSCL-OP153MH			1-20	1-8	1-8	1-16
Lutron	MS-OPS2H			1-20	1-8	1-6	1-16
Panel Modules							
Lutron	GP (Harrier) Card			NR			1-16
Lutron	HW-RPM-4A-120			1-20			1-16
Lutron	HW-RPM-4U-120			1-20			1-16
Lutron	LP-RPM-4U-120			1-20			1-16

KEY (May exhibit one or several of the described parameters within the group)

Best	No flicker above 10% Full Light Output, good dimming range. Possible minor pop-on.
OK	No flicker above 20% Full Light Output and/or minor flicker which is hard to find at one specific point above 20%. Some limit of dim-range. Relatively high pop-on position reducing mechanical range.
NR	Use of this dimmer/lamp combination not recommended for the quantity of lamps indicated (# or range) or at all (X).
	Lamp not yet tested with this dimmer, compatibility unknown.

¹ Audible noise may be observed when used with this dimmer, depending on the application.² This dimmer has low end trim adjustment that may be used for optimal performance.

BR lamps

Number of bulbs

BR lamps Number of bulbs									
			6W (50W Eq) BR20 WG	9W (65W Eq) BR30 WG	9.5W (65W Eq) Slim style BR30	9.5W (65W Eq) BR30 WG	12W BR40 AF	13W BR30 AF Dim Tone	
Dimmer Company	Model No.		9290011557 (456979) 9290011557 (456995) 9290011557 (456987)	9290011555 (457044)	9290011119 (452441) 9290011119 (452466) 9290011118 (452391) 9290011119 (452482) 9290011118 (452417) 9290011118 (452359)	9290011117 (452243) 9290011117 (452235) 9290011117 (452268) 9290011117 (452284)	9290002580 (451914)	9290002344 (426445)	
Leviton	6602	Professional Channel	1-25	1-16					
Leviton	6631								
Leviton	6633		1-25	1-16					
Leviton	6672		1-25	1-16	1-8				
Leviton	6674		1-25	1-16	1-8	1-12	1-10	1-4	
Leviton	6615P		1-12	1-8	1-5	1-7	1-5	1-5	
Leviton	DSE06								
Leviton	DSL06								
Leviton	DSM10								
Leviton	IPI06		1-25	1-16	1-8	1-6	1-10	1--7	
Leviton	IPL06								
Leviton	VPI06								
Lutron	AYCL-153P								
Lutron	CTCL-153P								
Lutron	CTCL-153PDH								
Lutron	DV-600P		1-25	1-16	1-8	1-12	1-10	1-5	
Lutron	DV-600PR								
Lutron	DVCL-153P								
Lutron	DVCL-253P								
Lutron	DVELV-300P		1-12	1-8	1-5	1-7	1-5	1-5	
Lutron	DVRP-253P								
Lutron	LGCL-153P								
Lutron	MACL-153M		1-25	1-16	1-8	1-12	1-12	1-11	
Lutron	MAELV-600							1-11	
Lutron	MALV-600								
Lutron	MRF2-6ND-120		1-25	1-16	1-8	1-12	1-10	1-11	
Lutron	NTCL-250								
Lutron	PD-5NE								
Lutron	PD-6WCL		1-15	1-16	1-15	1-15	1-12		
Lutron	RRD-3LD								
Lutron	RRD-6NA		1-25	1-16	1-15	1-12	1-10	1-11	
Lutron	S-600P								
Lutron	SCL-153P						1-12	1-11	
Lutron	SCL-153PR								
Lutron	SELV-300P								
Lutron	SLV-600P		1-15	1-12	1-7	1-7	1-8	1-11	
Lutron	TGCL-153PH								
Cooper	RI061-VW-K2							1-11	
Eaton	DAL06P								
Legrand	HCL453P								
Sensors									
Lutron	MSCL-OP153M		1-25	1-16	1-8	1-12	1-12	1-11	
Lutron	MSCL-OP153MH		1-15	1-16	1-8	1-12	1-12		
Lutron	MS-OPS2H		1-25	1-16	1-8	1-12	1-12		
Panel Modules									
Lutron	GP (Harrier) Card		1-25	1-16	1-26	1-27	1-18		
Lutron	HW-RPM-4A-120		1-25	1-16	1-38	1-38	1-25		
Lutron	HW-RPM-4U-120		1-25	1-16	1-38	1-38	1-25		
Lutron	LP-RPM-4U-120		1-25	1-16	1-38	1-38	1-25		

KEY (May exhibit one or several of the described parameters within the group)	
Best	No flicker above 10% Full Light Output, good dimming range. Possible minor pop-on.
OK	No flicker above 20% Full Light Output and/or minor flicker which is hard to find at one specific point above 20%. Some limit of dim-range. Relatively high pop-on position reducing mechanical range.
NR	Use of this dimmer/lamp combination not recommended for the quantity of lamps indicated (# or range) or at all (X).
	Lamp not yet tested with this dimmer, compatibility unknown.

¹ Audible noise may be observed when used with this dimmer, depending on the application.

² This dimmer has low end trim adjustment that may be used for optimal performance.

WG = Warm Glow AF = Air Flux DS = Diamond Spark CC = Clear Classic DC = Die Cast DW = Direct White SO = Single Optic

BR lamps

Number of bulbs

BR lamps					
Number of bulbs				13W BR30 AF	8W BR20 AF
Dimmer Company	Model No.			9290002198 (420281)	9290002192 (420331) 9290002192 (423400) 9290002192 (428813)
Leviton	6602	Professional Channel			
Leviton	6631				
Leviton	6633				
Leviton	6672				
Leviton	6674		1-11	1-14	
Leviton	6615P		1-5	1-9	
Leviton	DSE06				
Leviton	DSL06				
Leviton	DSM10				
Leviton	IPI06		1-11	1-18	
Leviton	IPL06				
Leviton	VPI06				
Lutron	AYCL-153P		1-11		
Lutron	CTCL-153P		1-11		
Lutron	CTCL-153PDH				
Lutron	DV-600P		1-11	1-8	
Lutron	DV-600PR				
Lutron	DVCL-153P				
Lutron	DVCL-253P		1-11		
Lutron	DVELV-300P		1-5	NR	
Lutron	DVRP-253P				
Lutron	LGCL-153P				
Lutron	MACL-153M		1-11	1-18	
Lutron	MAELV-600				
Lutron	MALV-600		1-11		
Lutron	MRF2-6ND-120		1-11	1-18	
Lutron	NTCL-250		1-11		
Lutron	PD-5NE				
Lutron	PD-6WCL				
Lutron	RRD-3LD				
Lutron	RRD-6NA		1-11	1-18	
Lutron	S-600P				
Lutron	SCL-153P		1-11	1-18	
Lutron	SCL-153PR				
Lutron	SELV-300P				
Lutron	SLV-600P		1-11	1-8	
Lutron	TGCL-153PH				
Cooper	RI061-VW-K2				
Eaton	DAL06P				
Legrand	HCL453P				
Sensors					
Lutron	MSCL-OP153M		1-11	1-18	
Lutron	MSCL-OP153MH			1-18	
Lutron	MS-OPS2H			1-18	
Panel Modules					
Lutron	GP (Harrier) Card				
Lutron	HW-RPM-4A-120				
Lutron	HW-RPM-4U-120				
Lutron	LP-RPM-4U-120				

KEY (May exhibit one or several of the described parameters within the group)

Best	No flicker above 10% Full Light Output, good dimming range. Possible minor pop-on.
OK	No flicker above 20% Full Light Output and/or minor flicker which is hard to find at one specific point above 20%. Some limit of dim-range. Relatively high pop-on position reducing mechanical range.
NR	Use of this dimmer/lamp combination not recommended for the quantity of lamps indicated (# or range) or at all (X).
	Lamp not yet tested with this dimmer, compatibility unknown.

¹ Audible noise may be observed when used with this dimmer, depending on the application.² This dimmer has low end trim adjustment that may be used for optimal performance.

Candles

Number of bulbs

							
		5B11/PER/CRI95WG/FR/G/E26/ WGD T20	3.5B11/PER/UD/CL/G/E26/ WGD 6/3PF T20	5B11/PER/UD/CL/G/E12/ WGD 4/3CT T20	5BA11/PER/CRI95WG/FR/G/ E26-E12/WGD 1CT T20	3.5BA11/PER/UD50/CL/G/E26-E12/ D 6/3PF T20	2.3BA11/PER/UD/CL/G/E12/WGD 6/3PFT20
Dimmer Company	Model No.	9290030949 (575175)	9290030899 (574392) 9290030899 (574327)	9290030855 (573378) 9290030855 (574368)	9290030825 (575191) 9290030824 (575183) 9290029908 (575167)	9290029919 (564948) 9290029916 (564930)	9290029918 (566653)
Leviton	6602		1-10	1-10	1-10	1-10	1-10
Leviton	6631	1-10	1-10	1-10	1-10	1-10	1-10
Leviton	6633	1-10	1-10	1-10	1-10	1-10	1-10
Leviton	6672	1-10	1-10	1-10	1-10	1-10	1-10
Leviton	6674	1-10	1-10	1-10	1-10	1-10	1-10
Leviton	6615P	NR	NR	NR	NR	NR	NR
Leviton	DSE06		1-10	1-10	1-10	1-10	1-10
Leviton	DSL06	1-10	1-10	1-10	1-10	1-10	1-10
Leviton	DSM10		1-10	1-10	1-10	1-10	1-10
Leviton	IPI06	1-10	1-10	1-10	1-10	1-10	1-10
Leviton	IPL06	1-10	1-10	1-10	1-10	1-10	1-10
Leviton	VPI06		1-10	1-10	1-10	1-10	1-10
Lutron	AYCL-153P		1-11	1-11	1-11	1-11	1-11
Lutron	CTCL-153P		1-10	1-10	1-10	1-10	1-10
Lutron	CTCL-153PDH		1-10	1-10	1-10	1-10	1-10
Lutron	DV-600P		1-10	1-10	1-10	1-10	1-10
Lutron	DV-600PR		1-10	1-10	1-10	1-10	1-10
Lutron	DVCL-153P	1-10	1-10	1-10	1-10	1-10	1-10
Lutron	DVCL-253P		1-20	1-20	1-20	1-20	1-20
Lutron	DVELV-300P		NR	NR	NR	NR	NR
Lutron	DVRP-253P		1-20	1-20	1-20	1-20	1-20
Lutron	LGCL-153P		1-10	1-10	1-10	1-10	1-10
Lutron	MACL-153M	1-9	1-10	1-10	1-10	1-10	1-10
Lutron	MAELV-600		1-10	1-10	1-10	1-10	1-10
Lutron	MALV-600		NR	NR	NR	NR	NR
Lutron	MRF2-6ND-120		1-10	1-10	1-10	1-10	1-10
Lutron	NTCL-250		1-20	1-20	1-20	1-20	1-20
Lutron	PD-5NE		1-10	1-10	1-10	1-10	1-10
Lutron	PD-6WCL	1-10	1-10	1-10	1-10	1-10	1-10
Lutron	RRD-3LD		1-10	1-10	1-10	1-10	1-10
Lutron	RRD-6NA	1-10	1-10	1-10	1-10	1-10	1-10
Lutron	S-600P		1-10	1-10	1-10	1-10	1-10
Lutron	SCL-153P		1-11	1-8	1-8	1-11	1-11
Lutron	SCL-153PR		1-11	1-8	1-8	1-11	1-11
Lutron	SELV-300P		1-10	1-10	1-10	1-10	1-10
Lutron	SLV-600P	1-10	1-10	1-10	1-10	1-10	1-10
Lutron	TGCL-153PH		1-10	1-10	1-10	1-10	1-10
Cooper	RI061-VW-K2		1-10	1-10	1-10	1-10	1-10
Eaton	DAL06P		1-10	1-10	1-10	1-10	1-10
Legrand	HCL453P		1-10	1-10	1-10	1-10	1-10
Sensors							
Lutron	MSCL-OP153M	1-10	1-10	1-10	1-10	1-10	1-10
Lutron	MSCL-OP153MH	1-10	1-10	1-10	1-10	1-10	1-10
Lutron	MS-OPS2H		1-10	1-10	1-10	1-10	1-10
Panel Modules							
Lutron	GP (Harrier) Card		NR	NR	NR	NR	NR
Lutron	HW-RPM-4A-120		1-20	1-20	1-20	1-20	1-20
Lutron	HW-RPM-4U-120		1-20	1-20	1-20	1-20	1-20
Lutron	LP-RPM-4U-120		1-20	1-20	1-20	1-20	1-20

KEY (May exhibit one or several of the described parameters within the group)

Best	No flicker above 10% Full Light Output, good dimming range. Possible minor pop-on.
OK	No flicker above 20% Full Light Output and/or minor flicker which is hard to find at one specific point above 20%. Some limit of dim-range. Relatively high pop-on position reducing mechanical range.
NR	Use of this dimmer/lamp combination not recommended for the quantity of lamps indicated (# or range) or at all (X).
	Lamp not yet tested with this dimmer, compatibility unknown.

¹ Audible noise may be observed when used with this dimmer, depending on the application.² This dimmer has low end trim adjustment that may be used for optimal performance.

WG = Warm Glow AF = Air Flux DS = Diamond Spark CC = Clear Classic DC = Die Cast DW = Direct White SO = Single Optic

Candles

Number of bulbs

									
			3.5BA11/PER/UD/CL/G/E26/ WGD T20	5BA11/PER/UD50/CL/G/E26/ D 6/3PF T20	5BA11/PER/UD/CL/G/E26-E12/ WGD 6/3PF T20	3.5BT1/VIN/820/E12/Amber/G/ SP D 4/2PF T20	6.6BA11/PER/UD/CL/G/E12+E26/ WGD 2PF T20	6.6BA11 WG E12/E26 T20	
Dimmer Company	Model No.		9290029917 (566679)	9290029915 (564922)	9290029911 (566695) 9290029910 (566687)	9290029887 (565804)	9290029866 (564492)	9290022957 (557470) 9290022956 (557462)	
Leviton	6602	Professional Channel	1-10	1-10	1-10	1-10	1-10		
Leviton	6631		1-10	1-10	1-10	1-10	1-10	1-23	
Leviton	6633		1-10	1-10	1-10	1-10	1-10	1-23	
Leviton	6672		1-10	1-10	1-10	1-10	1-10	1-23	
Leviton	6674		1-10	1-10	1-10	1-10	1-10	1-23	
Leviton	6615P		NR	NR	NR	NR	NR		
Leviton	DSE06		1-10	1-10	1-10	1-10	1-10		
Leviton	DSL06		1-10	1-10	1-10	1-10	1-10	1-30	
Leviton	DSM10		1-10	1-10	1-10	1-10	1-10		
Leviton	IPI06		1-10	1-10	1-10	1-10	1-10	1-23	
Leviton	IPL06		1-10	1-10	1-10	1-10	1-10	1-23	
Leviton	VPI06		1-10	1-10	1-10	1-10	1-10		
Lutron	AYCL-153P		1-11	1-11	1-11	1-11	1-11		
Lutron	CTCL-153P		1-10	1-10	1-10	1-10	1-10		
Lutron	CTCL-153PDH		1-10	1-10	1-10	1-10	1-10		
Lutron	DV-600P		1-10	1-10	1-10	1-10	1-10		
Lutron	DV-600PR		1-10	1-10	1-10	1-10	1-10		
Lutron	DVCL-153P		1-10	1-10	1-10	1-10	1-10	1-23	
Lutron	DVCL-253P		1-20	1-20	1-20	1-20	1-20		
Lutron	DVELV-300P		NR	NR	NR	NR	NR	1-11	
Lutron	DVRP-253P		1-20	1-20	1-20	1-20	1-20		
Lutron	LGCL-153P		1-10	1-10	1-10	1-10	1-10		
Lutron	MACL-153M		1-10	1-10	1-10	1-10	1-10	1-23	
Lutron	MAELV-600		1-10	1-10	1-10	1-10	1-10		
Lutron	MALV-600		NR	NR	NR	NR	NR		
Lutron	MRF2-6ND-120		1-10	1-10	1-10	1-10	1-10		
Lutron	NTCL-250		1-20	1-20	1-20	1-20	1-20		
Lutron	PD-5NE		1-10	1-10	1-10	1-10	1-10		
Lutron	PD-6WCL		1-10	1-10	1-10	1-10	1-10	1-23	
Lutron	RRD-3LD		1-10	1-10	1-10	1-10	1-10		
Lutron	RRD-6NA		1-10	1-10	1-10	1-10	1-10		
Lutron	S-600P		1-10	1-10	1-10	1-10	1-10		
Lutron	SCL-153P		1-11	1-8	1-8	1-11	1-8		
Lutron	SCL-153PR		1-11	1-8	1-8	1-11	1-8		
Lutron	SELV-300P		1-10	1-10	1-10	1-10	1-10		
Lutron	SLV-600P		1-10	1-10	1-10	1-10	1-10	1-17	
Lutron	TGCL-153PH		1-10	1-10	1-10	1-10	1-10		
Cooper	RI061-VW-K2		1-10	1-10	1-10	1-10	1-10		
Eaton	DAL06P		1-10	1-10	1-10	1-10	1-10		
Legrand	HCL453P		1-10	1-10	1-10	1-10	1-10		
Sensors									
Lutron	MSCL-OP153M		1-10	1-10	1-10	1-10	1-10	1-23	
Lutron	MSCL-OP153MH		1-10	1-10	1-10	1-10	1-10	1-23	
Lutron	MS-OPS2H		1-10	1-10	1-10	1-10	1-10		
Panel Modules									
Lutron	GP (Harrier) Card		NR	NR	NR	NR	NR		
Lutron	HW-RPM-4A-120		1-20	1-20	1-20	1-20	1-20		
Lutron	HW-RPM-4U-120		1-20	1-20	1-20	1-20	1-20		
Lutron	LP-RPM-4U-120		1-20	1-20	1-20	1-20	1-20		

KEY (May exhibit one or several of the described parameters within the group)

Best	No flicker above 10% Full Light Output, good dimming range. Possible minor pop-on.
OK	No flicker above 20% Full Light Output and/or minor flicker which is hard to find at one specific point above 20%. Some limit of dim-range. Relatively high pop-on position reducing mechanical range.
NR	Use of this dimmer/lamp combination not recommended for the quantity of lamps indicated (# or range) or at all (X).
	Lamp not yet tested with this dimmer, compatibility unknown.

¹ Audible noise may be observed when used with this dimmer, depending on the application.² This dimmer has low end trim adjustment that may be used for optimal performance.

WG = Warm Glow AF = Air Flux DS = Diamond Spark CC = Clear Classic DC = Die Cast DW = Direct White SO = Single Optic

Candles

Number of bulbs

							
		3.3W Dimmable B11 Filament T20, P0025721	4.5W (40W Eq) WG BA11 Filament T20, P0023793	2W (25 Eq) WG BA11 Filament T20, P0023793	5.5B11/PER/927-922/CL/G/E12/WGX T20	3.3B11/PER/927-922/CL/G/E26/WGX T20	3BA11/MOD/840/E12/CL/GL/DIM 8/1BC
Dimmer Company	Model No.	9290022602 (556555) 9290022073 (549436) 9290022077 (549477) 9290022062 (549170) 9290022076 (549463) 9290022058 (549139) 9290022075 (549451) 9290022057 (549121) 9290022074 (549444) 9290022083 (549386) 9290022050 (549279) 9290022081 (549378) 9290020513 (550250) 9290022054 (549311) 9290019701 (549576) 9290022051 (549287) 9290019693 (549550) 9290022049 (549261) 9290022048 (549253) 9290022043 (549246) 9290022046 (549345) 9290022045 (549337) 9290020472 (549584) 9290019694 (549568) 9290020012 (543173)					
Leviton	6602	1-3	2	2-20	1-10	1-10	3-15
Leviton	6631				1-10	1-10	
Leviton	6633	1-5	1-10	2-15	1-10	1-10	2-15
Leviton	6672	1-5	1-5	8-20	1-10	1-10	1-15
Leviton	6674				1-10	1-10	1-15
Leviton	6615P	1-2	1-10	1-10	NR	NR	1-15
Leviton	DSE06				1-10	1-10	
Leviton	DSL06				1-10	1-10	
Leviton	DSM10				1-10	1-10	
Leviton	IPI06	1-5	2-3	1-20	1-10	1-10	1-15
Leviton	IPL06	1-20			1-10	1-10	
Leviton	VPI06				1-10	1-10	
Lutron	AYCL-153P				1-11	1-11	
Lutron	CTCL-153P				1-10	1-10	
Lutron	CTCL-153PDH				1-10	1-10	
Lutron	DV-600P	1-5	1-5	1-20	1-10	1-10	1-15
Lutron	DV-600PR				1-10	1-10	
Lutron	DVCL-153P				1-10	1-10	
Lutron	DVCL-253P				1-20	1-20	
Lutron	DVELV-300P	1-20	1-10	1-20	NR	NR	1-15
Lutron	DVRP-253P				1-20	1-20	
Lutron	LGCL-153P				1-10	1-10	
Lutron	MACL-153M	1-5	1-10	1-20	1-10	1-10	
Lutron	MAELV-600				1-10	1-10	
Lutron	MALV-600				NR	NR	
Lutron	MRF2-6ND-120	3-5	2-10	2-20	1-10	1-10	1-15
Lutron	NTCL-250				1-20	1-20	
Lutron	PD-5NE				1-10	1-10	
Lutron	PD-6WCL	1-5	1-10	2-20	1-10	1-10	2-15
Lutron	RRD-3LD				1-10	1-10	
Lutron	RRD-6NA	1-3	1-10	1-20	1-10	1-10	
Lutron	S-600P				1-10	1-10	
Lutron	SCL-153P				1-8	1-11	
Lutron	SCL-153PR				1-8	1-11	
Lutron	SELV-300P				1-10	1-10	
Lutron	SLV-600P	1-10	1-10	1-20	1-10	1-10	1-15
Lutron	TGCL-153PH				1-10	1-10	
Cooper	RI061-VW-K2				1-10	1-10	
Eaton	DAL06P				1-10	1-10	
Legrand	HCL453P				1-10	1-10	
Sensors							
Lutron	MSCL-OP153M	1-5	1-10	1-20	1-10	1-10	
Lutron	MSCL-OP153MH	1-8	1-10	1-20	1-10	1-10	1-15
Lutron	MS-OPS2H	1-20	1-10	1-20	1-10	1-10	1-15
Panel Modules							
Lutron	GP (Harrier) Card	1-20	1-10	1-20	NR	NR	1-15
Lutron	HW-RPM-4A-120	1-5	1-10	1	1-20	1-20	1-15
Lutron	HW-RPM-4U-120	1-5	1-10	1	1-20	1-20	1-15
Lutron	LP-RPM-4U-120	1-5	1-10	1	1-20	1-20	1-15

KEY (May exhibit one or several of the described parameters within the group)

Best	No flicker above 10% Full Light Output, good dimming range. Possible minor pop-on.
OK	No flicker above 20% Full Light Output and/or minor flicker which is hard to find at one specific point above 20%. Some limit of dim-range. Relatively high pop-on position reducing mechanical range.
NR	Use of this dimmer/lamp combination not recommended for the quantity of lamps indicated (# or range) or at all (X).
	Lamp not yet tested with this dimmer, compatibility unknown.

¹ Audible noise may be observed when used with this dimmer, depending on the application.² This dimmer has low end trim adjustment that may be used for optimal performance.

WG = Warm Glow AF = Air Flux DS = Diamond Spark CC = Clear Classic DC = Die Cast DW = Direct White SO = Single Optic

Candles

Number of bulbs

												
			3.3BA11/PER/927-922/CL/G/E12/WGX T20	3.8W (40W Eq) WG Candle, P0020414, P0023247	2.5-8W Dimmable Candle and Vintage	5.5W BA11/G16.5 Candle	4.5W (40W Eq) 2700K					
Dimmer Company	Model No.		9290019692 (549543)	9290019514 (537621) 9290019514 (556852)	9290018427 (478719) 9290018426 (478701) 9290018425 (478693) 9290018424 (478685)	9290018423 (478677) 9290013151 (470781) 9290013149 (470765) 9290013148 (470757)	9290012687 (465567) 9290012687 (465583)	9290018418 (478842) 9290018417 (478834) 9290018416 (478826)	9290018415 (478818) 9290018414 (478800) 9290018413 (478792)	9290012138 (461921) 9290012138 (461939) 9290012138 (462358)	9290012137 (461855) 9290012137 (461863) 9290012137 (461871)	9290012137 (461889) 9290012137 (461897) 9290012137 (461905)
Leviton	6602	Professional Channel	1-10	3-20	3-20	1-5	2-30					
Leviton	6631		1-10									
Leviton	6633		1-10	2-20	2-20	1-10	2-30					
Leviton	6672		1-10	1-20	1-20	1-10	2-30					
Leviton	6674		1-10				2-30					
Leviton	6615P		NR	1-20	1-20	1-5	2-16					
Leviton	DSE06		1-10									
Leviton	DSL06		1-10									
Leviton	DSM10		1-10									
Leviton	IPI06		1-10	4-20	4-20	1-10	2-30					
Leviton	IPL06		1-10									
Leviton	VPI06		1-10									
Lutron	AYCL-153P		1-11									
Lutron	CTCL-153P		1-10									
Lutron	CTCL-153PDH		1-10									
Lutron	DV-600P		1-10	1-20	1-20	1-10	2-30					
Lutron	DV-600PR		1-10									
Lutron	DVCL-153P		1-10									
Lutron	DVCL-253P		1-20									
Lutron	DVELV-300P		NR	1-20	1-20	1-3	2-16					
Lutron	DVRP-253P		1-20									
Lutron	LGCL-153P		1-10									
Lutron	MACL-153M		1-10	1-20	1-20	1-10	2-30					
Lutron	MAELV-600		1-10									
Lutron	MALV-600		NR									
Lutron	MRF2-6ND-120		1-10	1-10	1-10	1-10	2-30					
Lutron	NTCL-250		1-20									
Lutron	PD-5NE		1-10									
Lutron	PD-6WCL		1-10	3-20	3-20	1-10	2-30					
Lutron	RRD-3LD		1-10									
Lutron	RRD-6NA		1-10	1-20	1-20	1-10	2-30					
Lutron	S-600P		1-10									
Lutron	SCL-153P		1-11									
Lutron	SCL-153PR		1-11									
Lutron	SELV-300P		1-10									
Lutron	SLV-600P		1-10	1-20	1-20	1-10	2-30					
Lutron	TGCL-153PH		1-10									
Cooper	RI061-VW-K2		1-10									
Eaton	DAL06P		1-10									
Legrand	HCL453P		1-10									
Sensors												
Lutron	MSCL-OP153M		1-10	1-20	1-20	1-10	2-30					
Lutron	MSCL-OP153MH		1-10	1-20	1-20	1-10	2-30					
Lutron	MS-OPS2H		1-10	1-20	1-20	1-10	2-30					
Panel Modules												
Lutron	GP (Harrier) Card		NR	1-20	1-20	1-8	2-30					
Lutron	HW-RPM-4A-120		1-20	1-20	1-20	1-10	2-30					
Lutron	HW-RPM-4U-120		1-20	1-20	1-20	1-10	2-30					
Lutron	LP-RPM-4U-120		1-20	1-20	1-20	1-10	2-30					

KEY (May exhibit one or several of the described parameters within the group)

Best	No flicker above 10% Full Light Output, good dimming range. Possible minor pop-on.
OK	No flicker above 20% Full Light Output and/or minor flicker which is hard to find at one specific point above 20%. Some limit of dim-range. Relatively high pop-on position reducing mechanical range.
NR	Use of this dimmer/lamp combination not recommended for the quantity of lamps indicated (# or range) or at all (X).
	Lamp not yet tested with this dimmer, compatibility unknown.

¹ Audible noise may be observed when used with this dimmer, depending on the application.² This dimmer has low end trim adjustment that may be used for optimal performance.

WG = Warm Glow AF = Air Flux DS = Diamond Spark CC = Clear Classic DC = Die Cast DW = Direct White SO = Single Optic

Candles
Number of bulbs

									
			4.5W (40W Eq) 5000K	3.5W Filament	7W (60W Eq) DS WG	4.5W (40Eq) DS WG	3.5W (25W Eq) WG DS	2.5W (25W Eq) DS	
Dimmer Company	Model No.		9290012130 (463901) 9290012130 (463919) 9290012130 (463943)	9290012103 (461681)	9290011821 (458679) 9290011820 (458687) 9290011821 (458661) 9290011820 (459321) 9290011821 (458653) 9290011820 (458703) 9290011820 (458695)	9290011673 (457200) 9290011671 (457218) 9290011673 (457192) 9290011670 (457119) 9290011673 (457184)	9290011668 (457242) 9290011668 (457234) 9290011668 (457226)	9290011151 (451831) 9290002799 (435149)	
Leviton	6602	Professional Channel	2-30	1-33	1-21	1-26	1-15	NR	
Leviton	6631								
Leviton	6633		2-30	1-33	1-21	1-26	1-25	1-7	
Leviton	6672		2-30	1-33	1-21	1-26	1-35	1-7	
Leviton	6674		2-30	1-10	1-21	1-10	1-20	1-7	
Leviton	6615P		2-16	1-17	1-11	1-13	1-17	NR	
Leviton	DSE06								
Leviton	DSL06								
Leviton	DSM10								
Leviton	IPI06		2-30	1-33	1-21	1-26	1-35	NR	
Leviton	IPL06								
Leviton	VPI06								
Lutron	AYCL-153P								
Lutron	CTCL-153P								
Lutron	CTCL-153PDH								
Lutron	DV-600P		2-30	1-33	1-21	1-26	1-15	1-7	
Lutron	DV-600PR								
Lutron	DVCL-153P								
Lutron	DVCL-253P								
Lutron	DVELV-300P		2-16	1-17	1-11	1-13	1-17	1-7	
Lutron	DVRP-253P								
Lutron	LGCL-153P								
Lutron	MACL-153M		2-30	1-33	1-21	1-26	1-35	1-7	
Lutron	MAELV-600								
Lutron	MALV-600								
Lutron	MRF2-6ND-120		2-30	1-33	1-21	1-26	1-35	1-7	
Lutron	NTCL-250								
Lutron	PD-5NE								
Lutron	PD-6WCL		NR	NR	NR	NR	1-35	1-7	
Lutron	RRD-3LD								
Lutron	RRD-6NA		2-30	1-15	1-25	NR	1-35	1-7	
Lutron	S-600P								
Lutron	SCL-153P								
Lutron	SCL-153PR								
Lutron	SELV-300P								
Lutron	SLV-600P		2-30	1-25	1-16	1-19	1-15	1-7	
Lutron	TGCL-153PH								
Cooper	RI061-VW-K2								
Eaton	DAL06P								
Legrand	HCL453P								
Sensors									
Lutron	MSCL-OP153M		2-30	1-33	1-21	1-26	1-35	1-7	
Lutron	MSCL-OP153MH		NR	1-33	NR	1-33	2-45		
Lutron	MS-OPS2H		2-30	1-33	1-21	1-33	1-45		
Panel Modules									
Lutron	GP (Harrier) Card		2-30	1-33	1-25	1-40	1-50		
Lutron	HW-RPM-4A-120		2-30	1-33	1-25	1-45	1-50		
Lutron	HW-RPM-4U-120		2-30	1-33	1-25	1-45	1-50		
Lutron	LP-RPM-4U-120		2-30	1-33	1-25	1-45	1-50		

KEY (May exhibit one or several of the described parameters within the group)	
Best	No flicker above 10% Full Light Output, good dimming range. Possible minor pop-on.
OK	No flicker above 20% Full Light Output and/or minor flicker which is hard to find at one specific point above 20%. Some limit of dim-range. Relatively high pop-on position reducing mechanical range.
NR	Use of this dimmer/lamp combination not recommended for the quantity of lamps indicated (# or range) or at all (X).
	Lamp not yet tested with this dimmer, compatibility unknown.

¹ Audible noise may be observed when used with this dimmer, depending on the application.

² This dimmer has low end trim adjustment that may be used for optimal performance.

WG = Warm Glow AF = Air Flux DS = Diamond Spark CC = Clear Classic DC = Die Cast DW = Direct White SO = Single Optic

Candles

Number of bulbs

				
		6.5W(60W Eq) DS	4.5W(40W Eq) DS	3.5W DW
Dimmer Company	Model No.	9290011121 (452813)	9290002889 (435156) 9290002798 (435164) 9290002797 (435172)	9290002419 (427773) 9290002417 (427765) 9290002419 (427815) 9290002417 (427799) 9290002418 (427781)
Leviton	6602	NR	NR	
Leviton	6631			
Leviton	6633	1-10	1-10	
Leviton	6672	1-10	1-10	
Leviton	6674	1-10	1-10	1-10
Leviton	6615P	NR	NR	1-17
Leviton	DSE06			
Leviton	DSL06			
Leviton	DSM10			
Leviton	IPI06	NR	NR	NR
Leviton	IPL06			
Leviton	VPI06			
Lutron	AYCL-153P			
Lutron	CTCL-153P			
Lutron	CTCL-153PDH			
Lutron	DV-600P	1-10	NR	NR
Lutron	DV-600PR			
Lutron	DVCL-153P			
Lutron	DVCL-253P			
Lutron	DVELV-300P	NR	NR	10-21
Lutron	DVRP-253P			
Lutron	LGCL-153P			
Lutron	MACL-153M	1-10	1-10	1-42
Lutron	MAELV-600			
Lutron	MALV-600			
Lutron	MRF2-6ND-120	1-10	1-10	1-42
Lutron	NTCL-250			
Lutron	PD-5NE			
Lutron	PD-6WCL	1-10	1-10	
Lutron	RRD-3LD			
Lutron	RRD-6NA	1-10	1-10	1-42
Lutron	S-600P			
Lutron	SCL-153P			4-42
Lutron	SCL-153PR			
Lutron	SELV-300P			
Lutron	SLV-600P	1-10	1-10	NR
Lutron	TGCL-153PH			
Cooper	RI061-VW-K2			
Eaton	DAL06P			
Legrand	HCL453P			
Sensors				
Lutron	MSCL-OP153M	1-10	1-10	1-42
Lutron	MSCL-OP153MH			
Lutron	MS-OPS2H			
Panel Modules				
Lutron	GP (Harrier) Card	1-10		
Lutron	HW-RPM-4A-120	1-10		
Lutron	HW-RPM-4U-120	1-10		
Lutron	LP-RPM-4U-120	1-10		

KEY (May exhibit one or several of the described parameters within the group)

Best	No flicker above 10% Full Light Output, good dimming range. Possible minor pop-on.
OK	No flicker above 20% Full Light Output and/or minor flicker which is hard to find at one specific point above 20%. Some limit of dim-range. Relatively high pop-on position reducing mechanical range.
NR	Use of this dimmer/lamp combination not recommended for the quantity of lamps indicated (# or range) or at all (X).
	Lamp not yet tested with this dimmer, compatibility unknown.

¹ Audible noise may be observed when used with this dimmer, depending on the application.

² This dimmer has low end trim adjustment that may be used for optimal performance.

Misc. (G25,ST19)

Number of bulbs

Misc. (G25,ST19) Number of bulbs									
			5G25/PER/UD50/E26/FR/G/D 4/ 2PFT20	3.5G16.5/PER/UD/CL/G/E26/ WGD T20	3.5G25/PER/UD/FR-CL/G/E26/ WGD T20	3.5G25/PER/UD50/CL/G/E26/ D 4/2PFT20	5G25/PER/UD50/CL/G/E26 D 4/ 3PFT20	6.5G25/VIN/820/E26/Amber/G/ SP D 4/1PFT20	
Dimmer Company	Model No.		9290030998 (575217)	9290030852 (573303) 9290030851 (573295)	9290030850 (573352) 9290030848 (573345)	9290030849 (573337)	9290029914 (564914)	9290029895 (565887)	
Leviton	6602	Professional Channel	1-10	1-10	1-10	1-10	1-10	1-10	
Leviton	6631		1-10	1-10	1-10	1-10	1-10	1-10	
Leviton	6633		1-10	1-10	1-10	1-10	1-10	1-10	
Leviton	6672		1-10	1-10	1-10	1-10	1-10	1-10	
Leviton	6674		1-10	1-10	1-10	1-10	1-10	1-10	
Leviton	6615P		NR	NR	NR	NR	NR	NR	
Leviton	DSE06		1-10	1-10	1-10	1-10	1-10	1-10	
Leviton	DSL06		1-10	1-10	1-10	1-10	1-10	1-10	
Leviton	DSM10		1-10	1-10	1-10	1-10	1-10	1-10	
Leviton	IPI06		1-10	1-10	1-10	1-10	1-10	1-10	
Leviton	IPL06		1-10	1-10	1-10	1-10	1-10	1-10	
Leviton	VPI06		1-10	1-10	1-10	1-10	1-10	1-10	
Lutron	AYCL-153P		1-11	1-11	1-11	1-11	1-11	1-11	
Lutron	CTCL-153P		1-10	1-10	1-10	1-10	1-10	1-10	
Lutron	CTCL-153PDH		1-10	1-10	1-10	1-10	1-10	1-10	
Lutron	DV-600P		1-10	1-10	1-10	1-10	1-10	1-10	
Lutron	DV-600PR		1-10	1-10	1-10	1-10	1-10	1-10	
Lutron	DVCL-153P		1-10	1-10	1-10	1-10	1-10	1-10	
Lutron	DVCL-253P		1-20	1-20	1-20	1-20	1-20	1-20	
Lutron	DVELV-300P		NR	NR	NR	NR	NR	NR	
Lutron	DVRP-253P		1-20	1-20	1-20	1-20	1-20	1-20	
Lutron	LGCL-153P		1-10	1-10	1-10	1-10	1-10	1-10	
Lutron	MACL-153M		1-10	1-10	1-10	1-10	1-10	1-10	
Lutron	MAELV-600		1-10	1-10	1-10	1-10	1-10	1-10	
Lutron	MALV-600		NR	NR	NR	NR	NR	NR	
Lutron	MRF2-6ND-120		1-10	1-10	1-10	1-10	1-10	1-10	
Lutron	NTCL-250		1-20	1-20	1-20	1-20	1-20	1-20	
Lutron	PD-5NE		1-10	1-10	1-10	1-10	1-10	1-10	
Lutron	PD-6WCL		1-10	1-10	1-10	1-10	1-10	1-10	
Lutron	RRD-3LD		1-10	1-10	1-10	1-10	1-10	1-10	
Lutron	RRD-6NA		1-10	1-10	1-10	1-10	1-10	1-10	
Lutron	S-600P		1-10	1-10	1-10	1-10	1-10	1-10	
Lutron	SCL-153P		1-8	1-11	1-11	1-11	1-8	1-8	
Lutron	SCL-153PR		1-8	1-11	1-11	1-11	1-8	1-8	
Lutron	SELV-300P		1-10	1-10	1-10	1-10	1-10	1-10	
Lutron	SLV-600P		1-10	1-10	1-10	1-10	1-10	1-10	
Lutron	TGCL-153PH		1-10	1-10	1-10	1-10	1-10	1-10	
Cooper	RI061-VW-K2		1-10	1-10	1-10	1-10	1-10	1-10	
Eaton	DAL06P		1-10	1-10	1-10	1-10	1-10	1-10	
Legrand	HCL453P		1-10	1-10	1-10	1-10	1-10	1-10	
Sensors									
Lutron	MSCL-OP153M		1-10	1-10	1-10	1-10	1-10	1-10	1-10
Lutron	MSCL-OP153MH		1-10	1-10	1-10	1-10	1-10	1-10	1-10
Lutron	MS-OPS2H		1-10	1-10	1-10	1-10	1-10	1-10	1-10
Panel Modules									
Lutron	GP (Harrier) Card		NR	NR	NR	NR	NR	NR	NR
Lutron	HW-RPM-4A-120		1-20	1-20	1-20	1-20	1-20	1-20	1-20
Lutron	HW-RPM-4U-120		1-20	1-20	1-20	1-20	1-20	1-20	1-20
Lutron	LP-RPM-4U-120		1-20	1-20	1-20	1-20	1-20	1-20	1-20

KEY (May exhibit one or several of the described parameters within the group)

Best	No flicker above 10% Full Light Output, good dimming range. Possible minor pop-on.
OK	No flicker above 20% Full Light Output and/or minor flicker which is hard to find at one specific point above 20%. Some limit of dim-range. Relatively high pop-on position reducing mechanical range.
NR	Use of this dimmer/lamp combination not recommended for the quantity of lamps indicated (# or range) or at all (X).
	Lamp not yet tested with this dimmer, compatibility unknown.

¹ Audible noise may be observed when used with this dimmer, depending on the application.² This dimmer has low end trim adjustment that may be used for optimal performance.

WG = Warm Glow AF = Air Flux DS = Diamond Spark CC = Clear Classic DC = Die Cast DW = Direct White SO = Single Optic

Misc. (G25,ST19)

Number of bulbs

Misc. (G25,ST19) Number of bulbs									
			5.5ST19/VIN/9xx/E26/CL/G/SP D 4/ 1PF T20	5.5A19/VIN/9xx/E26/CL/G/ SP DIM 1PF T20	3.5T10/VIN/820/E26/Amber/G/ SP D 4/1PFT20	3.5A15/VIN/820/E26/Amber/G/ SP D 4/1PFT20	6.5ST19/VIN/820/E26/Amber/G/ SP D 1PFT20	8.8ST19/PER/950/CL/G/E26/ DIM 1PF T20	
Dimmer Company	Model No.		9290029890 (565838) 9290029888 (565812)	9290029885 (565788)	9290029874 (565671)	9290029872 (565655)	9290029869 (565622)	9290022961 (556548)	
Leviton	6602	Professional Channel	1-10	1-10	1-10	1-10	1-10	1-19	
Leviton	6631		1-10	1-10	1-10	1-10	1-10	1-19	
Leviton	6633		1-10	1-10	1-10	1-10	1-10	1-19	
Leviton	6672		1-10	1-10	1-10	1-10	1-10	1-19	
Leviton	6674		1-10	1-10	1-10	1-10	1-10	1-19	
Leviton	6615P		NR	NR	NR	NR	NR	NR	
Leviton	DSE06		1-10	1-10	1-10	1-10	1-10	1-20	
Leviton	DSL06		1-10	1-10	1-10	1-10	1-10	1-20	
Leviton	DSM10		1-10	1-10	1-10	1-10	1-10	1-20	
Leviton	IPI06		1-10	1-10	1-10	1-10	1-10	1-19	
Leviton	IPL06		1-10	1-10	1-10	1-10	1-10	1-19	
Leviton	VPI06		1-10	1-10	1-10	1-10	1-10	1-19	
Lutron	AYCL-153P		1-11	1-11	1-11	1-11	1-11	1-19	
Lutron	CTCL-153P		1-10	1-10	1-10	1-10	1-10	1-19	
Lutron	CTCL-153PDH		1-10	1-10	1-10	1-10	1-10	1-19	
Lutron	DV-600P		1-10	1-10	1-10	1-10	1-10	1-19	
Lutron	DV-600PR		1-10	1-10	1-10	1-10	1-10	1-19	
Lutron	DVCL-153P		1-10	1-10	1-10	1-10	1-10	1-19	
Lutron	DVCL-253P		1-20	1-20	1-20	1-20	1-20	1-20	
Lutron	DVELV-300P		NR	NR	NR	NR	NR	NR	
Lutron	DVRP-253P		1-20	1-20	1-20	1-20	1-20	1-20	
Lutron	LGCL-153P		1-10	1-10	1-10	1-10	1-10	1-19	
Lutron	MACL-153M		1-10	1-10	1-10	1-10	1-10	1-19	
Lutron	MAELV-600		1-10	1-10	1-10	1-10	1-10	1-20	
Lutron	MALV-600		NR	NR	NR	NR	NR	NR	
Lutron	MRF2-6ND-120		1-10	1-10	1-10	1-10	1-10	1-19	
Lutron	NTCL-250		1-20	1-20	1-20	1-20	1-20	1-20	
Lutron	PD-5NE		1-10	1-10	1-10	1-10	1-10	1-20	
Lutron	PD-6WCL		1-10	1-10	1-10	1-10	1-10	1-19	
Lutron	RRD-3LD		1-10	1-10	1-10	1-10	1-10	1-9	
Lutron	RRD-6NA		1-10	1-10	1-10	1-10	1-10	1-19	
Lutron	S-600P		1-10	1-10	1-10	1-10	1-10	1-19	
Lutron	SCL-153P		1-11	1-11	1-11	1-11	1-8	1-5	
Lutron	SCL-153PR		1-11	1-11	1-11	1-11	1-8	1-5	
Lutron	SELV-300P		1-10	1-10	1-10	1-10	1-10	1-9	
Lutron	SLV-600P		1-10	1-10	1-10	1-10	1-10	1-14	
Lutron	TGCL-153PH		1-10	1-10	1-10	1-10	1-10	1-19	
Cooper	RI061-VW-K2		1-10	1-10	1-10	1-10	1-10	1-19	
Eaton	DAL06P		1-10	1-10	1-10	1-10	1-10	1-20	
Legrand	HCL453P		1-10	1-10	1-10	1-10	1-10	1-20	
Sensors									
Lutron	MSCL-OP153M		1-10	1-10	1-10	1-10	1-10	1-19	
Lutron	MSCL-OP153MH		1-10	1-10	1-10	1-10	1-10	1-19	
Lutron	MS-OPS2H		1-10	1-10	1-10	1-10	1-10	1-19	
Panel Modules									
Lutron	GP (Harrier) Card		NR	NR	NR	NR	NR	NR	NR
Lutron	HW-RPM-4A-120		1-20	1-20	1-20	1-20	1-20	1-20	1-20
Lutron	HW-RPM-4U-120		1-20	1-20	1-20	1-20	1-20	1-20	1-20
Lutron	LP-RPM-4U-120		1-20	1-20	1-20	1-20	1-20	1-20	1-20

KEY (May exhibit one or several of the described parameters within the group)

Best	No flicker above 10% Full Light Output, good dimming range. Possible minor pop-on.
OK	No flicker above 20% Full Light Output and/or minor flicker which is hard to find at one specific point above 20%. Some limit of dim-range. Relatively high pop-on position reducing mechanical range.
NR	Use of this dimmer/lamp combination not recommended for the quantity of lamps indicated (# or range) or at all (X).
	Lamp not yet tested with this dimmer, compatibility unknown.

¹ Audible noise may be observed when used with this dimmer, depending on the application.² This dimmer has low end trim adjustment that may be used for optimal performance.

Misc. (G25,ST19)

Number of bulbs

Misc. (G25,ST19) Number of bulbs									
			8ST19/PER/927-922/CL/G/E26/WGX T20	8W A15 Filament T20	2.7W WG G25 Filament T20	3.8W Dimmable G25 Filament T20, P0025721	5.5A15/PER/927-922/CL/G/E26/WGX1FB	4GU10/LED/930/F35/DIM/G/120V T20 10/1	
Dimmer Company	Model No.		9290022960 (556530)	9290022093 (548313)	9290022080 (549360) 9290022047 (549352)	9290022070 (549212) 9290022069 (549204) 9290022068 (549196) 9290022067 (549188)	9290020915 (547959) 9290020915 (572669)	9290020555 (468140)	
Leviton	6602	Professional Channel	1-10	1-15	2-20	1-3	1-10	1-20	
Leviton	6631		1-10				1-10	1-20	
Leviton	6633		1-10	1-15	2-15	1-5	1-10	1-20	
Leviton	6672		1-10	1-15	8-20	1-5	1-10	1-20	
Leviton	6674		1-10				1-10	1-20	
Leviton	6615P		NR	1-9	1-10	1-2	NR	1-20	
Leviton	DSE06		1-10				1-10	1-20	
Leviton	DSL06		1-10				1-10	1-20	
Leviton	DSM10		1-10				1-10	1-20	
Leviton	IPI06		1-10	1-15	1-20	1-5	1-10	1-20	
Leviton	IPL06		1-10	1-8			1-10	1-20	
Leviton	VPI06		1-10				1-10	1-20	
Lutron	AYCL-153P		1-11				1-11	1-20	
Lutron	CTCL-153P		1-10				1-10	1-20	
Lutron	CTCL-153PDH		1-10				1-10	NR	
Lutron	DV-600P		1-10	1-15	1-20	1-5	1-10	1-20	
Lutron	DV-600PR		1-10				1-10	1-20	
Lutron	DVCL-153P		1-10				1-10	1-20	
Lutron	DVCL-253P		1-20				1-20	1-20	
Lutron	DVELV-300P		NR	1-9	1-20	1-20	NR	1-20	
Lutron	DVRP-253P		1-20				1-20	1-20	
Lutron	LGCL-153P		1-10				1-10	1-20	
Lutron	MACL-153M		1-10	1-15	1-20	1-5	1-10	1-20	
Lutron	MAELV-600		1-10				1-10	1-20	
Lutron	MALV-600		NR				NR	NR	
Lutron	MRF2-6ND-120		1-10	1-15	2-20	3-5	1-10	1-20	
Lutron	NTCL-250		1-20				1-20	1-20	
Lutron	PD-5NE		1-10				1-10	1-20	
Lutron	PD-6WCL		1-10	1-15	2-20	1-5	1-10	1-20	
Lutron	RRD-3LD		1-10				1-10	1-20	
Lutron	RRD-6NA		1-10	1-15	1-20	1-3	1-10	1-20	
Lutron	S-600P		1-10				1-10	1-20	
Lutron	SCL-153P		1-8				1-8	1-20	
Lutron	SCL-153PR		1-8				1-8	1-9	
Lutron	SELV-300P		1-10				1-10	1-19	
Lutron	SLV-600P		1-10	1-15	1-20	1-10	1-10	1-20	
Lutron	TGCL-153PH		1-10				1-10	1-20	
Cooper	RI061-VW-K2		1-10				1-10	1-20	
Eaton	DAL06P		1-10				1-10	1-20	
Legrand	HCL453P		1-10				1-10	1-20	
Sensors									
Lutron	MSCL-OP153M		1-10	1-15	1-20	1-5	1-10	1-20	
Lutron	MSCL-OP153MH		1-10	2-15	1-20	1-8	1-10	1-20	
Lutron	MS-OPS2H		1-10	1-15	1-20	1-20	1-10	1-20	
Panel Modules									
Lutron	GP (Harrier) Card		NR	1-10	1-20	1-20	NR	1-20	
Lutron	HW-RPM-4A-120		1-20	1-5	1	1-5	1-20	1-20	
Lutron	HW-RPM-4U-120		1-20	1-5	1	1-5	1-20	1-20	
Lutron	LP-RPM-4U-120		1-20	1-5	1	1-5	1-20	1-20	

KEY (May exhibit one or several of the described parameters within the group)

Best	No flicker above 10% Full Light Output, good dimming range. Possible minor pop-on.
OK	No flicker above 20% Full Light Output and/or minor flicker which is hard to find at one specific point above 20%. Some limit of dim-range. Relatively high pop-on position reducing mechanical range.
NR	Use of this dimmer/lamp combination not recommended for the quantity of lamps indicated (# or range) or at all (X).
	Lamp not yet tested with this dimmer, compatibility unknown.

¹ Audible noise may be observed when used with this dimmer, depending on the application.² This dimmer has low end trim adjustment that may be used for optimal performance.

WG = Warm Glow AF = Air Flux DS = Diamond Spark CC = Clear Classic DC = Die Cast DW = Direct White SO = Single Optic

Misc. (G25,ST19)

Number of bulbs

Misc. (G25,ST19) Number of bulbs									
			4GU10/LED/927-22/F35/G/WG/T20 10/1	3G16.5/MOD/840/E12/CL/GL/DIM 4/BC	4T10/MOD/840/E26/CL/GL/DIM 4/1BC	4G25/MOD/840/E26/CL/GL/DIM 4/1BC	3.8W WG G25 Filament T20, P0023793	3.8W (40W Eq) WG Candle, P0020414, P0023247	
Dimmer Company	Model No.		9290020553 (471565)	9290020014 (543157)	9290020009 (543132)	9290020008 (543124)	9290019699 (549527)	9290019515 (537605) 9290019515 (556837) 9290019513 (537597) 9290019513 (556829)	
Leviton	6602	Professional Channel	1-20	3-15	3-15	3-15	2	3-20	
Leviton	6631		1-20						
Leviton	6633		1-20	2-15	2-15	2-15	1-10	2-20	
Leviton	6672		1-20	1-15	1-15	1-15	1-5	1-20	
Leviton	6674		1-20	1-15	1-15	1-15			
Leviton	6615P		1-19	1-15	1-15	1-15	1-10	1-20	
Leviton	DSE06		1-20						
Leviton	DSL06		1-20						
Leviton	DSM10		1-20						
Leviton	IPI06		1-20	1-15	1-15	1-15	2-3	4-20	
Leviton	IPL06		1-20						
Leviton	VPI06		1-20						
Lutron	AYCL-153P		1-20						
Lutron	CTCL-153P		1-20						
Lutron	CTCL-153PDH		1-20						
Lutron	DV-600P		1-20	1-15	1-15	1-15	1-5	1-20	
Lutron	DV-600PR		1-20						
Lutron	DVCL-153P		1-20		1-15	1-15			
Lutron	DVCL-253P		1-20						
Lutron	DVELV-300P		1-20	1-15	1-15	1-15	1-10	1-20	
Lutron	DVRP-253P		1-20						
Lutron	LGCL-153P		1-20						
Lutron	MACL-153M		1-20				1-10	1-20	
Lutron	MAELV-600		1-20						
Lutron	MALV-600		NR						
Lutron	MRF2-6ND-120		1-20	1-15	1-15	1-15	2-10	1-10	
Lutron	NTCL-250		1-20						
Lutron	PD-5NE		NR						
Lutron	PD-6WCL		1-20	2-15	2-15	2-15	1-10	3-20	
Lutron	RRD-3LD		1-19						
Lutron	RRD-6NA		NR				1-10	1-20	
Lutron	S-600P		1-20						
Lutron	SCL-153P		1-20						
Lutron	SCL-153PR		1-9						
Lutron	SELV-300P		1-20						
Lutron	SLV-600P		1-20	1-15	1-15	1-15	1-10	1-20	
Lutron	TGCL-153PH		1-20						
Cooper	RI061-VW-K2		1-20						
Eaton	DAL06P		1-20						
Legrand	HCL453P		1-20						
Sensors									
Lutron	MSCL-OP153M		1-20				1-10	1-20	
Lutron	MSCL-OP153MH		1-20	1-15	1-15	1-15	1-10	1-20	
Lutron	MS-OPS2H		1-20	1-15	1-15	1-15	1-10	1-20	
Panel Modules									
Lutron	GP (Harrier) Card		1-15	1-15	1-15	1-15	1-10	1-20	
Lutron	HW-RPM-4A-120		NR	1-15	1-15	1-15	1-10	1-20	
Lutron	HW-RPM-4U-120		NR	1-15	1-15	1-15	1-10	1-20	
Lutron	LP-RPM-4U-120		NR	1-15	1-15	1-15	1-10	1-20	

KEY (May exhibit one or several of the described parameters within the group)

Best	No flicker above 10% Full Light Output, good dimming range. Possible minor pop-on.
OK	No flicker above 20% Full Light Output and/or minor flicker which is hard to find at one specific point above 20%. Some limit of dim-range. Relatively high pop-on position reducing mechanical range.
NR	Use of this dimmer/lamp combination not recommended for the quantity of lamps indicated (# or range) or at all (X).
	Lamp not yet tested with this dimmer, compatibility unknown.

¹ Audible noise may be observed when used with this dimmer, depending on the application.² This dimmer has low end trim adjustment that may be used for optimal performance.

Misc. (G25,ST19)

Number of bulbs

Misc. (G25,ST19) Number of bulbs								
			4.5A19/VIN/820/E26/CL/GL/DIM 4/ FBH T20	7.5T20/modern/840/CL/G/DIM 2/1CT	7.5A50/modern/840/CL/G/DIM 2/1CT	7.5G63/modern/840/CL/G/DIM 2/1CT	7.5T20/VIN/820/CL/G/E26/amber/ SP/DIM 1CT	7.5A50/VIN/820/CL/G/E26/amber/ SP/DIM 1CT
Dimmer Company	Model No.		9290019509 (556795)	9290019368 (536318)	9290019367 (536300)	9290019366 (536292)	9290019365 (575241)	9290019364 (575233)
Leviton	6602	Professional Channel	3-20	1-3	1-3	1-3	1-3	1--3
Leviton	6631							
Leviton	6633		2-20	NR	NR	NR	NR	NR
Leviton	6672		1-20	1-3	1-3	1-3	1-3	1-3
Leviton	6674			1-3	1-3	1-3	1-3	1-3
Leviton	6615P		1-20	1-3	1-3	1-3	1-3	1-3
Leviton	DSE06							
Leviton	DSL06							
Leviton	DSM10							
Leviton	IPI06		4-20	1-3	1-3	1-3	1-3	1-3
Leviton	IPL06							
Leviton	VPI06							
Lutron	AYCL-153P							
Lutron	CTCL-153P							
Lutron	CTCL-153PDH							
Lutron	DV-600P		1-20	1-3	1-3	1-3	1-3	1-3
Lutron	DV-600PR							
Lutron	DVCL-153P			1-3	1-3	1-3	1-3	1-3
Lutron	DVCL-253P							
Lutron	DVELV-300P		1-20	1-3	1-3	1-3	1-3	1-3
Lutron	DVRP-253P							
Lutron	LGCL-153P							
Lutron	MACL-153M		1-20				1-3	1-3
Lutron	MAELV-600							
Lutron	MALV-600							
Lutron	MRF2-6ND-120		1-10	1-3	1-3	1-3	1-3	1-3
Lutron	NTCL-250							
Lutron	PD-5NE							
Lutron	PD-6WCL		3-20	1-3	1-3	1-3	1-3	1-3
Lutron	RRD-3LD							
Lutron	RRD-6NA		1-20				1-3	1-3
Lutron	S-600P							
Lutron	SCL-153P							
Lutron	SCL-153PR							
Lutron	SELV-300P							
Lutron	SLV-600P		1-20	1-3	1-3	1-3	1-3	1-3
Lutron	TGCL-153PH							
Cooper	RI061-VW-K2							
Eaton	DAL06P							
Legrand	HCL453P							
Sensors								
Lutron	MSCL-OP153M		1-20				1-3	1-3
Lutron	MSCL-OP153MH		1-20	1-3	1-3	1-3	1-3	1-3
Lutron	MS-OPS2H		1-20	1-3	1-3	1-3	1-3	1-3
Panel Modules								
Lutron	GP (Harrier) Card		1-20	1-3	1-3	1-3	1-3	1-3
Lutron	HW-RPM-4A-120		1-20	1-3	1-3	1-3	1-3	1-3
Lutron	HW-RPM-4U-120		1-20	1-3	1-3	1-3	1-3	1-3
Lutron	LP-RPM-4U-120		1-20	1-3	1-3	1-3	1-3	1-3

KEY (May exhibit one or several of the described parameters within the group)

Best	No flicker above 10% Full Light Output, good dimming range. Possible minor pop-on.
OK	No flicker above 20% Full Light Output and/or minor flicker which is hard to find at one specific point above 20%. Some limit of dim-range. Relatively high pop-on position reducing mechanical range.
NR	Use of this dimmer/lamp combination not recommended for the quantity of lamps indicated (# or range) or at all (X).
	Lamp not yet tested with this dimmer, compatibility unknown.

¹ Audible noise may be observed when used with this dimmer, depending on the application.² This dimmer has low end trim adjustment that may be used for optimal performance.

WG = Warm Glow AF = Air Flux DS = Diamond Spark CC = Clear Classic DC = Die Cast DW = Direct White SO = Single Optic

Misc. (G25,ST19)

Number of bulbs

Misc. (G25,ST19) Number of bulbs									
			7.5G63/VIN/820/CL/G/E26/amber/ SP/DIM 1CT	3-5.5W WG filament	2.5-8W Dimmable Candle and Vintage	4.5W (40W) G16.5 filament dimmable	4.5W (60W Eq) Filament		
Dimmer Company	Model No.		9290019363 (575225)	9290019337 (536950) 9290019336 (536746) 9290019335 (536938) 9290019333 (536524)	9290019326 (536888) 9290019325 (536870) 9290019321 (536839) 9290019324 (536862) 9290019323 (536854)	9290019322 (536847) 9290018438 (478925) 9290018433 (478776) 9290018430 (478743) 9290018429 (478735)	9290018428 (478727) 9290013357 (475848) 9290013356 (475830) 9290012687 (466524)	9290018434 (478784) 9290013354 (475814) 9290012102 (461673)	9290012740 (466235)
Leviton	6602	Professional Channel	1-3	2-10	3-20	3-20	1-33		
Leviton	6631								
Leviton	6633		NR	1-10	2-20	2-20	1-33		
Leviton	6672		1-3	1-10	1-20	1-20	1-33		
Leviton	6674		1-3				1-10		
Leviton	6615P		1-3	1-10	1-20	1-20	1-17		
Leviton	DSE06								
Leviton	DSL06								
Leviton	DSM10								
Leviton	IPI06		1-3	1-10	4-20	4-20	1-33		
Leviton	IPL06								
Leviton	VPI06								
Lutron	AYCL-153P								
Lutron	CTCL-153P								
Lutron	CTCL-153PDH								
Lutron	DV-600P		1-3	2-10	1-20	1-20	1-33		
Lutron	DV-600PR								
Lutron	DVCL-153P		1-3						
Lutron	DVCL-253P								
Lutron	DVELV-300P		1-3	1-10	1-20	1-20	1-17		
Lutron	DVRP-253P								
Lutron	LGCL-153P								
Lutron	MACL-153M		1-3	1-10	1-20	1-20	1-33		
Lutron	MAELV-600								
Lutron	MALV-600								
Lutron	MRF2-6ND-120		1-3	2-10	1-10	1-10	1-33		
Lutron	NTCL-250								
Lutron	PD-5NE								
Lutron	PD-6WCL		1-3	NR	3-20	3-20	NR		
Lutron	RRD-3LD								
Lutron	RRD-6NA		1-3	1-3	1-20	1-20	1-17		
Lutron	S-600P								
Lutron	SCL-153P								
Lutron	SCL-153PR								
Lutron	SELV-300P								
Lutron	SLV-600P		1-3	2-10	1-20	1-20	1-25		
Lutron	TGCL-153PH								
Cooper	RI061-VW-K2								
Eaton	DAL06P								
Legrand	HCL453P								
Sensors									
Lutron	MSCL-OP153M		1-3	1-10	1-20	1-20	1-33		
Lutron	MSCL-OP153MH		1-3	1-10	1-20	1-20	1-33		
Lutron	MS-OPS2H		1-3	1-10	1-20	1-20	1-33		
Panel Modules									
Lutron	GP (Harrier) Card		1-3	1-10	1-20	1-20	1-33		
Lutron	HW-RPM-4A-120		1-3	1-10	1-20	1-20	1-33		
Lutron	HW-RPM-4U-120		1-3	1-10	1-20	1-20	1-33		
Lutron	LP-RPM-4U-120		1-3	1-10	1-20	1-20	1-33		

KEY (May exhibit one or several of the described parameters within the group)

Best	No flicker above 10% Full Light Output, good dimming range. Possible minor pop-on.
OK	No flicker above 20% Full Light Output and/or minor flicker which is hard to find at one specific point above 20%. Some limit of dim-range. Relatively high pop-on position reducing mechanical range.
NR	Use of this dimmer/lamp combination not recommended for the quantity of lamps indicated (# or range) or at all (X).
	Lamp not yet tested with this dimmer, compatibility unknown.

¹ Audible noise may be observed when used with this dimmer, depending on the application.² This dimmer has low end trim adjustment that may be used for optimal performance.

Misc. (G25,ST19)

Number of bulbs

							
		4.5W (40W Eq) 2700K	10W (60W Eq) G25 WG CC Bulb	7W (60W Eq) DS WG	7W (40W Eq) G25 WG CC Bulb	4.5W (40Eq) DS WG	6.5W (60W Eq) DS
Dimmer Company	Model No.	9290012138 (461913) 9290012138 (461947) 9290012138 (461953)	9290011898 (459347) 9290011816 (458828) 9290011898 (459354) 9290011816 (458844) 9290011898 (459339) 9290011816 (458836)	9290011822 (458620) 9290011822 (458638)	9290011817 (458802) 9290011817 (458794) 9290011817 (458810)	9290011674 (457150) 9290011674 (457143) 9290011672 (457168) 9290011672 (457176)	9290002886 (435180)
Leviton	6602	2-30	9-15	1-21	1-21	1-26	NR
Leviton	6631						
Leviton	6633	2-30	1-15	1-21	1-21	1-26	1-10
Leviton	6672	2-30	1-15	1-21	1-21	1-26	1-10
Leviton	6674	2-30	1-15	1-21	1-21	1-10	1-10
Leviton	6615P	2-16	1-8	1-11	1-11	1-13	NR
Leviton	DSE06						
Leviton	DSL06						
Leviton	DSM10						
Leviton	IPI06	2-30	1-15	1-21	1-21	1-26	NR
Leviton	IPL06						
Leviton	VPI06						
Lutron	AYCL-153P						
Lutron	CTCL-153P						
Lutron	CTCL-153PDH						
Lutron	DV-600P	2-30	1-15	1-21	1-21	1-26	1-10
Lutron	DV-600PR						
Lutron	DVCL-153P						
Lutron	DVCL-253P						
Lutron	DVELV-300P	1-16	1-8	1-11	1-11	1-13	NR
Lutron	DVRP-253P						
Lutron	LGCL-153P						
Lutron	MACL-153M	2-30	1-15	1-21	1-21	1-26	1-10
Lutron	MAELV-600						
Lutron	MALV-600						
Lutron	MRF2-6ND-120	2-30	1-15	1-21	1-15	1-26	1-10
Lutron	NTCL-250						
Lutron	PD-5NE						
Lutron	PD-6WCL	2-30	1-15	NR	1-21	NR	1-10
Lutron	RRD-3LD						
Lutron	RRD-6NA	2-30	1-15	1-25	NR	NR	1-10
Lutron	S-600P						
Lutron	SCL-153P						
Lutron	SCL-153PR						
Lutron	SELV-300P						
Lutron	SLV-600P	2-30	1-11	1-16	1-16	1-19	1-10
Lutron	TGCL-153PH						
Cooper	RI061-VW-K2						
Eaton	DAL06P						
Legrand	HCL453P						
Sensors							
Lutron	MSCL-OP153M	2-30	1-15	1-21	1-21	1-26	1-10
Lutron	MSCL-OP153MH	2-30	11-15	NR	1-21	1-33	
Lutron	MS-OPS2H	2-30	1-15	1-21	1-21	1-33	
Panel Modules							
Lutron	GP (Harrier) Card	2-30	1-15	1-25	1-21	1-40	1-10
Lutron	HW-RPM-4A-120	2-30	1-15	1-25	1-21	1-45	1-10
Lutron	HW-RPM-4U-120	2-30	1-15	1-25	1-21	1-45	1-10
Lutron	LP-RPM-4U-120	2-30	1-15	1-25	1-21	1-45	1-10

KEY (May exhibit one or several of the described parameters within the group)

Best	No flicker above 10% Full Light Output, good dimming range. Possible minor pop-on.
OK	No flicker above 20% Full Light Output and/or minor flicker which is hard to find at one specific point above 20%. Some limit of dim-range. Relatively high pop-on position reducing mechanical range.
NR	Use of this dimmer/lamp combination not recommended for the quantity of lamps indicated (# or range) or at all (X).
	Lamp not yet tested with this dimmer, compatibility unknown.

¹ Audible noise may be observed when used with this dimmer, depending on the application.² This dimmer has low end trim adjustment that may be used for optimal performance.

WG = Warm Glow AF = Air Flux DS = Diamond Spark CC = Clear Classic DC = Die Cast DW = Direct White SO = Single Optic

Misc. (G25,ST19)

Number of bulbs

Misc. (G25,ST19) Number of bulbs					
			3.5W DW	4W (40W Eq) WG	3W
Dimmer Company	Model No.		9290002420 (427807)	469676	427237 420414 426916 410217 420430 410209 420422
Leviton	6602	Professional Channel		3-20	
Leviton	6631				NR
Leviton	6633			2-20	
Leviton	6672		1-10	1-20	
Leviton	6674		1-17		1-6
Leviton	6615P		NR	1-20	NR
Leviton	DSE06				
Leviton	DSL06				
Leviton	DSM10				
Leviton	IPI06		NR	4-20	NR
Leviton	IPL06				
Leviton	VPI06				
Lutron	AYCL-153P				NR
Lutron	CTCL-153P				NR
Lutron	CTCL-153PDH				
Lutron	DV-600P		1-21	1-20	1-8
Lutron	DV-600PR				
Lutron	DVCL-153P				
Lutron	DVCL-253P				NR
Lutron	DVELV-300P		1-42	1-20	1-2
Lutron	DVRP-253P				
Lutron	LGCL-153P				
Lutron	MACL-153M		1-42	1-20	1-12
Lutron	MAELV-600				1-12
Lutron	MALV-600				NR
Lutron	MRF2-6ND-120		1-10	1-10	NR
Lutron	NTCL-250				NR
Lutron	PD-5NE				
Lutron	PD-6WCL			3-20	
Lutron	RRD-3LD				
Lutron	RRD-6NA		1-42	1-20	1-12
Lutron	S-600P				NR
Lutron	SCL-153P		4-42		
Lutron	SCL-153PR				
Lutron	SELV-300P				1-12
Lutron	SLV-600P		NR	1-20	1-12
Lutron	TGCL-153PH				
Cooper	RI061-VW-K2				NR
Eaton	DAL06P				
Legrand	HCL453P				
Sensors					
Lutron	MSCL-OP153M		1-42	1-20	1-7
Lutron	MSCL-OP153MH			1-20	
Lutron	MS-OPS2H			1-20	
Panel Modules					
Lutron	GP (Harrier) Card			1-20	
Lutron	HW-RPM-4A-120			1-20	
Lutron	HW-RPM-4U-120			1-20	
Lutron	LP-RPM-4U-120			1-20	

KEY (May exhibit one or several of the described parameters within the group)

Best	No flicker above 10% Full Light Output, good dimming range. Possible minor pop-on.
OK	No flicker above 20% Full Light Output and/or minor flicker which is hard to find at one specific point above 20%. Some limit of dim-range. Relatively high pop-on position reducing mechanical range.
NR	Use of this dimmer/lamp combination not recommended for the quantity of lamps indicated (# or range) or at all (X).
	Lamp not yet tested with this dimmer, compatibility unknown.

¹ Audible noise may be observed when used with this dimmer, depending on the application.

² This dimmer has low end trim adjustment that may be used for optimal performance.

[illegible]



© 2025 Signify Holding. All rights reserved. The information provided herein is subject to change, without notice. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify.

08/2025 philips.com/lighting

Signify North America Corporation
200 Franklin Square Drive,
Somerset, NJ 08873
Telephone 855-486-2216

Signify Canada Ltd.
281 Hillmount Road,
Markham, ON, Canada L6C 2S3
Telephone 800-668-9008

Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.
All other trademarks are owned by Signify Holding or their respective owners.