

Philips MasterColor
CDM Elite MR16

Ideal for accent/decorative lighting, general lighting and downlighting in retail applications; or for outdoor landscaping and architectural effects.

MasterColor CDM Elite



Accent with sparkling, energy efficient light

Philips MasterColor CDM Elite MR16 combines the familiar compact shape of MR16 halogen lamps with the performance of ceramic metal halide MasterColor Elite lamps.

MasterColor Elite technology

- Long life—12,000 hours rated average life¹ for 39 watt and 50 watt, 15000 hours rated average life for 20 watt
- New 50 watt available
- Sparkling light— up to 90 CRI with crisp white light (3000K)
- Lamp-to-lamp color consistency up to 90CRI with crisp white light (3000K)

Easy to install, easy to replace

- GX10 twist-and-lock design locks base into place
- 100% compatible with existing HID systems in market today
- Miniturized reflector eliminates need for optical design

Excellent choice for today's lighting designs

- Compact size suitable for open fixtures
- Beam spreads available in 10°, 25° and 40°

(1. See back page for footnotes)

PHILIPS

Ordering Data (Subject to change without notice)

Product Number	Ordering Code	Nom. Watt.	MBCP ²	Approx. Beam Angle ³	Approx. Initial Lumens ⁴	Mean Lumens ⁵
42165-1	CDM-MRI6 20W/830 10D ELITE	20	12,500	10°	1050	850
42166-9	CDM-MRI6 20W/830 25D ELITE	20	4,500	25°	1050	850
42167-7	CDM-MRI6 20W/830 40D ELITE	20	2,100	40°	1050	850
41893-9	CDM-MRI6 35W/930 10D ELITE	39	20,000	10°	2400	2200
41894-7	CDM-MRI6 35W/930 25D ELITE	39	8,500	25°	2400	2200
41895-3	CDM-MRI6 35W/930 40D ELITE	39	4,400	40°	2400	2200
41553-9	CDM-MRI6 50W/930 25D ELITE	50	11,500	25°	3400	3200
41554-7	CDM-MRI6 50W/930 40D ELITE	50	7,000	40°	3400	3200

Electrical and Technical Data

Lamp Operating Volt. (rms)(Nom.)⁶ _____ 93 (20w)
 _____ 87 (39w)
 _____ 89 (50w)
 Initial Lamp Volt. Range (rms)⁷ _____ 88-98 (20w)
 _____ 79-95 (39w)
 _____ 80-98 (50w)
 Lamp Operating Current (Amps) Nominal _____ 0.215 (20w)
 _____ 0.45 (39w)
 _____ .575 (50w)
 Warm-up to 80% Full Brightness _____ 2 minutes
 Restrike Time for Hot Lamps _____ 15 minutes
 Ballast Open Circuit Voltage _____ 250 RMS Min. (20w)
 _____ 209 RMS Min. (39w)
 Pulse Peak Volts _____ 3000-4000
 Pulse Width @ 90% Peak _____ 2 Micro Sec. Minimum
 Pulse Repetition Rate (Minimum)⁸ _____ 1 per Half Cycle
 Minimum Operating Temp. _____ -30°C (-22°F)

Ordering Information

ANSI Designation _____ C156/O (20w)
 _____ C130/O (39w)
 _____ C193/O (50w)
 Package Quantity _____ 6

1) Rated average life is the life obtained, on the average, from large representative groups of lamps in laboratory tests under controlled conditions at 10 or more operating hours per start. It is based on survival of at least 50% of the lamps and allows for individual lamps or groups of lamps to vary considerably from the average.
 2) Maximum Beam Candlepower
 3) Beam Angle at 50% of MBCP
 4) Measured at 100 hrs. life. Approximate lumen values listed are for vertical operation of the lamp.

Physical Characteristics

Bulb Size _____ MR-16
 Bulb Finish _____ Clear
 Base _____ GX-10
 Max. Overall Length (MOL) _____ 2.6" (65.4mm)
 Max. Permissible Temperatures:
 Bulb _____ 300°C (572°F)
 Base _____ 200°C (392°F)
 Lens-to-Reflector Rim _____ 160°C (320°F)
 Arc Tube Material _____ Polycrystalline Alumina

Operating Characteristics

Rated Average Life, Hours¹ _____ 15,000 (20w)
 _____ 12,000 (39w, 50w)
 CRI _____ 87 (20w)
 _____ 91 (39w)
 _____ 90 (50w)
 Correlated Color Temp. (CCT)⁹ _____ 3000K
 CIE Chromaticity Approx.⁹ _____ x-.440, y-.400 (20w)
 _____ x-.439, y-.403 (39w)
 _____ x-.441, y-.406 (50w)
 Efficacy (lpw) _____ 52 (20w)
 _____ 61 (39w)
 _____ 68 (50w)

Operating Position

Universal—Open or Enclosed Luminaire

Note: Use on thermally protected electronic ballast only.

5) Approximate lumen output at 40% of lamp rated average life.
 6) Measured at rated lamp watts on a linear reactor.
 7) Measured with the lamp operating at rated watts.
 8) Option-Pulse Width @ 90% Peak, 1 micro second minimum with 2 pulses per half cycle.
 9) Measured at 100 hours life.
 Above specifications subject to change without notice.

WARNINGS, CAUTIONS AND OPERATING INSTRUCTIONS

R "WARNING: These lamps can cause serious skin burn and eye inflammation from short wave ultraviolet radiation if outer envelope of the lamp is broken or punctured. Do not use where people will remain for more than a few minutes unless adequate shielding or other safety precautions are used. Certain lamps that will automatically extinguish when the outer envelope is broken or punctured are commercially available." This lamp complies with FDA radiation performance standard 21 CFR subchapter J. (USA:21CFR 1040.30 Canada: SOR/DORS/80-381)

If the outer bulb is broken or punctured, turn off at once and replace the lamp to avoid possible injury from hazardous short wave ultraviolet radiation. Do not scratch the outer bulb or subject it to pressure as this could cause the outer bulb to crack or shatter. A partial vacuum in the outer bulb may cause glass to fly if the envelope is struck.

WARNING: The arc-tube of metal halide lamps are designed to operate under high pressure and at temperatures up to 1000° C and can unexpectedly rupture due to internal or external factors such as a ballast failure or misapplication. If the arc-tube ruptures for any reason, the outer bulb may break and pieces of extremely hot glass might be discharged into the surrounding environment. If such a rupture were to happen, **THERE IS A RISK OF PERSONAL INJURY, PROPERTY DAMAGE, BURNS AND FIRE.** These lamps are designed to retain all the glass particles should an arc tube rupture occur. The following operating instructions are recommended to minimize these occurrences.

RELAMP FIXTURES AT OR BEFORE THE END OF RATED LIFE. Allowing lamps to operate until they fail is not advised and may increase the possibility of inner arc tube rupture.

CAUTION: TO REDUCE THE RISK OF PERSONAL INJURY, PROPERTY DAMAGE, BURNS AND FIRE RESULTING FROM AN ARC-TUBE RUPTURE THE FOLLOWING **LAMP OPERATING INSTRUCTIONS** MUST BE FOLLOWED:

LAMP OPERATING INSTRUCTIONS:

- RELAMP FIXTURES AT OR BEFORE THE END OF RATED LIFE. Allowing lamps to operate until they fail is not advised and may increase the possibility of inner arc tube rupture.
- Before lamp installation/replacement, shut power off and allow lamp and fixture to cool to avoid electrical shock and potential burn hazards.
- Use only auxiliary equipment meeting Philips and/or ANSI standards. Use within voltage limits recommended by ballast manufacturer.
 - A. Operate lamp only within specified limits of operation.
 - B. For total supply load refer to ballast manufacturers electrical data.
 - C. Operate lamps only on thermally protected electronic ballast.**
- Periodically inspect the outer envelope. Replace any lamps that show scratches, cracks or damage.
- If a lamp bulb support is used, be sure to insulate the support electrically to avoid possible decomposition of the bulb glass.
- Protect lamp base, socket and wiring against moisture, corrosive atmospheres and excessive heat.
- Time should be allowed for lamps to stabilize in color when turned on for the first time. This may require several hours of operation, with more than one start. Lamp color is also subject to change under conditions of excess vibration or shock, and color appearance may vary between individual lamps.
- Lamps may require up to 15 minutes to re-light if there is a power interruption.
- Take care in handling and disposing of lamps. If an arc tube is broken, avoid skin contact with any of the contents or fragments.
- For proper installation and removal, lamp should be handled by the sides of the reflector and not by the aluminum front anti-glare cap.



Do not place in trash - dispose according to local, state, or federal laws



© 2012 Philips Lighting Company. A Division of Philips Electronics North America Corporation
 All rights reserved.
 Printed in USA 10/12
 P-5986-F
 www.philips.com

Philips Lighting Company
 200 Franklin Square Drive
 Somerset, NJ 08873
 1-800-555-0050

Philips Lighting
 281 Hillmount Road
 Markham, Ontario
 Canada L6C 2S3
 1-800-555-0050
 A Division of Philips Electronics Ltd.