



Compact Fluorescent
Energy Saver 3-Way
Twister Lamp

*Ideal for table lamps
and floor lamps*

ENERGY SAVER

Energy saver 3-Way twister

Philips 3-Way Twister Compact Fluorescent Lamp
is a new innovative approach to 3-Way lighting.

The ideal light bulb to replace the 50/100/150 Watt incandescent 3-Way in table lamps and floor lamps.

Direct replacement for incandescent bulbs

- Double Helix Technology—utilizes two separate burners to provide three distinctive light levels
- ENERGY STAR® qualified
- Light does not flicker
- Settings are low/medium/high
- Save 39/77/116 watts in your 3-Way lamps when you replace a 50/100/150 watt incandescent 3-Way with an 11/23/34 energy saver 3-Way twister
- Optimized color quality to match incandescent lamps
- Harp extenders included

Long life

- Lasts 9 years*

* Based on an average daily usage of 3–4 hours per day, 7 days per week.

PHILIPS

Compact Fluorescent Energy Saver 3-Way Twister Lamp

Ordering, Electrical and Technical Data (Subject to change without notice)

Product Number	Description	Volts	Approx. Nom. Watts	Incand. Equiv.	Color Base	Temp. (Kelvin)	Approx. CRI	Approx. Initial Lumens ¹	MOL (In.)	Diam. (In.)	Rated Avg. Life (Hrs.) ²	Min. Starting Temp.	Max. Ambient Temp.
21193-8	EL/3W 11-23-34	120	11/23/34	50/100/150	Med.	2700	82	700/1500/2200	6.7	2.9	10,000	-22°F/-30°C	140°F/60°C

Shipping Data

Product Number	SKU UPC (0-46677)	Outer Bar Code (5-00-46677)	Case Qty.	Case Weight (lbs.)	Case Cube (cu. ft.)	Pallet Qty.	SKUs Per Layer	Layers High	SKU Dimensions (W x D x H) (In.)	Case Dimensions (W x D x H) (In.)	Pallet Dimensions (W x D x H) (In.)
21193-8	21193-6	21193-1	6	2.7	.30	1080	180	6	3.0 x 3.0 x 7.5	9.4 x 6.3 x 7.5	49.0 x 4.01 x 47.6

1) Approximate initial lumens. The lamp lumen output is based upon lamp performance after 100 hours of operating life under standard laboratory conditions.

2) Average life under specified test conditions with lamps turned off and restarted no more frequently than once every 3 operating hours. Use in recessed cans or enclosed indoor fixtures could result in reduced lamp life. This product should not be used in a socket that is not suitable for 3-Way type lights.

WARNINGS AND CAUTIONS: Do not use with dimmers. Some electronic timer and photo sensor switches contain dimming circuitry, so before using such a switch, check with its manufacturer to ensure compatibility with electronic CFL bulbs. Do not use with emergency exit fixtures or lights. Outdoor use requires a weather-protected fixture. Turn off power before changing bulb. This device complies with Part 18 of the FCC Rules. Reliable operating temperature range -10°F/-23°C to 140°F/60°C.

Note: This product may cause interference with radios, televisions, telephones, or remote controls. If interference occurs, move this product away from device or plug into another outlet.

Bulb Type	Table/Floor Lamp	Outdoor Postlight	Wall Sconce	Surface Mount	Reading Lamp	Border Lights	Recessed Fixture	Open Hanging	Vanity Strip	Ceiling Fan	Chandelier
Twister	•	•	•	•	•			•			
3-Way	•				•						
GU24	•		•	•	•		•	•		•	
Soft White Plus	•	•	•		•	•		•		•	
Reflector Flood							•	•			
Dimmable Reflector Flood							•	•			
Decorative Globe		•						•	•	•	
Decorative Candle		•	•		•					•	•
Outdoor		•				•		•			
Bug-A-Way		•				•		•			
Universal	•	•	•	•	•	•	•	•			
Genie	•	•	•	•	•			•			



Do not place in trash - dispose according to local, state, or federal laws



© 2016 Philips Lighting Holding B.V. All rights reserved. Philips reserves the right to make changes in specifications and/or to discontinue any product at any time without notice or obligation and will not be liable for any consequences resulting from the use of this publication.



Philips Lighting North America Corporation
200 Franklin Square Drive, Somerset, NJ 08873
Tel. 855-486-2216

Philips Lighting Canada Ltd.
281 Hillmount Rd, Markham, ON, Canada L6C 2S3
Tel. 800-668-9008