

Energy saving silicone lamps.



PHILIPS ENERGY SAVER SILICONE COMPACT FLUORESCENT LAMPS

Philips Energy Saver Silicone compact fluorescent lamps provide worry-free energy savings and reduced operating costs.

Energy savings

- 14W saves up to \$40 in energy costs as compared to a 60W incandescent lamp*

Long life

- Lasts 8,000 hours**

Energy saving replacement for incandescent bulbs

- Shatter Resistant for safety
- Silicone cover contains broken glass for a no mess clean up
- Soft-to-the-Touch
- Provides warm, white light
- Smaller size fits most applications

*, **. See footnotes on reverse side.

PHILIPS

PHILIPS ENERGY SAVER SILICONE COMPACT FLUORESCENT LAMPS

Ordering, Electrical and Technical Data (Subject to change without notice)

Part Number	Ordering Code	Nom. Watts	Volts	Lamps per SKU	Lamp Type	Lamp Base	Rated Avg. Life (Hrs.) ¹	Approx. Lumens ²	CRI	Color Temp (K)	MOL (in.)	Mercury Max
41503-4	EL/A T2 SC 14W 6/2	14	120	2	Silicone A17	Medium	8000	800	82	2700	4	2.0
41504-2	EL/A T2 SC 9W 6/2	9	120	2	Silicone A17	Medium	8000	450	82	2700	4	2.0

1. Rated average life is the length of operation (in hours) at which point an average of 50% of the lamps will still be operational and 50% will not.
2. Approximate lumen output at 40% of lamp rated average

Footnotes from front:

* At \$0.11 kWh, this 14-Watt Energy Saver bulb rated at 800 lumens uses \$12.32 of electricity over its 8000 hour life. This is a \$40.48 savings when compared to the \$52.80 required to run a 60-watt incandescent bulb rated at 800 lumens over the same period. Actual savings will vary depending on cost per kWh in your area.

** Based on 3 hours average usage per day/7 days per week.

Shipping Data (Subject to change without notice)

Product Number	SKU UPC (0-46677)	Outer Bar Code (5-00-46677)	Case Qty.	Case Weight (lbs.)	Case Cube (cu. ft.)	Pallet Qty.	SKUs per Layer	Layers High	SKU Dimensions (W x D x H) (In.)	Case Dimensions (W x D x H) (In.)	Pallet Dimensions (W x D x H) (In.)
41503-4	41503-7	41503-2	6	2.53	0.66	288	72	4	8.2 x 2.4 x 7.4	8.9 x 15.7 x 8.1	39.4 x 47.2 x 38.1
41504-2	41504-4	41504-9	6	0.66	0.154	288	72	4	8.2 x 2.4 x 7.4	8.9 x 15.7 x 8.1	39.4 x 47.2 x 38.1

WARNINGS AND CAUTIONS:

Some electronic timer and photosensor switches contain dimming circuitry, so before using such a switch, check with its manufacturer to ensure compatibility with electronic CFL bulbs. Do not use with emergency exit fixtures or lights. Outdoor use requires weather-protected fixture. Do not use where directly exposed to water. Before replacing, turn off power and let lamp cool to avoid electrical shock or burn. This device complies with Part 18 of the FCC Rules. Not for use in totally enclosed recessed fixtures. Reliable operating temperature range -4°F/-20°C to 140°F/60°C.

Note: This product may cause interference with radios, televisions, telephones, or remote controls. If interference occurs, move this product away from device or plug into another outlet.



Do not place in trash - dispose according to local, state, or federal laws

© 2017 Philips Lighting Holding B.V. All rights reserved.
Philips reserves the right to make changes in specifications and/or to discontinue any product at any time without notice or obligation and will not be liable for any consequences resulting from the use of this publication.



Philips Lighting North America Corporation
200 Franklin Square Drive, Somerset, NJ 08873
Tel. 855-486-2216

Philips Lighting Canada Ltd.
281 Hillmount Rd, Markham, ON, Canada L6C 2S3
Tel. 800-668-9008