

# PHILIPS

## LED lamps

### CorePro Corn Cob with Selectable CCT

For a range of industrial,  
commercial and urban applications



Lumen  
Select Switch



CCT with  
Select Switch

# The flexibility of perfect light output for multiple applications with one lamp

Hassle-free UL Type-B retrofit lamps designed with lumen and CCT selectable features, offering customizable light output replacing up to 8500 lumens and continuous dimming down to 20%. Designed to fit fixtures in most relevant applications, these omni-directional ballast-bypass lamps provide an ideal and affordable way to upgrade existing HID fixtures to the latest LED technology.

## Benefits

- Reduce & streamline inventory with three color temperatures in one lamp
- Passive Cooling lamps eliminate fan noise and reduces moving parts which require additional maintenance over time
- Up to 80% energy savings<sup>1</sup>
- Long life lowers maintenance costs by reducing re-lamp frequency
- UL Type B solution allows installer to bypass the ballast and reduce maintenance costs


## Features

- Built in switch to select CCT for different applications
- Wide ambient temperature operating range from -22°F to +122°F (-30°C to 55°C)
- DLC 5.1 certified mogul based lamps
- UL damp rated (UL1993 + UL1598C)
- Built in surge protection
- Choose between 3000K, 4000K or 5000K color temperatures in one lamp (CCT)
- Built in Dial to select lumen output level down to 20%
- Universal burn positioning
- Suitable for both enclosed and open fixtures
- 5-year limited warranty<sup>2</sup>

1. LED system watts of 36 compared to 120 of a C100S54/ALTO.

2. Depending upon operating hours. For details please visit [www.signify.com/warranties](http://www.signify.com/warranties).

# Philips LED CorePro Corn Cob lamps with Selectable CCT



Ordering, electrical and technical data (Subject to change without notice)



|     | Product Model<br>No. (6nc)No. (12nc) | Description  | Watts<br>(W)                    | Replace<br>Watts (W) | Lumens<br>(lm) | Volts<br>(V)   | CRI<br>(min) | CCT<br>(K) | Lifetime¹<br>(hrs) | Qty per<br>pallet | DLC ID (Type A)² |              |
|-----|--------------------------------------|--------------|---------------------------------|----------------------|----------------|----------------|--------------|------------|--------------------|-------------------|------------------|--------------|
|     | CorePro EX39 lamps                   |              |                                 |                      |                |                |              |            |                    |                   |                  |              |
| D E | 570465                               | 929003065204 | 36CC/LED/3CCT/LS EX39 G3 BB 3/1 | 36                   | 150            | 4800/5000/5000 | 100-277      | 80         | 3000/4000/5000     | 50,000            | 408              | PLBJN6CXJY4T |
| D E | 570473                               | 929003065304 | 45CC/LED/3CCT/LS EX39 G3 BB 3/1 | 45                   | 175            | 5800/6200/6200 | 100-277      | 80         | 3000/4000/5000     | 50,000            | 306              | PLQBU4L9A885 |
| D E | 570481                               | 929003065404 | 54CC/LED/3CCT/LS EX39 G3 BB 3/1 | 54                   | 250            | 7000/7500/7500 | 100-277      | 80         | 3000/4000/5000     | 50,000            | 306              | PLI2F538JT5L |
| D E | 570499                               | 929003065504 | 63CC/LED/3CCT/LS EX39 G3 BB 3/1 | 63                   | 250            | 7800/8500/8500 | 100-277      | 80         | 3000/4000/5000     | 50,000            | 306              | PLKHJQIOIQ2U |

D = Damp location E = Enclosed fixtures

## Energy saving solution

### For CorePro LED Corn Cob G2 Passive cooling 63w

#### Estimated lighting costs using a 175 MH lamp with ballast

|                          |                                 |
|--------------------------|---------------------------------|
| Present Wattage          | 201 watts                       |
| × Annual operating hours | 4,000 hours                     |
| =                        | 804,000 watt-hours              |
| ÷ 1,000                  | = 804 kWh per year              |
| × kWh rate of \$0.11     | = \$88.44 per year              |
| × 100 lamps              | = \$8,844.00 annual energy cost |

#### Estimated lighting costs using a Philips Corn cob LED lamp

|                          |                                 |
|--------------------------|---------------------------------|
| Present Wattage          | 63 watts                        |
| × Annual operating hours | 4,000 hours                     |
| =                        | 252,000 watt-hours              |
| ÷ 1,000                  | = 252 kWh per year              |
| × kWh rate of \$0.11     | = \$27.72 per year              |
| × 100 lamps              | = \$2,772.00 annual energy cost |

#### Total estimated savings \$6,072.00 annual savings

Based on 100 lamps per space operating at 4000 hours per year.

This example shows an application of 100 lamps accenting a space, operating 4,000 hours. Your actual savings may vary depending on the energy costs in your geographic location.

#### WARNINGS AND CAUTIONS

**Risk of property damage or personal injury** – The weight of the lamp is within the UL weight specification of a mogul (E39) base. However, before installing the lamp please ensure that the lamp holder (or socket) is not damaged or loose. The lamp holder (or socket) must be secured firmly to the fixture. If the lamp holder is damaged, corroded, charred or blackened, it must be replaced.

**CAUTION:** Risk of electric shock – do not use where directly exposed to water.

**NOTES:** This device complies with Part 15 of the FCC rule. Operation is subject to the following two conditions: (1) this device may not cause harmful interference, and (2) this device must accept any interference received, including interference that may cause undesired operation. This Class B digital apparatus complies with Canadian ICES-005. Any changes or modifications not expressly approved by the party responsible for compliance could void the user's authority to operate the equipment. This lamp is suitable for dry and/or damp locations (indoor & outdoor applications). Suitable for use in outdoor luminaires as these luminaires provide a damp location for the lamp. This lamp is suitable for use in totally enclosed luminaires.

For more details visit: <https://www.usa.lighting.philips.com/products/product-highlights/led-hid-replacements>

- LED lifetime means the length of time (in hours) until half of the LED light sources maintain at least 70% of their initial lumen output (B50, L70). Lamps rated 50,000 hours is for bare lamp without fixture.
- Lamp may also be DLC certified as a Type C system. Search DLC by model number QPL for more information.



© 2021 Signify Holding. All rights reserved. The information provided herein is subject to change, without notice. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify.

PLT-21024BN 10/21 philips.com/lighting



Signify North America Corporation  
200 Franklin Square Drive,  
Somerset, NJ 08873  
Telephone 855-486-2216

Signify Canada Ltd.  
281 Hillmount Road,  
Markham, ON, Canada L6C 2S3  
Telephone 800-668-9008

Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V. All other trademarks are owned by Signify Holding or their respective owners.