


PHILIPS

LED lamps

MainsFit CorePro (UL Type-B)



- ✓ **Adjustable** colors
- ✓ **Energy saving**
- ✓ **Flexibility**

Philips MainsFit (Type B) CorePro Adjustable Color Temperature PL-C/PL-T replacement lamp family provides a unique solution to end users by providing three color choices in one lamp.


Benefits

- **Proven over 40% energy savings¹** over fluorescent systems.
- **Lifetime delivered** average life rating of 30,000 hours² means satisfied customers.
- **Ballast Bypass** – UL Type-B.
- **Socket compatibility** – ideal for use in 26w & 32w, 2pin & 4pin sockets (G24d-3, G24q-3 and GX24q-3) but compatible with other offset 2pin (G24d-2, G24q-1, G24q-2) and 4pin (GX24q-2, GX24q-4) sockets.
- **Adjustable Color Temperature** choose from 3000K, 3500K, or 4000K to suit the needs of end users
- **Optimized light distribution** available in horizontal or vertical lamp configuration to work in all applications
- **Light quality and performance predictability** providing consistent light output and no flicker which results in satisfied customers and no wasted time redoing a job.
- **Proven product history** from a company with a long history of innovation and reliability in the lighting industry.

1. Actual savings depend on the PL-C/PL-T lamp and ballast used.

2. Tested to B50 L70 requirement.

Philips MainsFit CorePro PLED lamps (UL Type B)



Ordering, electrical and technical data (Subject to change without notice)

Product No. (6nc)	Model No. (12nc)	DLC Product ID	Description	Volts (V)	Watts (W)	Lumens (lm)	CRI (min)	CCT (K)	Lifetime ¹ (hrs)	Beam Angle	MOL (in)	Materials	Pkg Qty
PL-C/PL-T Replacement CorePro													
577890	9290034776	Pending	8PL-C/T/COR/26H-3CCT/MF10/P/20/1	120-277	8	975/1000/1050	83	3000/3500/4000	30000	120	5.9	Plastic	20
577908	9290034777	Pending	8PL-C/T/COR/26V-3CCT/MF10/P/20/1	120-277	8	975/1000/1050	83	3000/3500/4000	30000	120	4.7	Plastic	20
577916	9290034778	Pending	11PL-C/T/COR/32H-3CCT/MF15/P/20/1	120-277	11	1425/1450/1500	83	3000/3500/4000	30000	120	5.9	Plastic	20
577924	9290034779	Pending	11PL-C/T/COR/32V-3CCT/MF15/P/20/1	120-277	11	1425/1450/1500	83	3000/3500/4000	30000	120	4.7	Plastic	20

1. Tested to B50 L70 requirement. LED lifetime means the length of time (in hours) until half of the LED light sources maintain at least 70% of their initial lumen output (B50, L70).

For more information on Philips' limited warranty please visit www.philips.com/warranties.



© 2022 Signify Holding. All rights reserved. The information provided herein is subject to change, without notice. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify.

PLt-22039BN 03/22 philips.com/lighting



Signify North America Corporation
400 Crossing Blvd, Suite 600
Bridgewater, NJ 08807
Telephone: 855-486-2216

Signify Canada Ltd.
281 Hillmount Road,
Markham, ON, Canada L6C 2S3
Telephone: 800-668-9008

Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V. All other trademarks are owned by Signify Holding or their respective owners.