



9290030338 Filament 75W E27 2700K A60 CL ND

1 x 1055 lm


Polar intensity diagram



Quantity estimation diagram



UGR diagram



Light output ratio 1.00
Service upward 0.50
Service downward 0.50

CIE flux code 16 41 70 50 100

UGRcen (4Hx8H, 0.25H) 28

Utilisation factor table

Room Index k	Reflectances (%) for ceiling, walls and working plane (CIE)											
	0.80 0.80				0.70 0.70				0.50 0.50			
	0.50	0.50	0.30	0.10	0.50	0.50	0.30	0.10	0.50	0.50	0.30	0.10
0.60	0.33	0.31	0.30	0.29	0.28	0.21	0.17	0.13	0.14	0.10	0.05	0.00
0.80	0.41	0.39	0.38	0.37	0.36	0.28	0.23	0.18	0.18	0.14	0.07	0.00
1.00	0.49	0.45	0.44	0.43	0.41	0.33	0.28	0.23	0.22	0.18	0.10	0.00
1.25	0.56	0.51	0.51	0.49	0.47	0.39	0.32	0.27	0.26	0.22	0.13	0.00
1.50	0.62	0.56	0.56	0.54	0.52	0.44	0.37	0.31	0.29	0.25	0.15	0.00
2.00	0.71	0.63	0.64	0.61	0.58	0.51	0.43	0.38	0.35	0.31	0.19	0.00
2.50	0.77	0.68	0.70	0.66	0.63	0.56	0.47	0.43	0.39	0.35	0.23	0.00
3.00	0.82	0.72	0.74	0.70	0.66	0.60	0.51	0.47	0.42	0.38	0.25	0.00
4.00	0.89	0.77	0.80	0.75	0.71	0.66	0.56	0.52	0.46	0.43	0.29	0.00
5.00	0.93	0.80	0.84	0.79	0.74	0.69	0.59	0.56	0.49	0.46	0.31	0.00

Ceiling mounted

Luminance Table

Plane Cone	0.0	15.0	30.0	45.0	60.0	75.0	90.0
45.0	19519	18002	17163	16895	17163	18002	19519
50.0	21007	19207	18226	17913	18226	19207	21007
55.0	22862	20714	19559	19194	19559	20714	22862
60.0	24955	22390	21032	20605	21032	22390	24955
65.0	27361	24289	22688	22189	22688	24289	27361
70.0	30141	26442	24548	23963	24548	26442	30141
75.0	33289	28812	26567	25879	26567	28812	33289
80.0	37140	31643	28950	28133	28950	31643	37140
85.0	41833	34973	31705	30725	31705	34973	41833
90.0	48139	39305	35240	34039	35240	39305	48139

(cd/m²)

2021-01-24