



2022

Lamps and luminaires

Solid lighting,
saving energy



PILA LAMPS

LED Bulbs	4
-----------	---

LED Candles and Lustres	11
-------------------------	----

LED Spots	16
-----------	----

LED Tubes	22
-----------	----

PILA INDOOR LUMINAIRES

LED Ceiling	24
-------------	----

LED Spotlights and Downlights	25
-------------------------------	----

LED Highbay	28
-------------	----

LED Panels	29
------------	----

LED Wall-mounted	31
------------------	----

LED Batten	32
------------	----

LED Waterproof	33
----------------	----

PILA OUTDOOR LUMINAIRES

LED Floodlights	36
-----------------	----

PILA

An established brand

PILA is the answer to the needs of those customers who are looking for affordable, yet reliable LED products. Our LED luminaires are an excellent replacement for their conventional equivalents.

Benefits:

- Affordable and economical luminaires
- Energy efficient
- Dedicated portfolio for basic applications
- Guaranteed luminous flux and durability
- Simple upgrade to LED
- Quick and easy to install

The factory in PILA began producing traditional Bulbs in 1958. As technology transformed into LED, the first PILA LED Bulbs appeared on the market in 2014, and LED Tubes in 2017.

In some European markets, PILA is a brand with a strong reputation and high awareness among consumers (34% source: HeartBeat) and is highly recognized by installers in the professional market.

So, in 2018, we decided to expand our offer with a comprehensive selection of economical professional installation fittings.



PILA LED Bulbs

Specifications

80
CRI

15,000h

30,000x

non dimmable

**PILA LED 40W
A60 E27 WW
FR ND 1CT/6**



**PILA LED 40W
A60 E27 CW
FR ND 1CT/6**



Lamp type	LED Bulb	LED Bulb
LED (W)	5.5	5
CCT (K)	2700	4000
Light output (lm)	470	470
Replacement wattage (W)	40	40
Shape	A60	A60
Material	Plastic	Plastic
Dimension Width / diameter (mm)	60	60
Dimension Height / length (mm)	108	108
EAN1	8727900968569	8727900968927
12NC	929002305931	929002306031

Benefits

- ▶ Up to 90% energy saving compared with traditional incandescent lamps
- ▶ Lower maintenance costs
- ▶ Low initial investment
- ▶ Reliable quality

PILA LED Bulbs

Specifications

80
CRI

15,000h

ON
OFF
30,000x

non dimmable

**PILA LED 60W
A60 E27 WW
FR ND 1CT/6**



**PILA LED 60W
A60 E27 CW
FR ND 1CT/6**



**PILA LED 60W
A60 E27 865
FR ND 1CT/10**



Lamp type	LED Bulb	LED Bulb	LED Bulb
LED (W)	8	8	8
CCT (K)	2700	4000	6500
Light output (lm)	806	806	806
Replacement wattage (W)	60	60	60
Shape	A60	A60	A60
Material	Plastic	Plastic	Plastic
Dimension Width / diameter (mm)	60	60	60
Dimension Height / length (mm)	108	108	108
EAN1	8727900968521	8727900968606	8727900971798
12NC	929002306231	929002306331	929002306451

Benefits

- ▶ Up to 90% energy saving compared with traditional incandescent lamps
- ▶ Lower maintenance costs
- ▶ Low initial investment
- ▶ Reliable quality

PILA LED Bulbs

Specifications

80
CRI

15,000h

ON
OFF
30,000x

non dimmable

**PILA LED 75W A60
E27 WW FR ND
1CT/6 G3**



**PILA LED 75W A60
E27 CW FR ND
1CT/6 G3**



**PILA LED 75W A60
E27 CDL FR ND
1CT/6**



Lamp type	LED Bulb	LED Bulb	LED Bulb
LED (W)	10	10	10
CCT (K)	2700	4000	6500
Light output (lm)	1055	1055	1055
Replacement wattage (W)	75	75	75
Shape	A60	A60	A60
Material	Plastic	Plastic	Plastic
Dimension Width / diameter (mm)	60	60	60
Dimension Height / length (mm)	108	108	108
EAN1	8727900968620	8727900968644	8727900968668
12NC	929002306531	929002306631	929002306731

Benefits

- ▶ Up to 90% energy saving compared with traditional incandescent lamps
- ▶ Lower maintenance costs
- ▶ Low initial investment
- ▶ Reliable quality

PILA LED Bulbs

Specifications

80
CRI

15,000h

ON
OFF
30,000x

non dimmable

**PILA LED 100W A60
E27 WW FR ND
1CT/6**



**PILA LED 100W A60
E27 CW FR ND
1CT/6 G3**



**PILA LED 120W A67
E27 WW FR ND
1CT/6**



Lamp type	LED Bulb	LED Bulb	LED Bulb
LED (W)	13	13	15
CCT (K)	2700	4000	2700
Light output (lm)	1521	1521	1900
Replacement wattage (W)	100	100	120
Shape	A60	A60	A67
Material	Plastic	Plastic	Plastic
Dimension Width / diameter (mm)	60	60	68
Dimension Height / length (mm)	120	120	128
EAN1	8727900968682	8727900968507	8727900967142
12NC	929002306831	929002306931	929002062231

Benefits

- ▶ Up to 90% energy saving compared with traditional incandescent lamps
- ▶ Lower maintenance costs
- ▶ Low initial investment
- ▶ Reliable quality

PILA LED Bulbs

Specifications

80

CRI



15,000h



20,000x



non dimmable

PILA LED classic 40W A60 E27 WWND 1CT/10



PILA LED CLA 40W A60 E27 WW CL ND 1CT/10



Lamp type	LED Bulb	LED Bulb
LED (W)	4.5	4.3
CCT (K)	2700	2700
Light output (lm)	470	470
Replacement wattage (W)	40	40
Shape	A60	A60
Material	Glass	Glass
Dimension Width / diameter (mm)	60	60
Dimension Height / length (mm)	104	104
EAN1	8727900963915	8727900966244
12NC	929001242972	929001890031

Benefits

- ▶ Around 90% energy saving
- ▶ Very long lifetime that reduces the need for replacement
- ▶ Easy replacement of classic conventional lamps
- ▶ Reliable quality

PILA LED Bulbs

Specifications

80

CRI



15,000h



20,000x



non dimmable

PILA LED classic 60W A60 E27 WWND 1CT/10



PILA LED CLA 60W A60 E27 WW CL ND 1CT/10



Lamp type	LED Bulb	LED Bulb
LED (W)	7	7
CCT (K)	2700	2700
Light output (lm)	806	806
Replacement wattage (W)	60	60
Shape	A60	A60
Material	Glass	Glass
Dimension Width / diameter (mm)	60	60
Dimension Height / length (mm)	104	104
EAN1	8727900970524	8727900970364
12NC	929003033331	9290030333931

Benefits

- ▶ Around 90% energy saving
- ▶ Very long lifetime that reduces the need for replacement
- ▶ Easy replacement of classic conventional lamps
- ▶ Reliable quality

PILA LED Bulbs

Specifications

80

CRI



15,000h



20,000x



non dimmable

PILA LEDCLA 75W
A60 E27 WW
CL ND 1CT/6



PILA LEDCLA 100W
A60 E27 WW
CL ND 1CT/6



Lamp type	LED Bulb	LED Bulb
LED (W)	8.5	10.5
CCT (K)	2700	2700
Light output (lm)	1055	1521
Replacement wattage (W)	75	100
Shape	A60	A60
Material	Glass	Glass
Dimension Width / diameter (mm)	60	60
Dimension Height / length (mm)	104	104
EAN1	8727900970340	8727900968545
12NC	929003033831	929002026131

Benefits

- ▶ Around 90% energy saving
- ▶ Very long lifetime that reduces the need for replacement
- ▶ Easy replacement of classic conventional lamps
- ▶ Reliable quality

PILA LED Candles

Specifications

80

CRI



15,000h



30,000x



non dimmable

**PILA LED 25W B35
E14 WW
FR ND 1CT/10**



**PILA LED 40W B35
E14 WW
FR ND 1CT/10**



Lamp type	LED Candle	LED Candle
LED (W)	3	5.5
CCT (K)	2700	2700
Light output (lm)	250	470
Replacement wattage (W)	25	40
Shape	B35	B35
Material	Plastic	Plastic
Dimension Width / diameter (mm)	35	35
Dimension Height / length (mm)	106	106
EAN1	8727900970388	8727900970401
12NC	929002966831	929002968431

Benefits

- ▶ Up to 90% energy saving compared with halogen lamps
- ▶ Low maintenance cost
- ▶ Easy choice and installation
- ▶ Reliable quality

PILA LED Candles

Specifications

80
CRI

15,000h

ON
OFF
30,000x

non dimmable

**PILA LED 60W
B35 E14 WW
ND 1CT/10**



**PILA LED 60W
B35 E14 CW
ND 1CT/10**



**PILA LED 60W
B35 E14 CDL
ND 1CT/10**



Lamp type	LED Candle	LED Candle	LED Candle
LED (W)	8	8	8
CCT (K)	2700	4000	6500
Light output (lm)	806	806	806
Replacement wattage (W)	60	60	60
Shape	B35	B35	B35
Material	Plastic	Plastic	Plastic
Dimension Width / diameter (mm)	38	38	38
Dimension Height / length (mm)	114	114	114
EAN1	8727900970241	8727900970265	8727900970289
12NC	929002972531	929002972731	929002972931

Benefits

- Up to 90% energy saving compared with halogen lamps
- Low maintenance cost
- Easy choice and installation
- Reliable quality

PILA LED Candles

Specifications

80
CRI

15,000h

20,000x

non dimmable

**PILA LED CLA 25W
B35 E14 WW
CL ND 1CT/10**



**PILA LED CLA 40W
B35 E14 WW
CL ND 1CT/10**



**PILA LEDCLA 60W
B35 E14 WW
CL ND 1CT/10**



Lamp type	LED Candle	LED Candle	LED Candle
LED (W)	2	4.3	6.5
CCT (K)	2700	2700	2700
Light output (lm)	250	470	806
Replacement wattage (W)	25	40	60
Shape	B35	B35	B35
Material	Glass	Glass	Glass
Dimension Width / diameter (mm)	97	97	97
Dimension Height / length (mm)	35	35	35
EAN1	8727900966206	8727900966220	8727900970302
12NC	929001238331	929001889731	929003035931

Benefits

- ▶ Around 90% energy saving
- ▶ Very long lifetime that reduces the need for replacement
- ▶ Easy replacement of classic conventional lamps
- ▶ Reliable quality

PILA LED Lustres

Specifications

80

CRI



15,000h



30,000x



non dimmable

PILA LED 40W P45 E14 WW P45 FR ND



PILA LED 40W P45 E27 WW P45 FR ND



Lamp type	LED Lustre	LED Lustre
LED (W)	5.5	5.5
CCT (K)	2700	2700
Light output (lm)	470	470
Replacement wattage (W)	40	40
Shape	P45	P45
Material	Plastic	Plastic
Dimension Width / diameter (mm)	45	45
Dimension Height / length (mm)	84	79
EAN1	8727900964271	8727900964295
12NC	929001253731	929001253831

Benefits

- ▶ Up to 90% energy saving compared with halogen lamps
- ▶ Low maintenance cost
- ▶ Easy choice and installation
- ▶ Reliable quality

PILA LED Lustres

Specifications

80
CRI

15,000h

20,000x

non dimmable

PILA LED CLA 25W
P45 E14 WW
CL ND 1CT/10

PILA LED CLA 40W
P45 E14 WW
CL ND 1CT/10

PILA LEDCLA 60W
P45 E14 WW
CL ND 1CT/10



Lamp type	LED Lustre	LED Lustre	LED Lustre
LED (W)	2	4.3	6.5
CCT (K)	2700	2700	2700
Light output (lm)	250	470	806
Replacement wattage (W)	25	40	60
Shape	P45	P45	P45
Material	Glass	Glass	Glass
Dimension Width / diameter (mm)	80	80	80
Dimension Height / length (mm)	45	45	45
EAN1	8727900966268	8727900966305	8727900970548
12NC	929001238631	929001890431	929003036131

Benefits

- ▶ Around 90% energy saving
- ▶ Very long lifetime that reduces the need for replacement
- ▶ Easy replacement of classic conventional lamps
- ▶ Reliable quality

PILA LED Spots

Specifications

80

CRI



15,000h



30,000x



non dimmable

**PILA LED 35W GU10
WW 36D ND 1CT/10**

**PILA LED 35W GU10
CW 36D ND 1CT/10**

**PILA LED 50W GU10
WW 36D ND 1CT/10**



Lamp type	LED Spot	LED Spot	LED Spot
LED (W)	3	3	4.7
CCT (K)	2700	4000	2700
Light output (lm)	250	265	400
Replacement wattage (W)	35	35	50
Cap	GU10	GU10	GU10
Material	Plastic	Plastic	Plastic
Dimension Width / diameter (mm)	50	50	50
Dimension Height / length (mm)	56	56	56
Beam angle (D)	36°	36°	36°
EAN1	8727900970500	8727900970487	8727900970449
12NC	929003038531	929003038231	929003038631

Benefits

- ▶ Up to 90% energy saving compared with traditional halogen lamps
- ▶ Lower maintenance costs
- ▶ Low initial investment
- ▶ Reliable quality

PILA LED Spots

Specifications

80

CRI



15,000h



30,000x



non dimmable

PILA LED 50W GU10 CW 36D ND 1CT/10



PILA LED 65W GU10 WW 36D ND 1CT/10



Lamp type	LED Spot	LED Spot
LED (W)	4.7	5.5
CCT (K)	4000	2700
Light output (lm)	430	460
Replacement wattage (W)	50	65
Cap	GU10	GU10
Material	Plastic	Plastic
Dimension Width / diameter (mm)	50	50
Dimension Height / length (mm)	56	56
Beam angle (D)	36°	36°
EAN1	8727900970425	8727900970609
12NC	929003038331	929003038831

Benefits

- ▶ Up to 90% energy saving compared with traditional halogen lamps
- ▶ Lower maintenance costs
- ▶ Low initial investment
- ▶ Reliable quality

PILA LED Spots

Specifications

80

CRI



15,000h



30,000x



non dimmable

PILA LED 65W GU10 CW 36D ND 1CT/10



PILA LED 50W GU10 CW 60D ND 1CT/10



Lamp type	LED Spot	LED Spot
LED (W)	5.5	4.7
CCT (K)	4000	4000
Light output (lm)	460	430
Replacement wattage (W)	65	50
Cap	GU10	GU10
Material	Plastic	Plastic
Dimension Width / diameter (mm)	50	50
Dimension Height / length (mm)	54	56
Beam angle (D)	36°	60°
EAN1	8727900964615	8718696537015
12NC	929001371231	929001912331

Benefits

- ▶ Up to 90% energy saving compared with traditional halogen lamps
- ▶ Lower maintenance costs
- ▶ Low initial investment
- ▶ Reliable quality

PILA LED Spots

Specifications

80

CRI



15,000h



30,000x



non dimmable

PILA LED 500lm GU10 WW 120D ND 1CT/10



PILA LED 500lm GU10 CW 120D ND 1CT/10



Lamp type	LED Spot	LED Spot
LED (W)	5.5	5
CCT (K)	2700	4000
Light output (lm)	500	500
Replacement wattage (W)	42	42
Cap	GU10	GU10
Material	Plastic	Plastic
Dimension Width / diameter (mm)	50	50
Dimension Height / length (mm)	58	58
Beam angle (D)	120°	120°
EAN1	8727900965254	8727900965230
12NC	929001372031	929001358631

Benefits

- ▶ Up to 90% energy saving compared with traditional halogen lamps
- ▶ Lower maintenance costs
- ▶ Low initial investment
- ▶ Reliable quality

PILA LED Spots

Specifications

80

CRI



15,000h



30,000x



non dimmable

PILA LED 35W GU5.3 WW 12V 36D ND



PILA LED 50W GU5.3 WW 12V 36D ND 1CT/10



Lamp type	LED Spot	LED Spot
LED (W)	4.5	7
CCT (K)	2700	2700
Light output (lm)	400	700
Replacement wattage (W)	35	50
Cap	GU5.3	GU5.3
Material	Plastic	Plastic
Dimension Width / diameter (mm)	50	50
Dimension Height / length (mm)	46	45
Beam angle (D)	36°	36°
EAN1	8727900964653	8727900968729
12NC	929001210931	929002404731

Benefits

- ▶ Up to 90% energy saving compared with traditional halogen lamps
- ▶ Lower maintenance costs
- ▶ Low initial investment
- ▶ Reliable quality

PILA LED Reflectors

Specifications

80
CRI

15,000h

30,000x

non dimmable

PILA LED 40W E14 WW R50 36D ND1CT/10



Lamp type	LED Reflector
LED (W)	3.5
CCT (K)	2700
Light output (lm)	260
Replacement wattage (W)	40
Cap	R50
Material	Plastic
Dimension Width / diameter (mm)	48.5
Dimension Height / length (mm)	84
Beam angle (D)	36°
EAN1	8727900968705
12NC	929002404231

Benefits

- ▶ Up to 90% energy saving compared with traditional halogen lamps
- ▶ Lower maintenance costs
- ▶ Low initial investment
- ▶ Reliable quality

PILA LED Tubes

Specifications

80
CRI

15,000h

50,000x

non dimmable

**PILA LED Tube
600mm 8W 840
G13**



**PILA LED Tube
600mm 8W 865
G13**



**PILA LED Tube
1200mm 16W 840
G13**



Lamp type	LED Tube	LED Tube	LED Tube
LED (W)	8	8	16
CCT (K)	4000	6500	4000
Light output (lm)	800	800	1600
Input current (mA)	70	70	134
Frequency (Hz)	50/60	50/60	50/60
Material	Glass	Glass	Glass
Dimension Width / diameter (mm)	28	28	28
Dimension Height / length (mm)	603	603	1212
EAN1	8727900971071	8727900971095	8727900971118
12NC	929003130902	929003131002	929003131102

Benefits

- Reliable quality
- Energy saving

PILA LED Tubes

Specifications

80
CRI

15,000h

50,000x

non dimmable

**PILA LED Tube
1200mm 16W 865
G13**



**PILA LED Tube
1500mm 19.5W 840
G13**



**PILA LED Tube
1500mm 19.5W 865
G13**



Lamp type	LED Tube	LED Tube	LED Tube
LED (W)	16	19.5	19.5
CCT (K)	6500	4000	6500
Light output (lm)	1600	2000	2000
Input current (mA)	134	155	155
Frequency (Hz)	50/60	50/60	50/60
Material	Glass	Glass	Glass
Dimension Width / diameter mm	28	28	28
Dimension Height / length mm	1212	1513	1513
EAN1	8727900971132	8727900971156	8727900971170
12NC	929003131202	929003131302	929003131402

Benefits

- Reliable quality
- Energy saving

PILA LED Ceiling

Specifications

**PILA Ceiling RD 10W
4000K W 06**



**PILA Ceiling RD 17W
4000K W 06**



Lamp type	LED Ceiling	LED Ceiling
Light output (lm)	1100	1900
Power (W)	10	17
CCT (K)	4000	4000
Housing Color	White	White
Lifetime(hr)	15000	15000
EAN1	8727900967807	8727900967821
12NC	915005778323	915005778923

Benefits

- ▶ Energy efficient
- ▶ Wide application range

PILA LED Spotlights

Specifications

80

CRI



15,000h



non dimmable

PILA SL252 EC RD 070 5W 27K W HV 06



PILA SL252 EC RD 070 5W 40K W HV 06



Product type	LED Spotlight	LED Spotlight
System power (W)	5	5
CCT (K)	2700	4000
Light output (lm)	290	300
LifeTime L70B50 (h)	15,000	15,000
CRI	80	80
Overall diameter (mm)	90	90
Height fix (mm)	67	67
Beam angle (D)	30°	30°
Switch Cycle (times)	7,500	7,500
EAN1	8727900967920	8727900967944
12NC	929002222647	929002222747

Benefits

- ▶ Accent light effect
- ▶ Energy saving
- ▶ Reliable performance

PILA LED Downlights

Specifications

80
CRI


20,000h


non dimmable

**PILA DN020B LED13/830
14W D150 RD EU**



**PILA DN020B LED13/840
14W D150 RD EU**



Product type	LED Downlight	LED Downlight
System power (W)	14	14
CCT (K)	3000	4000
Light output (lm)	1300	1300
CRI	80	80
LifeTime L70B50 (h)	20,000	20,000
Overall diameter (mm)	165	165
Height fix (mm)	38	38
Beam angle (D)	110°	110°
Switch Cycle (times)	10,000	10,000
EAN1	8727900967845	8727900967869
12NC	929002668382	929002668482

Benefits

- ▶ Bright and even light
- ▶ Energy saving
- ▶ Reliable performance

PILA LED Downlights

Specifications

80
CRI

20,000h

non dimmable

**PILA DN020B LED22/830
22.5W D200 RD EU**



**PILA DN020B LED22/840
22.5W D200 RD EU**



Product type	LED Downlight	LED Downlight
System power (W)	22.5	22.5
CCT (K)	3000	4000
Light output (lm)	2200	2200
CRI	80	80
LifeTime L70B50 (h)	20,000	20,000
Overall diameter (mm)	225	225
Height fix (mm)	38	38
Beam angle (D)	110°	110°
Switch Cycle (times)	10,000	10,000
EAN1	8727900967883	8727900967906
12NC	929002668682	929002668782

Benefits

- ▶ Bright and even light
- ▶ Energy saving
- ▶ Reliable performance

PILA LED Highbay

Specifications

**PILA BY007P LED150S/
840 PSU WB**



**PILA BY007P LED200S/
840 PSU WB**



Product type	LED Highbay	LED Highbay
Light output (lm)	15000	20000
System power (W)	150	200
CCT (K)	4000	4000
IP / IK	IP65/IK06	IP65/IK06
Safety Class	Class I	Class I
EAN1	8719514528260	8719514528277
12NC	911401846282	911401846382

Benefits

- Energy efficient
- Wide application range

PILA LED Panels

Specifications

80

CRI



220-240 Vac



35,000h



non dimmable

PILA RC007B LED12S/840 PSU W30L30 NOC



PILA RC007B LED32S/840 PSU W60L60 NOC



Lamp type	LED Panel	LED Panel
Light output (lm)	1200	3200
Power (W)	15	36
CCT (K)	4000	4000
IP / IK	IP20	IP20
Motion sensor	No	No
Safety Class	Class II	Class II
EAN1	8710163340173	8710163340166
12NC	911401801180	911401801080

Benefits

- Applicable for wide range of applications
- Supports energy saving
- Reliable quality

PILA LED Panels

Specifications

80

CRI



220-240 Vac



35,000h



non dimmable

PILA RC007B LED32S/840 PSU I W60L60 NOC



PILA RC007B LED32S/840 PSU I W60L60 OC



Lamp type	LED Panel	LED Panel
Light output (lm)	3200	3200
Power (W)	36	36
CCT (K)	4000	4000
IP / IK	IP20	IP20
Motion sensor	No	No
Safety Class	Class I	Class I
EAN1	8719514527294	8719514531833
12NC	911401714793	911401856982

Benefits

- Applicable for wide range of applications
- Supports energy saving
- Reliable quality

PILA LED

Wall-mounted

Specifications

80

CRI



220-240 Vac



35,000h

**PILA WL007C
LED10S/840
PSU RND WH G2**



**PILA WL007C
LED13S/840
PSU RND MDU WH**



**PILA WL007C
LED16S/840
PSU RND WH G2**



Light output (lm)	1000	1300	1600
Power (W)	12	15	20
CCT (K)	4000	4000	4000
Mains voltage	50-60Hz	50-60Hz	50-60Hz
Connection	Screw terminal	Screw terminal	Screw terminal
IP rating	IP54	IP54	IP54
Power factor	> 0.9	> 0.9	> 0.9
Safety class	Class II	Class II	Class II
Housing material	Polycarbonate	Polycarbonate	Polycarbonate
Color	White	White	White
EOC	8710163364421	8710163335117	8710163364438
12NC	911401774752	911401735142	911401774762

Benefits

- ▶ Available with motion sensor
- ▶ Supports energy saving
- ▶ Available in round and oval
- ▶ For wall and ceiling mounted

PILA LED Batten

Specifications

80
CRI


220-240 Vac


35,000h

PILA RC007B LED32S/840 PSU W60L60 NOC



Light output (lm)	3200
Power (W)	32
CCT (K)	4000
Mains voltage	50-60Hz
Connection	Fly wire 0.15m
IP rating	IP20
Power factor	> 0.9
Safety class	Class I
Housing material	Polycarbonate
Color	White
EOC	8710163335087
12NC	911401735152

Benefits

- ▶ Applicable for wide range of applications
- ▶ Supports energy saving
- ▶ Reliable quality

PILA LED Waterproof

Specifications

80
CRI

⚡
220-240 Vac

🕒
35,000h

**PILA WT007C
LED17S/840
PSU L600**



**PILA WT007C
LED34S/840
PSU L1200**



Light output (lm)	1700	3400
Power (W)	17	34
CCT (K)	4000	4000
Mains voltage	50+60Hz	50-60Hz
Connection	Wire	Wire
IP rating	IP65 / IK06	IP65 / IK06
Power factor	> 0.9	> 0.9
Safety class	Class II	Class II
Housing material	Polycarbonate	Polycarbonate
Color	Grey	Grey
EOC	871016334311299	8710163335148
12NC	911401809680	911401735772

Benefits

- ▶ Robust luminaire
- ▶ Supports energy saving
- ▶ Available in three sizes

PILA LED Waterproof

Specifications

80
CRI


220-240 Vac


35,000h

**PILA WT007C
LED34S/840 PSU
L1200**



**PILA WT007C
LED34S/865 PSU
L1200**



Light output (lm)	3400	3400
Power (W)	34	34
CCT (K)	4000	6500
Mains voltage	50+60Hz	50-60Hz
Connection	Wire	Wire
IP rating	IP65 / IK06	IP65 / IK06
Power factor	> 0.9	> 0.9
Safety class	Class II	Class II
Housing material	Polycarbonate	Polycarbonate
Color	Grey	Grey
EOC	8710163344430	8710163351124
12NC	911401822480	911401851080

Benefits

- ▶ Robust luminaire
- ▶ Supports energy saving
- ▶ Available in three sizes

PILA LED Waterproof

Specifications

80

CRI



220-240 Vac



35,000h

**PILA WT007C
LED54S/840 PSU
L1500**



**PILA WT007C
LED54S/840
PSU L1500**



**PILA WT007C
LED54S/865 PSU
L1500**



Light output (lm)	5400	5400	5400
Power (W)	54	54	54
CCT (K)	4000	4000	6500
Mains voltage	50+60Hz	50-60Hz	50-60Hz
Connection	Wire	Wire	Wire
IP rating	IP65 / IK06	IP65 / IK06	IP65 / IK06
Power factor	> 0.9	> 0.9	> 0.9
Safety class	Class II	Class II	Class II
Housing material	Polycarbonate	Polycarbonate	Polycarbonate
Color	Grey	Grey	Grey
EOC	8710163344447	8710163335155	8710163351131
12NC	911401822580	911401735782	911401851180

Benefits

- ▶ Robust luminaire
- ▶ Supports energy saving
- ▶ Available in three sizes

PILA LED Floodlights

Specifications

80

CRI



220-240 Vac



35,000h

**PILA BVP008
10W 3000k**



**PILA BVP008
20W 3000k**



**PILA BVP008
50W 3000k**



Light output (lm)	900	1800	4500
Power (W)	10	20	50
CCT (K)	3000	3000	3000
Mains voltage	50-60Hz	50-60Hz	50-60Hz
Connection	Flying wire	Flying wire	Flying wire
Motion sensor	No	No	No
IP rating	IP65 / IK06	IP65 / IK06	IP65 / IK06
Power factor	> 0.9	> 0.9	> 0.9
Safety class	Class I	Class I	Class I
Housing material	Glass / Aluminium	Glass / Aluminium	Glass / Aluminium
Color	Black	Black	Black
EOC	87195145329499	87195145329399	87195145329199
12NC	911401810583	911401811583	911401814583

Benefits

- ▶ Robust luminaire
- ▶ Supports energy saving
- ▶ Reliable quality

PILA LED Floodlights

Specifications

80

CRI



220-240 Vac



35,000h

**PILA BVP008
10W 4000k**



**PILA BVP008
20W 4000k**



**PILA BVP008
30W 4000k**



Light output (lm)	950	1900	2850
Power (W)	10	20	30
CCT (K)	4000	4000	4000
Mains voltage	50-60Hz	50-60Hz	50-60Hz
Connection	Flying wire	Flying wire	Flying wire
Motion sensor	No	No	No
IP rating	IP65 / IK06	IP65 / IK06	IP65 / IK06
Power factor	> 0.9	> 0.9	> 0.9
Safety class	Class I	Class I	Class I
Housing material	Glass / Aluminium	Glass / Aluminium	Glass / Aluminium
Color	Black	Black	Black
EOC	87195145329899	87195145329799	87195145329699
12NC	911401820583	911401821583	911401823583

Benefits

- ▶ Robust luminaire
- ▶ Supports energy saving
- ▶ Reliable quality

PILA LED Floodlights

Specifications

80

CRI



220-240 Vac



35,000h

**PILA BVP008
50W 4000k**



**PILA BVP008
100W 4000k**



**PILA BVP008
200W 4000k**



Light output (lm)	4750	9500	19000
Power (W)	50	100	200
CCT (K)	4000	4000	4000
Mains voltage	50-60Hz	50-60Hz	50-60Hz
Connection	Flying wire	Flying wire	Flying wire
Motion sensor	No	No	No
IP rating	IP65 / IK06	IP65 / IK06	IP65 / IK06
Power factor	> 0.9	> 0.9	> 0.9
Safety class	Class I	Class I	Class I
Housing material	Glass / Aluminium	Glass / Aluminium	Glass / Aluminium
Color	Black	Black	Black
EOC	87195145329599	87195145329499	87195145329399
12NC	911401824583	911401826583	911401828583

Benefits

- ▶ Robust luminaire
- ▶ Supports energy saving
- ▶ Reliable quality

PILA LED Floodlights

Specifications

80
CRI

⚡
220-240 Vac

🕒
35,000h

**PILA BVP008
20W 3000k
MDU**



**PILA BVP008
20W 4000k
MDU**



**PILA BVP008
50W 3000k
MDU**



**PILA BVP008
50W 4000k
MDU**



Light output (lm)	1800	1900	4500	4750
Power (W)	20	20	50	50
CCT (K)	3000	4000	3000	4000
Mains voltage	50-60Hz	50-60Hz	50-60Hz	50-60Hz
Connection	Flying wire	Flying wire	Flying wire	Flying wire
Motion sensor	Yes	Yes	Yes	Yes
IP rating	IP65 / IK06	IP65 / IK06	IP65 / IK06	IP65 / IK06
Power factor	> 0.9	> 0.9	> 0.9	> 0.9
Safety class	Class I	Class I	Class I	Class I
Housing material	Glass / Aluminium	Glass / Aluminium	Glass / Aluminium	Glass / Aluminium
Color	Black	Black	Black	Black
EOC	87195145329299	87195145329199	87195145329899	87195145329799
12NC	911401874883	911401874983	911401875483	911401875583

Benefits

- ▶ Robust luminaire
- ▶ Supports energy saving
- ▶ Reliable quality



www.pila-led.com

©2022 Signify Holding. All rights reserved. The information provided herein is subject to change, without notice. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify.