

CERTIFICATE

Issued to:
Applicant:
Signify Netherlands B.V.
High Tech Campus 48
5656 AE Eindhoven, Netherlands

Licensee:
Signify Netherlands B.V.
High Tech Campus 48
5656 AE Eindhoven, Netherlands

Product : LED Panel Light
Trade name(s) : N/A
Type(s)/model(s) : Fortimo HE BL Panel 6060 830-865 TW MD3,
Fortimo HE BL Panel 6060 830/840 MC MD3,
Fortimo HE BL Panel 6060 840 MC MD3,
Fortimo HE BL Panel 6262 830-865 TW MD3 and
Fortimo HE BL Panel 6262 840 MC MD3

The product and any acceptable variation thereof as specified in the Annex to this certificate and the documents referred to therein.

DEKRA hereby declares that the above-mentioned product has been certified based on:

- a type test according to EN IEC 60598-2-1:2021, EN IEC 60598-1:2021, EN IEC 60598-1:2021/A11:2022 and EN IEC 60598-2-2:2024
- an inspection of the factory location according to CENELEC Operational Document CIG 021
- a DEKRA certification agreement with the number 947556


DEKRA hereby grants the right to use the ENEC certification mark.

The ENEC certification mark may be applied to the product as specified in this certificate for the duration and under the conditions of the ENEC certification agreement.

This certificate is issued on 31 March 2025 and expires upon withdrawal of one of the above mentioned standards.

Certificate number: 31-134058 REV.1

DEKRA Certification B.V.



B.T.M. Holtus
Managing Director



Massimiliano Triulzi
Certification Manager

© Integral publication of this certificate is allowed

ACCREDITED BY THE
DUTCH ACCREDITATION
COUNCIL



SPECIFICATION OF THE CERTIFIED PRODUCT**Product data**

Product	: LED Panel Light
Trade name(s)	: N/A
Type(s)/model(s)	: Fortimo HE BL Panel 6060 830-865 TW MD3, Fortimo HE BL Panel 6060 830/840 MC MD3, Fortimo HE BL Panel 6060 840 MC MD3, Fortimo HE BL Panel 6262 830-865 TW MD3 and Fortimo HE BL Panel 6262 840 MC MD3
Input voltage	: 220-240 Vac
Input current	: 0,13 Aac
Input power	: 28 W
Classification	: Class II
Degree of protection	: IP20
Ambient temperature (ta)	: 45°C
Rated frequency	: 50/60 Hz

TESTS**Test requirements**

EN IEC 60598-2-1:2021
EN IEC 60598-1:2021
EN IEC 60598-1:2021/A11:2022
EN IEC 60598-2-2:2024

Test result

The test results are documented in DEKRA test file 621966900.

Additional information

Note:

Yes – the product is including switch or sensor

No – the product is not including switch or sensor

P – parallel

S – series

The product also complies with EN 62493:2015+A1:2022 in ENEC certificate

This certificate replaces certificate No. 31-134058 which we hereby declare invalid.

The list of components is laid down in test report 6219669.50(A-B).

Conclusion

The examination has confirmed that all requirements were met.

Factory location

The factory location is registered with the number 1845.