



Lightolier Mini downlight provides an easy to install three-inch solution for accent lighting. The small detachable junction box eliminates the need for a traditional frame or bulky remodeler kit making installation quick and easy.

Project: \_\_\_\_\_  
 Location: \_\_\_\_\_  
 Cat.No: \_\_\_\_\_  
 Type: \_\_\_\_\_  
 Lamps: \_\_\_\_\_ Qty: \_\_\_\_\_  
 Notes: \_\_\_\_\_

### Fixture

example: MD3R069301FW

Family	Size	Lumens	CRI	CCT	Voltage	Beam Spread	Finish
<b>MD</b>	<b>3R</b>	<b>06</b>	<b>9</b>	<b>30</b>	<b>1</b>	<b>F</b>	<b>W</b>
MD Mini downlight	3R 3-inch Round	06 550 lm	9 90CRI	30 3000K	1 120V	F Flood	W White

### Accessories

example: MDRN

Family	Model
<b>MD</b>	
MD Mini downlight	<b>RN</b> Round new construction plate <b>06C</b> 6' extension cable <b>20C</b> 20' extension cable

### Features

- 1. Flame:** Die cast aluminum. Painted.
- 2. Junction box:** Extruded aluminum steel. Clip attached on the side of the junction box to connect with fixture or new construction plate to meet NEC (National Electric Code). Also has key holes on the sides for mounting on joist.
- 3. Connector:** Locking power connection is used to connect junction box and fixture. Standard length of the connector is 12" from fixture to junction box. Extension cables are available as accessory.
- 4. Lifetime:** L70 at 50,000 hours and backed by a 5-year warranty (see Philips.com/warranties for details).
- 5. New construction plate:** Steel. Holes/slots on the side of the plate for mounting to joist.

- 6. Ceiling cutout:** Ceiling cutout template supplied with the product. 2 3/4" (70mm) diameter.

### Electrical

**Electronic power supply:** RoHS compliant. Class 2 power unit. Remote power supply can only accommodate one LED module and cannot be shared with other LED module.

Fixture can be daisy chained and cannot be through wired.

**Dimming:** Intended for TRIAC dimming. For more details, please see LED-DIM-DL spec sheet.

### Listings

cETLus listed.  
 Ceiling-mounted: suitable for damp location.  
 ENERGY STAR®.  
 Title 24 (JA8-2016).  
 IC rated.  
 AirSeal for minimal air leakage.

Electrical Specifications	Dimming	Input Volts	Input Frequency	Input Current	Input Power	THD Factor	Power Factor	Min. Operating Temp.	Max. Operating Temp.
Mini Downlight	TRIAC	120V	60 Hz	0.08A	8W MAX	<25%	>=0.9	0°c	40°c

## Light to go

Compatible configurations

Fixture

MG3R06930NF1W

Accessory


MD06C  
 MD20C  
 MDRN

# MD-US Mini Downlight LED 3"


## Round Mini Downlight

### Dimensions


#### Fixture



#### Junction box




#### New Construction Plate



### Components

1. Electrical box with knockouts
2. Mounting keyhole
3. NEC\* mounting clip
4. 6" (0.15) cord each side. 12" overall
5. Lockin power connector
6. Integrated LED Luminaire
7. Spring clip for easy mounting




# MD-US Mini Downlight LED 3"

## Round Mini Downlight

3000K, 7.9W, 71.8 lm/W

### Candela Curve



Fixture: **MD3R069301FW**

Output lumens: 567 lm  
 Input watts: 7.9 W  
 CRI: 90 min  
 CCT: 3000K  
 Spacing Crit.: 0.6  
 Beam Angle: 38°

### Zonal summary

Zone	Lumens	%Luminaire
0-30	509	89.7%
0-40	550	96.9%
0-60	562	99.0%
0-90	567	100.0%

Angle	Mean CP	Lumens
0	397	
5	395	113
10	388	
15	377	232
20	361	
25	342	164
30	320	
35	293	41
40	261	
45	227	7
50	190	
55	150	5
60	108	
65	67	3
70	32	
75	11	2
80	5	
85	1	0
90	0	

### Single unit data

Height to lighted plane	Initial center beam foot-candles	Beam diameter (ft)*
5'	16	3.0'
6'	11	3.6'
7'	8	4.2'
8'	6	4.8'
9'	5	5.4'

\* Beam diameter is where foot-candles drop to 50% of maximum.

### Multiple unit data - RCR 2

Spacing on center	Initial center beam foot-candles	Watts per sq. ft.
5'	26.6	0.35
6'	17.4	0.23
7'	12.5	0.16
8'	10.4	0.14
9'	8.3	0.11

38' x 38' x 10' Room, Workplane 2.5' above floor, 80/50/20% Reflectances

**Efficacy: 71.8 lm/w**

### Coefficients of utilization

Ceiling	80%				70%		50%		30%		0%
Wall	70	50	30	10	50	10	50	10	50	10	0
RCR	Zonal cavity method - Effective floor reflectance = 20%										
0	119	119	119	119	116	116	111	111	106	106	100
1	114	112	110	108	110	106	106	103	102	100	95
2	110	105	102	99	104	98	101	96	98	94	90
3	105	100	96	92	98	91	96	90	94	89	86
4	101	95	90	87	94	86	92	85	90	84	82
5	97	90	85	82	89	81	88	81	86	80	78
6	94	86	81	77	85	77	84	77	83	76	74
7	90	82	77	74	82	74	80	73	79	73	71
8	87	79	74	70	78	70	77	70	76	70	68
9	84	76	71	67	75	67	74	67	73	67	65
10	81	73	68	65	72	64	71	64	71	64	63

1. Correlated Color Temperature within specs as defined in ANSI\_NEMA\_ANSI C78.377-2008: Specifications for the Chromaticity of Solid State Lighting Products.
2. Tested using absolute photometry as specified in LM79: IESNA Approved Method for the Electrical and Photometric Measurements of Solid-State Lighting Products.

