




by @signify

Design ready

10-day QuickShip



Design ready

As the complexity of your projects skyrocket, faster delivery becomes increasingly important.

The Ledalite 10-day QuickShip program includes all of our high performance and award-winning LED linear, recessed, surface, and slot luminaire families.

Conditions

QuickShip must be requested when submitting an order and will be shipped within 10 working days

- **Linear Luminaires:** Limit of 500 linear ft per release
- **Recessed Troffers:** Limit of 100 luminaires per release

Exclusions

- Hold for Release or Do Not Ship Before orders
- Patterns or rows that require drawings
- All non-standard, 3rd party drivers and components
- Connected options (Interact Pro, PoE)
- Tunable White
- Thru-wiring for additional circuits
- 347V with Battery pack
- Surface mount only available in TruGroove and TruGroove micro
- Wall mount luminaires
- Air Return housing

Please refer to product spec sheets for all other product specific exclusions.

Table of contents

Architectural Linear

Suspended & Surface

TruGroove Suspended	6
TruGroove Surface	7
TruGroove Suspended micro	8
TruGroove Surface micro	9
ModiFly Suspended	10
BoldPlay Suspended	11
Sync Suspended.	12
Verge Suspended	13
Chopstick Suspended	14
Jump Suspended	15
Sona Suspended	16
FloatPlane Suspended	17
SyncLine Suspended	18

Recessed, Cove, & Perimeter

TruGroove Recessed	22
TruGroove Recessed micro	23
TruGroove Cove	24
TruGroove Perimeter	25

Architectural Recessed


Recessed

ArcForm Recessed	30
SilkSpace Recessed definition	31
SilkSpace Recessed	32
PureFX Recessed	33
Shine Recessed	34
Vectra Recessed	35




Architectural Linear


Suspended & Surface




TruGroove
Suspended



TruGroove
Surface



TruGroove micro
Suspended



TruGroove micro
Surface



ModiFly
Suspended



BoldPlay
Suspended




Sync
Suspended



Verge
Suspended



Chopstick
Suspended




Jump
Suspended



Sona
Suspended




FloatPlane
Suspended




SyncLine
Suspended

Architectural Recessed

Recessed, Cove, & Perimeter




TruGroove
Recessed



TruGroove micro
Recessed




TruGroove cove



TruGroove perimeter

Recessed



ArcForm
Recessed




SilkSpace definition
Recessed



SilkSpace
Recessed



PureFX
Recessed




Shine
Recessed



Vectra
Recessed


Suspended & Surface





TruGroove Suspended

Seamless 3" ribbon of light with **exceptional performance and versatility** for functional and decorative applications



Why choose TruGroove Suspended?

- Elevate performance to a whole new level in narrow aperture lighting
- Wide row spacing with fewer fixtures and less energy consumption
- Ideal for a variety of applications with multiple distributions and modules
- MesoOptics DX and innovative optics producing an optimal batwing distribution



Ordering guide

Family	Version	Distribution	Source	CRI/CCT
29 TruGroove	0 Suspended	1 Direct	L LED	950 CRI 90, 5000K
		3 Indirect		940 CRI 90, 4000K
		5 Indirect/Direct		935 CRI 90, 3500K
		6 Direct/Indirect		930 CRI 90, 3000K
				927 CRI 90, 2700K
Lumens	Optics			Run Length
40 4000lm/4ft	LN	Definition symmetric flush silk lens (Dn)		02 2ft
30 3000lm/4ft	QN	Performance symmetric flush MesoOptics lens (Dn)		04 4ft
22 2200lm/4ft	WN	Performance asymmetric wall wash flush MesoOptics lens (Dn)		06 6ft
15 1500lm/4ft				08 8ft
48 4800lm/4ft	NQ	Performance symmetric lens (Up)		XX Continuous run in 2ft increments (please specify length)
32 3200lm/4ft	NW	Performance asymmetric lens (Up)		
68 6800lm/4ft (70% up)	LQ	Definition symmetric flush silk lens (Dn)		
52 5200lm/4ft (60% up)		Performance symmetric lens (Up)		
46 4600lm/4ft (70% up)				
35 3500lm/4ft (60% up)	QQ	Performance symmetric MesoOptics lens (Dn)		
68 6800lm/4ft (60% down)		Performance symmetric lens (Up)		
52 5200lm/4ft (60% down)				
46 4600lm/4ft (70% down)	WW	Performance asymmetric wall wash MesoOptics lens (Dn)		
35 3500lm/4ft (60% down)		Performance asymmetric lens (Up)		
Voltage	Driver	Circuit	Wiring Option	System/Controls
D UNV 120-277V	E Advance Xitanium 0-10V (1% Dim)	1 Single circuit	N None	NN None
3 347V			B Battery pack	
			E Auxiliary wiring	
Finish	Mount Type			Suspension
W Standard white	A1	Non-accessible ceiling, 0°-15° slope mount	A6-1 T-Grid on-grid mount 15/16" (non tegular tile only)	24 24"
T Titanium silver	A2	T-Grid fixed position mount		48 48"
B Black	A3	Non-accessible ceiling, 0°-90° slope mount	A6-2 T-Grid on-grid mount 9/16" (non tegular tile only)	96 96"
G Graphite grey	A5	T-Grid 24" span mount (non tegular tile only)	A6-3 T-Grid on-grid mount 9/16" x 5/16" (slot tee & tegular tile)	144 144"

*Please refer to exclusions.

DLC Note: Not all product variations are DLC qualified. To ensure that a specific model is qualified, visit www.designlights.org/search




interact
ready.



TruGroove Surface

Exceptional uniformity and wide row spacing from a 3" aperture continuous line of light



Why choose TruGroove Surface?

- MesoOptics DX and innovative optics producing optimal batwing distribution
- An extended family and refined design are perfect for lighting any professional space
- Wide row spacing with fewer fixtures and less energy consumption
- Ideal for a variety of applications with multiple distributions and modules

Ordering guide

Family	Version	Distribution	Source	CRI/CCT
29 TruGroove	1 Surface	1 Direct	L LED	950 CRI 90, 5000K 940 CRI 90, 4000K 935 CRI 90, 3500K 930 CRI 90, 3000K 927 CRI 90, 2700K
Lumens	Optics		Run Length	
40 4000lm/4ft 30 3000lm/4ft 22 2200lm/4ft 15 1500lm/4ft	LN Definition symmetric flush silk lens (Dn) QN Performance symmetric flush MesoOptics lens (Dn) WN Performance asymmetric wall wash flush MesoOptics lens (Dn)		02 2ft 04 4ft 06 6ft 08 8ft XX Continuous run in 2 ft increments (please specify length)	
Voltage	Driver	Circuit	Wiring Option	System/Controls
D UNV 120-277V 3 347V	E Advance Xitanium 0-10V (1% Dim)	1 Single circuit	N None B Battery pack E Auxiliary wiring	NN None
Finish		Mount Type		
W Standard white T Titanium silver B Black G Graphite grey		SF Surface mounted		

*Please refer to exclusions.




interact
ready.



TruGroove Suspended micro

Seamless 1.75" ribbon of light with **exceptional performance and versatility** for functional and decorative applications



Why choose TruGroove Suspended micro?

- Unique Quad Optic louver cells offer a wide range of options from graze to stack to asymmetric wall wash
- Wide row spacing with fewer fixtures and less energy consumption
- 20+ Lighting distributions which are ideal for a variety of applications




Ordering guide

Family	Version	Distribution	Source	CRI/CCT	
TM TruGroove micro	0 Suspended	1 Direct 3 Indirect 5 Indirect/Indirect 6 Direct/Indirect	L LED	950	CRI 90, 5000K
				940	CRI 90, 4000K
				935	CRI 90, 3500K
				930	CRI 90, 3000K
				927	CRI 90, 2700K
Optics (Direct)		Lumens (Direct)	Optics (Indirect)		Lumens (Indirect)
Lens	Louver Cell				
N No lens (specify direct louver and/or indirect optic)	NNNN None	NN None	N None	NN	None
Q Performance symmetric batwing flush MesoOptics		40 4000lm/4ft	Q Performance symmetric	70	7000 lm/4ft
W Performance asymmetric/wall wash flush MesoOptics		35 3500lm/4ft	W Performance asymmetric	60	6000 lm/4ft
L Definition symmetric flush silk		30 3000lm/4ft		50	5000 lm/4ft
		25 2500lm/4ft		40	4000 lm/4ft
		20 2000lm/4ft		30	3000 lm/4ft
		15 1500lm/4ft		20	2000 lm/4ft
		10 1000lm/4ft		10	1000 lm/4ft
Run Length	Voltage	Driver	Circuit	Wiring Option	Systems/Controls
02 2ft 05 5ft 03 3ft 06 6ft 04 4ft 08 8ft XX Continuous run in 1ft increments (please specify length)	D UNV 120-277V 3 347V	E Advance Xitanium 0-10V (1% Dim)	1 Single circuit	N None B Battery pack E Auxiliary wiring	NN None
Finish	Mount Type		Suspension		
W Standard white T Titanium silver B Black G Graphite grey	A1 Non-accessible ceiling, 0°-15° slope mount A2 T-Grid, fixed position mount A3 Non-accessible ceiling, 0°-90° slope mount A5 T-Grid 24" span mount (non tegular tile only)	A6-1 T-Grid on-grid mount 15/16" (non tegular tile only) A6-2 T-Grid on-grid mount 9/16" (non tegular tile only) A6-3 T-Grid on-grid mount 9/16" x 5/16" (slot tee & tegular tile)	24	24"	
			48	48"	
			96	96"	
			144	144"	

*Please refer to exclusions.

DLC Note: Not all product variations are DLC qualified. To ensure that a specific model is qualified, visit www.designlights.org/search





TruGroove Surface micro

Innovative optics deliver **exceptional uniformity and wide row spacing** from a 1.75" aperture continuous line of light



Why choose TruGroove Surface micro?

- MesoOptics DX and innovative optics producing optimal batwing distribution
- Innovative quad optic louver cell provides visual comfort with excellent performance
- Smaller and more versatile
- Ideal for a variety of applications with multiple distributions and modules

Ordering guide

Family	Version	Distribution	Source	CRI/CCT
TM TruGroove micro	1 Surface	1 Direct	L LED	950 CRI 90, 5000K 940 CRI 90, 4000K 935 CRI 90, 3500K 930 CRI 90, 3000K 927 CRI 90, 2700K
Optics (Direct)		Lumens (Direct)	Optics (Indirect)	Lumens (Indirect)
Lens	Louver Cell			
N No lens (specify direct louver) Q Performance symmetric batwing flush MesoOptics W Performance asymmetric/wall wash flush MesoOptics L Definition symmetric flush silk	NNNN None	NN None 40 4000lm/4ft 35 3500lm/4ft 30 3000lm/4ft 25 2500lm/4ft 20 2000lm/4ft 15 1500lm/4ft 10 1000lm/4ft	N None	NN None
Run Length	Voltage	Driver	Circuit	Wiring Option
02 2ft 05 5ft 03 3ft 06 6ft 04 4ft 08 8ft XX Continuous run in 1ft increments (please specify length)	D UNV 120-277V 3 347V	E Advance Xitanium 0-10V (1% Dim)	1 Single circuit	N None B Battery pack E Auxiliary wiring
Systems/Controls	Finish	Mount Type		
NN None	W Standard white T Titanium silver B Black G Graphite grey	SF Surface mounted		

*Please refer to exclusions.



interact
ready.



ModiFly Suspended

The new **action hero** for lighting design. Simple, yet sophisticated, ModiFly has a style that lends itself perfectly to a variety of spaces.



Why choose ModiFly Suspended?

- Vertical Light Guide technology produces a controlled batwing distribution with 72% downlight and up to 16ft o.c. spacing
- Multiple lumen package from 1500lm/4ft to 4500lm/4ft in 500lm steps
- Choose from 6 standard paint finishes, including Hero Gold, Silver Nova & Venom Black
- Fully articulating Bi-Link, Tri-Link & Quad-Link joints give you unlimited design options



Ordering guide

Family	Version	Type	Source	CRI/CCT
MF ModiFly	O Standard	S Suspended	L LED	950 CRI 90, 5000K 940 CRI 90, 4000K 935 CRI 90, 3500K 930 CRI 90, 3000K 927 CRI 90, 2700K
Lumens	Optics	Distribution	Run Length	
45 4500lm/4ft 40 4000lm/4ft 35 3500lm/4ft 30 3000lm/4ft 25 2500lm/4ft 20 2000lm/4ft 15 1500lm/4ft	Q Vertical light guide	N 75% down/25% up	02 2ft 04 4ft 05 5ft 06 6ft 08 8ft XX Continuous run >4ft in 1ft increments (please specify length)	
Voltage	Driver	Circuit	Wiring Option	System/Controls
D UNV 120-277V 3 347V	E Advance Xitanium 0-10V (1% Dim)	1 Single circuit	N None B Battery pack E Auxiliary wiring	NN None
Finish	Mount Type	Suspension		
W Standard white H Hero gold S Silver nova V Venom black T Titanium silver B Black	M1 Non-accessible ceiling, 0°-15° slope mount M2 T-grid fixed position mount M3 Non-accessible ceiling, 0°-90° slope mount M6-1 T-grid on-grid mount 15/16" (non tegular tile only) M6-2 T-grid on-grid mount 9/16" (non tegular tile only) M6-3 T-grid on-grid mount 9/16" x 5/16" (slot tee & tegular tile)	24 24" 48 48" 96 96" 144 144"		

*Please refer to exclusions.



BoldPlay Suspended

Unrivalled performance and **effortless style** make BoldPlay a benchmark for LED luminaires



Why choose BoldPlay Suspended?

- MesoOptics and Light Guide technology
- Palette of color temperatures
- Optimal batwing distribution enabling wide row spacing
- Striking aesthetics characterized by effortless style and urban edginess

Ordering guide

Family	Version	Type	Source	CRI/CCT
78 BoldPlay	0 Suspended	6 Direct/Indirect	L LED	A CRI 80, 4000K B CRI 80, 3500K C CRI 80, 3000K
Lumens	Optics	Distribution	Run Length	
A 6500lm/4ft C 4600lm/4ft E 3400lm/4ft	Q MesoOptics lens	N Lightguide (75% up) D 55% down kit G 80% down kit J 100% down kit	04 4ft 08 8ft XX Continuous run in 4ft increments (please specify length)	
Circuit/Wiring Option	Voltage	Driver	Finish	Options
7 Single circuit N Single circuit + Battery pack M Single circuit + Auxiliary wiring	D UNV 120-277V 3 347V	E Advance Xitanium 0-10V (1% Dim)	W Standard white T Titanium silver B Black	N None
System/Controls	Mount Type			Suspension
N None	A1 Non-accessible ceiling, 0°-15° slope mount A2 T-grid fixed position mount A3 Non-accessible ceiling, 0°-90° slope mount A5 T-grid 24" span mount (non regular tile only)	A6-1 T-grid on-grid mount 5/16" (non regular tile only) A6-2 T-grid on-grid mount 9/16" (non regular tile only) A6-3 T-grid on-grid mount 9/16" x 5/16" (slot tee & regular tile)	24 24" 48 48" 96 96" 144 144"	

*Please refer to exclusions.



Sync Suspended

Sophisticated performance in a **clean and simple design** aesthetic for mainstream applications



Why choose Sync Suspended?

- Low-profile design
- MesoOptics and Light Guide panel producing optimal batwing distribution
- Allows aesthetic continuity in a space when paired with Sync Wall
- Wide row spacing with fewer fixtures and less energy consumption



Ordering guide

Family	Version	Type	Source	CRI/CCT
74 Sync	O Suspended	6 Direct/Indirect	L LED	A CRI 80, 4000K B CRI 80, 3500K C CRI 80, 3000K
Lumens	Optics	Distribution	Run Length	
A 6500lm/4ft C 4600lm/4ft E 3400lm/4ft	Q MesoOptics lens	N Lightguide (75% up) D 55% down kit G 80% down kit J 100% down kit	O4 4ft O8 8ft XX Continuous run in 4ft increments (please specify length)	
Circuit/Wiring Option	Voltage	Driver	Finish	
7 Single circuit N Single circuit + Battery pack M Single circuit + Auxiliary wiring	D UNV 120-277V 3 347V	E Advance Xitanium 0-10V (1% Dim)	W Standard white T Titanium silver B Black	
Mount Type			Suspension	
A1 Non-accessible ceiling, 0°-15° slope mount A2 T-grid fixed position mount A3 Non-accessible ceiling, 0°-90° slope mount A5 T-grid 24" span mount (non tegular tile only)	A6-1 T-grid on-grid mount 5/16" (non tegular tile only) A6-2 T-grid on-grid mount 9/16" (non tegular tile only) A6-3 T-grid on-grid mount 9/16" x 5/16" (slot tee & tegular tile)		24 24" 48 48" 96 96" 144 144"	

*Please refer to exclusions.



Verge Suspended

Uncompromising performance in an ultra slim, contemporary design



Why choose Verge Suspended?

- Suspended and complementary wall mount versions
- Exceptional direct/indirect lighting performance in a sleek, geometric design
- Complete visual comfort with the perfect balance of brightness and glare control from all viewing angles
- Engineered to allow for wider spacings

Ordering guide

Family	Version	Type	Source	CRI/CCT
76 Verge	0 Suspended	6 Direct/Indirect	L LED	A CRI 80, 4000K B CRI 80, 3500K C CRI 80, 3000K
Lumens	Optics	Distribution	Run Length	
A 6500lm/4ft C 4600lm/4ft E 3400lm/4ft	Q MesoOptics lens	N Lightguide (75% up) D 55% down kit G 80% down kit J 100% down kit	04 4ft 08 8ft XX Continuous runs in 4ft increments (please specify length)	
Circuit/Wiring Option	Voltage	Driver	Finish	
7 Single circuit N Single circuit + Battery pack M Single circuit + Auxiliary wiring	D UNV 120-277V 3 347V	E Advance Xitanium 0-10V (1% Dim)	W Standard white T Titanium silver B Black	
Mount Type				Suspension
A1 Non-accessible ceiling, 0°-15° slope mount	A6-1 T-grid on-grid mount 15/16" (non tegular tile only)	24 24"		
A2 T-grid fixed position mount	A6-2 T-grid on-grid mount 9/16" (non tegular tile only)	48 48"		
A3 Non-accessible ceiling, 0°-90° slope mount	A6-3 T-grid on-grid mount 9/16" x 5/16" (slot tee & tegular tile)	96 96"		
A5 T-grid 24" span mount (non tegular tile only)		144 144"		

*Please refer to exclusions.



Chopstick Suspended

Clean, minimalist design with **big performance** and **optimal energy-efficiency** for mainstream architectural applications



Why choose Chopstick Suspended?

- Small size with big lighting performance and a price point that makes it ideal for use in many different types of spaces
- Up to 108lm/W efficacy
- Wide lateral distribution in the upper hemisphere enabling wider row spacing
- MesoOptics and Light Guide panel producing optimal batwing distribution



Ordering guide

Family	Version	Type	Source	CRI/CCT
75 Chopstick	0 Suspended	5 Indirect/Direct	L LED	A CRI 80, 4000K B CRI 80, 3500K C CRI 80, 3000K
Lumens	Optics	Distribution	Run Length	
A 6500lm/4ft C 4800lm/4ft E 3400lm/4ft	Q MesoOptics lens	N Lightguide (88% up)	04 4ft 06 6ft 08 8ft XX Continuous run >4ft in 2ft increments (please specify length)	
Circuit/Wiring Option	Voltage	Driver	Finish	
7 Single circuit N Single circuit + Battery pack M Single circuit + Auxiliary wiring	D UNV 120-277V 3 347V	E Advance Xitanium 0-10V (1% Dim)	W Standard white T Titanium silver B Black	
Mount Type			Suspension	
A1 Non-accessible ceiling, 0°-15° slope mount A2 T-grid fixed position mount A3 Non-accessible ceiling, 0°-90° slope mount A5 T-grid 24" span mount (non tegular tile only)	A6-1 T-grid on-grid mount 15/16" (non tegular tile only) A6-2 T-grid on-grid mount 9/16" (non tegular tile only) A6-3 T-grid on-grid mount 9/16" x 5/16" (slot tee & tegular tile)		24 24" 48 48" 96 96" 144 144"	

*Please refer to exclusions.



Jump Suspended

Aesthetic design elements and **playful patterns** with multiple distributions in seamless continuum of luminance.



Why choose Jump Suspended?

- Highly flexible choice for functional environments
- Contemporary aesthetic combines the latest lighting technologies with texture, pattern, and rhythm
- Maximum control, performance and energy savings
- Three sophisticated aesthetic styles: SplashPerf, PixelPerf and SolidSide

Ordering guide

Family	Version	Distribution	Source	CRI/CCT
12 Jump	0 Suspended	1 Direct	L LED	A CRI 80, 4000K B CRI 80, 3500K C CRI 80, 3000K
Lumens	Optics	Housing	Run Length	
C 4900lm/4ft E 3600lm/4ft G 2400lm/4ft	Q Ribbed MesoOptics lens	E SolidSide P PixelPerf S SplashPerf	04 4ft 08 8ft XX Continuous run in 4ft increments (please specify length)	
Circuit/Wiring Option	Voltage	Driver	Finish	
7 Single circuit N Single circuit + Battery pack M Single circuit + Auxiliary wiring	D UNV 120-277V 3 347V	E Advance Xitanium 0-10V (1% Dim)	W Standard white T Titanium silver B Black	
Mount Type				Suspension
A1 Non-accessible ceiling, 0°-15° slope mount	A6-1 T-grid on-grid mount 15/16" (non tegular tile only)	24 24"		
A2 T-grid fixed position mount	A6-2 T-grid on-grid mount 9/16" (non tegular tile only)	48 48"		
A3 Non-accessible ceiling, 0°-90° slope mount	A6-3 T-grid on-grid mount 9/16" x 5/16" (slot tee & tegular tile)	96 96"		
A5 T-grid 24" span mount (non tegular tile only)		144 144"		

*Please refer to exclusions.



Sona Suspended

Incredible efficacy & boundless lighting choices ensure Sona LED linear is destined to become a **future classic**



Why choose Sona Suspended?

- Flexible optical design for a myriad of tasks within each space
- Budget friendly
- Flexible up/down distributions and tailored LED optics – the right light for every task



Ordering guide

Family	Version	Type	Source	CRI/CCT
77 Sona	0 One light engine - upper	3 Indirect	L LED	A CRI 80, 4000K
		5 Indirect/Direct		B CRI 80, 3500K
	1 One light engine - lower	1 Direct		C CRI 80, 3000K
Lumens	Optics & Distribution		Run Length	Circuit/Wiring Option
C 4900lm/4ft	NA Solid housing/Acrylic diffuser (100% up)		04 4ft	7 Single circuit
E 3400lm/4ft			08 8ft	N Single circuit + Battery pack
B 6100lm/4ft	AA Acrylic diffuser (70% up)		XX Continuous run in 4ft increments (please specify length)	M Single circuit + Auxiliary wiring
C 4500lm/4ft	VD White louvers + 50 % down kit			
E 3100lm/4ft				
C 4500lm/4ft	AN Acrylic diffuser/Solid housing (100% down)			
E 3200lm/4ft	VG White louvers/Acrylic diffuser (75-80% down)			
G 2100lm/4ft				
Voltage	Driver		Finish	Option
D UNV 120-277V	E Advance Xitanium 0-10V (1% Dim)		W Standard white	N None
3 347V			T Titanium silver	
			B Black	
System/Controls	Mount Type			Suspension
NN None	A1 Non-accessible ceiling, 0°-15° slope mount	A6-1	T-grid on-grid mount 15/16" (non tegular tile only)	24 24"
	A2 T-grid fixed position mount			48 48"
	A3 Non-accessible ceiling, 0°-90° slope mount	A6-2	T-grid on-grid mount 9/16" (non tegular tile only)	96 96"
	A5 T-grid 24" span mount (non tegular tile only)	A6-3	T-grid on-grid mount 9/16" x 5/16" (slot tee & tegular tile)	144 144"

*Please refer to exclusions.



interact
ready.





FloatPlane Suspended

Coast-to-coast style that your budget will love



Why choose FloatPlane Suspended?

- Sleek and low profile design of only 1.2" h x 8" w
- Compelling performance of up to 129 LPW
- Fresh and playful, with Curve and Edge profile options
- Multiple lumen package and color temperature options
- Affordable performance for your budget

Ordering guide

Family	Version	Type	Source	CRI/CCT
24 FloatPlane	G Edge suspended R Curve suspended	5 Indirect/Direct	L LED	A 80CRI, 4000K B 80CRI, 3500K C 80CRI, 3000K
Lumens	Optics	Distribution	Run Length	Circuit/Wiring Option
A 7500lm/4ft B 6000lm/4ft C 4500lm/4ft E 3200lm/4ft	A Acrylic diffuser	A Acrylic diffuser (70% up) D 45% down kit G 75% down kit H 90% down kit J 100% down kit	04 4ft 06 6ft 08 8ft XX Continuous run >4ft in 2ft increments (please specify length)	7 Single circuit N Single circuit + Battery pack M Single circuit + Auxiliary wiring
Voltage	Driver	Finish	Options	System/Controls
D UNV 120-277V 3 347V	E Advance Xitanium 0-10V (1% Dim)	W Standard white T Titanium silver B Black	N None	N None
Mount Type				Suspension
A1 Non-accessible ceiling, 0°-15° slope mount		A6-1 T-grid on-grid mount 15/16" (non tegular tile only)		24 24"
A2 T-grid fixed position mount		A6-2 T-grid on-grid mount 9/16" (non tegular tile only)		48 48"
A3 Non-accessible ceiling, 0°-90° slope mount		A6-3 T-grid on-grid mount 9/16" x 5/16" (slot tee & tegular tile)		96 96"
A5 T-grid 24" span mount (non tegular tile only)				144 144"

*Please refer to exclusions.



SyncLine Suspended

Aimed at **budget driven** interiors, SyncLine provides a clean, modern aesthetic with the **performance** you expect from Ledalite.



Why choose SyncLine Suspended?

- Small housing (6.75" wide x 1.5" high)
- Budget friendly
- Efficacy up to 150 lm/W
- AccuRender CRI 90+ across the CCT range
- 10+ optical configurations with wide indirect distributions



Ordering guide

Family			Version	Distribution	Source	CRI/CCT
SL SyncLine			0 Suspended - one light engine	1 Direct	L LED	950 CRI 90, 5000K
				3 Indirect		940 CRI 90, 4000K
				6 Direct/Indirect		935 CRI 90, 3500K
			1 Suspended - two light engines	6 Direct/Indirect		930 CRI 90, 3000K 927 CRI 90, 2700K
Lumens			Optics		Run Length	Voltage
One light engine	Total fixture lumens	NN D/I lumens determined by optics	AJ Acrylic Diffuser (100% Down, Max 4000 lm/4ft)		04 4ft	D UNV 120-277V
	80 8000 lm/4ft				06 6ft	3 347V
	70 7000 lm/4ft		NA Dust Cover (100% Up, Max 7000 lm/4ft)		08 8ft	
	60 6000 lm/4ft		NB Open - No Dust Cover (100% Up, Max 7000 lm/4ft)		XX Continuous run in 2ft increments > 4ft (please specify)	
	50 5000 lm/4ft		AA Acrylic Diffuser/Dust Cover (30% Down/70% Up)			
	40 4000 lm/4ft		AB Acrylic Diffuser/Open - No Dust Cover (20% Down/80% Up)			
	30 3000 lm/4ft		AD Acrylic Diffuser/Dust Cover (50% Down/50% Up)			
	20 2000 lm/4ft		AE Acrylic Diffuser/Open - No Dust Cover (40% Down/60% Up)			
			AG Acrylic Diffuser/Dust Cover (80% Down/20% Up, Max 5000 lm/4ft)			
Driver			Circuit	Wiring Option	System/Controls	Finish
X Advance 0-10V (10% Dim)			1 Single circuit	N None	NN None	W Standard white
E Advance Xitanium 0-10V (1% Dim)				B Battery pack		B Black
				N Auxiliary wiring		
Options		Mount Type				Suspension
N None	V Variable mount housing	A1 Non-accessible ceiling, 0°-15° slope mount	A6-1 T-grid on-grid mount 15/16" (non tegular tile only)			24 24"
		A2 T-grid fixed position mount	A6-2 T-grid on-grid mount 9/16" (non tegular tile only)			48 48"
		A3 Non-accessible ceiling, 0°-90° slope mount	A6-3 T-grid on-grid mount 9/16" x 5/16" (slot tee & tegular tile)			96 96"
		A5 T-grid 24" span mount (non tegular tile only)				144 144"

*Please refer to exclusions.



Recessed, Cove, & Perimeter





TruGroove Recessed

Seamless 3" ribbon of light with **exceptional performance and versatility** for functional and decorative applications



Why choose TruGroove Recessed?

- Elevated performance to a whole new level in narrow aperture recessed lighting
- Wide row spacing with fewer fixtures and less energy consumption
- Designed to integrate seamlessly with any drywall or T-grid ceiling condition
- Continuous lines of uninterrupted luminance



Ordering guide

Family	Version	Distribution	Source	CRI/CCT
39 TruGroove	O Recessed	1 Performance symmetric	L LED	950 CRI 90, 4000K
		8 Performance asymmetric wall wash		940 CRI 90, 4000K
		0 Definition symmetric		935 CRI 90, 3500K
				930 CRI 90, 3000K
				927 CRI 90, 2700K
Lumens	Optics	Housing	Ceiling/Trim	Run Length
40 4000lm/4ft	Q Flush MesoOptics lens	S Standard	1 T-grid	02 2ft
30 3000lm/4ft	R Regressed MesoOptics lens	C Chicago Plenum	3 Drywall trimless (ceiling)	04 4ft
22 2200lm/4ft	Q Flush MesoOptics lens		4 Drywall trim	06 6ft
15 1500lm/4ft				08 8ft
				XX Continuous runs 2-20ft in 2ft increments (please specify length)
	L Flush silk lens			
	M Regressed silk lens			
Voltage	Driver	Circuit	Wiring Option	System/Controls
D UNV 120-277V	E Advance Xitanium 0-10V (1% Dim)	1 Single circuit	N None	NN None
3 347V			B Battery pack	
			E Auxiliary wiring	
Trim Finish				
W Standard white				
B Black				

*Please refer to exclusions.



1.75"
aperture

TruGroove Recessed micro

Seamless 1.75" ribbon of light delivers the perfect combination of slender aesthetic and lighting control

Why choose TruGroove Recessed micro?

- Ideal for a variety of applications
- Elevated performance to a whole new level in narrow aperture lighting
- Wide row spacing with fewer fixtures and lower energy consumption
- Continuous lines of uninterrupted luminance to 1/8"
- Exceptional uniformity and wide row spacing from a 1.75" aperture continuous line-of light

Ordering guide

Family	Version	Distribution	Source	CRI/CCT
23 TruGroove micro	0 Recessed	1 Direct	L LED	950 CRI 90, 4000K 940 CRI 90, 4000K 935 CRI 90, 3500K 930 CRI 90, 3000K 927 CRI 90, 2700K
Optics		Lumens (Direct)	Housing	Ceiling/Trim
Lens	Louver Cell			
Q Performance Symmetric Batwing Flush MesoOptics W Performance Asymmetric/ Wall Wash Flush MesoOptics L Definition Symmetric Flush Silk	NNNN	NN None 40 4000 lm/4ft 35 3500 lm/4ft 30 3000 lm/4ft 25 2500 lm/4ft 20 2000 lm/4ft 15 1500 lm/4ft 10 1000 lm/4ft	S Standard C Chicago Plenum	1 T-grid 3 Drywall trimless (ceiling) 4 Drywall trim
Run Length	Voltage	Driver	Circuit	Wiring Option
02 2ft 04 4ft 06 6ft 08 8ft XX Continuous run 2-20ft in 2ft increments (please specify length)	D UNV 120-277V 3 347V	E Advance Xitanium 0-10V (1% Dim)	1 Single circuit	N None B Battery pack E Auxiliary wiring
System/Controls		Trim Finish		
NN None		W Standard white B Black		

*Please refer to exclusions.



interact
ready.



TruGroove Cove

TruGroove cove offers a **highly-controlled asymmetric light throw**, evenly lighting the space and ceiling



Why choose TruGroove Cove?


- Highly-controlled asymmetric light throw
- Single spec housing that can adjust the peak candela angle based on mounting orientation
- High performance in a smaller than 5"x2" cross-section
- Free of striations and any "socket shadow" effects
- Focus and fill optics



Ordering guide

Family	Version	Distribution	Source	CRI/CCT
TC TruGroove	O Cove	8 Asymmetric	L LED	950 CRI 90, 4000K 940 CRI 90, 4000K 935 CRI 90, 3500K 930 CRI 90, 3000K 927 CRI 90, 2700K
Lumens	Optics	Housing	Ceiling/Trim	Run Length
60 6000lm/4ft 50 5000lm/4ft 40 4000lm/4ft 30 3000lm/4ft 25 2500lm/4ft 20 2000lm/4ft 15 1500lm/4ft 10 1000lm/4ft	WN Focus optics (micro silver) LN Fill optics (white reflector)	S Standard C Chicago Plenum	N None	02 2ft C2 2.5ft 03 3ft C3 3.5ft 04 4ft 05 5ft 06 6ft 08 8ft XX Continuous runs in 6in increments (please specify length)
Voltage	Driver	Circuit	Wiring Option	System/Controls
D UNV 120-277V 3 347V	E Advance Xitanium 0-10V (1% Dim)	1 Single circuit	N None B Battery pack E Auxiliary wiring	NN None
Finish				
N Satin Coat				

*Please refer to exclusions.



TruGroove Perimeter

Seamless ribbon of light with **exceptional performance and versatility** for functional and decorative applications



Why choose TruGroove Perimeter?

- Architectural recessed lighting for making a statement, or setting a mood
- Ambient provides ambient lighting that creates soft light for wayfinding
- Graze allows for making maximum impact along wall sculptures or architectural features

Ordering guide

Family	Version		Distribution	Source	CRI/CCT
49 TruGroove	O Perimeter		8 Ambient	L LED	950 CRI 90, 5000K
			9 Graze		940 CRI 90, 4000K
					935 CRI 90, 3500K
					930 CRI 90, 3000K
				927 CRI 90, 2700K	
Lumens	Optics		Housing	Surface	Run Length
40 4000lm/4ft 30 3000lm/4ft 22 2200lm/4ft 15 1500lm/4ft	Q Flush MesoOptics lens		S Standard C Chicago Plenum	N All ceiling trims: endset, slot & trim* (please specify separately)	02 2ft
					04 4ft
					06 6ft
					08 8ft
	P Reverse parabolic optic w/ flush lens				XX Continuous run 2-20ft in 2ft increments (please specify length)
Voltage	Driver		Circuit	Wiring Option	System/Controls
D UNV 120-277V 3 347V	E Advance Xitanium 0-10V (1% Dim)		1 Single circuit	N None B Battery pack E Auxiliary wiring	NN None
Finish	Endset (left)	Endset (right)	Slot height	Slot panel	Ceiling/Trim
W Standard white	C Variable/Wall	C Variable/Wall	2 1.75"	S Standard solid	1 T-grid
	S Fixed/Pocket	S Fixed/Pocket	4 4"		3 Drywall trimless
					4 Drywall trim
B Black			4 4"	A Air return	1 T-grid

*Please refer to exclusions.








Recessed





ArcForm

Inspired by the **classic curve** and **innovative design** delivers exceptional performance and energy saving



Why choose ArcForm?

- Graceful aesthetic
- State-of-the-art LED optical design
- Three-dimensional batwing lighting distribution
- Patented MesoOptics nanotechnology
- Multiple lumen packages and color temperatures



Ordering guide

Family	Size	Version	Configuration	Source
36 ArcForm	14 1' x 4'	D1 Standard T-grid	ST Standalone	L LED
	22 2' x 2'	D2 Slot T-grid		
		C1 Standard T-grid + Chicago Plenum		
		C2 Slot T-grid + Chicago Plenum		
CRI/CCT	Lumens	Optics	Circuit/Wiring Option	
950 CRI 90, 5000K	45 4500lm	Q MesoOptics with 3D batwing	1 Single circuit	
940 CRI 90, 4000K	35 3500lm		B Single circuit + Battery pack	
935 CRI 90, 3500K	30 3000lm			
920 CRI 90, 2000K				
927 CRI 90, 2700K				
Voltage	Driver	Option	System/Controls	
D UNV 120-277V	E Advance Xitanium 0-10V (1% Dim)	N None	NN None	
3 347V				

*Please refer to exclusions.



SilkSpace definition

Minimalist, modern good looks
that's perfect for your tight
budget projects



Why choose SilkSpace definition?

- Graceful aesthetic
- State-of-the-art LED optical design
- High efficiency with a fully luminous optic, minimizing harsh shadows
- Multiple lumen packages and color temperatures



Ordering guide

Family	Size	Version	Configuration	Source
42 SilkSpace definition	14 1' x 4'	D1 Standard T-grid	ST Standalone	L LED
	22 2' x 2'	C1 Standard T-grid + Chicago Plenum		
	24 2' x 4'			
CRI/CCT	Lumens	Optics	Circuit/Wiring Option	
950 CRI 90, 5000K	50 5000lm	A Acrylic Silk Lens	1 Single circuit B Single circuit + Battery pack	
940 CRI 90, 4000K	45 4500lm			
935 CRI 90, 3500K	40 4000lm			
930 CRI 90, 3000K	35 3500lm			
927 CRI 90, 2700K	30 3000lm			
	25 2500lm			
	80 8000lm			
	75 7500lm			
	70 7000lm			
	65 6500lm			
	60 6000lm			
	55 5500lm			
	50 5000lm			
	45 4500lm			
40 4000lm				
Voltage	Driver	Option	System/Controls	
D UNV 120-277V 3 347V	E Advance Xitanium 0-10V (1% Dim)	N None	NN None	

*Please refer to exclusions.



SilkSpace

SilkSpace delivers discrete, comfortable lighting with great performance and **ultra low-glare**



Why choose SilkSpace?

- Fully luminous, minimalist aesthetic superior performance and ultra low-glare
- Optional controls and sensors
- Wide variety of sizes, lumen packages and color temperatures
- Available in 1'x4', 2'x2' & 2'x4'

Ordering guide

Family	Size	Version	Configuration	Source
42 SilkSpace	14 1' x 4'	D1 Standard T-grid	ST Standalone	L LED
	22 2' x 2'	C1 Standard T-grid + Chicago Plenum		
	24 2' x 4'			
CRI/CCT	Lumens	Optics	Circuit/Wiring Option	
940 CRI 90, 4000K	40 4000lm	Q Light Guide with MesoOptics	1 Single circuit B Single circuit + Battery pack	
935 CRI 90, 3500K	30 3000lm			
930 CRI 90, 3000K	17 1700lm			
	68 6800lm			
	52 5200lm			
	40 4000lm			
Voltage	Driver	Option	System/Controls	
D UNV 120-277V 3 347V	E Advance Xitanium 0-10V (1% Dim)	N None	NN None	

*Please refer to exclusions.



interact
ready.



PureFX

Exceptional lighting performance and styling. The perfect blend of brightness, control and energy efficiency



Why choose PureFX?

- Graceful aesthetic
- State-of-the-art LED optical design
- High efficiency with a fully luminous optic, minimizing harsh shadows
- Multiple lumen packages and color temperatures




Ordering guide

Family	Size	Version	Configuration	Source
94 PureFX	14 1' x 4'	D1 Standard T-grid	ST Standalone	L LED
	22 2' x 2'	D2 Slot T-grid		
CRI/CCT	Lumens	Housing	Circuit/Wiring Option	
A CRI 90, 4000K	44 4400lm	S Standard	1 Single circuit	
B CRI 90, 3500K	36 3600lm	C Chicago Plenum	B Single circuit + Battery pack	
C CRI 90, 3000K				
Voltage	Driver	Option	System/Controls	
D UNV 120-277V	E Advance Xitanium 0-10V (1% Dim)	N None	NN None	
3 347V				

*Please refer to exclusions.





Shine

A family of uniformly luminous fixtures combines Ledalite **quality** and **value**



Why choose Shine?

- High efficiency with a fully luminous optic, minimizing harsh shadows
- Wide range of fixture sizes
- Multiple lumen packages and color temperatures to meet any specification
- Outstanding performance with superior energy savings

Ordering guide

Family	Size	Version	Configuration	Source
33 Shine	14 1' x 4'	D1 Standard T-Grid C1 Standard T-Grid + Chicago Plenum	ST Standalone	L LED
	22 2' x 2'			
	24 2' x 4'			
CRI/CCT	Lumens	Optics	Circuit/Wiring Option	
950 CRI 90, 5000K	50 5000lm	A Acrylic silk lens	1 Single circuit B Single circuit + Battery pack	
940 CRI 90, 4000K	45 4500lm			
935 CRI 90, 3500K	40 4000lm			
930 CRI 90, 3000K	35 3500lm			
927 CRI 90, 2700K	30 3000lm			
	25 2500lm			
	80 8000lm			
	75 7500lm			
	70 7000lm			
	65 6500lm			
	60 6000lm			
	55 5500lm			
	50 5000lm			
	45 4500lm			
	40 4000lm			
Voltage	Driver	Option	System/Controls	
D UNV 120-277V 3 347V	E Advance Xitanium 0-10V (1% Dim)	N None	NN None	

*Please refer to exclusions.



interact
ready.



Vectra

Controlled brightness, energy efficiency, **design flexibility** and **easy maintenance** in a refined aesthetic for modern architectural spaces



Why choose Vectra?

- Graceful aesthetic
- State-of-the-art LED optical design
- Three-dimensional batwing lighting distribution
- Patented MesoOptics nanotechnology
- Available in 1'x4' & 2'x2'
- Multiple lumen packages and color temperatures



Ordering guide

Family	Size	Version	Configuration	Source
97 Vectra	14 1' x 4'	D1 Standard T-grid	ST Standalone	L LED
	22 2' x 2'	D2 Slot T-grid		
CRI/CCT	Lumens	Housing	Circuit/Wiring Option	
A CRI 90, 4000K	44 4400lm	S Standard	1 Single circuit	
B CRI 90, 3500K	36 3600lm	C Chicago Plenum	B Single circuit + Battery pack	
C CRI 90, 3000K				
Voltage	Driver	Option	System/Controls	
D UNV 120-277V	E Advance Xitanium 0-10V (1% Dim)	N None	NN None	
3 347V				

*Please refer to exclusions.





© 2023 Signify Holding. All rights reserved. The information provided herein is subject to change, without notice. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify.

Signify North America Corporation
400 Crossing Blvd, Suite 600
Bridgewater, NJ 08807
Telephone: 800-555-0050

Signify Canada Ltd.
281 Hillmount Road,
Markham, ON, Canada L6C 2S3
Telephone: 800-668-9008

All trademarks are owned by Signify Holding or their respective owners.