

# PHILIPS

Bulb 60W A19 GU24

LED

3000K

800lm

15000h

Dimming

046677557683



## Bright LED lighting with excellent light quality

Familiar shapes you know and love. They use around 80% less energy than traditional light bulbs and last ten times longer.

### High quality light

- Cool, energizing light

### Choose for a sustainable solution

- Long life tubes - Lasts up to 15 years
- Saves up to 80% Energy

### Light beyond illumination

- Dimmable

### High quality LED light that lasts for decades

- Designed for the comfort of your eyes

# Highlights

## 3500K [LED Lamps]



This bulb has a color temperature of 3500K providing you with a cool, energizing light, perfect for creating an inviting ambiance to host friends or wind down with a book.

## 15,000-hour rated average life



With a lifetime of up to 15,000 hours, you can reduce the hassle of frequently replacing your light tubes and enjoy a perfect lighting solution for over 15 years.

## Saves up to 80% Energy



Enjoy the energy-savings of LEDs without sacrificing light quality. Instantly save over 80% in energy by replacing your existing incandescent or halogen bulbs

## Dimmable

This bulb can be used with most dimmers to create your desired ambience with smooth dimming to 10% of full light levels. Please check the dimmability compatibility chart to be certain that your particular dimmer can be used with this bulb.

## Designed for the comfort of your eyes



It's easy to see how harsh lighting can strain the eyes. Too bright, and you get glare. Too soft and you experience flicker. Now you can gently light up your world with LEDs designed to go easy on the eyes, and create the perfect ambience for your home.

# Specifications

## Bulb characteristics

- Intended use: Indoor
- Lamp shape: Non directional bulb
- Socket: GU24
- Bulb Finish: Frosted
- Dimmable: Yes
- Bulb Material: Plastic

## Durability

- Number of switch cycles: 50,000
- Nominal lifetime: 15,000

## Environmental

- Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

#### Light characteristics

- Beam angle: 250 degree(s)
- Color rendering index (CRI): 90
- Color temperature: 3000 K
- Nominal luminous flux: 800 lm
- Warm-up time to 60% light: 0.5
- Color Code: 930 | CCT of 3000K
- Luminous Efficacy (rated) (Nom): 90 lm/W

#### Miscellaneous

- EyeComfort: Yes
- LED Innovations: EyeComfort
- Extra Features: Dimmable

#### Packaging information

- EAN: 046677557683
- EOC: 557686
- Product title: 8.8A19/PER/930/P/GU24/DIM 4/1FB T20

#### Power consumption

- Power factor: 0.7
- Voltage: 120 V
- Wattage equivalent: 60 W
- Power Consumption: 8.8 W

#### Product dimensions and weight

- Overall height: 106 mm
- Overall length: 106 mm
- Overall width: 60 mm

#### Technical specifications

- Frequency: 60
- UL Wet/ damp/ dry location: Damp location

#### Packaging dimensions and weight

- EAN/UPC – product: 046677557683
- Net weight: 0.05 kg
- Gross weight: 0.07 kg
- Height: 10.8 cm
- Length: 6.2 cm
- Width: 6.2 cm



Issue date: 2025-08-30  
Version: 0.153

© 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)