

PHILIPS

Bulb 60W A19 E26

LED

2700/5000/2200K

800;800;80lm

15000h

046677568931



State-of-the-art LED for the home

State-of-the-art LED light bulb providing a general lighting solution for daily indoor activities. You will save on energy costs immediately and reduce the frequency of bulb replacements, without compromising on the quality of your lighting.

High quality light

- Learn about light
- No visible flicker

Create the right light for your home

- A simple LED for everyday use

Light beyond illumination

- One bulb, four color settings

Highlights

Learn about light



Color temperature: light can have different color temperatures, indicated in units called Kelvin (K). Bulbs with a low Kelvin value produce a warm, more tranquil light, while those with a higher Kelvin value produce a cool, more energizing light. **CRI:** the color rendering index (CRI) is used to

describe the effect of a light source on color appearance. Natural sunlight has a CRI of 100. The CRI of Philips LED light bulbs is always higher than 80, which ensures colors are shown as true and natural.

No visible flicker

When your light flickers in quick succession it could be hard on the eyes, cause headaches, and even set off an attack for those with photosensitive epilepsy. It's both unpleasant and unnecessary. LEDs can flicker because of their rapid response to the driver current. However, because Philips LEDs are designed so that variations in your driver current's output are minimized, they eliminate the factors that cause flicker. So, you won't see it, not even a hint.

A Simple LED for Everyday Use

The Philips everyday LED is the perfect bulb for your basic lighting needs. It provides the beautiful light and dependable performance you expect from Philips LED at an affordable price.

Color Light Settings

Flip from regular bright white, to red, to green, to blue with any existing switch or lamp. Set it once for everyday bright white light, or change it to red, green, or blue to decorate your home for holidays and special occasions, all with the flip of the switch - it's that simple!

Specifications

Bulb characteristics

- Intended use: Indoor
- Lamp shape: Non directional bulb
- Socket: E26
- Dimmable: No
- Bulb Finish: Frosted
- Bulb Material: Plastic

Durability

- Number of switch cycles: 100,000
- Nominal lifetime: 15,000

Environmental

- Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

Light characteristics

- Beam angle: 200 degree(s)
- Color rendering index (CRI): 80
- Color temperature: 2200-2700-5000 K
- Nominal luminous flux: 800, 800, 80 lm
- Warm-up time to 60% light: instant full light
- Color Code: 827/850/822 | CCT of 2700K/5000K/2200K
- Luminous Efficacy (rated) (Nom): 84 lm/W

Miscellaneous

- EyeComfort: Yes
- LED Innovations: EyeComfort

Packaging information

- EAN: 046677568931
- EOC: 568931
- Product title: 9.5A19/PER/827-50-22/FR/P/E26/SS 4/1PF

Power consumption

- Power factor: 0.6
- Voltage: 120 V
- Wattage equivalent: 60 W
- Power: 9.5, 8, 3 W

Product dimensions and weight

- Overall height: 111 mm
- Overall length: 111 mm
- Overall width: 61 mm

Technical specifications

- Frequency: 60

Packaging dimensions and weight

- EAN/UPC - product: 046677568931
- Net weight: 0.06 kg
- Gross weight: 0.09 kg
- Height: 17.1 cm
- Length: 6.5 cm
- Width: 7.5 cm



Issue date: 2025-12-27
Version: 0.64

© 2025 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com