

# PHILIPS

Capsule 40W  
Capsule G9 x3

LED

3000K

370lm

15000h

046677571061



## A familiar beam meets an innovative design

This Mains voltage LED capsule provides bright, all around, white light.

### High quality light

- Bright white light

### Choose for a sustainable solution

- Long life bulbs – Lasts up to 15 years

### Create the right light for your home

- A simple LED for everyday use

# Highlights

## Bright white light



This bulb has a color temperature of 3000K providing you with a bright, warm light, perfect for creating an

inviting ambiance to host friends or wind down with a book.

## 15,000-hour rated average life



With a lifetime of up to 15,000 hours, you can reduce the hassle of frequently replacing your light bulbs, and enjoy a perfect lighting solution for over 15 years.

## A Simple LED for Everyday Use

The Philips everyday LED is the perfect bulb for your basic lighting needs. It provides the beautiful light and dependable performance you expect from Philips LED at an affordable price.

# Specifications

## General

- Suitable For Accent Lighting: No

## Bulb characteristics

- Intended use: Indoor
- Lamp shape: Non directional capsule
- Socket: G9
- Dimmable: No

## Durability

- Number of switch cycles: 50,000
- Nominal lifetime: 15,000
- Ambient temperature range: -20 to +40 °C

## Environmental

- Disposal of the product: At the end of (economic) life, dispose the product according to local rules and do not dispose the product with regular household waste. The correct disposal of your product will help prevent potential negative consequences for the environment and human health.

## Light characteristics

- Color rendering index (CRI): 80
- Color temperature: 3000 K
- Nominal luminous flux: 370 lm
- Warm-up time to 60% light: 0.5 s
- Color Code: 830 | CCT of 3000K
- Correlated Color Temperature (Nom): 3000 K
- Luminous Flux: 370 lm
- Luminous Efficacy (rated) (Nom): 102.00 lm/W

## Miscellaneous

- EyeComfort: Yes
- LED Innovations: EyeComfort

## Other characteristics

- EU RoHS compliant: Yes

## Packaging information

- EAN: 046677571061
- EOC: 571067
- Product title: 3.6T3/PER/830/ND/G9/120V 6/3PF

## Power

- Power Factor (Fraction): 0.5

**Power consumption**

- Power factor: 0.5
- Voltage: 120 V
- Wattage equivalent: 40 W
- Power: 3.6 W

**Product dimensions and weight**

- Overall height: 51.5 mm
- Overall length: 51.5 mm
- Overall width: 17 mm

**Packaging dimensions and weight**

- EAN/UPC - product: 046677571061
- Net weight: 0.02 kg
- Gross weight: 0.03 kg
- Height: 14.6 cm
- Length: 4 cm
- Width: 7.5 cm

**Rated values**

- Rated lifetime: 15,000

**Technical specifications**

- Frequency: 60
- Diameter: 17 mm
- Dimmable: No
- Line Frequency: 60
- Cap-Base: G9
- UL Wet/ damp/ dry location: Damp location
- can it be used in closed luminaires: Yes



Issue date: 2026-01-31  
Version: 0.76

© 2026 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)