


Ceiling Dip SW RD 15.5W 1 x 9290025622 4000K


1 x 1400 lm

Polar intensity diagram

Light output ratio 1.00
 Service upward 0.12
 Service downward 0.88


CIE flux code 42 72 91 88 100

UGRcen (4Hx8H, 0.25H) 21

Quantity estimation diagram**Utilisation factor table**

Room Index k	Reflectances (%) for ceiling, walls and working plane (CIE)												
	0.80 0.80			0.70 0.70 0.70 0.70				0.50 0.50		0.30 0.30			0.00
	0.50 0.50			0.50 0.50 0.50 0.30				0.30 0.10		0.30 0.10			0.00
	0.30 0.10			0.30 0.20 0.10 0.10				0.10 0.10		0.10 0.10			0.00
0.60	0.44	0.42	0.43	0.42	0.41	0.33	0.32	0.27	0.31	0.27	0.24		
0.80	0.54	0.51	0.53	0.51	0.50	0.42	0.40	0.35	0.39	0.34	0.31		
1.00	0.63	0.58	0.61	0.59	0.57	0.49	0.47	0.42	0.45	0.41	0.37		
1.25	0.71	0.65	0.68	0.66	0.63	0.56	0.54	0.49	0.51	0.47	0.43		
1.50	0.77	0.70	0.74	0.71	0.68	0.61	0.59	0.54	0.56	0.52	0.48		
2.00	0.87	0.78	0.84	0.79	0.76	0.70	0.67	0.62	0.64	0.60	0.55		
2.50	0.94	0.83	0.90	0.85	0.80	0.75	0.72	0.68	0.69	0.65	0.61		
3.00	0.98	0.86	0.94	0.89	0.84	0.79	0.76	0.72	0.72	0.69	0.64		
4.00	1.05	0.91	1.00	0.94	0.88	0.84	0.81	0.78	0.77	0.74	0.69		
5.00	1.09	0.93	1.04	0.97	0.91	0.88	0.84	0.81	0.80	0.78	0.72		

Ceiling mounted

UGR diagram**Luminance Table**

Plane Cone	0.0	15.0	30.0	45.0	60.0	75.0	90.0
45.0	4240	4240	4240	4240	4240	4240	4240
50.0	4078	4078	4078	4078	4078	4078	4078
55.0	3893	3893	3893	3893	3893	3893	3893
60.0	3672	3672	3672	3672	3672	3672	3672
65.0	3470	3470	3470	3470	3470	3470	3470
70.0	3235	3235	3235	3235	3235	3235	3235
75.0	2996	2996	2996	2996	2996	2996	2996
80.0	2781	2781	2781	2781	2781	2781	2781
85.0	2634	2634	2634	2634	2634	2634	2634
90.0	2659	2659	2659	2659	2659	2659	2659

(cd/m²)

2020-06-19