


1 x TLED 26.7W 3000K 9290037750


1 x 3700 lm

Polar intensity diagram

Light output ratio 1.00
 Service upward 0.24
 Service downward 0.76


CIE flux code 36 64 85 76 100

UGRcen (4Hx8H, 0.25H) 28

Quantity estimation diagram**Utilisation factor table**

Room Index k	Reflectances (%) for ceiling, walls and working plane (CIE)											
	0.80			0.70			0.50			0.30		
	0.80	0.50	0.30	0.80	0.50	0.30	0.80	0.50	0.30	0.80	0.50	0.30
0.60	0.40	0.38	0.30	0.38	0.38	0.37	0.29	0.27	0.23	0.25	0.21	0.18
0.80	0.50	0.47	0.48	0.46	0.45	0.37	0.34	0.29	0.32	0.27	0.23	0.23
1.00	0.58	0.54	0.55	0.53	0.51	0.44	0.40	0.35	0.37	0.33	0.28	0.28
1.25	0.66	0.60	0.62	0.60	0.58	0.50	0.46	0.41	0.43	0.38	0.33	0.33
1.50	0.72	0.65	0.68	0.65	0.62	0.55	0.51	0.46	0.47	0.43	0.37	0.37
2.00	0.81	0.73	0.77	0.73	0.69	0.63	0.58	0.54	0.54	0.50	0.43	0.43
2.50	0.88	0.77	0.83	0.78	0.74	0.68	0.63	0.59	0.58	0.55	0.48	0.48
3.00	0.92	0.81	0.87	0.82	0.78	0.72	0.67	0.63	0.62	0.59	0.51	0.51
4.00	0.99	0.86	0.93	0.87	0.82	0.78	0.72	0.69	0.66	0.64	0.55	0.55
5.00	1.03	0.88	0.97	0.91	0.85	0.81	0.75	0.72	0.69	0.67	0.58	0.58

Ceiling mounted

UGR diagram**Luminance Table**

Plane Cone	0.0	15.0	30.0	45.0	60.0	75.0	90.0
45.0	23744	23573	24221	25018	26813	30755	37199
50.0	22858	22621	23240	23892	25583	29575	36545
55.0	22197	21846	22385	22806	24271	28179	35550
60.0	21528	21108	21613	21809	23049	26694	34253
65.0	20981	20510	21005	20918	21843	25051	32564
70.0	20633	20051	20481	20126	20745	23268	30271
75.0	20305	19652	20064	19459	19793	21302	26894
80.0	20115	19433	19892	19017	19032	19207	21722
85.0	20187	19413	19872	18857	18766	17633	14111
90.0	20379	19538	20053	19003	19027	18006	2891

(cd/m²)

s23120014a

2024-01-31