


DN020B G4 LED6 7W D100 1 x 9290032788 6500K


1 x 600 lm

Polar intensity diagram

Light output ratio 1.00
 Service upward 0.00
 Service downward 1.00


CIE flux code 49 80 95 100 100

UGRcen (4Hx8H, 0.25H) 26

Quantity estimation diagram**Utilisation factor table**

Room Index k	Reflectances (%) for ceiling, walls and working plane (CIE)											
	0.80			0.70			0.50			0.30		
	0.80			0.50			0.30			0.10		
	0.30			0.20			0.10			0.10		
0.60	0.49	0.47	0.49	0.47	0.46	0.39	0.39	0.34	0.38	0.34	0.32	0.32
0.80	0.60	0.56	0.59	0.57	0.56	0.48	0.48	0.43	0.47	0.42	0.40	0.40
1.00	0.69	0.64	0.68	0.65	0.63	0.56	0.55	0.50	0.54	0.50	0.48	0.48
1.25	0.77	0.71	0.76	0.73	0.70	0.63	0.62	0.58	0.61	0.57	0.55	0.55
1.50	0.84	0.76	0.82	0.78	0.75	0.69	0.68	0.63	0.67	0.63	0.60	0.60
2.00	0.94	0.84	0.91	0.87	0.83	0.77	0.76	0.72	0.75	0.71	0.69	0.69
2.50	1.00	0.88	0.97	0.92	0.87	0.83	0.81	0.78	0.80	0.77	0.74	0.74
3.00	1.05	0.92	1.02	0.96	0.91	0.86	0.85	0.82	0.83	0.81	0.78	0.78
4.00	1.11	0.96	1.07	1.00	0.95	0.91	0.89	0.87	0.88	0.86	0.83	0.83
5.00	1.14	0.98	1.11	1.03	0.97	0.94	0.92	0.90	0.91	0.89	0.86	0.86

Ceiling mounted

UGR diagram**Luminance Table**

Plane Cone	0.0	15.0	30.0	45.0	60.0	75.0	90.0
45.0	18372	18372	18372	18372	18372	18372	18372
50.0	17701	17701	17701	17701	17701	17701	17701
55.0	17017	17017	17017	17017	17017	17017	17017
60.0	16312	16312	16312	16312	16312	16312	16312
65.0	15559	15559	15559	15559	15559	15559	15559
70.0	14744	14744	14744	14744	14744	14744	14744
75.0	13837	13837	13837	13837	13837	13837	13837
80.0	12714	12714	12714	12714	12714	12714	12714
85.0	10928	10928	10928	10928	10928	10928	10928
90.0	8106	8106	8106	8106	8106	8106	8106

(cd/m²)

2023-05-18