


Removability Introduction







Disposal at End of Life

Light source reference control setting


Composition Explanation – PHI RGBICWW LED Strips

A. Composition Explanation



Control gear 	Switch cover 	Switch 
Switch housing 	Connector 	Connector2 

Light source:




- LED-PCBA
- 3M tape

Removability Introduction on Disposal at End of Life

Composition Explanation – PHI RGBICWW LED Strips

B. Steps to remove the components



Type: without permanent damage
Recommendation on disposal
Plastic part: reuse and recycling
Electrical part: disposal
Metal part: recycling

Removability Introduction on Disposal at End of Life

Composition Explanation – PHI RGBICWW LED Strip

C. Setup the test



RGBICWW Strip (cut 0.4m off the light strip)

D. Reference control setting

For the test point, you are suggested to find the CCT point by following the below steps:

- To cut strip in length as above and with plug and control part, and power on
- To open WiZ APP → Connect the light strip to WiZ App → Color → CCT → Key in “6000” in CCT Value → Apply → Start the test



@ 6000K for RGBICWW Strip:

9290047097LSPHI, 9290047099LSPHI, 9290047100LSPHI,
9290047191LSPHI, 9290047192LSPHI, 9290047193LSPHI