








Removability Introduction


Disposal at End of Life

Light source reference control setting

Composition Explanation – WiZ Low Cost LED Tapes

A. Composition Explanation


Control gear 	Switch cover 	Switch 
Switch housing 	Connector 	Connector2 


Light source:


- LED-PCBA
- 3M tape

Removability Introduction on Disposal at End of Life

Composition Explanation – WiZ Low Cost LED Tapes

B. Steps to remove the components




Type: without permanent damage
Recommendation on disposal
Plastic part: reuse and recycling
Electrical part: disposal
Metal part: recycling


Removability Introduction on Disposal at End of Life

Composition Explanation – WiZ Low Cost LED Tapes

C. Setup the test



RGB Strip (cut 0.68m off the light strip)



RGBIC Strip (cut 0.5m off the light strip)

D. Reference control setting

RGB strip is decorative purpose product, it is not intended to produce white color light, it is possibly to generate the white color light in someway, to get the RCS of light source, the possible way to find the RCS CCT point (non-preset point) by:

- To cut strip in length as above and with plug and control part, and power on
- To open WiZ APP → Connect the light strip to WiZ App → Custom → find the proper test color point → start the test

For the test point, you are suggested to find the CCT point in the white circle area
@ 4000K for 9290041259LSW, 9290041260LSW, 9290041261LSW, 9290041265LSW,
9290041266LSW, **9290047066LSW**
and @ 4500K for 9290041258LSW, 9290041264LSW, 9290041257LSW

