



DN020 G3 LED6 WW 7W 220-240V D 1 x 9290025091 3000K**1 x 550 lm****Polar intensity diagram**

Light output ratio 1.00
 Service upward 0.01
 Service downward 0.99


CIE flux code 47 78 95 99 100

UGRcen (4Hx8H, 0.25H) 27

Quantity estimation diagram**Utilisation factor table**

Room Index k	Reflectances (%) for ceiling, walls and working plane (CIE)													
	0.80 0.80		0.70 0.70 0.70 0.70				0.50 0.50		0.30 0.30		0.00			
	0.50 0.50		0.50 0.50 0.50 0.30				0.30 0.10		0.30 0.10		0.00			
	0.30 0.10		0.30 0.20 0.10 0.10				0.10 0.10		0.10 0.10		0.00			
0.60	0.48	0.46	0.47	0.46	0.45	0.38	0.37	0.32	0.37	0.32	0.30			
0.80	0.59	0.55	0.58	0.56	0.54	0.47	0.46	0.41	0.45	0.41	0.39			
1.00	0.68	0.63	0.66	0.64	0.62	0.54	0.54	0.48	0.53	0.48	0.46			
1.25	0.76	0.70	0.74	0.71	0.69	0.62	0.61	0.56	0.60	0.55	0.53			
1.50	0.83	0.75	0.81	0.77	0.74	0.67	0.66	0.62	0.65	0.61	0.58			
2.00	0.93	0.83	0.90	0.86	0.81	0.76	0.75	0.70	0.73	0.70	0.67			
2.50	0.99	0.88	0.96	0.91	0.86	0.82	0.80	0.76	0.78	0.75	0.73			
3.00	1.04	0.91	1.01	0.95	0.90	0.86	0.84	0.81	0.82	0.79	0.77			
4.00	1.10	0.95	1.06	1.00	0.94	0.90	0.89	0.86	0.87	0.85	0.82			
5.00	1.14	0.98	1.10	1.03	0.96	0.94	0.92	0.89	0.90	0.88	0.85			

Ceiling mounted

UGR diagram**Luminance Table**

Plane Cone	0.0	15.0	30.0	45.0	60.0	75.0	90.0
45.0	21621	21621	21621	21621	21621	21621	21621
50.0	21202	21202	21202	21202	21202	21202	21202
55.0	20711	20711	20711	20711	20711	20711	20711
60.0	20055	20055	20055	20055	20055	20055	20055
65.0	19334	19334	19334	19334	19334	19334	19334
70.0	18315	18315	18315	18315	18315	18315	18315
75.0	16958	16958	16958	16958	16958	16958	16958
80.0	15001	15001	15001	15001	15001	15001	15001
85.0	11027	11027	11027	11027	11027	11027	11027
90.0	4533	4533	4533	4533	4533	4533	4533

(cd/m²)

2020-08-24