

PHILIPS

Free floor standing

Product declaration



Environmental Product Declaration

Free floor standing Gen2

as per ISO 14021, based on ISO 14040/14044

Free floor standing Gen2 is a product with complete family of slim luminaires designed for Circularity & enhanced Wellbeing and Future proof connectivity.

Combined with state-of-the-art efficacy (at CRI>90), upgradability features, a long lifetime, repairability, and design for recyclability making this a true 'Green choice'. One luminaire can light two desks to the levels required for offices.

- Best-in-class efficacy up to 140 lm/W with CRI>90
- Integrated sensors for daylight harvesting and presence detection
- Comfortable LED lighting that can be personally controlled
- More energy-efficient than similar conventional solutions – operational cost savings
- Attractive, unobtrusive design



Product

Product family range

The Free floor standing gen2 is a configurator product, the assembly of the products is implemented on the manufacturing site in Tamási Hungary Kft. (HU). The manufacturing site of the product has achieved carbon neutrality as of 2019.

The EPD does not present the assessment of the impacts of the whole range, and focused on representation through the most probable worst case scenario rather than through average impacts with assessment of deviations. This approach is based on the Signify developed EPD framework.

Representative product

Free floor standing gen2 product FS486F LED150S 930 PSD-T ACL WH CCE is chosen as a representative product for the family as the luminaire with the highest power consumption over the lifetime, with inclusion of an emergency power supply module. Based on multiple LCA studies of the LED based luminaires, it is defined that the use stage (and electricity consumption in particular) tends to contribute the majority of the life-cycle impacts. Thus, a product with the largest power consumption over the lifetime in the family is most likely to have the largest impacts, and thus represent a worst case. That choice of a product aligns with pessimistic assumptions and the precautionary principle in view of

the task to represent other products in the family. This approach is based on the Signify developed EPD framework.

Product application

The luminaires of the family are designed for indoor standard lighting, specifically standard office applications.

Technical Data

The system comprises a set of modules that are the key building blocks for a luminaire. A typical application has the following technical features:

- 2x Xitanium driver
- 5xFortimo OC
- Steel foot
- Aluminium pole and head
- Plastic light distribution parts
- Sensor
- Switch button
- Cable with plug

Delivery status

Product weight: 19,83 kg (including 3,14 kg packaging), dimensions of the packed product: 2000*410*90.

Driver 1

i.	Type	Xitanium 36W 0.3-1.0A 54V TD 230V G2
ii.	Failure rate (max % @lifetime)	10%
iii.	Dimensions, mm	350x30x21 (36W)

Driver 2

i.	Type	Xitanium 90W 0.15-0.5A 300V TD21 S 230V
ii.	Failure rate (max % @lifetime)	10%
iii.	Dimensions, mm	280x30x21 (90W)

LED board 1

i.	Type	FortimoLEDStripOC 2ft 2200lm 930 FC LV5
ii.	Dimension board, mm	560x20
iii.	Amount of PCBA per luminaire	1
iv.	Number of LEDs per PCBA	48

LED board 2

i.	Type	FortimoLEDStripOC 2ft 2200lm 930 BC HV5
ii.	Dimension board, mm	560x20
iii.	Amount of PCBA per luminaire	4
iv.	Number of LEDs per PCBA	48

Constructional data

Name	Value	Unit
Dimensions	2000*700*380	Mm*mm*mm
Luminous flux	15000	Lm
Luminous efficacy	127	Lm/W
Radiation angle	120	Deg
Colour temperature	3000	K

Base materials/Ancillary materials

Materials	Mass, kg
Metals / Steel	9,780
Metals / Aluminium	4,430
Packaging / Paper	3,020
Plastics / PMMA	0,560
Electric Comp's / Electronic ballasts with connectors	0,510
Plastics / PC (Polycarbonate)	0,442
Electric Comp's / Cables PVC	0,310
Electric Comp's / PCBA without cables	0,195
Electric Comp's / Connectors	0,135
Electric Comp's / Sensors	0,098
Packaging / Labels, ink, adhesives	0,082
Plastics / PP	0,073
Plastics / ABS	0,046
Packaging / Plastic Wrapping	0,032
Lamps / General Lighting	0,030
Plastic / Silicone	0,030
Electric Comp's / OTHERS	0,020
Electric Comp's / Connectors PA	0,010
Plastic / PVC flexible	0,010
LEDs	0,006
Metals / Stainless Steel	0,005
Packaging / PE	0,002
Product weight (including packaging): 19.83 kg	

Manufacturing

Manufacturing of the driver and LED boards is done by Philips Poland (Pila). Part of the wiring is made in China, and other plastic and metal mechanical parts are manufactured in Hungary and Europe. Manufacturing of switches, labels, cables and painting of metal parts is done at the Signify Tamasi site, Hungary. Final assembly of the luminaire is also performed at the Tamasi site, Hungary.

Product processing/Installation

Product is a stand alone pole.

Packaging

3,14 kg, including cardboard box and PE bag.

Condition of use

Designed for indoor use in average European conditions. No extreme exposure to chemicals or pollution is implied. Applications may apply dimming or lighting controls to lower further energy saving. The product is used in the European market context and assumed to use the average European electricity mix.

Environment and health during use

The product is compliant with the European RoHS Directive 2011/65/EU of 8 June 2011 on Restriction of the use of certain Hazardous Substances in Electrical and Electronic equipment and with the European REACH regulation (EC) No 1907/2006 of 18 December 2006 on the Registration, Evaluation, Authorization and Restriction of Chemicals.

Reference service life

The RSL is established as 41 000 hours operation, the equivalent of 16,4 years operation in an office application (2500 hours per year).

End of life

In the European Union, luminaires fall within the scope of the WEEE directive. Efforts are made to improve collection, reuse and recycling of the product mainly via collective Collection & Recycling Service Organizations (CRSOs). In the end of life, the luminaire is 85% collected and disassembled. The collected parts are disassembled and steel, aluminium, glass, electronic parts, and cables and are sent to recycling. Batteries are collected and sent to treatment. The quantitative assessments are based on a material split and respective recycling rates. Non-collected and non-recycled after disassembly content is disposed to the municipal waste stream where it undergoes separation, preparation and treatment according to the average European statistics. Waste generated in installation and parts replacement are 100% collected and sent to respective treatment.

Extraordinary effects

- Fire: effects of fire can lead to emissions of PBDD/F (brominated compounds).
- Water: no known impacts on the environment following unforeseeable influence of water, e.g. flooding.
- Mechanical destruction: no known impacts on the environment following unforeseeable mechanical destruction.

Further information

Details of the product are published on: <https://www.lighting.philips.nl/>

Calculation rules

Declared unit

Declared product	Value	Declared unit
FS486F LED150S 930 PSD-T ACL WH CCE	Unit	1 piece

The declared unit is a luminaire with a steel foot, aluminium pole and head, 2 drivers, 5 LED boards, cables, and other plastic and metal constructive components totalling a weight of 16,69 kg excluding packaging, providing a luminous flux of 15 000 lm, including luminaire losses. The luminaire, provides sufficient light for a typical office application, operated in a European context for 41 000 hours.

System boundary

Cradle to gate with options

Modules A1-A3 include: raw material extraction, processing, energy and materials and manufacture of modules and packaging.

The following scenarios are also included:

- Transport to installation (A4);
- Disposal of packaging materials (A5);
- Replacement of driver (10% rate) (B3);
- Operational energy use (B6);
- Transport to end of life (C2);
- Waste processing (C3);
- Final disposal for WEEE fraction not recycled (C4).

Recycling of cardboard packaging, electronics, cables, steel elements of luminaire. (D)

Estimates and assumptions

Background data are used for suppliers' specific processes. Foreground data are used for the assembly of the lighting unit in regards to the components of the luminaire (system). When necessary, generic data was generated based on averaging the data of multiple products of the same category. Data on collection and recycling are based on data of the generic European statistics. The end of life scenario assumes recycling of the separated materials, but does not include energy recovery from incineration of the waste. Representation of the family is assumed on the worst case scenario with largest power consumption over the lifetime, and is not compliant with EN15804+A1.

Cut-off criteria

Where no data was available, items that represent less than 1% of the total product weight were neglected. No excluded flows were of any known particular environmental concern.

Background data

Necessary background data are sourced from the Signify database and the Ecoinvent database v3.8.

Data quality

Specific data used is less than 5 years old. Background data is geographically representative of the production location, and is less than 10 years old.

Period under review

The period under review is the year 2022 for the product composition, RSL, and product performance and characteristics, year 2021 for the energy and material consumption at the assembly factory.

Allocation

Avoided burden approach is applied to allocation of recycled and/or secondary raw materials, as well as loads and benefits beyond the system boundary from material recycling. No loads and benefits beyond the system boundary from energy recovery in the end of life of the product or packaging is included. Energy consumption, material and waste generation at the manufacturing site not attributed to bill of materials of the products, is allocated by partitioning, on the basis of units produced.

Comparability

A comparison or an evaluation of the presented data is only possible if the data to be compared were created according to the Signify/Philips lighting framework and the building context, respectively the product specific characteristics of performance, are taken into account.

LCA: Scenarios and additional technical information

Transport to the site (A4)

Name	Value	Unit
Transport distance	1200	Km
Transport mode	truck, unspecified generic	-
Capacity utilisation incl. empty runs	45	%
Bulk density of transported product	104	kg/m ³

Installation at the site (A5)

Name	Value	Unit
Packaging waste	3,14	kg

Reference service life

Name	Value	Unit
Reference service life	16,4	Years
Operating hours per year	2500	Hours
Quality of work	L90B50	-
Environment of operation	Average European conditions. No extreme exposure to chemicals or pollution is implied.	-
Usage conditions	Indoor	-

Repair (B3)

Name	Value 1	Unit
Repair process	Replacement of the drivers	-
Repair cycle	0,10	Number/RSL
Resources	0,51	Kg
Transportation distance	4,8	Km
Transportation mode	Van	-

Operational energy use (B6)

Name	Value	Unit
Electricity consumption	3885,4	kWh
Equipment output	117,6	W

End of life (C1-C4)

Name	Value	Unit
Collected separately	13,75	kg
Sent to recycling	11,27	kg
Sent to energy recovery	2,47	kg
Sent to landfilling	2,44	kg
Transportation distance from point of use to collection and sorting point	30	km
Transportation distance from collection point to incineration and landfilling	30	km
Mode of transportation	Truck, unspecified	-

LCA Results

Description of the system boundary (X = included in lca; MND = module not declared; MNR = module not relevant)

Product stage			Construction process stage		Use stage							End of life stage				Benefits and loads beyond the system boundaries
Raw material supply	Transport	Manufacturing	Transport from the gate to the site	Assembly	Use	Maintenance	Repair	Replacement	Refurbishment	Operational energy use	Operational water use	Deconstruction demolition	Transport	Waste Processing	Disposal	Reuse- Recovery- Recycling potential
A1	A2	A3	A4	A5	B1	B2	B3	B4	B5	B6	B7	C1	C2	C3	C4	D
X	X	X	X	X	MND	MND	X	MNR	MNR	X	MND	MND	X	X	X	X

Results of the LCA - environmental impact

Parameter	Unit	A1-A3	A4	A5	B3	B6	C2	C3	C4	D
GWP	[kg CO2Eq.]	2,5E+02	3,1E+00	2,6E-01	4,3E+00	1,5E+03	2,3E-01	1,5E+00	9,5E+00	-3,9E+01
ODP	[kg CFC11Eq.]	3,7E-05	5,8E-07	2,4E-08	4,5E-07	8,9E-05	4,3E-08	1,4E-07	1,1E-08	-3,7E-06
AP	[kg SO2Eq.]	1,5E+00	1,3E-02	1,3E-03	2,3E-02	7,4E+00	9,9E-04	8,5E-03	4,2E-03	-3,0E-01
EP	[kg (PO4)3Eq.]	2,4E-01	2,5E-03	1,7E-04	3,2E-03	9,5E-01	1,8E-04	1,7E-03	3,0E-04	-2,8E-02
POCP	[kg Ethen Eq.]	7,9E-02	4,3E-04	7,7E-05	1,7E-03	3,0E-01	3,1E-05	5,3E-04	1,8E-04	-2,0E-02
ADPE	[kg Sb Eq.]	5,9E-02	9,6E-06	9,0E-06	4,0E-04	1,4E-02	7,5E-07	3,9E-05	8,2E-05	-4,7E-03
ADPF	[MJ]	2,8E+03	4,7E+01	3,2E+00	5,1E+01	1,7E+04	3,5E+00	1,6E+01	4,6E+00	-4,0E+02
Caption	GWP = Global warming potential; ODP = Depletion potential of the stratospheric ozone layer; AP = Acidification potential of land and water; EP = Eutrophication potential; POCP = Formation potential of tropospheric ozone photochemical oxidants; ADPE = Abiotic depletion potential for non fossil resources; ADPF = Abiotic depletion potential for fossil resources									

The use phase of the product is associated with electricity consumption for lighting (stage B6 on the chart) and has the highest and most significant contribution to the overall environmental impacts of the product over its life cycle, in all impact categories except abiotic depletion potential (elements) (ADPE). In particular, impacts in global warming potential (GWP), acidification potential (AP), eutrophication potential (EP), photochemical ozone creation potential (POCP), and abiotic depletion potential (fossil) (APDF) categories are attributed to the electricity consumption at a rate above 81%. Abiotic depletion potential (elements) (ADPE) impacts and ozone layer depletion potential (ODP) impacts also have a considerable impact contribution of the product manufacturing, including sourcing and processing the raw materials (stage A1-A3 on the chart). In that stage,

the impact to the ADPE is mostly due to extraction of virgin materials used to make electric components, as well as due to extraction and production of metal mechanical elements. The ODP impacts of stage A1-A3 could be attributed to sourcing temperature-resistant polymers. The end of life (stage D on the chart) of the product has a marginal contribution to the reduction of overall impacts in all categories apart from ADPE. There, recycling in the end of life (stage D on the chart) reduces the cumulative impact of production (A1-A3), distribution and installation (A4-A5), use (B3, B6), and end of life treatment (C2-C4) by 6,4%, relating to -6,8% of the total ADPE over the life cycle. This is achieved by high rates of luminaires collection in the end of their service, and high rates of recycling of the metals in the end of life of the luminaire.

Requisite evidence

The measurements are based on documentation and bill of materials of the product.

References

EN 15804:2012-04+A1 2013, Sustainability of construction works — Environmental Product Declarations — Core rules for the product category of construction products.

ISO 14021:2016, Environmental labels and declarations — Self-declared environmental claims (Type II environmental labelling)

ISO 14040:2006, Environmental management — Life cycle assessment — Principles and framework

ISO 14044:2006, Environmental management — Life cycle assessment — Requirements and guidelines

Disclaimer

All environmental calculations are based on a luminaire used in European context. The calculations are performed on the most commonly used luminaire in the range. The implemented life cycle analysis is compliant with DIN EN ISO 14040:2006: Environmental management - Life Cycle Assessment - Principles and framework. The LCA has been performed to the best of Signify's knowledge. No right or claim might be derived from this. Signify disclaims any and all claims with respect thereto.

Further information Please contact:

sustainability@signify.com

Collection and Recycling (brochure)

[Ecoinvent](#) (website)

Glossary

ADP (Abiotic Depletion Potential): Impact related to the depletion of non-renewable resources, i.e. fossil fuels (ADPF), metals and minerals (ADPE).

AP (Acidification Potential): Contributions of SO₂, NO_x, HCl, NH₃ and HF to the potential acid deposition, causing a wide range of impacts on soil, groundwater, surface water, organisms, ecosystems and buildings.

EP (Eutrophication Potential): Potential to cause over-fertilization of water and soil, which can result in increased growth of biomass.

GWP (Global Warming Potential): Relative measure of how much heat a greenhouse gas (CO₂, N₂O, CH₄...) traps in the atmosphere. It is calculated over a specific time interval, commonly 20, 100 or 500 years.

LCA: Life cycle assessment.

PCR: Product Category Rules.

PERE: Use of renewable primary energy excluding renewable primary energy resources used as raw materials.

PERM: Use of renewable primary energy resources used as raw materials.

PERT: Total use of renewable primary energy resources.

PENRE: Use of non-renewable primary energy excluding non-renewable primary energy resources used as raw materials.

PENRM: Use of non-renewable primary energy resources used as raw materials.

PENRT: Total use of non-renewable primary energy resources.

POCP (Photo-chemical Oxidation Potential or photochemical smog): Formation of reactive substances (mainly ozone) which are injurious to human health and ecosystems and which also may damage crops.

RSL: Reference service life.



© 2023 Signify Holding. All rights reserved. The information provided herein is subject to change, without notice. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify.

Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V. All other trademarks are owned by Signify Holding or their respective owners.

www.lighting.philips.com