



## EU Declaration of Conformity

Document No.: 20260407\_01\_V0 PHILIPS lamp  
Year in which CE Mark was first affixed: 2026

### 1. Product Range / Model:

Product Range / Model:	<b>NAME:</b> LED lamp <b>DESCRIPTION:</b> LED Lamp <b>BRAND:</b> PHILIPS
------------------------	--

### 2. Manufacturer Name & Address:

**Signify**  
 I.B.R.S./C.C.R.I. /Numéro 10461  
 5600 VB Eindhoven, The Netherlands

**3. This declaration of conformity is issued under the sole responsibility of the manufacturer.**

### 4. Object of the declaration:

Product Code:	See Annex Specification of the products
---------------	---

**5&6. The object of the declaration described above is in conformity with the following relevant Union harmonization legislation and with the applicable requirements of the following harmonized standards and technical specifications:**

Radio Equipment Directive 2014/53/EU and applicable Delegated Regulations	
EN 18031-1:2024	Common security requirements for radio equipment. Part 1: Internet connected radio equipment
EN 18031-2:2024	Common security requirements for radio equipment. Part 2: Radio equipment processing data, namely Internet connected radio equipment, childcare radio equipment, toys radio equipment and wearable radio equipment
EN 18031-3:2024	Common security requirements for radio equipment. Part 3: Internet connected radio equipment processing virtual money or monetary value
ETSI EN 301 489-17 V3.3.1: 2024-09	ElectroMagnetic Compatibility (EMC) standard for radio equipment and services. Part 17: Specific conditions for Broadband Data Transmission Systems. Harmonised Standard for ElectroMagnetic Compatibility
ETSI EN 301 489-17 V3.2.4: 2020-09	ElectroMagnetic Compatibility (EMC) standard for radio equipment and services. Part 17: Specific conditions for Broadband Data Transmission Systems. Harmonised Standard for ElectroMagnetic Compatibility
ETSI EN 301 489-1 V2.2.3: 2019-11	ElectroMagnetic Compatibility (EMC) standard for radio equipment and services. Part 1: Common technical requirements. Harmonised Standard for ElectroMagnetic Compatibility
ETSI EN 300 328 V2.2.2: 2019-07	Wideband transmission systems. Data transmission equipment operating in the 2,4 GHz band. Harmonised Standard for access to radio spectrum
EN IEC 55015: 2019 + A11:2020	Limits and methods of measurement of radio disturbance characteristics of electrical lighting and similar equipment
EN IEC 61547:2023	Equipment for general lighting purposes. EMC immunity requirements
EN IEC 61000-3-2:2019 + A1:2021 +A2:2024	Electromagnetic compatibility (EMC). Part 3-2: Limits. Limits for harmonic current emissions (equipment input current ≤16 A per phase)
EN 61000-3-3: 2013 + A1: 2019 +A2:2021	Electromagnetic compatibility (EMC). Part 3-3: Limits. Limitation of voltage changes, voltage fluctuations and flicker in public low-voltage supply systems, for equipment with rated current ≤ 16 A per phase and not subject to conditional connection
EN 62493:2015+A1:2022	Assessment of lighting equipment related to human exposure to electromagnetic Field
EN IEC 62311:2020	Assessment of electronic and electrical equipment related to human exposure to electromagnetic Field (0Hz -300Hz)
EN 62560:2012 + A1: 2015 + A11:2019	Self-ballasted LED-lamps for general lighting services by voltage > 50V - Safety specifications



## EU Declaration of Conformity

Document No.: 20260407\_01\_V0 PHILIPS lamp

**EcoDesign requirements for energy-related products Directive (ErP), 2009/125/EC and applicable Implementing Measures**

Commission Regulation (EU) 2019/2020 and amendment Commission Regulation (EU) 2021/341  
EN-IEC 62612:2013/A2:2018 Self-ballasted LED lamps for general lighting services with supply voltages > 50 V – Performance requirements

**Restriction of the use of certain Hazardous Substances in electrical and electronic equipment Directive (RoHS), 2011/65/EU and applicable Delegated Directives**

EN IEC 63000:2018

Technical documentation for the assessment of electrical and electronic products with respect to the restriction of hazardous substances

**Packaging and Packaging Waste Regulation (PPWR), (EU) 2025/40**

**7. Additional information: The products in this declaration are produced under a quality scheme at least in conformity with ISO 9001 or CENELEC permanent documents.**

**Signed for and on behalf of:**

SIGNIFY  
I.B.R.S/C.C.R.I./Numéro 10461  
5600 VB Eindhoven  
The Netherlands

April 7, 2026

Building 9, Lane 888, Tianlin Road, Minhang District, Shanghai  
Mr. Chen Liang

Quality Head of Line of Business Wiz Connected / Consumer Business





## EU Declaration of Conformity

Document No.: 20260407\_01\_VO PHILIPS lamp

### Annex: Specification of the products:

12NC	Model Name	Product Description	EAN1
929003601021	9290036010C	PHI WFB 60W A60 E27 822-65 RGB 1PF/6	8720169170933
929003601036	9290036010C	PHI WFB 60W A60 E27 822-65 RGB 3CT/6	8720169204423
929003601041	9290036010C	PHI WFB 60W A60 E27 822-65 RGB 2PF/6	8720169171060
929003601062	9290036010C	PHI WFB 60W A60 E27 822-65 RGB 1PF/6 SD	8720169171121
929003601064	9290036010C	PHI WFB 60W A60 E27 822-65 RGB 4CT/6	8721103160126
929003602002	9290036020C	PHI WFB 60W A60 B22 822-65 RGB 1PF/6	8720169170957
929003602041	9290036020C	PHI WFB 60W A60 B22 822-65 RGB 2PF/6	8720169171084
929003604721	9290036047C	PHI WFB 75W G95 E27 822-65 RGB 1PF/6	8720169170919
929003611221	9290036112A	PHI WFB 60W A60 E27 RGB 1PK + Remote	8721103159700
929003649641	9290036496A	PHI WFB 60W A60 E27 RGB 2PK + Remote	8721103160102
929003781921	9290037819B	PHI WFB 60W A60 E27 827-65 TW 1PF/6	8720169302990
929003781936	9290037819B	PHI WFB 60W A60 E27 827-65 TW 3CT/6	8720169303010
929003781941	9290037819B	PHI WFB 60W A60 E27 827-65 TW 2PF/6	8720169303034
929003782021	9290037820B	PHI WFB 60W A60 B22 827-65 TW 1PF/6	8720169302952
929003782121	9290037821B	PHI WFB 75W G95 E27 827-65 TW 1PF/6	8720169303058
929004583341	9290045833	PHI WFB 100W A60 E27 822-65 RGB 2PF/6	8721103160003
929002448864	9290024488C	PHI WFB 40W C37 E14 922-65 RGB 4CT/6	8721103160027
929003772364	9290037723	PHI WFB 50W GU10 GLASS 922-65 RGB 4CT/6	8721103160041
929002448721	9290024487B	PHI WFB 40W C37 E14 927-65 TW 1PF/6	8719514372382
929002448736	9290024487B	PHI WFB 40W C37 E14 927-65 TW 3CT/6	8720169210332
929002448741	9290024487B	PHI WFB 40W C37 E14 927-65 TW 2PF/6	8719514372702
929003499721	9290034997A	PHI WFB 40W P45 E14 922-65 RGB 1PF/6	8719514437333
929003499821	9290034998A	PHI WFB 40W P45 E27 922-65 RGB 1PF/6	8719514437395
929002448821	9290024488C	PHI WFB 40W C37 E14 922-65 RGB 1PF/6	8719514372405
929002448836	9290024488C	PHI WFB 40W C37 E14 922-65 RGB 3CT/6	8720169210318
929002448841	9290024488C	PHI WFB 40W C37 E14 922-65 RGB 2PF/6	8719514372726
929003008921	9290030089A	PHI WFB 60W A60 E27 927-65 FR TW 1PF/6	8719514371965
929003067621	9290030676A	PHI WFB 50W ST64 B22 920-50 Amb 1PF/6	8719514372283
929003017921	9290030179A	PHI WFB 50W G125 E27 920-50 Amb 1PF/6	8719514372122
929003017821	9290030178A	PHI WFB 60W G125 E27 927-65 CL 1PF/6	8719514372108
929003017721	9290030177A	PHI WFB 25W C35 E14 920-50 Amb 1PF/6	8719514372085
929003017621	9290030176A	PHI WFB 40W C35 E14 927-65 CL 1PF/6	8719514372061
929003017521	9290030175A	PHI WFB 50W A60 B22 920-50 Amb 1PF/6	8719514372047
929003017421	9290030174A	PHI WFB 50W A60 E27 920-50 Amb 1PF/6	8719514372023
929003017321	9290030173A	PHI WFB 60W A60 B22 927-65 CL 1PF/6	8719514372009
929003017241	9290030172A	PHI WFB 60W A60 E27 927-65 CL 2PF/6	8719514372627
929003017221	9290030172A	PHI WFB 60W A60 E27 927-65 CL 1PF/6	8719514371989
929003018741	9290030187A	PHI WFB 50W ST64 E27 920-50 Amb 2PF/6	8719514372641
929003018721	9290030187A	PHI WFB 50W ST64 E27 920-50 Amb 1PF/6	8719514372269
929003018621	9290030186A	PHI WFB 60W ST64 E27 927-65 CL 1PF/6	8719514372245
929003018521	9290030185A	PHI WFB 25W PS160 E27 920-50 Amb 1CT/2	8719514372221



## EU Declaration of Conformity

Document No.: 20260407\_01\_VO PHILIPS lamp

929003018321	9290030183A	PHI WFB 50W G95 E27 920-50 Amb 1PF/6	8719514372207
929003018221	9290030182A	PHI WFB 60W G95 E27 927-65 CL 1PF/6	8719514372184
929003018121	9290030181A	PHI WFB 25W G200 E27 920-50 Amb 1CT/2	8719514372160
929003018021	9290030180A	PHI WFB 40W G200 E27 927-65 CL 1CT/2	8719514372146
929003500021	9290035000	PHI WFB 150W A80 E27 922-65 RGB 1PF/6	8719514437319
929004583321	9290045833	PHI WFB 100W A60 E27 822-65 RGB 1PF/6	8721103046611
929004583332	9290045833	AMZ WFB 100W A60 E27 822-65 RGB 2PF/6	8720169078888
929004583421	9290045834	PHI WFB 100W A60 E27 827-65 TW 1PF/6	8721103046635
929004583521	9290045835	PHI WFB 100W A60 B22 822-65 RGB 1PF/6	8721103046673
929004583621	9290045836	PHI WFB 100W A60 B22 822-65 TW 1PF/6	8721103061669
929003850521	9290038505	PHI WFB 60W A60 B22 827-40 TW EELA 1PF	8720169353718
929003772236	9290037722	PHI WFB 50W GU10 GLASS 927-65 TW 3CT/6	8720169296701
929003772336	9290037723	PHI WFB 50W GU10 GLASS 922-65 RGB 3CT/6	8720169296725
929003772221	9290037722	PHI WFB 50W GU10 GLASS 927-65 TW 1PF/6	8720169296787
929003772241	9290037722	PHI WFB 50W GU10 GLASS 927-65 TW 2PF/6	8720169296749
929003772321	9290037723	PHI WFB 50W GU10 GLASS 922-65 RGB 1PF/6	8720169296800
929003772341	9290037723	PHI WFB 50W GU10 GLASS 922-65 RGB 2PF/6	8720169296763
929003714021	9290037140	PHI WFB 60W A60 E27 827-40 TW EELA 1PF	8720169241435
929002448421	9290024484A	PHI WFB 50W GU10 922-65 RGB 1PF/6	8719514372344
929002448341	9290024483A	PHI WFB 50W GU10 927-65 TW 2PF/6	8719514372665
929003267121	9290032671	PHI WFB 40W A60 E27 822-65 RGB CL 1PF/6	8720169165779
929003267221	9290032672	PHI WFB 40W G95 E27 822-65 RGB CL 1PF/6	8720169165793
929003267321	9290032673	PHI WFB 40W ST64 E27 822-65 RGB CL 1PF/6	8720169165816
929002383664	9290023836AA	PHI WFB 60W A60 E27 922-65 RGB 6PF/6	8720169157750