

PHILIPS

Recessed

**EvoKit Gen X
Service Kit**



Give new life to your aging EvoKits

The Philips EvoKit Gen X Service Kit allows customers to replace previous generations of EvoKits with the new service kits with updated LED boards and drivers. These service kits are easy to install (less than 5 minutes), lumen output configurable with a NFC smartphone app, and provides energy savings up to 33% as compared to previous EvoKit versions.

Philips EvoKit Gen X Service Kit



Ordering, electrical and technical data (Subject to change without notice)

Evokit GenX Service Kit with 0-10V Dimming ordering guide

| Product No. (6nc) | Description | Watts (W) ¹ | Volts (V) | Lumen Maintenance (hours) ² | Approx. Lumens (lm) ³ | Color Temp. (K) | Efficacy ¹ (lm/W) |
|-------------------------------|---------------------------------------|---------------------------|--------------|--|--|--------------------|---------------------------------|
| High efficiency 0-10V Dimming | | | | | | | |
| 116715 | EvoKit HE 2x2 32L 21W 835 UNV 0-10 GX | 21W | 120-277 | 70,000 | 3200 | 3500 | 152 |
| 116673 | EvoKit HE 2x2 32L 20W 840 UNV 0-10 GX | 20W | 120-277 | 70,000 | 3200 | 4000 | 160 |
| 116707 | EvoKit HE 2x4 42L 26W 835 UNV 0-10 GX | 26W | 120-277 | 70,000 | 4200 | 3500 | 162 |
| 116665 | EvoKit HE 2x4 42L 26W 840 UNV 0-10 GX | 26W | 120-277 | 70,000 | 4200 | 4000 | 162 |

Evokit GenX Service Kit with Sensor Ready (SR) ordering guide

| Product No. (6nc) | Description | Watts (W) ¹ | Volts (V) | Lumen Maintenance (hours) ² | Approx. Lumens (lm) ³ | Color Temp. (K) | Efficacy ¹ (lm/W) |
|-----------------------------------|-------------------------------------|---------------------------|--------------|--|--|--------------------|---------------------------------|
| High efficiency Sensor Ready (SR) | | | | | | | |
| 116731 | EvoKit HE 2x2 32L 20W 835 UNV SR GX | 20W | 120-277 | 70,000 | 3200 | 3500 | 160 |
| 116699 | EvoKit HE 2x2 32L 20W 840 UNV SR GX | 20W | 120-277 | 70,000 | 3200 | 4000 | 160 |
| 116723 | EvoKit HE 2x4 42L 26W 835 UNV SR GX | 26W | 120-277 | 70,000 | 4200 | 3500 | 162 |
| 116681 | EvoKit HE 2x4 42L 26W 840 UNV SR GX | 26W | 120-277 | 70,000 | 4200 | 4000 | 162 |

1. L70 72,000 hours @ 35°C based on TM21 and LM80.
2. Based on photometric testing consistent with IES LM-79. Actual wattage may differ by +/- 10%. Actual initial lumen output may vary between -10 and +10% of the rated lumens.
3. 0-10V Dimming products that are not HE (High Efficiency) do not support lumen level tuning with SimpleSet technology using the MultiOne Mobile smartphone app.

Restrictions on Hazardous Substances (RoHS) is a European directive (2002/95/EC) designed to limit the content of 6 substances [lead, mercury, cadmium, hexavalent chromium, polybrominated biphenyls (PBB), and polybrominated diphenyl ethers (PBDE)] in electrical and electrical products. For products used in North America, compliance with RoHS is voluntary and self-certified.



© 2024 Signify Holding. All rights reserved. The information provided herein is subject to change, without notice. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify.



Signify North America Corporation
400 Crossing Boulevard,
Bridgewater, NJ 08807
Telephone 800-555-0050

Signify Canada Ltd.
281 Hillmount Road,
Markham, ON, Canada L6C 2S3
Telephone 800-668-9008

Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V. All other trademarks are owned by Signify Holding or their respective owners.