

# Product Information Sheet

COMMISSION DELEGATED REGULATION (EU) 2019/2015 with regard to energy labelling of light sources

**Supplier's name or trade mark:** PHILIPS

**Supplier's address:** Customer Care Philips, I.B.R.S./C.C.R.I. /Numéro 10461, 5600VB Eindhoven, NL

**Model identifier:** 9290037907

## Type of light source:

|                                                     |     |                                 |      |
|-----------------------------------------------------|-----|---------------------------------|------|
| Lighting technology used:                           | LED | Non-directional or directional: | NDLS |
| Light source cap-type (or other electric interface) | G9  |                                 |      |
| Mains or non-mains:                                 | MLS | Connected light source (CLS):   | No   |
| Colour-tuneable light source:                       | No  | Envelope:                       | -    |
| High luminance light source:                        | No  |                                 |      |
| Anti-glare shield:                                  | No  | Dimmable:                       | No   |


## Product parameters

| Parameter                                                                                                                                      | Value                | Parameter                                                                                                                                                  | Value                  |
|------------------------------------------------------------------------------------------------------------------------------------------------|----------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------|------------------------|
| <b>General product parameters:</b>                                                                                                             |                      |                                                                                                                                                            |                        |
| Energy consumption in on-mode (kWh/1000 h), rounded up to the nearest integer                                                                  | 2                    | Energy efficiency class                                                                                                                                    | E                      |
| Useful luminous flux ( $\phi_{use}$ ), indicating if it refers to the flux in a sphere (360°), in a wide cone (120°) or in a narrow cone (90°) | 230 in Sphere (360°) | Correlated colour temperature, rounded to the nearest 100 K, or the range of correlated colour temperatures, rounded to the nearest 100 K, that can be set | 4 000                  |
| On-mode power ( $P_{on}$ ), expressed in W                                                                                                     | 1,9                  | Standby power ( $P_{sb}$ ), expressed in W and rounded to the second decimal                                                                               | 0,00                   |
| Networked standby power ( $P_{net}$ ) for CLS, expressed in W and rounded to the second decimal                                                | -                    | Colour rendering index, rounded to the nearest integer, or the range of CRI-values that can be set                                                         | 80                     |
| Outer dimensions without separate control gear, lighting control                                                                               | Height               | Spectral power distribution in the range 250 nm to 800 nm, at full-load                                                                                    | See image in last page |
|                                                                                                                                                | Width                |                                                                                                                                                            |                        |
|                                                                                                                                                | Depth                |                                                                                                                                                            |                        |

|                                                                                                                         |      |                                       |                |  |
|-------------------------------------------------------------------------------------------------------------------------|------|---------------------------------------|----------------|--|
| parts and non-lighting control parts, if any (millimetre)                                                               |      |                                       |                |  |
| Claim of equivalent power <sup>(a)</sup>                                                                                | Yes  | If yes, equivalent power (W)          | 25             |  |
|                                                                                                                         |      | Chromaticity coordinates (x and y)    | 0,382<br>0,380 |  |
| <b>Parameters for LED and OLED light sources:</b>                                                                       |      |                                       |                |  |
| R9 colour rendering index value                                                                                         | 0    | Survival factor                       | 0,90           |  |
| the lumen maintenance factor                                                                                            | 0,93 |                                       |                |  |
| <b>Parameters for LED and OLED mains light sources:</b>                                                                 |      |                                       |                |  |
| displacement factor (cos $\phi_1$ )                                                                                     | 0,70 | Colour consistency in McAdam ellipses | 6              |  |
| Claims that an LED light source replaces a fluorescent light source without integrated ballast of a particular wattage. | -(b) | If yes then replacement claim (W)     | -              |  |
| Flicker metric (Pst LM)                                                                                                 | 1,0  | Stroboscopic effect metric (SVM)      | 0,4            |  |

(a) '-': not applicable;

(b) '-': not applicable;



Model placed on the Union market from 28/06/2024.



**EPREL registration number:** 1932583

<https://eprel.ec.europa.eu/qr/1932583>

**Supplier:** Signify Netherlands B.V. (Manufacturer)

**Website:** [www.signify.com](http://www.signify.com)

**Customer care service:**

**Name:** Customer Care Philips

**Website:** [www.philips.com/lighting](http://www.philips.com/lighting)

**Email:** [EPREL.PhilipsLighting@Signify.com](mailto:EPREL.PhilipsLighting@Signify.com)

**Phone:** 00800 744 547 75

**Address:**

I.B.R.S./C.C.R.I. /Numéro 10461  
5600VB Eindhoven  
Netherlands