

PHILIPS

Arbour Post Light
6W

myGarden

4000K

Antracite

Water Resistant



16463/93/P3



Enjoy a beautiful garden with light


Philips Arbour LED outdoor post light in anthracite grey suspends a cube of light within a durable die-cast aluminium cradle. The ingenious design casts beams of diffuse cool white light over pathways and open areas outdoors.

Sustainable light solutions

- Energy saving
- High quality LED light
- Long operating life of up to 25 years
- Cool white light
- Philips offers a 5-year warranty on the LED module and driver

Designed for your garden

- IP44 - weatherproof



Highlights

Energy saving



This Philips energy-saving lamp conserves energy compared with traditional light sources, helping you to save money on your electricity bills and do your bit for the environment.

High quality LED light



The LED technology integrated into this Philips lamp is a unique solution developed by Philips. It turns on instantly, enables an optimal light output and brings out vivid colours in your home.

Long operating life



A light source you can trust. The LED bulb, delivered with this Philips LED lamp, will last up to 25,000 hours (which equals 25 years on the basis of an average use of 3 hours/day with at least of 13,000 on/off switching cycles). It feels so good to think that you won't have to worry about maintenance or light bulb replacement while having the perfect light ambience in your home.

Cool white light



Light can have different colour temperatures, indicated in units called Kelvin (K). Lamps with a low Kelvin value produce a warm, more cosy light, while those with a higher Kelvin value produce a cool, more energising light. This Philips light offers cool white light that keeps you energised.

5-year warranty on LED system



On top of the standard 2-year warranty for this lamp, Philips offers a 5-year warranty on the LED system, meaning the LED module and the driver in this lamp.

IP44 - weatherproof



This Philips outdoor light is especially designed for humid outdoor environments. It was tested rigorously to ensure its water resistance. The IP level is described by two figures: the first one refers to the protection level against dust, the second against water. This outdoor light is designed with IP44: it is protected against splashing water. This product is most commonly used and ideal for general outdoor use.

Specifications

Design and finishing

- Colour: Anthracite
- Material: Metal

Durability

- Nominal lifetime: 25,000

Environmental

- Disposal of the product: At the end of (economic) life, dispose of the product in accordance with local rules. Do not dispose of the product with regular household waste. The correct disposal of your product will help to prevent potential negative consequences for the environment and human health.

Extra feature/accessory incl.

- Fully weatherproof: Yes
- LED integrated: Yes

Garden area

- Garden area: Garden and Patio

Miscellaneous

- Especially designed for: Garden, Patio
- Style: Contemporary
- Type: Post Lights
- EyeComfort: No
- Extra Features: Water Resistant

Power consumption

- Power: 6

Product dimensions and weight

- Net weight: 2.010 kg
- Overall height: 770 mm
- Overall length: 100 mm
- Overall width: 100 mm

Service

- Warranty: 2 year(s)

Technical specifications

- Total lumen output fixture: 600 lm
- Bulb technology: LED
- Mains power: 50 Hz
- Energy class included light source: E
- IP code: IP44 | Wire-protected and splash-proof
- Class of protection: Class II – Double Insulated
- Light source replaceable: No
- Number of light sources: 1

The bulb

- Software upgradable: No

What's supported

- Compatible with Effects feature: No
- Defined support period: Not applicable
- Compatible operating systems: Not applicable
- Communication protocol: Not applicable

Packaging dimensions and weight

- EAN/UPC - product: 8718696150498
- Net weight: 2.01 kg
- Gross weight: 2.24 kg
- Height: 79.1 cm
- Length: 11.1 cm
- Width: 11.1 cm



Issue date: 2026-04-15
Version: 0.591

© 2026 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

www.lighting.philips.com