

## Wall light

Linea

LINEAR LED 2700K

white

LED



85087/31/16

# Decorate your home with light

Save up to 80% energy with this Philips LED Linear batten. Its integrated LED provides high-quality warm white light, perfect for general illumination. The modular system makes it easy to connect several battens to each other.

**Sustainable light solutions**

- Energy saving
- High quality LED light
- Long operating life of up to 20 years
- Warm white light
- Philips offers a 5-year warranty on the LED module and driver

**Special characteristics**

- Can be connected to products from the same family
- On/off switch on article

# Highlights

## Energy saving



This Philips energy-saving lamp conserves energy compared with traditional light sources, helping you to save money on your electricity bills and do your bit for the environment.

## High quality LED light




The LED light bulb delivered with this Philips lamp is a unique solution developed by Philips. It turns on instantly, enables an optimal light output and brings out vivid colours in your home.

## Long operating life



A light source you can trust. The integrated LEDs used in this Philips LED lamp will last up to 20,000 hours (which equals 20 years on the basis of an average use of 3 hours/day with at least 13,000 on/off switching cycles). It feels so good to think that you won't have to worry about maintenance or light bulb replacement while having the perfect light ambience in your home.

## Warm white light



Light can have different colour temperatures, indicated in units called Kelvin (K). Lamps with a low Kelvin value produce a warm, more cosy light, while those with a higher Kelvin value produce a cool, more energising light. This Philips lamp offers warm white light for a cosy atmosphere.

## 5-year warranty on LED system



On top of the standard 2-year warranty for this lamp, Philips offers a 5-year warranty on the LED system, meaning the LED module and the driver in this lamp.

## Connectable product



This product is connectable with a similar product or with any other product from the same family.

## On/off switch on article



With the button discreetly integrated into the lamp, you can easily switch the light on and off.

# Specifications

## Design and finishing

- Colour: White
- Material: Synthetic

## Durability

- Nominal lifetime: 20,000

## Extra feature/accessory incl.

- 5 year warranty on the LED module: Yes
- LED integrated: Yes
- On/off switch on article: Yes

## Miscellaneous

- Especially designed for: Functional
- Style: Contemporary
- Type: Wall Lights
- EyeComfort: No

## Product dimensions and weight

- Net weight: 0.255 kg
- Height: 3.6 cm
- Length: 112.4 cm
- Width: 2.2 cm

## Service

- Warranty: 5 year(s)

## Technical specifications

- Light source equivalent to traditional bulb of: 200
- Total lumen output fixture: 1600 lm
- Bulb technology: LED
- Light colour: Warm white light
- Mains power: Range 220 V–240 V, 50–60 Hz
- Wattage bulb included: 18 W
- IP code: IP20 | Finger-protected
- Class of protection: Class II – Double Insulated
- Number of light sources: 1

## Packaging dimensions and weight

- EAN/UPC – product: 8718696127490
- Net weight: 0.26 kg
- Gross weight: 0.6 kg
- Height: 0 mm
- Length: 0 mm
- Width: 0 mm



Issue date: 2026-01-14  
Version: 0.1255

© 2026 Signify Holding. All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. Philips and the Philips Shield Emblem are registered trademarks of Koninklijke Philips N.V.

[www.lighting.philips.com](http://www.lighting.philips.com)